




GV2ME Enclosures

Application	Type	Degree of Protection of Enclosure	Catalog Number	Weight / kg (lbs)
For GV2ME manual starters and protectors with or without accessories (maximum of 1 accessory on right and left for GV2MC and GV2MP01 or MP02, 1 accessory only on right for GV2MP03 and GV2MP04)	Surface mounting, double insulated with protective (saleable) cover.	IP 41	GV2MC01	0.290 (0.64)
		IP 55	GV2MC02	0.300 (0.66)
		IP 55 for temperature < + 5 °C (41 °F)	GV2MC03	0.300 (0.66)
	Flush with protective cover.	IP 41 (full size) mounting	GV2MP01	0.115 (0.25)
		IP 41 (reduced size)	GV2MP03	0.115 (0.25)
		IP 55 (full size)	GV2MP02	0.130 (0.29)
		IP 55 (reduced size)	GV2MP04	0.130 (0.29)

Front Plate

Application		Degree of Protection of Enclosure	Sold in Lots Of	Catalog Number	Weight / kg (lbs)
Padlocking device (1) for GV2M operator (padlocking is only possible in the "O" position)			1	GV2V01	0.075 (0.17)
Mushroom head "stop" pushbutton (1) Ø 40 mm, red	Spring return		1	GV2K011	0.052 (0.11)
	Latching	Key release (key #455)	1	GV2K021	0.100 (0.22)
		Turn to release	1	GV2K031	0.052 (0.11)
		Latching/Padlockable	Turn to release	1	GV2K04
Sealing kit	For enclosures and front plate	IP 55	10	GV2E01	0.120 (0.26)
		IP 55 for temperature < + 5 °C (41 °F)	10	GV2E02	0.120 (0.26)
Neutral link			10	GV2N01	0.030 (0.06)
Description	Voltage	Color	Sold in Lots Of	Catalog Number	Weight / kg (lbs)
Neon indicator light (2)	110 V	Green	10	GV2SN13	0.019 (0.06)
		Red	10	GV2SN14	0.019 (0.06)
		Orange	10	GV2SN15	0.019 (0.06)
		Clear	10	GV2SN17	0.019 (0.06)
	220/240 V	Green	10	GV2SN23	0.019 (0.06)
		Red	10	GV2SN24	0.019 (0.06)
		Orange	10	GV2SN25	0.019 (0.06)
		Clear	10	GV2SN27	0.019 (0.06)
	380/440 V	Green	10	GV2SN33	0.019 (0.06)
		Red	10	GV2SN34	0.019 (0.06)
		Orange	10	GV2SN35	0.019 (0.06)
		Clear	10	GV2SN37	0.019 (0.06)

(1) Supplied with IP 55 sealing kit.

(2) Leads are approximately 9.5" (260 mm).