RG130/0800-3612

EC centrifugal fan

single inlet

with housing (small flange), Gas blower for gas-condensing heating



ebm-papst Landshut GmbH
Hofmark-Aich-Straße 25
84030 Landshut
Phone: +49 871 707-0
Fax: +49 871 707-465
www.ebmpapst.com
info3@de.ebmpapst.com

Nominal data

Type	RG130/0800-3612	
Nominal voltage	[VDC]	24
Speed	[min^{-1}]	8000
Power input	[W]	40
Air flow	[m^3/h]	115

ml = max. load · me = max. efficiency · rfa = running at free air · cs = customer specs · cu = customer unit
Subject to alterations

Technical features


Connection line	A and C
Design	Vibration-free motor mount
Mounting position	To be specified for corresponding support elements
Bearing	Ball bearings
Mass	1.4 kg
Housing material	Die-cast aluminum
Option	Honeywell flange on request

EC centrifugal fan

single inlet

with housing (small flange), Gas blower for gas-condensing heating

Product drawing




ebm-papst Landshut GmbH · Hofmark-Aich-Straße 25 · 84030 Landshut · Phone: +49 871 707-0 · Fax: +49 871 707-465 · www.ebmpapst.com · info3@de.ebmpapst.com

EC centrifugal fan

single inlet

with housing (small flange), Gas blower for gas-condensing heating

Charts: Air flow




ebm-papst Landshut GmbH · Hofmark-Aich-Straße 25 · 84030 Landshut · Phone: +49 871 707-0 · Fax: +49 871 707-465 · www.ebmpapst.com · info3@de.ebmpapst.com

EC centrifugal fan

single inlet

with housing (small flange), Gas blower for gas-condensing heating

Charts: Speed



ebm-papst Landshut GmbH · Hofmark-Aich-Straße 25 · 84030 Landshut · Phone: +49 871 707-0 · Fax: +49 871 707-465 · www.ebmpapst.com · info3@de.ebmpapst.com