

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:				
believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or FOU	UNLESS OTHERWISE	Kavitha	06/09/07	27-10M TGG				
	SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	CHECKED BY:	DATE:	SIZE DWG NO.	M10000535		ELECTRONIC FILE 1169681_DWG	
		Suresh	06/09/07					
		APPROVED BY:	DATE:]				
possibility of such loss of damage ansing) is excluded. This will not operate to limit restrict the Group's liability for death or personal injury resulting from its negligence. C MULTICOMP is the registered trademark of the Group. © Premier Famel pic 2007.		G.Cook	21/09/07	SCALE: NTS	U.O.M.: mm (Inches)		SHEET: 1 O	F 3

•	PART NO.			REVISIONS							
	TARTNO.		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DAT
		27-10M TGG	-	A	RELEASED	Kavitha	06/9/07	Suresh	06/9/07	G. C	21/9
	ical Characteristics:ency Range: DC-6GHz.al Impedance: 50 ohms.										
Specifications:											
Electrical Characteristics:											
Frequency Range	: DC-6GHz.										
Nominal Impedance	: 50 ohms.										
Maximum Working Voltage	: 170 volts.										
Proof Voltage	: 500 volts.										
Maximum VSWR	: 1.22 at 1G	Hz									
	: 1.35 at 3G	Hz.									
Materials:											
Bodies	: Brass per 、	JIS-C3604.									
Centre Contact	: Beryllium c	copper per ASTM B196 UNS C	17300.								
Insulation	: PTFE per /	ASTM D1457 and ASTM D171	0.								
Crimp Ferrule	: Brass per 、	JIS-C2700.									
Mechanical Characteristics:											
Interface in accordance with CI	ECC 22220.										
For use with RG402 or similar	style cable.										
Cable Attachment	: Outer	: Crimp									

Cable Attachment	: Outer	: Crimp
	Inner	: Solder.
Minimum Cable Retention	: 6lbs.	
Crimp Size Required	: Contact	: Solder.
	Ferrule	: 2.8 (0.110) hexagon crimp tool.

Environmental Characteristic:

Operating Temperature Range

: -55°C to +155°C.

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:					
information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change with-	UNLESS OTHERWISE	Kavitha	06/09/07	27-10M TGG					
believed to be accurate but the Group assumes no responsibility for its accuracy or	SPECIFIED,	CHECKED BY:	DATE:	SIZE DWG NO.		ELECT	RONIC FILE		REV
(the "Group") or are licensed to it. No licence is grainted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or FOR REI	DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Suresh	06/09/07	Δ	M10000535	1169681 DWG			А
		APPROVED BY:	DATE:				—		
		G.Cook	21/09/07	SCALE: NTS	U.O.M.: mm (Inches)		SHEET: 2	OF	3

	PART NO.		REVISIONS									
		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE		
	27-10M TGG	-	А	RELEASED	Kavitha	06/9/07	Suresh	06/9/07	G. C	21/9/07		

Specification Table

Number	Description	Material	Finish	Part Number
1	Nut		Cold	
2	Washer	Brass	Gold	
3	Body		Gold 3µ" Minimum	
4	4InsulationPTFE5ChassisBrass6Centre ContactBeryllium Co		None	27-10M TGG
5			Gold 3µ" Minimum	
6			Gold 30µ" Minimum	
7	Crimp Ferrule	Brass	Gold	

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk

believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any relance on the Information or	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:							
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Kavitha	06/09/07	27-10M TGG							
		CHECKED BY:	DATE:	SIZE DWG NO.		ELECTR	RONIC FILE	REV			
		Suresh	06/09/07		M10000535	1169681 DWG		А			
		APPROVED BY:	DATE:		U.O.M.: mm (Inches) SHEET: 3		_				
		G.Cook	21/09/07	SCALE: NTS			SHEET: 3	OF 3			