



Metric Fine Adjustable Dies

Tolerance	6g Adjustable
Chamfer Lead	2 Threads
Surface Treatment	Bright
Application	For production of components less than 3 x D in length.

Entry Code	MF x P mm	d ₂ ∅ inch /"	h ₁ inch /"	Entry Code	MF x P mm	d ₂ ∅ inch /"	h ₁ inch /"
F310M3X.35X13/16	3 x 0,35	13/16	1/4	F310M14X1.25X1.5/16	14 x 1,25	1.5/16	7/16
F310M4X.5X13/16	4 x 0,50	13/16	1/4	F310M14X1.5X1.5/16	14 x 1,50	1.5/16	7/16
F310M4X.75X13/16	4 x 0,75	13/16	1/4	F310M16X1.0X1.1/2	16 x 1,00	1.1/2	1/2
F310M5X.5X13/16	5 x 0,50	13/16	1/4	F310M16X1.5X1.1/2	16 x 1,50	1.1/2	1/2
F310M5X.9X13/16	5 x 0,90	13/16	1/4	F310M18X1.5X1.1/2	18 x 1,50	1.1/2	1/2
F310M6X.75X13/16	6 x 0,75	13/16	1/4	F310M20X1.0X1.1/2	20 x 1,00	1.1/2	1/2
F310M8X.75X1	8 x 0,75	1	3/8	F310M20X1.5X2	20 x 1,50	2	5/8
F310M8X1.0X1	8 x 1,00	1	3/8	F310M20X2.0X1.1/2	20 x 2,00	1.1/2	1/2
F310M9X1.0X1	9 x 1,00	1	3/8	F310M22X1.5X2	22 x 1,50	2	5/8
F310M10X.75X1	10 x 0,75	1	3/8	F310M24X1.5X2	24 x 1,50	2	5/8
F310M10X1.0X1	10 x 1,00	1	3/8	F310M24X2.0X2	24 x 2,00	2	5/8
F310M10X1.25X1	10 x 1,25	1	3/8	F310M25X1.5X2	25 x 1,50	2	5/8
F310M10X1.25X1.5/16	10 x 1,25	1.5/16	7/16	F310M27X2.0X2.1/4	27 x 2,00	2.1/4	11/16
F310M12X1.0X1.5/16	12 x 1,00	1.5/16	7/16	F310M30X2.0X2.1/4	30 x 2,00	2.1/4	11/16
F310M12X1.25X1.5/16	12 x 1,25	1.5/16	7/16				
F310M12X1.5X1.5/16	12 x 1,50	1.5/16	7/16				