







1		2	
REVISIONS			
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE	



RECOMMENDED
MOUNTING HOLE



- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
 2. BRASS PER QQ-B-613
 3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 4. PHOSPHOR BRONZE PER QQ-B-750
 5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 6. PTFE MIL-P-19468
 7. JIS H 3250, C 2700

ACCEPTS $\phi 0.75 \sim 0.9$ CENTER CONDUCTOR TYPICAL

1. CRIMPED FERRULE
2. CRIMPED CONTACT PIN
3. MAX. PANEL THICKNESS=6.5mm

6	HEX NUT	NOTE 1	NOTE 3	1	HN127-3/8-32X3	DIMENSIONS ARE IN MILLIMETERS			PART NO. F6411A2-NT3G-3-75	Amphenol
5	LOCK WASHER	NOTE 2	NOTE 3	1	LW-127/97X05	UNLESS OTHERWISE SPECIFIED				
4	FERRULE	NOTE 7	NOTE 3	1	FR-75/66X127	TOLERANCES				
3	CONTACT PIN	NOTE 4	NOTE 5	1	F6411B3-3-16	0.5-6 = ±0.2				
					/076	6-30 = ±0.4				
						30-120 = ±0.6				
2	INSULATOR	NOTE 6	NATURAL	1	F6411B3-2	120-315 = ±1			CHECKED	DATE
1	BODY	NOTE 1	NOTE 3	1	F6411A2-1-56/39	315-1000 = ±1.6			DRAWN	DATE
						1000-2000 = ±2.4				10-11-01*
NO.	DESCRIPTION	MATERIAL	FINISH	QTY	DRAWING NO.	SCALE	2.5/1	ISSUE	A	FILE NO.
DRAWING NO. KU-F6411A2-NT3G-59U-75										
ITEM NO.										