



PART NO.

19-02V-11-TGG

		REVISIONS						
ECN #	CN # REV DESCRIPTION		DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	А	RELEASED	Sapna	01/9/07	Suresh	01/9/07	G. C	18/9/07





(1000 (1000) (

Dimensions: Millimetres (Inches)

Specifications:

Bodies : Brass per JIS-C3604. Centre Contact : Brass per JIS-C3604.

Insulation : PTFE per ASTM D1457 and ASTM D1710.

Crimp Ferrule : Brass per JIS-C2700. Connector interface per MIL-STD-348A. Part to be clean and free of burrs.

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from regigence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell pic 2007.

TOLERANCES:	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	

	DRAWN BY:	DATE:				
	Sapna	01/09/07				
	CHECKED BY:	DATE:				
	Suresh	01/09/07				
	APPROVED BY:	DATE:				
	G.Cook	18/09/07				

DRAW	ING TITLE:	19-02V-	11-TC	G G		
SIZE	DWG NO.	DWG NO. M10000485			E G	REV A
SCALE: NTS		U.O.M.: mm (Inches)		SHEET:	1 C)F 2



PART NO.

19-02V-11-TGG

		REVISIONS						
ECN#	REV	REV DESCRIPTION		DATE	CHECKD	DATE	APPRVD	DATE
-	А	RELEASED	Sapna	01/9/07	Suresh	01/9/07	G. C	18/9/07

Specification Table

Number	Number Description		Finish	Part Number		
1	Shell	Brass	Gold 3μ" Minimum			
2	Insulation	PTFE				
3	Gasket	Silicone None				
4	Washer	Stainless Steel		19-02V-11-TGG		
5	Body		Gold 3μ" Minimum			
6	Centre Contact	Brass	Gold 50μ" Minimum			
7	Chassis	DIASS	Cold 2u" Minimum			
8	Сар		Gold 3μ" Minimum			

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group is liability for death or personal injury resulting from its negligence.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:	DATE:				
Sapna	01/09/07				
CHECKED BY:	DATE:				
Suresh	01/09/07				
APPROVED BY:	DATE:				
G.Cook	18/09/07				

DRAWING TITLE:			19-02V-1	11-TC	G G			
SIZE DWG NO.		ſ	M10000485		TRONIC FILE 9625_DWG			REV A
SCALE: NTS			U.O.M.: mm (Inches)		SHEET:	2	OF	- 2