

Micrometer Heads

SERIES 148



148-215

148-203

148-201

FEATURES

- Miniature micrometer heads for ease of incorporating into machines.

SPECIFICATIONS

Metric


Range	Order No. (plain stem)		Order No. (w/ clamp nut)		Graduation	Accuracy	Remarks
	w/o spindle lock	w/ spindle lock	w/o spindle lock	w/ spindle lock			
0 - 5mm	148-215	—	148-216	—	0.02mm	±5µm	Spherical face type
0 - 6.5mm	148-201	—	148-203	—	0.01mm	±5µm	—
	148-205	—	148-207	—	0.01mm	±5µm	Spherical face type
	148-209	—	148-211	—	0.01mm	±5µm	Reverse reading type

Inch

Range	Order No. (plain stem)		Order No. (w/ clamp nut)		Graduation	Accuracy	Remarks
	w/o spindle lock	w/ spindle lock	w/o spindle lock	w/ spindle lock			
0 - .2"	148-217	—	148-218	—	.001"	±.0002"	Spherical face type
0 - .25"	148-202	—	148-204	—	.001"	±.0002"	—
	148-206	—	148-208	—	.001"	±.0002"	Spherical face type
	148-210	—	148-212	—	.001"	±.0002"	Reverse reading type


Dimensions

Plain stem




148-215


with clamp nut



148-216



148-201



148-203

Unit: mm
Scale: 1/1

