


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


REVISIONS				DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398						
DCP #	RE∨	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVI	DATE		
2063	Α	RELEASED	JN	08/04/09	JWM	08/06/09	JWM	08/06/09		

SPC-F005.DWG




REV






SPECIFICATION

- 1. Lead Material: Tin plated copper
- 2. Soldering characteristic: MIL-STD-202, Method 208E.
- 3. Insulating coating: Flame retardant epoxy, UL-94V-0
- 4. Operating Current: 2.5A~14.0A
- 5. Maximum Voltage: 16V
- 6. Temperature Range: -40°C to 85°C





Mas - D/N	A	В	С	D	E	F	Hold Current	Trlp Current	Max.Tlme To Trip	MaxImum Current	Rated Voltage	Typical Power		tance rance	Time-to-Trip
Mfg. P/N	Maximum	Maximum	Typical	Minimum	Maximum	Typical	Current	Current	тотпр	Current	Voltage	rowei	RMIN	R ₁ MAX	Curve option
							Ін, А	IT, A	at 5xH	lmax, A	VMAX, Vdc	Pd, W	ohms	ohms	
MC33151	7.1	11	5.1	7.6	3	1.2	3	5.1	2	100	16	2.3	0.034	0.105	Option B
MC33152	8.9	12.8	5.1	7.6	3	1.2	4	6.8	3.5	100	16	2.4	0.02	0.063	Option C
MC33153	10.4	14.3	5.1	7.6	3	1.2	5	8.5	3.6	100	16	2.6	0.014	0.044	Option D

DISCLA	MMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

TOLERANCES:

DRAWN BY:	DATE:			
Jason Nash	08/06/09			
CHECKED BY:	DATE:			
JWM	08/06/09			
APPROVED BY:	DATE:			
JWM	08/06/09			

DRAWING TITLE:

Radial Leaded PTC Resettable Fuse

SIZE DWG. ND. | ELECTRONIC FILE

A Ta-1189 Ta-1189.dwg

SCALE: NTS U.D.M.: INCHES [mm] SHEET: 1 DF 1