


VE50 Series

50Watts Desk Top AC Adapter



Electrical specifications

Input

Voltage 90 - 264 VAC (wide range)
 Current 1.2Arms Max.
 Frequency 47 - 63 Hz

Out put

Voltage (Vo) 5.1V,.....,15V,24V
 Tolerance 5%
 Power (Po) 50W Max.
 Hold up time 12ms minimum at full load, 115 VAC
 Overvoltage protection ... (see table)
 Overcurrent protection ... Built-in
 Short circuit protection ... Pulsing mode, auto recovery
 Efficiency 80% typ. at full load and 115 VAC
 Ripple/Noise(Vp-p) 1% (20MHz bandwidth)

Output Electronic Specifications

Model No.	Po	Vo	Io max	OVP max
VE50-1200	48W	12.0V	4.0A	15V
VE50-1500	50W	15.0V	3.4A	18V
VE50-2400	48W	24.0V	2.0A	27V
VE50-050A	30.6W	5.1V	6.0A	7.0V
VE50-150A	37.5W	15.0V	2.5A	18V

Features

- Three pin IEC C-14 input receptacle
- Wide range AC input
- Level B EMI filter
- Fully enclosed plastic case
- Fully regulated output
- High efficiency
- High Quality

Environmental

Operating temperature

0 deg. C to +40 deg. C ambient

Storage temperature

-20 deg. C to +80 deg. C ambient

EMI

Meet FCC class B, CISPR 22 class B, VCCI class B

Safety

UL,CUL UL1950, CSA 22.2 NO. 950
 TUV EN 60950
 BS TUV BS950
 AS Australia Standard
 PSB (VE50-050A)
 IEC 950
 C-Tick
 CCEE,CCIB
 CE

