




NOTES

DESIGNED TO MEET THE REQUIREMENTS OF IP65, & NEMA 4X  
 TONGUE & GROOVE CONSTRUCTION WITH A MOLDED ONE PIECE SILICON GASKET.  
 COMES WITH 4 STAINLESS STEEL MACHINE LID SCREWS, CAPTIVATED WITH 4 RUBBER O-RINGS.  
 COMES WITH 2 GROUNDING SCREWS AND WASHERS.  
 FINISH: NONE OR SUFFIX "BK" BLACK, OR SUFFIX "GY" GRAY (RAL 7001) POLYESTER POWDER

M4 THREAD FOR LID SCREWS 4 PLACES



SIDE VIEWS DO NOT DETAIL SCREW CHANNELS SEE "A - A" FOR CHANNEL DETAIL

BOX

LID

For the best fit print on legal size paper.

THIS DRAWING IS PROPRIETARY INFORMATION OF HAMMOND MFG.CO.LTD. NOT TO BE USED WITHOUT EXPRESSED WRITTEN PERMISSION OF HAMMOND MFG.CO.LTD.

△	N/A	RELEASE	---	10/25/02	MJM
Rev	ECN	Description		Date	By

Unless otherwise spec'd dimensions are in millimeters Tolerances are:

X ±2.5  
 .XX ±1.50  
 .XXX ±.500  
 .XXXX ±.1300  
 Holes ±.1300  
 Angles ±5°

Dwn	M. MERCER
Date	10/25/02
Chk	---
Mat'l	CAST ALUMINUM

HAMMOND MANUFACTURING CO. LTD. Electronics Group, Waterloo, Ont. - Cheektowaga, NY	
HAMMOND 1590Z SERIES CASTED AL ENCLOSURES	
Part #:	1590Z130
Dwg:	1590Z130/A

