

Probes for Current Measurement Systems



A6303XL, A6304XL and A6302XL. The Eight-meter XL Series Current Probes.

**A6312 • A6302 • A6302XL • A6303 • A6303XL
• A6304XL • CT4**

Features & Benefits

Product Information

[> Introduction](#)

[Ordering Information](#)

Pricing Information

[Check List Price](#)

[Request a Quote](#)

Additional Resources

[Find an Authorized Distributor](#)

A6312

2 Meter Cable
20 Amps Continuous/50 Amps Peak
DC to 100 MHz
Up to 0.15 in. Conductor Diameter

A6302

2 Meter Cable
20 Amps Continuous/50 Amps Peak
DC to 50 MHz
Up to 0.15 in. Conductor Diameter

A6302XL

8 Meter Cable
20 Amps Continuous/50 Amps Peak
DC to 17 MHz

A6303

2 Meter Cable
100 Amps Continuous/500 Amps Peak
DC to 15 MHz
Up to 0.83 in. Conductor Diameter

A6303XL

8 Meter Cable
100 Amps Continuous/500 Amps Peak
DC to 10 MHz

A6304XL

8 Meter Cable
500 Amps Continuous/700 Amps Peak
DC to 2 MHz

CT4

Pulsed Currents to 20,000 A
Continuous Currents up to 2,000 A_{p-p}
Accepts 1.5 in. Diameter Conductors
Measurements on Bare Conductors to 3,000 V_p
(1,000 V_{RMS} CAT III)
AC
Split Core
Use with A6312, A6302, A6302XL, P6021 or TCP202

Applications

Motor Drives
Satellite Systems
Inverters
Transportation Systems
Power Supplies
Avionics



AM503 Current Measurement Family.

AM503 Family Current Probes - A6312, A6302, A6302XL, A6303, A6303 XL, A604XL, CT4

A total of six current probes are available for use with the AM503B and AM5030 Current Probe Amplifiers. Since all six probes are of the split-core mechanical design, they easily clip on and off of a conductor. All the probes provide simultaneous DC and AC current measurements with a wide range of current amplitude and bandwidth capabilities.

The AM503 Current Probes convert the DC and AC flux field of a conductor to a voltage signal which is sent to an AM503B or AM5030 Amplifier. The probes include both a Hall Effect device, which senses the DC current, and a ferrite transformer which senses the AC current. The probes also utilize a bucking current from the Amplifier, which eliminates core saturation. The bucking current for the A6302XL is 20 A, 100 A for the A6303XL and 500 A for the A6304XL.

A6312, A6302 and A6303 Current Probes

The A6312, A6302 and A6303 offer a wide range of current measurement capability for the lab and bench environment. The A6312 covers frequencies from DC to 100 MHz while the A6302 covers DC to 50 MHz. Both clip onto conductors up to 3.81 mm (0.15 in.) and measure continuous currents up to 20 A and peak

currents up to 50 A as long as they do not exceed the amp*second product of 100 A* μ s.

The larger A6303 measures higher amplitude, lower frequency currents. It clips onto conductors up to 21.1 mm (0.83 in.) in diameter. Its frequency range is DC to 15 MHz. It will measure continuous currents up to 100 A and peak currents up to 500 A, as long as the Amp*second product of 10,000 A* μ s is not exceeded.

The A6302 and A6303 are also compatible with the 11A16 2-CH Current Probe Amplifier for the 11000 and DSA Series oscilloscopes. With the 11A16, the A6302 is rated for 10.5 A, and the A6303 for 52.5 A.

(Note: The A6312, A6302XL, A6303XL and the A6304XL are not compatible with the 11A16.)

XL Series Current Probes

The three XL current probes add both convenience and expanded current measurement capability. The XL probes are designed to operate with the AM503B and AM5030 Current Probe Amplifiers. They are incompatible with the older AM503 and AM503A amplifiers. The XL (for extra long) probes have eight-meter cables, which allow you to reach test points on large devices such as heavy duty motors or automobiles. In addition, connecting to test points on transportation platforms such as trains, ships or aircraft is much easier with the XL probes.

The A6302XL and A6303XL are modified versions of the A6302 and A6303 probes. The A6302XL can measure 20 A continuous (50 A peak) signals from DC to 17 MHz. The A6303XL can measure 100 A continuous (500 A peak) signals from DC to 10 MHz.

The A6304XL is rated for 500 A continuous (700 A peak) and is the same size as the A6303XL. The A6304XL has a bandwidth of DC to 2 MHz and is especially well suited for measurements on high-performance inverters, motor drives and other high current switch-mode control devices. The eight meter cable makes it very easy to access test points on devices physically separated

from your measurement instrument.

Safety

AM503S/AM5030S — Certified to base standard UL3111-1, CSA1010.1, EN61010-1, IEC61010-1.

A6302/6312/6303/6303XL/6304XL — Certified to probe standard UL3111-2-032, CSA1010.2.032, EN61010-2-032, IEC61010-032.



CT4.

CT4 Current Probe

The CT4 is a robust clip-on high current transformer that extends the measurement capability of the P6021, A6302/XL, A6302, A6312 and TCP202 clip-on current probes. Maximum low frequency performance down to 0.5 Hz is obtained using the AM 503S. Current amplitudes to 20,000 A may be measured using the A6302/XL, P6021, A6302, A6312 or TCP202 (with passive termination), provided the amp*second ratings are not exceeded.

The CT4 may be used with the P6021 for measurements at normal line frequency and above. (The P6022 and A6303 are not compatible with the CT4.)

The CT4 has receptacles for current probes in either 20:1 or 1000:1 step-down ratios.

The 1.5 in. square split-core opening makes it possible to clip onto large conductors without breaking the circuit under test. Insulated core and shield assemblies allow measurements on bare wires to 3000 V_P (1000 V_{RMS} CAT III) and to 14 kV with the included high voltage bushing.

[▲ back to top](#)

[> Introduction](#)
[Ordering Information](#)

[Check List Price](#)

[Request a Quote](#)

[Find an Authorized Distributor](#)



Product(s) are manufactured in ISO registered facilities.

51W-10939-1C, 12-MAR-2004

Search

Product Portfolio

Oscilloscope Probes

Logic Analyzer

Probes/P6400

Logic Analyzer

Probes/P68/6900

Optical Products

Application Software

Request a Catalog

Product Finder

Resources

Application Notes

Manuals

Software & Drivers

Service & Support

E-Newsletters

What's New

Promotions

News

Events



A6303XL, A6304XL and A6302XL. The Eight-meter XL Series Current Probes.

Product Information

[Introduction](#)

> Ordering Information

Pricing Information

[Check List Price](#)

[Request a Quote](#)

Additional Resources

[Find an Authorized Distributor](#)

Probes for Current Measurement Systems

A6312 • A6302 • A6302XL • A6303 • A6303XL • A6304XL • CT4

Ordering Information

A6312

100 MHz, 2 m, 20 A current probe.

Includes: 6 in. (152 mm) ground lead (196-3120-01) and A6312 instruction manual (070-9603-00).

A6302

50 MHz, 2 m, 20 A Current Probe.

Includes: 6 in. (152 mm) ground lead (196-3120-01), A6302 and A6302/XL instruction manual (070-3905-04).

A6303

15 MHz, 2 m, 100 A current probe.

Includes: A6303 and A6303/XL instruction manual (070-3906-04).

Note: A6302/A6303 probes must be used with an AM503,

AM503A, AM503B or AM5030 current probe amplifier.

A6302XL

17 MHz, 8 m, 20 A current probe.

Includes: Same as A6302 current probe.

A6303XL

10 MHz, 8 m, 100 A current probe.

Includes: Same as A6303 current probe.

A6304XL

2 MHz, 8 m, 500 A current probe.

Includes: A6304XL instructions (070-8939-02).

Note: XL probes work only with AM503B or AM5030 current probe amplifiers.

CT4

Current probe, high current.

Includes: Carrying case (202-0318-00); 12 in. wide, 4 ft. long high voltage bushing (015-0194-00); Instruction manual (070-6478-02).

Service

Opt. C3 - Calibration Service 3 Years.

Opt. C5 - Calibration Service 5 Years.

Opt. D1 - Calibration Data Report.

Opt. D3 - Calibration Data Report 3 Years (with Option C3).

Opt. D5 - Calibration Data Report 5 Years (with Option C5).

Opt. R3 - Repair Service 3 Years.

Opt. R5 - Repair Service 5 Years.

See [Customer Support](#) for further information.

[▲ back to top](#)

[Introduction](#)

[> Ordering Information](#)

[Check List Price](#)

[Request a Quote](#)

[Find an Authorized Distributor](#)



Product(s) are manufactured in ISO registered facilities.

51W-10939-1C, 12-MAR-2004



Have an
Account
Manager
Contact Me



Request a
Demo



Email This
Page



Printable Page

Tektronix Site

[Home](#) | [Products](#) | [Support](#) | [Buy](#) | [Contact Us](#) | [Investors](#) | [Careers](#) | [International](#) | [myTek](#)

[Sitemap](#) | © Copyright Tektronix, Inc. | [Privacy Statement](#)

Set Pricing Preferences

Please choose the country in which you will use this product.

Country

Language for pricing descriptions

</HTML

Application Solutions[Serial Data](#)[Mobile/Wireless](#)[Video](#)[Design & Analysis](#)**Product Portfolio**[Oscilloscopes](#)[Video Test](#)[Network Management &
Diagnostics](#)[RF/Wireless Test](#)[Logic Analyzers](#)[Signal Sources](#)[Accessories](#)[Optical Communications](#)[Other T&M](#)**Resources**[Manuals](#)[Software](#)[FAQs](#)[Support](#)

Request A Quote

Need Pricing Information?

A Tektronix representative will contact you shortly with pricing information on the product(s) you selected. For Distributor Products, your request will be forwarded to a distributor near you.

Email Address*

Check here if you are a US Government agency.

Product Information

Product Model	A6312
	A6302
	A6302XL
	A6303
	A6303XL
	A6304XL
	CT4

Options

Quantity

Please select the statement that best describes your situation (one only).*

I plan to purchase within the next 6 months.

I plan to purchase within the next 6-12 months.

I have no timeline or plans for purchasing at this time.

Please have an account manager contact me.

Comments:

Find an Authorized Distributor

Welcome to the **Tektronix Locator!**

This system will facilitate your search for authorized distributors for your Test and Measurement needs. You can choose to browse the distributor listings or search for distributors based on name.

Enter one or more search criteria in the form below, then click a "GO" button.

Partner Locator

*** required fields**

Country:*

State/province:*

(where available)

Preferred Distributor:

(Name starts with...)