Polysnap® Power Inlet Modules **B**BULGIN






How to Order


- Screw Fixing to Panel
- Vertical Module Arrangement
- Snap-in Components
- Inlet Variations (with various tag sizes)
- Single Pole Switch Variations
- Filtered Inlet Option
- Options of O/I marked switches
- Fused
- Screw Fixing to Panel
- Vertical Module Arrangement
- Snap-in Components
- Inlet Variations (with various tag sizes)
- Single Pole Switch Variations
- Filtered Inlet Option
- Options of O/I marked switches

BVy yy / yyyyy / yy

Fused



IEC Fused Inlet - Polyflange



¥	V	V	↓ I I I I I I I I I I I I I I I I I I I
Flange Type	Type of Inlet / Outlet	Filtered or Non Filtered Inlet	Combination of Other Components
A = Top fixing B = Side fixing	Fused Power Inlet (cold condition), 6.3 or 2.8mm tabs: 01 = PF0011/63 02 = PF0011/28 Twin Fused Power Inlet (cold condition), 6.3 or 2.8mm tabs: 15 = PF0033/63 16 = PF0033/28	Z0000 = Non Filtered Axxxx = Standard Bxxxx = Medical Cxxxx = High Performance Standard (Single Fuse Version only)	Single Pole Switch: 01 = S.P. Switch Single Pole Neon Switch: 02 = S.P. Red Neon Switch 08 = S.P. Green Neon Switch Neon Indicator: 03 = Red Neon Indicator Single Pole High Inrush Switch:
		For Filtered inlet use 6th to 9th characters from filter ordering code see pages 71-74. E.g. BVA01/ A0620 /01	 46 = S.P. High Inrush Switch Single Pole Switch Marked O/I: 69 = S.P. Switch (O/I) Single Pole Neon Switch Marked (O/I): 71 = S.P. Red Neon Switch (O/I) 74 = S.P. Green Neon Switch (O/I) Single Pole High Inrush Switch Marked (O/I) 98 = S.P. High Inrush Switch (O/I)

Note: For technical details of individual components please see page 54