



HONEYWELL PART NUMBER
23SX39-T
PRODUCT CODE VDP3900
JG-NUMBER JG-83701
MILITARY PART NUMBER MS24547-2

REV	DOCUMENT	CHANGED BY	CHECK
13	0051992	DSK 07MAY09	CMH



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - MOVABLE CONTACT MATERIAL - 24 K SOLID GOLD
- 4 - STATIONARY CONTACT MATERIAL - GOLD ALLOY
- 5 - SWITCH WILL WITHSTAND TEMPERATURE OF 185° F

RELEASE NO.	SR 12677
REPLACES	

CHARACTERISTICS	
OPERATING FORCE - - -	5 OZ MAX
RELEASE FORCE - - - -	1 OZ MIN
DIFFERENTIAL TRAVEL - - -	.005 MAX
OVERTRAVEL - - - - -	.004 MIN

ELECTRICAL DATA		
CONTACT ARRANGEMENT SPDT		
30 VOLTS DC RATING		
	SEA LEVEL	50,000 FT
INDUCTIVE	0.5 AMP	0.5 AMP
RESISTIVE	1 AMP	1 AMP
MAXIMUM INRUSH 2 AMP		
APPROVALS	KEMA, CE	1A 250 V - T125 25E3
	UL, CSA	1A 125 VAC
	MILITARY	MS24547 - 2

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ±
ONE PLACE .X ±
TWO PLACE .XX ±
THREE PLACE .XXX ±
FOUR PLACE .XXXX ±
ANGLES ±
THIRD ANGLE PROJECTION

DRAWN	SPK	21FEB08
CHECK	RJ	21FEB08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	23SX39-T	13
SCALE	NONE	WEIGHT: .003 LB MAX	SHEET 1 OF 1