



Revision Date: 04/07/2006

Issue date: 04/12/2006

1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

Product name: 50ML BEARING/MT/B/ADH SEALANT
Product type: Anaerobic Adhesive
Company address:
Henkel Corporation
1001 Trout Brook Crossing
Rocky Hill, Connecticut 06067

Item No. : 08531
Region: United States
Contact Information:
Telephone: 860.571.5100
Emergency telephone: 860.571.5100
Internet: www.loctite.com

2. COMPOSITION/INFORMATION ON INGREDIENTS

Hazardous components	%	ACGIH TLV	OSHA PEL	OTHER
Polyglycol dimethacrylate 25852-47-5	60-100	None	None	None
Polyglycol dioctanoate 18268-70-7	10-30	None	None	None
Cumene hydroperoxide 80-15-9	1-5	None	None	1 ppm (6 mg/m ³) Skin (WEEL), 1ppm, skin TWA, (WEEL)
Cellulose ester 9004-36-8	1-5	None	None	None
Saccharin 81-07-2	1-5	None	None	None

3. HAZARDS IDENTIFICATION**EMERGENCY OVERVIEW****HMIS:**

Physical state: Liquid
Color: Yellow
Odor: Mild

HEALTH: 2*
FLAMMABILITY: 1
PHYSICAL HAZARD: 1
Personal Protection: See Section 8

WARNING: CAUSES EYE AND SKIN IRRITATION.
MAY CAUSE RESPIRATORY TRACT IRRITATION.
MAY CAUSE ALLERGIC SKIN REACTION.
MAY BE HARMFUL IF SWALLOWED.

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects

Inhalation: May cause irritation to nose and throat.
Skin contact: Irritating to skin. May cause allergic skin reaction.
Eye contact: Vapors may irritate eyes. Contact with eyes will cause irritation.
Ingestion: May cause irritation to the gastrointestinal tract, mouth and mucous membranes.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders.

Item No. : 08531

Product name: 50ML BEARING/MT/B/ADH SEALANT

See Section 11 for additional toxicological information.

4. FIRST AID MEASURES

Inhalation:	Remove to fresh air. If symptoms develop and persist, get medical attention.
Skin contact:	Wash with soap and water. Remove contaminated clothing and shoes. Wash clothing before reuse. Get medical attention if symptoms occur.
Eye contact:	Flush with copious amounts of water, preferably, lukewarm water for at least 15 minutes, holding eyelids open all the time. Get medical attention.
Ingestion:	Do not induce vomiting. Keep individual calm. Obtain medical attention.

5. FIRE-FIGHTING MEASURES

Flash point:	Greater than 93°C (200°F)
Autoignition temperature:	Not available
Flammable/Explosive limits-lower %:	Not available
Flammable/Explosive limits-upper %:	Not available
Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special fire fighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
Unusual fire or explosion hazards:	None
Hazardous combustion products:	Oxides of carbon. Irritating organic vapors.

6. ACCIDENTAL RELEASE MEASURES

Environmental precautions:	Prevent product from entering drains or open waters.
Clean-up methods:	Ensure adequate ventilation. Soak up with inert absorbent. Store in a partly filled, closed container until disposal.

7. HANDLING AND STORAGE

Handling:	Avoid contact with eyes, skin and clothing. Do not breathe mist or vapors.
Storage:	For safe storage, store at or below 38°C (100°F).
Incompatible products:	Refer to Section 10.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Engineering controls:	Use local exhaust ventilation to maintain airborne concentrations below established exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
Skin protection:	Use impermeable gloves and protective clothing as necessary to prevent skin contact. Neoprene gloves. Butyl rubber gloves. Natural rubber gloves.
Eye/face protection:	Safety goggles or safety glasses with side shields.

Item No. : 08531

Product name: 50ML BEARING/MT/B/ADH SEALANT

See Section 2 for exposure limits.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid
Color:	Yellow
Odor:	Mild
Vapor pressure:	Less than 5 mm Hg at 27°C (80°F)
pH:	Not applicable
Boiling point/range:	Greater than 149°C (300°F)
Melting point/range:	Not available
Specific gravity:	1.066
Vapor density:	Not available
Evaporation rate:	Not available
Solubility in water:	Not soluble
Partition coefficient (n-octanol/water):	Not available
VOC content:	1.8598%; 17.7526 grams/liter

10. STABILITY AND REACTIVITY

Stability:	Stable.
Hazardous polymerization:	Will not occur.
Hazardous decomposition products:	Oxides of carbon. Irritating organic vapors.
Incompatibility:	Strong oxidizers. Strong reducing agents. Strong alkalis. Amines. Other polymerization initiators.
Conditions to avoid:	See "Handling and Storage" (Section 7) and "Incompatibility" (Section 10).

11. TOXICOLOGICAL INFORMATION

Product toxicity data:	Acute LD50 (oral) :Greater than 5000 (rat). (estimated). Acute dermal LD50 greater than 2000 mg/kg (rabbit) (estimated).
------------------------	--

Carcinogen Status

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen
Polyglycol dimethacrylate 25852-47-5	No	No	No
Polyglycol dioctanoate 18268-70-7	No	No	No
Cumene hydroperoxide 80-15-9	No	No	No
Cellulose ester 9004-36-8	No	No	No
Saccharin 81-07-2	No	No	No

Literature Referenced Target Organ & Other Health Effects

Hazardous components	Health Effects/Target Organs
Polyglycol dimethacrylate 25852-47-5	Allergen, Irritant
Polyglycol dioctanoate 18268-70-7	Irritant
Cumene hydroperoxide 80-15-9	Allergen, Central nervous system, Corrosive, Irritant, Mutagen
Cellulose ester 9004-36-8	No Target Organs
Saccharin 81-07-2	No Target Organs

12. ECOLOGICAL INFORMATION

Ecological information: Not available

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Dispose of according to Federal, State and local governmental regulations.

EPA hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

U.S. Department of Transportation Ground (49 CFR):

Proper shipping name:	Unrestricted
Hazard class or division:	None
Identification number:	None
Packing group:	None

International Air Transportation (ICAO/IATA):

Proper shipping name:	Unrestricted
Hazard class or division:	None
Identification number:	None
Packing group:	None

WaterTransportation (IMO/IMDG):

Proper shipping name:	Unrestricted
Hazard class or division:	None
Identification number:	None
Packing group:	None
Marine pollutant:	None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: 4-Methoxyphenol (150-76-5).

CERCLA/SARA Section 302 EHS: None above reporting de minimus.
CERCLA/SARA Section 311/312: Immediate Health Hazard, Delayed Health Hazard
CERCLA/SARA 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Cumene hydroperoxide (CAS# 80-15-9) . Acrylic acid (CAS# 79-10-7).

California Proposition 65: This product contains a chemical known to the State of California to cause cancer and birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Domestic Substances List.
WHMIS hazard class: D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: 15

Prepared by:

Kyra Kozak Woods, Product Safety and Regulatory Affairs Specialist

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.