


SECTION 2 PCB TERMINAL BLOCKS

3.5mm Pitch **Ultra Low Profile** Rising Clamp Terminal 3882639 + 3882640

Features

- 2-12 pole interlocking
- Ultra low profile
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 0.75mm² cable entry
- V & CE approved
- cUL applied for
- Captive screws
- Guided pin alignment
- Double interlock mechanism for increased strength


CTB0305



Type No.	Poles	Length
CTB0305/2	2	7mm
CTB0305/3	3	10.5mm
CTB0305/4	4	14mm
CTB0305/5	5	17.5mm
CTB0305/6	6	21mm
CTB0305/7	7	24.5mm
CTB0305/8	8	28mm
CTB0305/9	9	31.5mm
CTB0305/10	10	35mm
CTB0305/11	11	38.5mm
CTB0305/12	12	42mm

Specification

Rating	9A/130Vac
Dielectric strength	1.5kV/60sec
Insulation resistance	≥ 5MΩ
Working temperature	-20°C to 125°C
Short period	160°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	5μ tinned, nickel plated brass
Rising clamp	Nickel plated brass
Screw/torque	M2 steel, 6μ zinc colour passivated and tropicalised/0.3Nm
Recommended PCB hole size	ø1.1mm




3.5mm Pitch **Ultra Low Profile 90°** Rising Clamp Terminal

Features

- 2-12 pole interlocking
- Ultra low profile
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 0.75mm² cable entry
- V & CE approved
- cUL applied for
- Captive screws
- Guided pin alignment
- Double interlock mechanism for increased strength

CTB0355



Type No.	Poles	Length
CTB0355/2	2	7mm
CTB0355/3	3	10.5mm
CTB0355/4	4	14mm
CTB0355/5	5	17.5mm
CTB0355/6	6	21mm
CTB0355/7	7	24.5mm
CTB0355/8	8	28mm
CTB0355/9	9	31.5mm
CTB0355/10	10	35mm
CTB0355/11	11	38.5mm
CTB0355/12	12	42mm

Specification

Rating	9A/130Vac
Dielectric strength	1.5kV/60sec
Insulation resistance	≥ 5MΩ
Working temperature	-20°C to 125°C
Short period	160°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	5μ tinned, nickel plated brass
Rising clamp	Nickel plated brass
Screw/torque	M2 steel, 6μ zinc colour passivated and tropicalised/0.3Nm
Recommended PCB hole size	ø1.1mm

