



Circieninç Nisal: Time	naf.on کا ۲ مارد آن ج ۲۰ Failure = ۲ مارد آن ۲ Solit		cter"	Ta = 7 ి ఎ)						
°AR'IN ∠R		,		C' RRF'	LUM/INC is INT : JITY IVC :20mA (mix)	`VAVF .F.⊴GTH , ∵ (nm) 	עידר 'דיר עידר 'איד' י	୍ ନ'.ଦ _M.P ୁନ୍ଦ୍ର		
				G'H IN' E	NSTY					
5.23 105- 53	Ri 🥼	ا - گهرس سمو	1 -28	8-/1	، OC	6_7	-40 - + 35^	- <i>^</i> ~ +55	Ye	
<i>(</i> 33-102-63	F 1 (.)4As	ល្អ ហាព្រៃ ខណ	12-28	8-1)ر`∆	d J	ر، دن ~ +85^	-40 ~ +85	Yes	
53 1 711-62	Yello:/ 😽	Colour ⊡iffu⊸sd	 12 <i>⊘</i> 8	0? 0		ngr	-/^ 35^		ا جز``	
1 J? 11	jree 🚺	j Colo:		8-70	r.,	65	-40 d ^r	f +8₹	Yes	
530-100 . J	i 🤣	Colour Dittused	110Vac	6	100	527	-40 ~ +85^	-40 ~ +85	Yes	
533-10:⊱ ∪	Rec - JaAlAs) 🌗	່ ເຫັນມາ Diffu ່	inovac	: : 0	450	000	~ = *	-40 - +oo	ĭes	
3 75	Vel / 💔	່ ⊂ າlo、 ∉ iffuser'	ز 'ر	,		90	^ر	-40 ~ +85	Yes	
j: −75	Gr r. 👘	Colocy Diff	116	6	۶	565	-40 ~	40 ~ +85	Yes	
U 1				<u>г.</u> (Д			•r	,		

Prime as is a contract of a long in the Lace is the second and in the long in the Lace is second and the long in the long in the lace is a contract of the long in the lace is a contract of the long in the lace is a contract of the lace is a contract

How to Order:

website: v v v an all v vato eta dr. sales@r -c.ur

• Tak shore +44 (0)12 JBN JJ F90 11 (0) 220 J 155

The rise station on teleptum this duit sheet up to an eonstitute part of any order or control and sherid not be regarded when the presentation talking the the products or parvice. Next international records the up to take up bed notice the sect fication to up profor presents or sample.



533 Series Below 50Vac/dc Above 50Vac/dc Ø12.7^{+0.1} 9.0 22.5 5.0 9.0 22.5 6.0 \square Ø17.0 Ø10.0 017.0 Ø10.0 2.8 Mounting Hole Dimensions in mm (Typical) Anode termination indicated by red sleeve Not to scale Mounting hole to be clean and burr free MATERIALS **PUSH-ON CONNECTORS** Nickel plated brass to BS 2874 CZ121 Body Nut Stainless Steel grade 303 14.5 Panel Seal Viton Termination Copper with silver flash finish m. Lock Washer Zinc plated steel Fresnel lens Polycarbonate Encapsulation PC5430 Dimensions in mm (Typical) 925-000-00 is brass tin plated. Header Nylon6 A82 Not to scale For use with 533 series lamps. **TECHNICAL CHARACTERISTICS** SERIES MAXIMUM PANEL NUT MINIMUM MIN/MAX. POWER CUTOUT MOUNTING MOUNTING PANEL DISSIPATION TORQUE CENTRES THICKNESS 533 825 12.7 1.0 x,y=19.5 1.5-8.0

mm

mm

How to Order:

website: www.marl.co.uk • email: sales@marl.co.uk •

• Telephone +44 (0)1229 582430 • Fax: +44 (0)1229 585155

mW

mm

The information contained in this datasheet does not constitute part of any order or contract and should not be regarded as a representation relating to either products or service. Marl International reserve the right to alter without notice the specification or any conditions of supply for products or service.

Nm

© MARL INTERNATIONAL LTD 2007 : DS 068/07 Issue 1

SAMPLES AVAILABLE