Vishay



Wet Tantalum Capacitors Surface Mount, Molded Case



PERFORMANCE CHARACTERISTICS

Operating Temperature: - 55 °C to + 85 °C (To + 125 °C with voltage derating.)

Capacitance Tolerance: At 120 Hz, + 25 °C, \pm 20 % standard, \pm 10 %

DC Leakage Current (DCL Max.): At + 25 °C and above: Leakage current shall not exceed the values listed in the Standard Ratings Tables.

Life Test: Capacitors are capable of withstanding a 2000 h life test at a temperature of + 85 °C or + 125 °C at the applicable rated DC working voltage.

Following life test:

- 1. DCL, measured at + 85 °C rated voltage, shall not be in excess of the original requirement.
- 2. The equivalent series resistance shall not exceed 150 % of the initial requirement.
- Change in capacitance shall not exceed 10 % from the initial measurement.

FEATURES

 Terminations: standard tin/lead (SnPb), 100 % tin (RoHS compliant) terminations available




COMPLIANT

Very high capacitance, 10 μF to 470 μF
 V to 125 V, - 55 °C to + 125 °C

- Very low ESR
- · High ripple current capability
- Low DCL
- Model M34 wet tantalum electrolytic chip capacitors incorporate the advantages of all the varieties of electrolytic capacitors and eliminate most of the disadvantages. These units have a transient reverse voltage capability and a higher ripple current capability than any other electrolytic type with similar combinations of capacitance and case size.
- Compliant to RoHS directive 2002/95/EC

APPLICATION NOTES


- a) No continuous reverse voltage permissible.
- b) Transient reverse voltage surges are acceptable under the following conditions:
 - The peak reverse voltage does not exceed 1.5 V and the peak current times the duration of the reverse transient does not exceed 0.05 A. In addition, the repetition frequency of the reverse voltage surge is less than 10 Hz.
- c) The peak of the applied AC ripple and the applied DC voltage must not exceed the DC voltage rating of the capacitor.




^{*} Pb containing terminations are not RoHS compliant, exemptions may apply



Wet Tantalum Capacitors Surface Mount, Molded Case





MOUNTING

Due to the size and weight of these capacitors, we recommend that a supplemental mounting restraint to be used in printed circuit board attachment in addition to the reflowed solder.

One recommendation is to use an adhesive such as defined in the J-STD-001DS.

This is the Space Application Electronic Hardware Addendum to J-STD-001 (Requirements for Solder Electrical and Electronic Assemblies).

Vishay

Wet Tantalum Capacitors Surface Mount, Molded Case



Document Number: 40106

Revision: 11-Aug-09

STANDARD RATINGS										
			ESR	MAX. IMP.	MAX. DCL (μA) AT		MAX. CAPACITANCE CHANGE (%) AT			MAX. RIPPLE
CAP (μF)	CASE	PART NUMBER	AT + 25 °C 120 Hz (Ω)	AT - 55 °C 120 Hz (Ω)	+ 25 °C	+ 85 °C + 125 °C	- 55 °C	+ 85 °C	+ 125 °C	40 kHz rms (mA)
	25 WVDC AT + 85 °C 15 WVDC AT + 125 °C									
120	С	M34C127(1)025(2)ZSS	1.3	25	1.0	5.0	- 42	+ 8	+ 12	1250
	30 WVDC AT + 85 °C 20 WVDC AT + 125 °C									
100	С	M34C107(1)030(2)ZSS	1.3	25	1.0	5.0	- 38	+ 8	+ 12	1200
	50 WVDC AT + 85 °C 30 WVDC AT + 125 °C									
68	С	M34C686(1)050(2)ZSS	1.5	35	1.0	5.0	- 25	+ 8	+ 15	1050
	60 WVDC AT + 85 °C 40 WVDC AT + 125 °C									
47	С	M34C476(1)060(2)ZSS	2.0	44	1.0	5.0	- 25	+ 8	+ 12	1050
	75 WVDC AT + 85 °C50 WVDC AT + 125 °C									
33	С	M34C336(1)075(2)ZSS	2.5	66	1.0	5.0	- 25	+ 5	+ 9	1050
100 WVDC AT + 85 °C 65 WVDC AT + 125 °C										
15	С	M34C156(1)100(2)ZSS	3.5	125	1.0	5.0	- 18	+ 3	+ 10	1050
	125 WVDC AT + 85 °C 85 WVDC AT + 125 °C									
10	С	M34C106(1)125(2)ZSS	5.5	175	1.0	5.0	- 15	+ 3	+ 10	1050

Notes

- 1. Capacitance tolerance: K, M
- Capacitance tolerance. N, M
 Termination/packaging: A = 100 % tin (RoHS compliant), bulk; B = Std, tin/lead, bulk
 Reliability level: Z = Non-ER
 Temperature: S = STD
 ESR: S = STD

PERFORMANCE CHARACTERISTICS OF M34 CAPACITORS

ITEM	PERFORMANCE CHARACTERISTICS
Operating temperature range	- 55 °C to + 125 °C
Capacitor tolerance	± 20 %, ± 10 %, at 120 Hz
Capacitance change (maximum)	Limits per standard ratings table
ESR	Limits per standard ratings table
AC ripple current	Limits per standard ratings table
DCL (maximum leakage current)	Limits per standard ratings table
Impedance (maximum)	Limits per standard ratings table
Reverse voltage	Reverse voltage shall be in accordance with DSCC drawing 93026. There shall be no continuous reverse voltage. Transient reverse voltage surges are acceptable under the following conditions: a) Peak reverse voltage is equal to or less than 1.5 V and the product of the peak current times the duration of the reverse transient is 0.05 As or less. b) The repetition rate of the reverse voltage surges is less than 10 Hz
Surge voltage	Surge voltage shall be in accordance with MIL-PRF-39006 and Table II of DSCC93026. The DC rated surge voltage is the maximum voltage to which the capacitors should be subjected under any conditions. This includes transcients and ripple at the highest line voltage. The surge voltage is 115 % of rated DC working voltage.
Life test	The capacitors shall be capable of withstanding a 2000 h life test at 85 °C at rated voltage


For technical questions, contact: wettants@vishay.com



Wet Tantalum Capacitors Surface Mount, Molded Case

ENVIRONMENTAL CHARACTERISTICS					
ITEM	CONDITION	COMMENTS			
Hermeticity	MIL-PRF-39006	There shall be no evidence of leakage after testing to MIL-PRF-39006 specifications.			
Moisture resistance	MIL-PRF-39006	Tested in accordance to MIL-PRF-39006 for 30 cycles.			
Altitude	MIL-STD-202G, Method 105 D	100 000 feet test			

MECHANICAL CHARACTERISTICS				
ITEM	CONDITION	COMMENTS		
Thermal shock	MIL-STD-202G, Method 107 A	Per M39006 and DSCC93026, 30 cycles		
Shock	MIL-STD-202G, Method 213 I	Per M39006 and DSCC93026, 100 g		
Vibration (high frequency)	MIL-STD-202G, Method 204 D	Per M39006 and DSCC93026, 20 g		
Resistance to solder heat	MIL-STD-202G, Method 210 F	Terminals at 260 °C for 10 s. The capacitor must not be visibly damaged and the electrical characteristics must not be affected.		
Solderability	ANSI J-STD-002	The terminations must be solderable per the Mil Standard.		
Terminals	MIL-STD-1276	All terminals shall be permanently secured internally and externally, as applicable. All external joints shall be welded.		
Part markings	MIL-STD-1285	The part marking shall include Vishay name, trademark, capacitance, voltage, date code and lot symbol.		
Weight (typical) in g	3.5			



STANDARD PACKAGING QUANTITY					
SERIES	CASE CODE				
5225	OZINES OAGE GODE				
M34	С				



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com