


Z40M18S-F-640-pe

New product for high-end applications, positioning, science, vision, analysis, automotive industry, textile industry, measurement & more

Z-LASER



Features

- Analogue intensity control (up to 32 steps) with digital TTL Trigger up to 1 KHz
- Simple, external hand focusing mechanism
- Thread mounted for simple and versatile mounting
- LED laser operation and pre-failure indicator
- Over voltage protection with surge/spike protection

Main characteristics

Wavelength / Optic	640nm / Elliptical point
Power / Laser class	40mW / Laser class 3B (EN 60825-1:2007)

Optical specifications

Optical power stability	3% over operating temperature range
Wavelength vs. temperature	Typ. 0,25nm / °C
Range of focus	100mm up to ∞
Divergence of beam (FWHM)	< 1 mrad (with dot optic)
Pointing stability	< 15μrad / °C

Electrical specifications

Supply voltage	5-30VDC
Modulation	APC: Analogue intensity control (up to 32 steps) and digital TTL Trigger up to 1 kHz
Protection	reverse polarity and transient/ESD, over temperature protection and LED pre-failure indicator
Connection	M12 plug, 4-pin


Mechanical specifications

Dimensions	128mm x Ø 20mm (focusable version)
Housing	Laser: M18 industry housing, chromed brass Optic head: anodised aluminium
Protection category	IP 67, fully waterproof
Weight	ca. 87g
Electrical isolation	potential-free housing

Environmental conditions

Case temperature	-10°C up to +50°C (heat dissipation e.g. with mounting H8-M18)
Storage temperature	-10°C up to +80°C
Humidity	Max. 90%, non condensing
MTTF at 25°C	> 30.000h (640nm)

Z X M18S - X - X - X



WARNING!

Laser Light -
Avoid Direct
Eye Exposure

Configuration scheme



1: Voltage supply +
2: TTL mod.
3: Voltage supply -
4: Ana mod.

Z-LASER Optoelektronik GmbH • Merzhauser Str. 134 • 79100 Freiburg • Germany
Tel.: +49/761/296 44 44 • Fax: +49/761/296 44 55 • info@z-laser.de • www.z-laser.com