

# Agilent 33220A 20 MHz Function/Arbitrary Waveform Generator

Data Sheet

- Fully compliant to LXI Class C specification
- 20 MHz Sine and Square waveforms
- Pulse, Ramp, Triangle, Noise, and DC waveforms
- 14-bit, 50 MSa/s, 64 k-point Arbitrary waveforms
- AM, FM, PM, FSK, and PWM modulation types
- Linear & logarithmic sweeps and burst operation
- 10 mV $_{\rm pp}$  to 10 V $_{\rm pp}$  amplitude range
- Graph mode for visual verification of signal settings
- Connect via USB, GPIB and LAN



# Uncompromising performance for functions and waveforms

The Agilent Technologies 33220A Function/Arbitrary Waveform Generator uses direct digital synthesis (DDS) techniques to create a stable, accurate output signal for clean, low distortion sine waves. It also gives you square waves with fast rise and fall times up to 20 MHz and linear ramp waves up to 200 kHz.

#### **Pulse** generation

The 33220A can generate variable-edge-time pulses up to 5 MHz. With variable period, pulse width, and amplitude the 33220A is ideally suited to a wide variety of applications requiring a flexible pulse signal.

#### **Custom waveform generation**

Use the 33220A to generate complex custom waveforms. With 14-bit resolution, and a sampling rate of 50 MSa/s, the 33220A gives you the flexibility to create the waveforms you need. It also lets you store up to four waveforms in nonvolatile memory.

The Agilent IntuiLink Arbitrary Waveform software allows you to easily create, edit, and download complex waveforms using the waveform editor. Or you can capture a waveform using IntuiLink for Oscilloscope and send it to the 33220A for output. To find out more about IntuiLink, visit www.agilent.com/find/intuilink.



#### **Measurement Characteristics**

#### **Easy-to-use functionality**

Front-panel operation of the 33220A is straight-forward and user friendly. You can access all major functions with a single key or two. The knob or numeric keypad can be used to adjust frequency, amplitude, offset, and other parameters. You can even enter voltage values directly in  $V_{pp}$ ,  $V_{rms}$ , dBm, or as high and low levels. Timing parameters can be entered in Hertz (Hz) or seconds.

Internal AM, FM, PM, FSK, and PWM modulation make it easy to modulate waveforms without the need for a separate modulation source. Linear and logarithmic sweeps are also built in, with sweep rates selectable from 1 ms to 500 s. Burst mode operation allows for a user-selected number of cycles per period of time. GPIB, LAN, and USB interfaces are all standard, plus you get full programmability using SCPI commands.

# External frequency reference (Option 001)

The 33220A external frequency reference lets you synchronize to an external 10 MHz clock, to another 33220A, or to an Agilent 33250A. Phase adjustments can be made from the front panel or via a computer interface, allowing precise phase calibration and adjustment.

	Triangle, Pulse,
	Noise, DC
Built-in arbitrary	Exponential rise,
,	Exponential fall,
	Negative ramp,
	Sin(x)/x, Cardiac
Waveforms Charact	teristics
Frequency Range	1 μHz to 20 MHz
rrequeries riarige	ι μιτέ το 20 Ινίτιε

Amplitude Flatness	(relative to 1 kHz)	
	< 100 kHz	0.1 dB
	100 kHz to 5 MHz	0.15 dB
	5 MHz to 20 MHz	0.3 dB
Harmonic distortion[2]	[3]	
		$V_{PP}$
DC to 20 kHz	-70 dBc -70	dBc
20 kHz to 100 kHz		dBc
100 kHz to 1 MHz		dBc
1 MHz to 20 MHz		dBc
Total harmonic distor		
DC to 20 kHz	0.04%	
Spurious (non-harmo	nic) <sup>[2],[4]</sup>	
DC to 1 MHz	-70 dBc	
1 MHz to 20 MHz	-70 dBc + 6 dB	octave/
Phase noise		
(10 kHz offset)	-115 dBc / Hz,	typical
Square		
Frequency range	1 μHz to 20 MH	Z
Rise/Fall time	< 13 ns	
Overshoot	< 2%	
Variable duty cycle	20% to 80% (to 40% to 60% (to	
Asymmetry (@ 50% du	ty)	
	1% of period +	5 ns
Jitter (RMS)	1 ns +	
	100 ppm of peri	od
Ramp, Triangle		
Frequency range	1 μHz to 200 kH	lz
Linearity	< 0.1% of peak	output
Variable Symmetry	0.0% to 100.0%	
Pulse		
Frequency range	500 μHz to 5 M	Hz
Pulse width	20 ns minimum	
(period ≤ 10s)	10 ns resolution	•
Variable edge time	< 13 ns to 100 i	
Overshoot	< 2%	
Jitter (RMS)	300 ps +	
Jitter (NIVIS)	0.1 ppm of perio	nd
	an ppin or poin	

Noise	
Bandwidth	9 MHz typical
Arbitrary	
Frequency range	1 μHz to 6 MHz
Waveform length	2 to 64 k points
Amplitude resolution	14 bits (including sign)
Sample rate	50 MSa/s
Min. Rise/Fall Time	35 ns typical
Linearity	< 0.1% of peak output
Settling Time	< 250 ns to 0.5%
	of final value
Jitter (RMS)	6 ns + 30 ppm
Non-volatile memory	four waveforms

Common Characteristics		
Frequency		
Accuracy <sup>[5]</sup>	± (10 <sub>ppm</sub> + 3 pHz) in 90 days	
	$\pm$ (20 <sub>ppm</sub> + 3 pHz) in 1 year	
Resolution	1 μHz	
Amplitude		
Range	10 mV <sub>PP</sub> to 10 V <sub>PP</sub> into 50 $\Omega$ 20 mV <sub>PP</sub> to 20 V <sub>PP</sub> into open circuit	
Accuracy[1],[2] (at 1 kHz)	± 1% of setting ± 1 mV <sub>PP</sub>	
Units	V <sub>PP</sub> , V <sub>rms</sub> , dBm	
Resolution	4 digits	
DC Offset		
Range (peak AC + DC)	$\pm$ 5 V into 50 $\Omega$ $\pm$ 10 V into open circuit	
Accuracy <sup>[1],[2]</sup>	± 2% of offset setting ± 0.5% of amplitude ± 2 mV	
Resolution	4 digits	
Main Output		
Impedance	50 $\Omega$ typical	
Isolation	42 Vpk maximum to earth	
Protection	Short-circuit protected, overload automatically disables main output	

External Frequency Reference (Option 001)		
Rear Panel Input		
Lock Range	10 MHz ± 500 Hz	
Level	100 mV <sub>PP</sub> to 5 V <sub>PP</sub>	
Impedance	1 k $\Omega$ typical, AC coupled	
Lock Time	< 2 seconds	
Rear Panel Output		
Frequency	10 MHz	
Level	632 mV <sub>PP</sub> (0 dBm), typical	
Impedance	50 $\Omega$ typical, AC coupled	

# **Measurement Characteristics** (Continued)

Phase Offset	
Range	+ 360° to - 360°
Resolution	0.001°
Accuracy	20 ns

Modulation	
AM	
Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Depth	0.0% to 120.0%
FM	
Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Deviation	DC to 10 MHz
PM	
Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Deviation	0.0 to 360.0 degrees
PWM	
Carrier waveform	Pulse
Source	Internal/External
Internal modulation	Sine, Square, Ramp, Triangle, Noise, Arb (2 mHz to 20 kHz)
Deviation	0% to 100% of pulse width
FSK	
Carrier waveforms	Sine, Square, Ramp, Arb
Source	Internal/External
Internal modulation	50% duty cycle square (2 mHz to 100 kHz)
External Modulation II (for AM, FM, PM, PV	
Voltage range	± 5 V full scale
Input impedance Bandwidth	5 kΩ typical DC to 20 kHz
	· ·

Sweep	
Waveforms	Sine, Square, Ramp, Arb
Туре	Linear or Logarithmic
Direction	Up or Down
Sweep time	1 ms to 500 s
Trigger	Single, External, or Internal
Marker	falling edge of sync signal (programmable frequency)
Burst <sup>[7]</sup>	
Waveforms	Sine, Square, Ramp, Triangle, Pulse, Noise, Arb
Туре	Counted (1 to 50,000 cycles), Infinite, Gated
Start/Stop Phase	-360° to +360°
Internal Period	1 μs to 500 s
Gate Source	External trigger
Trigger source	Single, External or Internal

#### Trigger input TTL compatible Input level Slope Rising or Falling, selectable Pulse width > 100 ns Input impedance >10 k $\Omega$ , DC coupled < 500 ns Latency 6 ns (3.5 ns for pulse) Jitter (rms) Trigger output TTL compatible Level into $\geq 1~k\Omega$ Pulse width > 400 ns

50  $\Omega$ , typical

≤ 4 Agilent 33220As

191.7 ms 336.5 ms

80.7 ms

19.8 ms

48.4 ms

14.6 ms

1 MHz

**Trigger Characteristics** 

**Output Impedance** 

Maximum rate

Fanout

64 k points

16 k points

4 k points

#### **Programming Times (typical)** Configuration times USB LAN **GPIB Function Change** 111 ms 111 ms 111 ms Frequency Change 1.5 ms 1.2 ms 2.7 ms Amplitude Change 30 ms $30 \; \text{ms}$ 30 ms Select User Arb 124 ms 124 ms 123 ms Arb Download Times (binary transfer) USB LAN **GPIB**

General	
Power Supply	CAT II 100 - 240 V @ 50/60 Hz (-5%, +10%) 100 - 120 V @ 400 Hz (±10%)
Power Consumption	50 VA max
Operating Environment	IEC 61010 Pollution Degree 2 Indoor Location
Operating Temperature	0°C to 55°C
Operating Humidity	5% to 80% RH, non-condensing
Operating Altitude	Up to 3000 meters
Storage Temperature	-30°C to 70°C
State Storage Memory	Power off state automatically saved. Four user-configurable stored states
Interface	USB, GPIB, and LAN standard
Language	SCPI - 1993, IEEE-488.2
Dimensions (W x H x D) Bench top  Rack mount	261.1 mm x 103.8 mm x 303.2mm 212.8mm x 88.3mm
\Maight	x 272.3mm
Weight Safety Designed to	3.4 kg (7.5 lbs) UL-1244, CSA 1010, EN61010
EMC Tested to	MIL-461C, EN55011, EN50082-1
Vibration and Shock	MIL-T-28800, Type III, Class 5
Acoustic Noise	30 dBa
Warm-up Time	1 hour
Warranty	1 year standard

#### **Footnotes**

- [1] add 1/10th of output amplitude and offset spec per °C for operation outside the range of 18°C to 28°C
- [2] Autorange enabled
- [3] DC offset set to 0 V
- [4] spurious output at low amplitude is -75 dBm typical
- [5] add 1 ppm/°C average for operation outside the range of 18°C to 28°C
- [6] FSK uses trigger input (1 MHz maximum)
- [7] Sine and square waveforms above 6 MHz are allowed only with an "infinite" burst count

96.9 ms

24.5 ms

7.3 ms

## **Ordering Information**

#### Agilent 33220A

20 MHz Function/Arbitrary Wavefrom Generator

#### Accessories included

Operating manual, service manual, quick reference guide, IntuiLink waveform editor software, test data, USB cable, and power cord (see language option).

#### **Options**

-	
Opt. 001	External timebase reference
Opt. 0B0	Delete manual
Opt. 1CM	Rackmount kit
	(also sold as Agilent 34190A)
Opt. A6J	ANSI Z540 calibration
Opt. AB0	Taiwan: Chinese manual
Opt. AB1	Korea: Korean manual
Opt. AB2	China: Chinese manual
Opt. ABA	English: English manual
Opt. ABD	Germany: German manual
Opt. ABF	France: French manual
Opt. ABJ	Japan: Japanese manual
Other Accessories	

34131A	Carrying case
34161A	Accessory pouch
34190A	Rackmount kit

#### Agilent Technologies' Test and Measurement Support, Services, and Assistance

Agilent Technologies aims to maximize the value you receive, while minimizing your risk and problems. We strive to ensure that you get the test and measurement capabilities you paid for and obtain the support you need. Our extensive support resources and services can help you choose the right Agilent products for your applications and apply them successfully. Every instrument and system we sell has a global warranty. Two concepts underlie Agilent's overall support policy: "Our Promise" and "Your Advantage."

#### **Our Promise**

Our Promise means your Agilent test and measurement equipment will meet its advertised performance and functionality. When you are choosing new equipment, we will help you with product information, including realistic performance specifications and practical recommendations from experienced test engineers. When you receive your new Agilent equipment, we can help verify that it works properly and help with initial product operation.

#### Your Advantage

Your Advantage means that Agilent offers a wide range of additional expert test and measurement services, which you can purchase according to your unique technical and business needs. Solve problems efficiently and gain a competitive edge by contracting with us for calibration, extra-cost upgrades, out-of-warranty repairs, and on-site education and training, as well as design, system integration, project management, and other professional engineering services. Experienced Agilent engineers and technicians worldwide can help you maximize your productivity, optimize the return on investment of your Agilent instruments and systems, and obtain dependable measurement accuracy for the life of those products.



# Agilent Email Updates

#### www.agilent.com/find/emailupdates

Get the latest information on the products and applications you select.



#### Agilent Direct

## www.agilent.com/find/agilentdirect

Quickly choose and use your test equipment solutions with confidence.



#### Agilent Open

# www.agilent.com/find/open

Agilent Open simplifies the process of connecting and programming test systems to help engineers design, validate and manufacture electronic products. Agilent offers open connectivity for a broad range of system-ready instruments, open industry software, PC-standard I/O and global support, which are combined to more easily integrate test system development.

## www.agilent.com

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

#### Phone or Fax

#### **United States:**

(tel) 800 829 4444 (fax) 800 829 4433

#### Canada:

(tel) 877 894 4414 (fax) 800 746 4866

#### China:

(tel) 800 810 0189 (fax) 800 820 2816

#### Europe:

(tel) 31 20 547 2111

#### Japan:

(tel) (81) 426 56 7832 (fax) (81) 426 56 7840

#### Korea:

(tel) (080) 769 0800 (fax) (080) 769 0900

#### Latin America:

(tel) (305) 269 7500

#### Taiwan:

(tel) 0800 047 866 (fax) 0800 286 331

#### **Other Asia Pacific Countries:**

(tel) (65) 6375 8100 (fax) (65) 6755 0042 Email: tm ap@agilent.com Contacts revised: 09/26/05

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2006 Printed in the USA, April 19, 2006 5988-8544EN

