


Thick Film Chip Dividers, High Voltage



FEATURES

- High voltage up to 3000 V
- Typical resistance ratios of 250:1, 500:1, etc.
- Flow solderable
- Tape and reel packaging available
- Available with either wraparound terminations or as a single termination flip chip
- Suitable for solderable, epoxy bondable, or wire bondable applications
- Termination: Gold, palladium silver, platinum gold, platinum silver, platinum palladium gold or solder-coated nickel barrier available
- Multiple styles, termination materials and configurations, allow wide design flexibility
- Non-magnetic terminations available
- Compliant to RoHS directive 2002/95/EC
- Halogen-free according to IEC 61249-2-21 definition



RoHS*
COMPLIANT
HALOGEN
FREE

| STANDARD ELECTRICAL SPECIFICATIONS | | | | | | |
|------------------------------------|---|----------------------------------|---------------------------|---|----------------------------------|---|
| GLOBAL MODEL | POWER RATING $P_{70^\circ\text{C}}$ W | RESISTANCE RANGE (1) Ω | TOLERANCE (2) $\pm \%$ | TEMPERATURE COEFFICIENT (3) (- 55 °C to + 150 °C) $\pm \text{ppm}/^\circ\text{C}$ | MAXIMUM WORKING VOLTAGE (4) V | TCR TRACKING $\pm \text{ppm}/^\circ\text{C}$ |
| CDHV 2512 | Contact factory | 12M to 1G | 1, 2, 5, 10, 20 | 100 | 3000 | 50 (typical) |

Notes

- (1) Resistance values are calibrated at 100 V_{DC}. Calibration at other voltages available upon request. Contact factory for lower values.
- (2) Contact factory for tighter tolerances.
- (3) Reference only: Not for all values specified. Consult factory for your value.
- (4) Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less.

| VOLTAGE AND TEMPERATURE COEFFICIENTS OF RESISTANCE CHART TYPICAL | | | |
|--|-----------------|-------------|----------------------------------|
| RESISTANCE (Ω) | RATIO (typical) | VCR (ppm/V) | TCR (ppm/°C) - 55 °C to + 150 °C |
| 20M | 250:1 | 10 | 100 |
| 150M | 300:1 | 10 | 150 |
| 800M | 500:1 | 10 | 200 |

Note

- Contact factory for other ratios.

| GLOBAL PART NUMBER INFORMATION | | | | | | | | | | | | | | | | | |
|--|-----------------------------|---|-----------------------|-----------|--|--|--|--|--|---|---|---|---|---|---|---|---|
| New Global Part Numbering: CDHVAF20M0J2500GFB (preferred part number format) | | | | | | | | | | | | | | | | | |
| C | D | H | V | A | F | 2 | 0 | M | 0 | J | 2 | 5 | 0 | 0 | G | F | B |
| GLOBAL MODEL | TERM STYLE | TERM MATERIAL | | | RESISTANCE VALUE (R1) | TOLERANCE | RATIO R1/R2 | RATIO TOLERANCE | SOLDER TERMINATION | | PACKAGING | | | | | | |
| CDHV = CDHV2512 | A = 3-sided B = Top only | F = Nickel barrier A = Palladium silver B = Platinum gold C = Gold D = Platinum silver E = Platinum palladium gold | | | M = M Ω G = G Ω 20M0 = 20 M Ω 800M = 800 M Ω 1G00 = 1 G Ω | F = $\pm 1 \%$ G = $\pm 2 \%$ J = $\pm 5 \%$ K = $\pm 10 \%$ M = $\pm 20 \%$ | 3 digit significant figure, followed by a multiplier 2500 = 250:1 3000 = 300:1 5000 = 500:1 | G = $\pm 2 \%$ H = $\pm 3 \%$ J = $\pm 5 \%$ | E = Sn100 F = Sn95/Ag5 N = No solder S = Sn62/Pb36/Ag2 T = Sn90/Pb10 | | B = Bulk T = Tape and reel W = Waffle | | | | | | |
| Historical Part Numbering: CDHV2512AF2005J2500Ge2 (will continue to be accepted) | | | | | | | | | | | | | | | | | |
| CDHV2512 | A | F | 2005 | J | 2500 | G | e2 | | | | | | | | | | |
| HISTORICAL MODEL | TERM STYLE | TERM MATERIAL | RESISTANCE VALUE (R1) | TOLERANCE | RATIO R1/R2 | RATIO TOLERANCE | SOLDER TERMINATION | | | | | | | | | | |

* Pb containing terminations are not RoHS compliant, exemptions may apply


| MECHANICAL SPECIFICATIONS | |
|---------------------------|---|
| Resistive element | Ruthenium oxide |
| Encapsulation | Glass |
| Substrate | 96 % alumina |
| Termination | Solder-coated nickel barrier standard. Gold, palladium silver, platinum gold, platinum silver, platinum palladium gold terminations available. |
| Solder finish | Pure tin or tin/lead solder alloys standard. Hot solder dipped tin/silver or tin/lead/silver solder alloys available. |

ENVIRONMENTAL SPECIFICATIONS

Operating temperature: - 55 °C to + 150 °C


Life: Less than 0.5 % change when tested at full rated power
(Reference only: Not for all values specified. Consult factory
for your size and value.)

DIMENSIONS in inches (millimeters)



| TERMINATION | LENGTH (L) ± 0.006 (0.152) | WIDTH (W) ± 0.006 (0.152) | THICKNESS (T) ± 0.005 (0.127) | A ± 0.005 | B ± 0.005 | C ± 0.005 | E ± 0.005 |
|---------------------------------|-------------------------------|------------------------------|----------------------------------|-----------|-----------|-----------|-----------|
| STYLE A (3-sided wraparound) | 0.250 | 0.126 | 0.025 | 0.025 | 0.025 | 0.040 | 0.046 |
| STYLE B (top only) | 0.240 | 0.126 | 0.025 | 0.025 | 0.025 | 0.040 | - |

DERATING CURVE



(Reference only: Not for all values specified. Consult factory for your specific value.)

| TYPE | TERMINATION MATERIAL | TERMINATION STYLE | TERMINATION STYLE/ MATERIAL CODE | SOLDER TERMINATION CODE |
|----------------------------------|---------------------------------|----------------------|----------------------------------|-----------------------------|
| Solderable | Nickel barrier | 3-sided (wraparound) | AF | E, F, S or T ⁽³⁾ |
| | | Top only (flip chip) | BF | |
| Wire bondable/ solderable | Platinum palladium gold | Top only (flip chip) | BE | N, F or S ⁽¹⁾ |
| Wire bondable/ epoxy bondable | Gold | Top only (flip chip) | BC | N |
| Epoxy bondable | Palladium silver ⁽²⁾ | Top only (flip chip) | BA | N |
| | Platinum gold | | BB | |
| | Platinum silver | | BD | |

Notes

- ⁽¹⁾ Use solder termination N for applications requiring wire bondable mounting, and solder terminations F or S for applications requiring solderable mounting.
- ⁽²⁾ While not recommended, palladium silver terminations could be used for solderable applications when using a solder alloy containing silver.
- ⁽³⁾ Standard solder plating for the nickel barrier parts are solder terminations E or T. Hot solder dipped terminations F or S are also available.



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.