

# PRODUCT SPECIFICATION

**CKI:** Carl Kammerling  
International Ltd.

<b>Brand</b>	C.K
<b>Product Range</b>	Bolsters and Chisels
<b>Catalogue number</b>	3086, 3087, 3088, 3091 and 3383
<b>Date</b>	26/04/2007

<b>Range Description</b> A range of quality chisels manufactured from the finest materials, designed for construction professionals	
--	--

## Features

- Hardened and tempered to BS3066 for performance
- Powder coated for corrosion protection
- Precision ground cutting edges – sharp and durable



*Electrician's bolster*



*Electricians bolster with grip*



*Brick bolster*



*Brick bolster with grip*



*Plugging chisel*



*Scutch chisel*



*Cold chisel*

Item Number	Item Description	EAN No	Commodity code	Shelf box Qty
T3086	Electricians bolster 55mm, 225mm long	5013969806908	82055910	10
T3086S	Electricians bolster with rubber grip 55mm, 225mm long	5013969416800	82055910	10
T3087 3	Brick bolster chisel 75mm, 75mm long	5013969807004	82055910	10
T3087 4	Brick bolster chisel 100mm, 230mm long	5013969807103	82055910	10
T3087S 3	Brick bolster chisel with rubber grip 75mm, 75mm long	5013969807202	82055910	10
T3087S 4	Brick bolster chisel with rubber grip 100mm, 230mm long	5013969807301	82055910	10
T3088	Plugging chisel 25mm, 250mm long	5013969807400	82055910	10
406001	Scutch chisel 25mm	5051074060013	82055910	3
406002	Scutch chisel 38mm	5051074060020	82055910	3
T4211/1	Spare comb for scutch chisel 25mm		82052000	10
T4211/2	Spare drove for scutch chisel 25mm		82052000	10
T4211/3	Spare comb for scutch chisel 38mm		82052000	10
T4211/4	Spare drove for scutch chisel 38mm		82052000	10
T3383 06	Cold chisel 12mm, 150mm long	5013969318500	82055990	10
T3383 07	Cold chisel 16mm, 180mm long	5013969318609	82055990	10
T3383 08	Cold chisel 19mm, 200mm long	5013969318708	82055990	10
T3383 10	Cold chisel 19mm, 250mm long	5013969318807	82055990	10
T3383 101	Cold chisel 25mm, 250mm long	5013969318906	82055990	10
T3383 12	Cold chisel 25mm, 300mm long	5013969319002	82055990	10
T3383 18	Cold chisel 19mm, 460mm long	5013969319101	82055990	10

Technical product information	Material of construction – high carbon steel , hardened and tempered
Standards compliance	Manufactured in accordance with BS3066
User health and safety information	Users are advised to wear safety goggles and replace the chisel when burrs appear at the striking end
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	Not applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered These products will naturally wear in use, such wear is not covered
Country of origin	United Kingdom

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3086	57	16	230	414				
T3086S	57	73	230	500				
T3087 3	75	20	240	705				
T3087 4	102	21	240	825				
T3087S 3	75	73	240	806				
T3087S 4	100	73	240	855				
T3088	25	18	250	337				
406001	27	16	220	368	44	25	280	375
406002	38	18	228	523	44	28	275	530
T4211/1	25	6	30	15				
T4211/2	25	6	30	15				
T4211/3	40	6	30	25				
T4211/4	40	6	30	25				
T3383 06	13	13	150	149				
T3383 07	15	15	180	247				
T3383 08	19	18	200	302				
T3383 10	19	19	250	381				
T3383 101	21	21	250	751				
T3383 12	25	21	300					
T3383 18	19	15	460	731				

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g Inc product	No of cartons on base	Number of rows high
T3086	115	243	50	4256		
T3086S	240	310	110	5134		
T3087 3	200	260	50	7206		
T3087 4	200	260	50	8406		
T3087S 3	240	320	215	8339		
T3087S 4	240	320	215	8829		
T3088	120	265	53	3492		
406001	85	225	65	1153		
406002	85	225	65	1618		
T4211/1	65	10	130	151		

T4211/2	65	10	130	151		
T4211/3	65	20	130	251		
T4211/4	65	20	130	251		
T3383 06	75	170	30	1533		
T3383 07	120	220	50	2575		
T3383 08	115	220	50	3121		
T3383 10	115	265	55	3930		
T3383 101	120	270	55	7629		
T3383 12						
T3383 18	115	475	37	7469		

### Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3086							116	Box
T3086S							134	Box
T3087 3							156	Box
T3087 4							156	Box
T3087S 3							279	Box
T3087S 4							279	Box
T3088							122	Box
406001							49	Box
406002							49	Box
T4211/1					1	Bag		
T4211/2					1	Bag		
T4211/3					1	Bag		
T4211/4					1	Bag		
T3383 06							43	Box
T3383 07							105	Box
T3383 08							101	Box
T3383 10							120	Box
T3383 101							120	Box
T3383 12								Box
T3383 18							159	Box