
## DISCRETE SEMICONDUCTORS



Product data sheet Supersedes data of 2002 May 08 2005 Jan 11



### FEATURES

- Low collector-emitter saturation voltage
- High current capability
- Replaces two SC-70 packaged low  $V_{\mbox{CEsat}}$  transistors on same PCB area
- Reduces required PCB area
- Reduced pick and place costs.

### APPLICATION

- General purpose switching and muting
- Low frequency driver circuits
- LCD backlighting
- Supply line switching circuits
- Battery driven equipment (mobile phones, video cameras and hand-held devices).

### DESCRIPTION

NPN/PNP low  $\mathsf{V}_{\mathsf{CEsat}}$  transistor pair in a SC-88 plastic package.

#### MARKING

TYPE NUMBER	MARKING CODE		
PBSS2515YPN	N8*		

### Note

- 1. \* = -: made in Hong Kong
- \* = t: made in Malaysia
  - \* = W: made in China.

### **ORDERING INFORMATION**

TYPE NUMBER		PACKAGE			
	NAME	DESCRIPTION VERSIC			
PBSS2515YPN	SC-88	plastic surface mounted package; 6 leads SOT			

### QUICK REFERENCE DATA

SYMBOL	PARAMETER	MAX.	UNIT
V <sub>CEO</sub>	collector-emitter voltage	15	V
I <sub>CM</sub>	peak collector current	1	А
R <sub>CEsat</sub>	equivalent on-resistance	<500	mΩ

### PINNING

PIN	DESCRIPTION	
1, 4	emitter	TR1; TR2
2, 5	base	TR1; TR2
6, 3	collector	TR1; TR2




Fig.1 Simplified outline SC-88 (SOT363) and symbol.

Product data sheet

### PBSS2515YPN

### LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
Per transi	stor; for the PNP transistor with n	egative polarity			
V <sub>CBO</sub>	collector-base voltage	open emitter	-	15	V
V <sub>CEO</sub>	collector-emitter voltage	open base	_	15	V
V <sub>EBO</sub>	emitter-base voltage	open collector	_	6	V
I <sub>C</sub>	collector current (DC)		_	500	mA
I <sub>CM</sub>	peak collector current		_	1	А
I <sub>BM</sub>	peak base current		-	100	mA
P <sub>tot</sub>	total power dissipation	$T_{amb} \le 25 \ ^{\circ}C$	_	200	mW
T <sub>stg</sub>	storage temperature		-65	+150	°C
Tj	junction temperature		_	150	°C
T <sub>amb</sub>	operating ambient temperature		-65	+150	°C
Per device	9				
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> ≤ 25 °C; note 1	_	300	mW

### Note

1. Transistor mounted on an FR4 printed-circuit board.

### THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT	
R <sub>th(j-a)</sub>	thermal resistance from junction to ambient	note 1	416	K/W	

#### Note

1. Transistor mounted on an FR4 printed-circuit board.

### PBSS2515YPN


### CHARACTERISTICS


 $T_{amb}$  = 25 °C unless otherwise specified.


SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
Per transi	stor; for the PNP transistor with	negative polarity				
I <sub>CBO</sub>	collector-base cut-off current	V <sub>CB</sub> = 15 V; I <sub>E</sub> = 0 A	-	-	100	nA
		V <sub>CB</sub> = 15 V; I <sub>E</sub> = 0 A; T <sub>j</sub> = 150 °C	_	-	50	μA
I <sub>EBO</sub>	emitter-base cut-off current	V <sub>EB</sub> = 5 V; I <sub>C</sub> = 0 A	-	-	100	nA
h <sub>FE</sub>	DC current gain	V <sub>CE</sub> = 2 V; I <sub>C</sub> = 10 mA	200	-	-	
		V <sub>CE</sub> = 2 V; I <sub>C</sub> = 100 mA; note 1	150	-	-	
		$V_{CE} = 2 \text{ V}; I_{C} = 500 \text{ mA}; \text{ note } 1$	90	-	-	
V <sub>CEsat</sub>	collector-emitter saturation	I <sub>C</sub> = 10 mA; I <sub>B</sub> = 0.5 mA	-	-	25	mV
	voltage	I <sub>C</sub> = 200 mA; I <sub>B</sub> = 10 mA	-	-	150	mV
		$I_{C} = 500 \text{ mA}; I_{B} = 50 \text{ mA}; \text{ note } 1$	-	-	250	mV
R <sub>CEsat</sub>	equivalent on-resistance	$I_{C} = 500 \text{ mA}; I_{B} = 50 \text{ mA}; \text{ note } 1$	-	300	<500	mΩ
V <sub>BEsat</sub>	base-emitter saturation voltage	$I_{C} = 500 \text{ mA}; I_{B} = 50 \text{ mA}; \text{ note } 1$	-	-	1.1	V
V <sub>BEon</sub>	base-emitter turn-on voltage	V <sub>CE</sub> = 2 V; I <sub>C</sub> = 100 mA; note 1	-	-	0.9	V
NPN trans	sistor					
f <sub>T</sub>	transition frequency	I <sub>C</sub> = 100 mA; V <sub>CE</sub> = 5 V; f = 100 MHz	250	420	-	MHz
C <sub>c</sub>	collector capacitance	$V_{CB} = 10 \text{ V}; I_E = I_e = 0 \text{ A}; f = 1 \text{ MHz}$	_	4.4	6	pF
PNP trans	istor	·				
f <sub>T</sub>	transition frequency	$I_{C} = -100 \text{ mA}; V_{CE} = -5 \text{ V};$ f = 100 MHz	100	280	-	MHz
C <sub>c</sub>	collector capacitance	$V_{CB} = -10 \text{ V}; \text{ I}_{E} = \text{ I}_{e} = 0 \text{ A}; \text{ f} = 1 \text{ MHz}$	_	_	10	pF


#### Note

1. Pulse test:  $t_p \le 300 \ \mu s$ ;  $\delta \le 0.02$ .










PBSS2515YPN

# 15 V low $V_{CE(sat)}$ NPN/PNP transistor

### **PACKAGE OUTLINE**



### PBSS2515YPN

#### DATA SHEET STATUS

DOCUMENT STATUS <sup>(1)</sup>	PRODUCT STATUS <sup>(2)</sup>	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

#### Notes

- 1. Please consult the most recently issued document before initiating or completing a design.
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

#### DISCLAIMERS

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions

above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

**Terms and conditions of sale** — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

## **NXP Semiconductors**

#### **Customer notification**

This data sheet was changed to reflect the new company name NXP Semiconductors, including new legal definitions and disclaimers. No changes were made to the technical content, except for package outline drawings which were updated to the latest version.

#### **Contact information**

For additional information please visit: http://www.nxp.com For sales offices addresses send e-mail to: salesaddresses@nxp.com

© NXP B.V. 2009

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands

R75/03/pp11

Date of release: 2005 Jan 11

Document order number: 9397 750 14428

