

storm

1000 Series Vandal Resistant Keypads



Robust, attack resistant keypads for use in the most exposed and hostile public environments

- Rugged, reliable and responsive data entry
- Vandal resistant (20J BS EN 60068-2-75: 1997)
- Weather, water and dust resistant (IP65)
- All metal keytops and casing
- 4 key, 12 key and 16 key formats
- Permanent, high contrast, engraved keytop graphics
- Raised "home pip" on the "5" key
- Simple 'row and column' circuit matrix, terminated by a male, gold-plated, square pin, 0.1" (2.54mm) pitch connector with locking ramp
- Can be fixed to a flat surface or under panel mounted for a flush, low profile installation



UK Email: sales@storm-interface.com Tel: +44 (0)1895 431421
USA Email: sales.usa@storm-keypads.com Tel: +1 (630) 469 2981

www.storm-interface.com


Storm Interface products include technology protected by international patents and design registration. All rights reserved.

storm

1000 Series vandal resistant keypads


A series of attack resistant keypads for use in the most hostile public environments. Designed and constructed to ensure rapid and reliable data entry in the most challenging applications, the Storm 1000 Series keypads are field proven and lab tested to survive hard use, abuse and vandalism. Ideal for use in a wide range of industrial, commercial and public applications.

Overall Dimensions




Mounting & Connection Details

All dimensions are in mm




Connection Details for 4 Key Keypad



KEY LOCATION	ROW/ COLUMN
A	1
B	2
C	3
D	4
	5

CONN. PIN	ROW/ COLUMN
1	common
2	D
3	C
4	B
5	A


Connection Details for 12 Key Keypad



KEY LOCATION	ROW/ COLUMN
A	1
B	2
C	3
D	4
	5
	6
	7
	8

CONN. PIN	ROW/ COLUMN
1	A
2	B
3	1
4	2
5	3
6	-
7	D
8	C

Connection Details for 16 Key Keypad



KEY LOCATION	ROW/ COLUMN
A	1
B	2
C	3
D	4
	5
	6
	7
	8

CONN. PIN	ROW/ COLUMN
1	A
2	B
3	1
4	2
5	3
6	4
7	D
8	C

Electrical

Contact Bounce	5ms (max)
Contact Resistance	100 ohms (max)
Insulation Resistance	50 Mohms (min)
Breakdown Voltage	500V AC (max 60 secs.)
Operating Voltage	24V DC (max)
Operating Current	50mA (max)

Mechanical

Operational Life	4 million cycles (min) per key
Keypop Travel	1.4mm nominal
Actuation Force	180gms nominal
Connector	0.1" pitch, gold plated square pin, male connector with locking ramp

Environmental

Water / Dust Sealed	IP65 (when mounted to suitable enclosure)
Operational Temperature	-40°C to +100°C (Dry)
Impact	20 Joules via 50mm fl steel impactor

Material

Casing	Chromed die-cast zinc
Keypops	Chromed die-cast zinc
Keypop Legends	Engraved
Contact Circuit	Gold on Nickel plated FR4

Accessories

Item	Stock No.	Notes
PC Interface	4200-00-XX	PS2/USB
Rear Casing	RC1202	Supplied complete with fixing hardware, sealing gaskets and fixing instructions.
Blank Keypops	1K0000	Supplied without keytop graphics. Suitable for engraving.
Privacy Shield	1KFS02	Supplied complete with fixing hardware, sealing gaskets and fixing instructions.

Whilst every effort is made to ensure details are correct at time of print, specifications are subject to change without notice.



Brochure designed & produced by NIK Design: +44 (0)7810 551046

1000-LIT-01 Rev 2 Oct 2004



FM 39602



USA Office:

Storm Interface
Suite 202

364 Pennsylvania Avenue
Glen Ellyn IL 60137 USA

Tel: (630) 469 2981

Fax: (630) 469 2975

Email: sales.usa@storm-keypads.com

UK Office:

Storm Interface
14 Bentinck Court

Bentinck Road
West Drayton

Middlesex UB7 7RQ

Tel: +44 (0)1895 431421

Fax: +44 (0)1895 431132

Email: sales@storm-interface.com

www.storm-interface.com

Storm is a trademark of Keymat Technology Ltd
Storm Interface is a trading name of Keymat Technology Ltd

Storm Interface products include technology protected by international patents and design registration. All rights reserved.