

6

5

4

3

2

1

Rev	AWO #	Description	Date	Appr
-	9427	RELEASED	3/06/09	

APPROVED: _____

DATE: _____ TITLE: _____

D

D

C



C

B

B

A

A



SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contact: Bronze, Tin plated

Screw: Steel, M3/Zn plated

Electrical:

Operation voltage: 300 VAC max

Current rating: 30 Amps max per Pole

Rated surge voltage: 1.6/2.5/4 KV

Mechanical:

Torque (Lb-in): 7

Solid wire: 26-10 AWG

Environmental:

Operating temperature: -40°C to +105°C

Lead free, RoHS compliant.

Recommended soldering temp: 235°C for 5 sec.



ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

TERMINAL BLOCK, PCB, VERTICAL, 6.35MM PITCH

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM TOLERANCES: EXCEPT AS NOTED							
INCHES				HOLES			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	DY		3/06/09	CHECKED			
APPROVED							
SIZE				PART NO.			
X				EB4-XX-P			
REF:				SCALE: NTS			
S00024T				SHEET 1 OF 1			