


Model 6


Window Diameter 2.06"







6SFT



6RL



6SHT



Application

With Ammeters, wattmeters, and cross current compensation.

Frequency

50-400Hz

Insulation Level

0.6kV, 10kV BIL full wave

- Flexible leads are UL 1015 105°C, CSA approved #16 AWG, 24" long
- Non-standard length to be specified
- Terminals are brass studs No 8-32 UNC with one flat washer, lockwasher and regular nut
- SFT and SHT case styles also available as SFL and SHL with leads
- Mounting bracket kit when required for Model 6SHT
- Approximate weight: 1.2 lbs

Approvals



UL 257877

CSA 223647

Catalogue Number	Current Ratio	Accuracy at 60Hz	Burden VA at 60Hz
6 **-101	100:5	± 2%	2.0
6 **-151	150:5	± 1%	5.0
6 **-201	200:5	± 1%	5.0
6 **-251	250:5	± 1%	7.5
6 **-301	300:5	± 1%	12.5
6 **-401	400:5	± 1%	15.0
6 **-501	500:5	± 1%	25.0
6 **-601	600:5	± 1%	30.0
6 **-751	750:5	± 1%	25.0
6 **-801	800:5	± 1%	25.0
6 **-102	1000:5	± 1%	35.0
6 **-122	1200:5	± 1%	40.0
6 **-152	1500:5	± 1%	50.0

****NOTE:** When ordering, prefix Catalogue Number with model designation required, i.e. 6SHT - 201, 6RL - 301, etc.