




SPC
TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS		DOC. NO.	SPC-F005	Effective:	7/8/02	DCP No:	1398	
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			ASH	16-08-10	JAG	17-08-10	XXX	30-08-10





Part Number Table

Description	Part Number
Transformer, Power, Rectifier	SPC20992

Electrical Characteristics:

- Primary: 117V +/- 15%
FREQUENCY = (50,60) Hz
- Secondary: 25.2vct at 2.0ARMS
- Regulation: 13.13% RMS (approx)
- Transformer Isolation: Pri/Sec 1500V
Wind/Care 1500V
- LEADS:
 - Primary: 22 AWG
 - Secondary: 18 AWG
 - UL 1015 105°C PVC
 - Length: 6.0 ±0.5
 - Ends Stripped: 0.5 ±0.125



DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
ASH	16-08-10
CHECKED BY:	DATE:
JAG	19-08-10
APPROVED BY:	DATE:
XXX	30-08-10

DRAWING TITLE:		ELECTRONIC FILE	
Transformer, Power, Rectifier		92N4400	
SIZE	DWG. NO.	SCALE:	SHEET:
XXX	XXX	NTS	1 OF 1
U.O.M.: INCHES [mm]		REV	