

**KLIPPON STB 3 SS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-2083  
 www.weidmueller.com



Ideally suited for the energy and process industry and transportation, the Klippon® STB series is the perfect complement to our existing Klippon housing product line. Enclosures of this series comply with international standards such as EN 62208 and EN 60079-0/7 (ATEX).

Features:

- A standard seal that is resistant to high temperatures - extended temperature range of -50°C to +100°C (+120°C on request)
- Approved according to ATEX, IECEx, cULus, Lloyds Register, Germanischer Lloyd, GOST
- Flexible options when mounting the internal rail
- IP66 protection
- The seal is protected against compression; this ensures that a permanent and secure seal is maintained.
- Earth stud in housing cover and bottom section
- Lasered welding seams offer improved quality
- Delivered with welded-on mounting to ensure an optimal housing installation

Weidmüller can manufacture and supply this enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

**General ordering data**

Order No.	<a href="#">1002720000</a>
Part designation	KLIPPON STB 3 SS
Version	Enclosures, Stainless steel 1.4004 (316L) 1.50mm, 190 mm, 100 mm, 190 mm
GTIN (EAN)	4032248695652
Qty.	1 pc(s).

**KLIPPON STB 3 SS**

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

**Technical data**

**Dimensions**

Length	100 mm	Width	190 mm
Height	190 mm	Fixing dimension, width	219 mm
Weight	2.59 kg		

**General information**

Fixing dimension, width	219 mm	Material	Stainless steel 1.4004 (316L) 1.50mm
Surface	Mirror polished	Cover fixing	M5 hexagon stainless-steel slotted screw with 10mm spanner width
Enclosure fixing	Welded-on mounting foot with 8-mm holes	Integral fixing	TAS 20 rail welded to floor
Material	Stainless steel 1.4004 (316L) 1.50mm	Material thickness of enclosure	1.5 mm
Resistance to shocks	10 J version standard 7 J ATEX version	Sealing material	Silicone
Surface	Mirror polished		

**Cable glands top/bottom**

M 12	21	M 16	15
M 40	3	M 50	2
M 63	1	M20	10
M25	8	M32	3

**cable glands, left**

M 12 (3)	21	M 16 (3)	15
M 20 (3)	10	M 25 (3)	8
M 32 (3)	3	M 40 (3)	2
M 50 (3)	1		

**cable glands, right**

M 12 (2)	21	M 16 (2)	15
M 20 (2)	8	M 25 (2)	6
M 32 (2)	3	M 40 (2)	2
M 50 (2)	1		

**vertical assembly**

WDU 10 / ZDU 10 (2)	15	WDU 16 / ZDU 16 (2)	13
WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	30	WDU 4 / ZDU 4 (2)	25
WDU 6 / ZDU 6 (2)	20		

**Approvals**

Approvals institutes	CULUS; GERMLLOYD; GOSTME25; IBEXUATEX; IECEXIBE; LLOYDSREG
----------------------	--

**Classifications**

eClass 6.0	27-14-91-07
------------	-------------

Creation date October 27, 2010 4:02:21 PM CEST

Last update 27.09.2010 / We reserve the right to make technical changes.