NC4MD-LX-BAG

4 pole male receptacle, solder cups, black metal housing, silver contacts

The DLX series features a compact all metal housing with an ingenious duplex ground contact, which offers excellent RF protection and shielding. It is the ideal match for mating with Neutrik's EMC XLR cable connector.

Features & Benefits

- All metal housing offers best overall RF protection and electromagnetic shielding
- New duplex ground contact for excellent contact integrity between chassis and cable connector
- Male connector#s retention bar replaces plastic design with all metal version improving pull-out force
- Larger solder contacts for easier termination
- Optional connection to easily join pin1 to chassis ground
- D-style housing provides installation compatibility with industry standard D mounting dimensions

Product				
Connector Type	XLR			
Gender	male			
Electrical				
Capacitance between contacts	≤ 7 pF			
Contact resistance	≤ 3 mΩ			
Dielectric strength	1,5 kVdc			
Insulation resistance	> 2 GΩ (initial)			
Insulation resistance	$> 1~{\rm G}\Omega$ (after damp heat test)			
Rated current per contact	10 A			
Rated voltage	50 V			
Mechanical				
Insertion force	≤ 20 N			
Withdrawal force	≤ 20 N			
Lifetime	> 1000 mating cycles			
Wire size	max. 1.5 mm²			
Wire size	max. 16 AWG			
Wiring	Solder contacts			
Locking device	latch lock			
Mounting direction	front & rear			
Chassis shape	D			
Material				
Contact plating	2 μm Ag over 2 μm Ni			
Contacts	Brass (CuZn39Pb3)			
Insert	Polyamide (PA 6.6 30 % GR)			
Locking element	Steel Ck67			
Shell	Zinc diecast (ZnAl4Cu1)			
Shell plating	Black chromium			
Environmental				
Flammability	UL 94 HB			
Standard compliance	IEC 61076-2-103			
Solderability	Complies with IEC 68-2-20			
Temperature range	-30 °C to +80 °C			