



	PART NO.		REVISIONS									
🐢 multicomp		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE		
	2212S-18SG-85	-	А	RELEASED	Veena	01/8/08	Suresh	01/8/08	G. C	15/8/08		
	Γ											









Specifications:

Current rating Voltage rating Maximum contact resistance Minimum insulation resistance Withstanding voltage Operating temperature range **Material and Finish:** Insulator Insulator colour Contact Finish

- : 3.0A ac/dc.
- : 250V ac/dc.
- : **20m**Ω.
- : 1000MΩ.
- : 600V ac for one minute.
- : -40°C to +105°C.
- : High temperature plastic (PBT).
- : Black.
- : Phosphor Bronze.
- : Selective gold plated.

Dimensions : Millimetres


Information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change with- out notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:				
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Veena	01/08/08	PCB Socket Double Row Straight - 18 Way				
		CHECKED BY:	DATE:	SIZE DWG NO.		ELECTRONIC FILE	REV	
		Suresh	01/08/08		110001436	2212S-XXSG-85-F1(REV)_DWG	Α	
		APPROVED BY:	DATE:				L	
		G.Cook	15/08/08	SCALE: NTS	U.O.M.: mm	SHEET: 1 OF	F 2	

	PART NO.		REVISIONS								
	2212S-18SG-85	ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
		-	А	RELEASED	Veena	01/8/08	Suresh	01/8/08	G. C	15/8/08	

Specification Table

	Number of Positions	Α	В	Part Number						
18		46.22	43.18	2212S-18SG-85						
	Dimensions : Millimetres									

Part Number Explanation:



Plated: SG = Selective Gold Plated.Plastic Height: 85 = 8.5mm.

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk

(the Group) for are indensed to it. No licence is granied for the bas of inder trian inor information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The information is subject to change with- out notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or ornision from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or ornited. Liability for loss or damage resulting from any relance on the Information or	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:					
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Veena	01/08/08	PCB Socket Double Row Straight - 18 Way					
		CHECKED BY:	DATE:	SIZE DWG NO.		ELECTRONIC FILE 2212S-XXSG-85-F1(REV)_10_DWG		REV	
		Suresh	01/08/08		M10001435			A	
		APPROVED BY:	DATE:			l			
		G.Cook	15/08/08	SCALE: NTS	U.O.M.: mm		SHEET: 2 O	F 2	