

# SPECIFICATION

Product : Thermoelectric module

Part Number : PF-199-14-15

1 . Scope

- 1—1 This specification is applied to Multicomp thermoelectric modules
- 1—2 Revision of these specifications is carried out after consent.

2 . Specification

2 - 1 Parameters

Parameters		Remarks
Internal resistance	3.54 Ω ± 10%	Note-1
I <sub>max</sub> .	6.1 A	Note-2
V <sub>max</sub> .	24.4 V	Note-3
	Th=25°C	
Q <sub>max</sub> .	85.7 W	Note-4
ΔT <sub>max</sub> .	73°C	Note-5
solder melting point	232 °C	Note-6
Maximum. compress.	1MPa	Note-7

Note-1 Measured by AC 4-terminal method at 25°C.

Note-2 Maximum current at ΔT<sub>max</sub>.

Note-3 Maximum voltage at ΔT<sub>max</sub>.

Note-4 Maximum cooling capacity at I<sub>max</sub>.,V<sub>max</sub>. and ΔT = 0°C.

Note-5 Maximum temperature difference at I<sub>max</sub>.,V<sub>max</sub>. and Q = 0W.

( Maximum parameters are measured in a vacuum 1.3P )

Note-6 The solder melting point of thermoelectric module

Note-7 Recommended maximum compression (not destruction limit)

## 2 - 2 Recommendations:

- maximum temperature for short time: 200 °C
- operation temperature up to 150°C for long lifetime
- high power cycling applications in ON/OFF mode
- recommended operation current not higher than 0.7 of Imax
- preferable application; thermal management

## 2 - 3 Performance Graph (298K)

