

Model CLSM-200LA **Closed Loop Hall Effect**

Description

The Model CLSM-200LA is a closed loop Hall effect current sensor that accurately measures DC and AC currents and provides electrical isolation between the current carrying conductor and the output of the sensor.

Features

- Low Cost
- Fast response
- High overload capacity
- Moistureproof, Shockproof
- Noncontact measurement of high current
- Measures DC, AC and impulse currents



Applications

- Variable speed drives for motors
- Welding Equipment
- Power Supply Equipment
- Measure and control system
- Over current protection
- Protection of power semiconductors

Electrical Specifications

CLSM-200LA

Nominal current (I_N)	± 200 A
Current range	0 to ± 250 A
Nominal output current (I_M)	100 mA
Turns Ratio	2000 / 1
Measuring Resistance (R_M)	0 to 20 Ω
Overall accuracy at 25°C	± 0.5 % of I_N
Supply voltage (Vdc).....	± 15 to ± 18
Current consumption	15 mA + output current

Accuracy-Dynamic Performance

Zero current offset at 25°C	< ± 0.2 mA
Offset current temperature drift (0°C to +70°C) (1).....	< ± 0.3 mA
Linearity	better than ± 0.1 %
Response time	less than 1 μ s
di / dt	better than 70A/ μ s
Frequency range	DC to 150KHz (-3dB)

General Information

Operating temperature.....	-40°C to +85°C
Storage temperature	-40°C to +90°C
Package	flame retardant plastic case, UL94V-0
Isolation voltage	5kV/50Hz/1 min.
Output reference.....	To obtain a positive output on terminal M, input current must flow in the direction of the arrow (conventional flow)
Weight	38 grams
Mounting	Panel mount via 1 hole, 4.5 mm dia.
Aperture size (mm).....	10.2 x 20.2

Notes:

1. Excludes zero current offset
2. Busbar temperature should not exceed 100°C.
3. The dynamic performance is the best when the busbar fills the aperture.
4. Due to continuous process improvement, all specifications are subject to change without notice.