



Test Report

No. 2019722/EC

Date : Jun 22 2005

Page 1 of 2

MULTICOMP PRODUCTS MANUFACTURED BY
EASY MAGNET CORP
12F-7, NO. 79, SEC.1, HSIN TAI WU RD, HSI-CHIH
TAIPEI HSIEN, TAIWAN, R.O.C

Report on the submitted sample said to be EMI SLEEVES

SGS Job No. : 1742629
Part Description : 33RH Type
Buyer : PREMIER FARNELL ASIA PTE LTD
Supplier : EASY MAGNET CORP
Sample Receiving Date : APR 15 2005
Testing Period : APR 15-25 2005

Test Requested : With reference to RoHS Directive 2002/95/EC
1) To determine the Cadmium content in the submitted sample.
2) To determine the Lead content in the submitted sample.
3) To determine the Mercury content in the submitted sample.
4) To determine the Hexavalent Chromium content on the submitted sample.
5) Determination of PBBs (polybrominated biphenyls), PBDEs (Polybrominated diphenylethers) of the submitted sample.

Test Method : 1-3) In-House Method.
The sample was digested by acid. Analysis was performed by Inductively Coupled Argon Plasma - Atomic Emission Spectrometry (ICP-AES) or Atomic Absorption Spectrometry.
4) As specified in EPA Method 3060A & 7196A.
The sample was alkaline digested by using EPA Method 3060A, and then analyzed by using Colorimetric method 7196A.
5) With reference to SGS in-house method. Analysis was performed by GC/MS.

Test Results : 1-5) Please refer to next page.

Conclusion : 1-5) When tested as specified, the submitted sample complies with the requirements of RoHS Directive Consultation document on 2002/95/EC.

Signed for and on behalf of
SGS Hong Kong Ltd


Ho Ka Ting, Family
Laboratory Executive

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company.

H11987849



Test Report

No. 2019722/EC

Date : Jun 22 2005

Page 2 of 2

Test Results :

| Element | 1 | Limit of RoHS Consultant Document |
|--|---------|-----------------------------------|
| 1) Cadmium (Cd) | < 2 ppm | 100 ppm |
| 2) Lead (Pb) | 98 ppm | 1000 ppm |
| 3) Mercury (Hg) | < 2 ppm | 1000 ppm |
| 4) Hexavalent Chromium (Cr ⁶⁺) | < 2 ppm | 1000 ppm |

(Results shown are of the total weight of samples)

Note : < = Less than
ppm = mg/kg

5)

| Flame Retardants | 1 | Detection Limit | Limit of RoHS Consultant Document |
|---|-----------|-----------------|-----------------------------------|
| Polybrominated Biphenyls (PBBs) | ND | 50 ppm | 1000 ppm |
| Monobromobiphenyl | ND | 5 ppm | -- |
| Dibromobiphenyl | ND | 5 ppm | -- |
| Tribromobiphenyl | ND | 5 ppm | -- |
| Tetrabromobiphenyl | ND | 5 ppm | -- |
| Pentabromobiphenyl | ND | 5 ppm | -- |
| Hexabromobiphenyl | ND | 5 ppm | -- |
| Heptabromobiphenyl | ND | 5 ppm | -- |
| Octabromobiphenyl | ND | 5 ppm | -- |
| Nonabromobiphenyl | ND | 5 ppm | -- |
| Decabromobiphenyl | ND | 5 ppm | -- |
| Polybrominated Diphenylether (PBDEs) | ND | 50 ppm | 1000 ppm |
| Monobromodiphenyl ether | ND | 5 ppm | -- |
| Dibromodiphenyl ether | ND | 5 ppm | -- |
| Tribromodiphenyl ether | ND | 5 ppm | -- |
| Tetrabromodiphenyl ether | ND | 5 ppm | -- |
| Pentabromodiphenyl ether | ND | 5 ppm | -- |
| Hexabromodiphenyl ether | ND | 5 ppm | -- |
| Heptabromodiphenyl ether | ND | 5 ppm | -- |
| Octabromodiphenyl ether | ND | 5 ppm | -- |
| Nonabromodiphenyl ether | ND | 5 ppm | -- |
| Decabromodiphenyl ether | ND | 5 ppm | -- |

Note: ND = Not Detected

Non-detected is lower than detection limit value.

Sample Description:

1. Dark Grey Magnet

Remark: Photo appendix is included

*** End of Report ***

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company.


H11987848



Test Report No. : 2019722EC


Sample Receiving Date : APR 15 2005

PHOTO APPENDIX



SGS authenticate the photo on original report only

Page 1 of 1


Authorized Signature
Ho Ka Ting, Family
Laboratory Executive

This test document cannot be reproduced in any way, except in full context, without prior approval in writing from SGS.