



## Test Report

No. 2022030/EC

Date : Jun 30 2005

Page 1 of 2

MULTICOMP PRODUCTS MANUFACTURED BY  
 PAN OVERSEAS ELECTRONIC CO LTD  
 11F,NO.480, RUEIGUANG ROAD  
 NEIHU CHIU , TAIPEI, 114, TAIWAN , R.O.C.

Report on the submitted sample said to be RADIAL CERAMIC DISC AND PLATE CAPACITOR

SGS Job No. : 1758422  
 Part Description : Y5V DIELECTRIC  
 Buyer : PREMIER FARNELL ASIA PTE LTD  
 Supplier : PAN OVERSEAS ELECTRONIC CO., LTD.  
 Sample Receiving Date : MAY 06 2005  
 Testing Period : MAY 06-17 2005


Test Requested : With reference to RoHS Directive 2002/95/EC  
 1) To determine the Cadmium content in the submitted sample.  
 2) To determine the Lead content in the submitted sample.  
 3) To determine the Mercury content in the submitted sample.  
 4) To determine the Hexavalent Chromium content on the submitted sample.  
 5) Determination of PBBs (polybrominated biphenyls), PBDEs (Polybrominated diphenylethers) of the submitted sample.

Test Method : 1-3) In-House Method.  
 The sample was digested by acid. Analysis was performed by Inductively Coupled Argon Plasma - Atomic Emission Spectrometry (ICP-AES) or Atomic Absorption Spectrometry.  
 4) As specified in EPA Method 3060A & 7196A.  
 The sample was alkaline digested by using EPA Method 3060A, and then analyzed by using Colorimetric method 7196A.  
 5) With reference to SGS in-house method. Analysis was performed by GC/MS.

Test Results : 1-5) Please refer to next page.

Conclusion : When tested as specified, the submitted sample complies with the requirements of RoHS Directive Consultation document on 2002/95/EC.

Signed for and on behalf of  
 SGS Hong Kong Ltd

  
 Ho Ka Ting, Family  
 Laboratory Executive

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company.

H11991872



## Test Report

No. 2022030/EC

Date : Jun 30 2005

Page 2 of 2

### Test Results :

Element	1	2	Limit of RoHS Consultant Document
1) Cadmium (Cd)	< 2 ppm	< 2 ppm	100 ppm
2) Lead (Pb)	110 ppm	13 ppm	1000 ppm
3) Mercury (Hg)	< 2 ppm	< 2 ppm	1000 ppm
4) Hexavalent Chromium (Cr <sup>6+</sup> )	< 2 ppm	< 2 ppm	1000 ppm

(Results shown are of the total weight of samples)

Note : < = Less than  
ppm = mg/kg  
0.01% = 100 ppm

5)

Flame Retardants	1	2	Detection Limit	Limit of RoHS Consultant Document
<b>Polybrominated Biphenyls (PBBs)</b>	ND	ND	<b>50 ppm</b>	<b>1000 ppm</b>
Monobromobiphenyl	ND	ND	5 ppm	--
Dibromobiphenyl	ND	ND	5 ppm	--
Tribromobiphenyl	ND	ND	5 ppm	--
Tetrabromobiphenyl	ND	ND	5 ppm	--
Pentabromobiphenyl	ND	ND	5 ppm	--
Hexabromobiphenyl	ND	ND	5 ppm	--
Heptabromobiphenyl	ND	ND	5 ppm	--
Octabromobiphenyl	ND	ND	5 ppm	--
Nonabromobiphenyl	ND	ND	5 ppm	--
Decabromobiphenyl	ND	ND	5 ppm	--
<b>Polybrominated Diphenylether (PBDEs)</b>	ND	ND	<b>50 ppm</b>	<b>1000 ppm</b>
Monobromodiphenyl ether	ND	ND	5 ppm	--
Dibromodiphenyl ether	ND	ND	5 ppm	--
Tribromodiphenyl ether	ND	ND	5 ppm	--
Tetrabromodiphenyl ether	ND	ND	5 ppm	--
Pentabromodiphenyl ether	ND	ND	5 ppm	--
Hexabromodiphenyl ether	ND	ND	5 ppm	--
Heptabromodiphenyl ether	ND	ND	5 ppm	--
Octabromodiphenyl ether	ND	ND	5 ppm	--
Nonabromodiphenyl ether	ND	ND	5 ppm	--
Decabromodiphenyl ether	ND	ND	5 ppm	--

Note: ND = Not Detected  
Non-detected is lower than detection limit value.

### Sample Description:

1. Bronze Ceramic w/ Black Printing w/ Silvery Metal (Body)
2. Silvery Metal (Pin)

Remark: Photo appendix is included.

\*\*\* End of Report \*\*\*

This Test Report is issued by the Company subject to its General Conditions of Service printed overleaf. Attention is drawn to the limitations of liability, indemnification and jurisdictional issues defined therein. The results shown in this test report refer only to the sample(s) tested unless otherwise stated. This Test Report cannot be reproduced, except in full, without prior written permission of the Company.


H11991871



Test Report No. : 2022030/EC

Sample Receiving Date : MAY 06 2005

### PHOTO APPENDIX



SGS authenticate the photo on original report only

Page 1 of 1

Authorized Signature

Ho Ka Ting, Family  
Laboratory Executive

This test document cannot be reproduced in any way, except in full context, without prior approval in writing from SGS.