


SECTION 2 PCB TERMINAL BLOCKS


7.62mm Pitch **Standard Profile** Rising Clamp Terminal

Features

- 2 & 3 pole double interlocking mechanism for increased strength
- 4-12 pole pre-assembled
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 2.5mm² cable entry
-  approved cUL applied for
- Guided pin alignment



Type No.	Poles	Length
CTB0118/2	2	15.24mm
CTB0118/3	3	22.86mm
CTB0118/4	4	30.48mm
CTB0118/5	5	38.10mm
CTB0118/6	6	45.72mm
CTB0118/7	7	53.34mm
CTB0118/8	8	60.96mm
CTB0118/9	9	68.58mm
CTB0118/10	10	76.20mm
CTB0118/11	11	83.82mm
CTB0118/12	12	91.44mm



Specification


Rating	20A/750V
Dielectric strength	≥ 3kV/60sec
Insulation resistance	≥ 5MΩ
Working temperature	-20°C to 125°C
Short period	160°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	5μ tinned, nickel plated brass
Wire protect	Nickel plated brass
Screw/torque	M3 steel, 6μ zinc colour passivated and tropicalised/0.5Nm
Recommended PCB hole size	ø1.3mm

If you use

- Limit Switches
- Industrial Micro Switch
- Push Buttons
- Control Stations
- Control Boxes
- Key Switches
- Rotary Switches
- Joysticks
- Solenoid Switches

Please contact our sales desk and request our **Controls Catalogue** for all your industrial and control product requirements.

Tel: +44 (0)1727 864437
 Fax: +44 (0)1727 855400
sales@camden-electronics.co.uk
www.camden-electronics.co.uk



PCB TERMINAL BLOCKS
 FUSES & FUSE HOLDERS
 RELAYS
 BATTERIES
 LEDS
 PHOTOVOLTAIC CELLS
 PHOTOVOLTAIC CONTROLS
 PHOTOVOLTAIC SYSTEMS