# DATA SHEET



# MINIATURE SIGNAL RELAY

# Low power consumption Non-polarized standard miniature relay

### DESCRIPTION


This series is a plastic sealed miniature relay designed to offer completely dust and waterproof package with bifurcated and crossbar contacts for assuring high reliability.

## **FEATURES**

- O Low power consumption and non-polarized relay (200 mW)
- O Plastic sealed package for flow-soldering process
- O Super reliability at signal level

# **APPLICATIONS**

Electronic switching systems, test equipment, LAN systems, modems, facsimile, factory automation systems, audiovisual aids, and other electronic equipment



#### For Right Use of Miniature Relays

#### DO NOT EXCEED MAXIMUM RATINGS.

Do not use relays under exceeding conditions such as over ambient temperature, over voltage and over current. Incorrect use could result in abnormal heating, damage to related parts or cause burning.

#### READ CAUTIONS IN THE SELECTION GUIDE.

Read the cautions described in NEC/TOKIN's "Miniature Relays" (0123EMDD03VOL01E) when you choose relays for your application.

Date Published August 2002 M Printed in Japan


© NEC TOKIN Corporation 2002


⚠

•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.

# NEC/TOKIN

#### PIN CONFIGURATIONS (BOTTOM VIEW)






(Note) The coil has no polarity.


(Note) General tolerance ±0.2 (0.008) mm

#### OUTLINE DRAWINGS AND DIMENSIONS Unit : mm (inch)




(Note) The tolerance is  $\pm 0.2$  (0.008) unless otherwise specified. The dimension in the box shows basic size.

#### MARKING (SIDE VIEW)



#### SAFETY STANDARD AND RATING



\* Spacing : UL114, UL478

2

 $\triangle$ 


•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.

## PERFORMANCE CHARACTERISTICS

Contact Form		2 form c		
Contact Material		Silver alloy with gold alloy overlay		
	Max. Switching Power	60 W, 125 VA		
	Min. Switching Power	100 mVdc, 100 <i>µ</i> A		
Contact Ratings	Max. Switching Voltage	200 Vdc, 250 Vac		
	Max. Switching Current	2 A		
	Max. Carrying Current	2 A		
Initial Contact Resistance		50 mΩ typ.		
Nominal Operating Power	ſ	200 mW		
Operate Time (Excluding Bounce)		Approx. 5.5 ms without diode (at nominal coil voltage)		
Release Time (Excluding Bounce)		Approx. 2 ms without diode (at nominal coil voltage)		
Insulation Resistance		Above 1000 MΩ at 500 Vdc		
	Between Open Contacts	500 Vac (for one mimute)		
Breakdown Voltage	Between Adjacent Contacts	1000 Vac (for one minute)		
	Between Coil and Contact	1500 V surge (10 × 160 <i>µ</i> s * <sup>1</sup> )		
Shock Resistance		294 m / s <sup>2</sup> (misoperating)		
		980 m / s <sup>2</sup> (destructive failure)		
Vibration Resistance		10 to 55 Hz, at double amplitude of 1.5 mm (misoperating) 10 to 55 Hz, at double amplitude of 5 mm (destructive failure)		
Ambient Temperature		-40 to +85°C		
Coil Temperature Rise		Approx. 22°C at nominal coil voltage (200 mW)		
	Noload	Above 10 × 10 <sup>6</sup> operations		
Running Specifications	Load	50 Vdc 0.1A (resistive) Above 1 × 10 <sup>6</sup> operations at 85°C 10 Vdc 10 mA(resistive) Above 1 × 10 <sup>6</sup> operations at 85°C		
Weight	·	Approx. 5 grams		

\*1 rise time : 10  $\mu$ s, decay time to half crest : 160  $\mu$ s

#### PART NUMBER SYSTEM



#### **Recommended relay drive conditions**

Drive under conditions		
Nonlatch type	Voltage: within ±5% at nominal voltage	Ambient temperature -40 to +85°C

3

⚠

•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.

# NEC/TOKIN

# **PRODUCT LINEUP**

					at 20°C
	Part Number	Nominal Coil Voltage	Coil Resistance	Must Operate Voltage*	Must Release Voltage*
	MR82-4.5USR	(Vdc) 4.5	(Ω) ± 10% 101	(Vdc) 3.15	(Vdc) 0.23
	MR82-5USR	5	125	3.5	0.25
	MR82-6USR	6	180	4.2	0.3
	MR82-9USR	9	405	6.3	0.45
	MR82-12USR	12	720	8.4	0.6
Γ	MR82-24USR	24	2880	16.8	1.2

\* Test by pulse voltage

⚠


4


•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.

# **TYPICAL PERFORMANCE DATA**


#### ■COIL TEMPERATURE RISE


Temperature is measured by coil resistance.







#### SWITCHING CAPACITY This is allowed maximum value.





■ APPLIED VOLTAGE VS. TIMING (Sample: MR82-5USR)






5

⚠

•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.


## ■OPERATE AND RELEASE VOLTAGE VS. AMBIENT TEMPERATURE

This shows a typical change of operate (release) voltage. Maximum value of operate estimated, so it must be applied more than this value for safety operation. In case of "hot start operation", please inquiry for NEC.




## RUNNING TEST (Nonload)

(Load: None, Driving: 5V.DC, 50 Hz, 50% duty, Ambient temperature: Room temperature, Sample: MR82-5USR 20 pieces)



### RUNNING TEST (Load)

(Load: 50 V.DC 0.1 A resistive, Driving: 5V.DC, 5 Hz, 50% duty, Ambient temperature: 85 degree C, Sample: MR82-5USR 10 pieces)




6

 $\triangle$ 


•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.

#### BREAKDOWN VOLTAGE

Sample: MR82-5USR 10 pieces







7


⚠

•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.

# PACKEGE


Dimension of Relay Tube (Unit : mm)





25 pieces / Tube Material : Polyvinyl chloride (auti-static treated)

### **Outline of Package**



⚠

•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.

#### Notes on Correct Use

#### 1. Notes on contact load

Make sure that the contact load is within the specified range; otherwise, the lifetime of the contacts will be shortened considerably. Note that the running performance shown is an example, and that it varies depending on parameters such as the type of load, switching frequency, driver circuit, and ambient temperature under the actual operating conditions.


Evaluate the performance by using the actual circuit before using the relay

#### 2. Driving relays

- If the internal connection diagram of a relay shows + and - symbols on the coil, apply the rated voltage to the relay in the specified direction. If a rippled DC current source is used, abnormalities such as beat at the coil may occur.

- The maximum voltage that can be applied to the coil of the relay varies depending on the ambient temperature. Generally, the higher the voltage applied to the coil, the shorter the operating time. Note, however, that a high voltage also increases the bounce of the contacts and the contact opening and closing frequency, which may shorten the lifetime of the contacts

- If the driving voltage waveform of the relay coil rises and falls gradually, the inherent performance of the relay may not be fully realized. Make sure that the voltage waveform instantaneously rises and falls as a pulse.




- For a latching relay, apply a voltage to the coil according to the polarity specified in the internal connection diagram of the relay. - If a current is applied to the coil over a long period of time, the coil temperature rises, promoting generation of organic gas inside the relay, which may result in faulty contacts. In this case, use of a latching relay is recommended.

- The operating time and release time indicate the time required for each contact to close after the voltage has been applied to or removed from the coil. However, because the relay has a mechanical structure, a bounce state exists at the end of the operating and release times. Furthermore, because additional time is required until the contact stabilizes after being in a high-resistance state, care must be taken when using the relay at high speeds.

#### 3. Operating environment

- Make sure that the relay mounted in the application set is used within the specified temperature range. Use of a relay at a temperature outside this range may adversely affect insulation or contact performance. - If the relay is used for a long period of time in highly humid (RH

85% or higher) environment, moisture may be absorbed into the relay. This moisture may react with the NOx and SOx generated by glow discharges that occur when the contacts are opened or closed, producing nitric or sulfuric acid. If this happens, the acid produced may corrode the metallic parts of the relay, causing operational malfunction



Because the operating temperature range varies depending on the humidity, use the relay in the temperature range illustrated in the figure below. Prevent the relay from being frozen and avoid the generation of condensation. - The relay maintains constant sealability under normal atmospheric

pressure (810 to 1,200 hpa). Its sealability may be degraded or the relay may be deformed and malfunction if it is used under barometric conditions exceeding the specified range.

- The same applies when the relay is stored or transported. Keep the upper-limit value of the temperature to which the relay is exposed after it is removed from the carton box to within 50°C.

- If excessive vibration or shock is applied to the relay, it may malfunction and the contacts remain closed. Vibration or shock applied to the relay during operation may cause considerable damage to or wearing of the contacts. Note that operation of a snap switch mounted close to the relay or shock due to the operation of magnetic solenoid may also cause malfunctioning.

#### 4. Notes on mounting relays

- When mounting a relay onto a PC board using an automatic chip mounter, if excessive force is applied to the cover of the relay when the relay is chucked or inserted, the cover may be damaged or the characteristics of the relay degraded. Keep the force applied to the relay to within 1 kg.

- Avoid bending the pins to temporarily secure the relay to the PC board. Bending the pins may degrade sealability or adversely affect the internal mechanism.

- It is recommended to solder the relay onto a PC board under the following conditions:

<1> Reflow soldering

Refer to the recommended soldering temperature profile. <2> Flow soldering

Solder temperature: 250°C max., Time: 5 to 10 seconds, Preheating: 100°C max./1 minute max.

<3> Manual soldering Solder temperature: 350°C, Time: 2 to 3 seconds

Ventilation immediately after soldering is recommended. Avoid immersing the relay in cleaning solvent immediately after soldering due to the danger of thermal shock being applied to the relay. - Use an alcohol-based or water-based cleaning solvent. Never use

thinner and benzene because they may damage the relay housing. - Do not use ultrasonic cleaning because the vibration energy

generated by the ultrasonic waves may cause the contacts to remain closed

#### 5. Handling

- Relays are packaged in magazine cases for shipment. If a space is created in the case after some relays have been removed, be sure to insert a stopper to secure the remaining relays in the case. If relays are not well secured, vibration during transportation may cause malfunctioning of the contacts.

- Exercise care in handling the relay so as to avoid dropping it or allowing it to fall. Do not use a relay that has been dropped. If a relay drops from a workbench to the floor, a shock of 9,800 m/s2 (1,000 G) or more is applied to the relay, possibly damaging its functions. Even if a light shock has been applied to the relay, thoroughly evaluate its operation before using it.

Latching relays are factory-set to the reset state for shipment. A latching relay may be set, however, by vibration or shock applied while being transported. Be sure to forcibly reset the relay before using it in the application set. Also note that the relay may be set by unexpected vibration or shock when it is used in a portable set.

- The sealability of a surface-mount relay may be lost if the relay absorbs moisture and is then heated during soldering. When storing relays, therefore, observe the following points: <1> The storage humidity must be no more than 70% RH. The

recommended storage period is 3 months maximum. <2> To store the relay for 3 months or longer, keep the storage humidity to within 50% RH. Do not store the relay for more than 6 months

Â

•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. Please request for a specification sheet for detailed product data prior to the purchase

⚠

•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.

⚠

•All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.

Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.

11

No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC/TOKIN Corporation. NEC/TOKIN Corporation assumes no responsibility for any errors which may appear in this document.

NEC/TOKIN Corporation does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a device described herein or any other liability arising from use of such device. No license, either express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC/TOKIN Corporation or others.

While NEC/TOKIN Corporation has been making continuous effort to enhance the reliability of its electronic components, the possibility of defects cannot be eliminated entirely. To minimize risks of damage or injury to persons or property arising from a defect in an NEC/TOKIN electronic component, customers must incorporate sufficient safety measures in its design, such as redundancy, fire-containment, and anti-failure features. NEC/TOKIN devices are classified into the following three quality grades: "Standard", "Special", and "Specific". The Specific quality grade applies only to devices developed based on a customer designated "quality assurance program" for a specific application. The recommended applications of a device depend on its quality application.

- Standard: Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots
- Special: Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)
- Specific: Aircrafts, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems or medical equipment for life support, etc. The quality grade of NEC/TOKIN devices is "Standard" unless otherwise specified in NEC/TOKIN's Data Sheets

The quality grade of NEC/TOKIN devices is "Standard" unless otherwise specified in NEC/TOKIN's Data Sheets or Data Books. If customers intend to use NEC/TOKIN devices for applications other than those specified for Standard quality grade, they should contact an NEC/TOKIN sales representative in advance.

(Note)

- "NEC/TOKIN" as used in this statement means NEC/TOKIN Corporation and also includes its majorityowned subsidiaries.
- (2) "NÉC/TOKIN electronic component products" means any electronic component product developed or manufactured by or for NEC/TOKIN (as defined above).

DE0202

Printed on recycled paper

⚠

<sup>•</sup>All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC Tokin for updated product data. •Please request for a specification sheet for detailed product data prior to the purchase.