

Z 55 0 06



Wiha. Premium Werkzeuge für Profis.

Stripping Pliers Professional electric.
Insulation 1,000 V AC, VDE-tested and with GS Mark.



- Standards DIN ISO 5744.
Manufactured acc. to EN/IEC 60900:2004.
- Head shape Precision cutting edge prism for even cutting of cable insulation.
- Design An easy to use adjusting screw allows the stripping diameter to be set.
Opening spring for effortless and sensitive handling of pliers.
- Material Special tool steel, tempered.
- Application Simple stripping of cables and strands of up to $\varnothing 5 \text{ mm} = 10 \text{ mm}^2$ conductor cross-section.
For all work on or around electrical components up to 1000 V AC.

Order No.	mm	in	mm	mm		
26847	160	6 1/2	125	5		



Wiha. Premium Werkzeuge
für Profis.

Z 05 0 06

**Needle Nose Pliers Professional electric with Cutting Edge.
Insulation 1,000 V AC, VDE-tested and with GS Mark.**



Standards	DIN ISO 5745.
	Manufactured acc. to EN/IEC 60900:2004.
Head shape	Straight shape.
Design	Extra long cutting edge for flat and round cables. Gripping surfaces serrated in parts. Cutting edges additionally inductively hardened to approx. 60 HRC.
Material	Special tool steel, tempered.
Application	Gripping and holding as well as cutting soft and hard wires and cables. Preferred choice in the mechanical and electrical sectors. For all work on or around electrical components up to 1000 V AC.

Order No.								
26720	160	6 1/2	2,5	1,6	145	5		
26727	200	8	2,8	1,8	190	5		



Wiha. Premium Werkzeuge
für Profis.

Z 01 0 06

**Combination Pliers Professional electric.
Insulation 1,000 V AC, VDE-tested and with GS Mark.**



- Standards DIN ISO 5746.
- Head shape Manufactured acc. to EN/IEC 60900:2004.
Extra long cutting edge for flat and round cables.
Serrated gripper jaws.
- Design Cutting edges additionally inductively hardened to approx. 60 HRC.
- Material Special tool steel, tempered.
- Application General purpose pliers for gripping and holding as well as cutting soft and hard wires and cables.
For all work on or around electrical components up to 1000 V AC.

Order No.	←→ mm	←→ in	○	●	↕	▬	Gross	Net
26705	160	6 ½	3,0	2,0	210	5	14,60	14,60
26711	200	8	3,6	2,5	325	5	17,60	17,60



Wiha. Premium Werkzeuge für Profis.

Z 12 0 06

Diagonal Cutters Professional electric.
Insulation 1,000 V AC, VDE-tested and with GS Mark.



Standards DIN ISO 5749.
 Manufactured acc. to EN/IEC 60900:2004.

Head shape Semi-circular, Swedish style.

Design Low wear lap joint, riveted and able to withstand high loads.
 Lightweight action, clean cutting achieved by specially milled precision cutting edges.
 Long term cutting is achieved through additional inductive hardening to approx. 60 HRC.

Material Special tool steel, tempered.

Application Universal cutter for cutting soft and hard wires and cables, also suitable for cutting and stripping cables.
 For all work on or around electrical components up to 1000 V AC.

Order No.	$\overleftarrow{\text{mm}}$	$\overleftarrow{\text{H}}$	○	○	●			Gross	Net
26737	140	5 ½	4,0	2,5	1,8	175	5	17,00	17,00
26744	180	7	4,6	3,0	2,5	280	5	19,60	19,60



Wiha. Premium Werkzeuge
für Profis.

Z 16 0 06

**Heavy Duty Diagonal Cutters Professional electric.
Insulation 1,000 V AC, VDE-tested and with GS Mark.**



Standards DIN ISO 5749.
 Manufactured acc. to EN/IEC 60900:2004.

Head shape Semi-circular.

Design Low wear lap joint, riveted and able to withstand high levels of load.
 Lightweight action, clean cutting achieved by specially milled precision cutting edges.
 Long term cutting is achieved through additional inductive hardening to approx. 64 HRC.

Material C 60 Special tool steel, tempered.

Application Power-assisted all-round side cutter for cutting soft to extremely hard wires and cables.
 For all work on or around electrical components up to 1000 V AC.

Order No.	←→ mm	←→ in	○	◐	●	⚖	≡	Gross	Net
26748	160	6 ½	3,5	2,5	2,0	220	5	22,20	22,20
26751	180	7	3,8	2,7	2,3	260	5	23,90	23,90
26754	200	8	4,2	3,0	2,5	290	5	25,60	25,60



Wiha. Premium Werkzeuge
für Profis.

Z 02 0 05

High Leverage Combination Pliers Professional.



- Standards: DIN ISO 5746.
- Head shape: Extra long cutting edge for flat and round cables. Serrated gripper jaws.
- Design: Particularly powerful leverage results in 40% less effort being required for cutting tasks compared with standard combination pliers. Cutting edges additionally inductively hardened to approx. 64 HRC, therefore also appropriate for cutting piano wire.
- Material: C 60 Special tool steel, tempered.
- Application: Power assisted general purpose pliers for gripping and holding as well as cutting wires and cables ranging in hardness from soft to extremely hard.

Order No.	mm	in	⊙	●	●	⚖	🔪	Gross	Net
26713	200	8	3,8	2,7	2,3	310	5	17,70	17,70
26716	225	9	4,4	3,0	2,5	360	5	19,90	19,90



Wiha. Premium Werkzeuge
für Profis.

Z 16 0 05

Heavy Duty Diagonal Cutters Professional.



Standards DIN ISO 5749.
Head shape Semi-circular.
Design Low wear lap joint, riveted and able to withstand high levels of load.
 Lightweight action, clean cutting achieved by specially milled precision cutting
 edges.
 Long term cutting is achieved through additional inductive hardening to approx.
 64 HRC.
Material C 60 Special tool steel, tempered.
Application Power assisted, all round diagonal cutter for soft wire as well as the most
 stringent of demands made by piano wires.

Order No.	↔ mm	↔ "	○	●	●	↔ mm	↔ "	Gross	Net
26747	160	6 1/2	3,5	2,5	2,0	220	5	20,20	20,20
26750	180	7	3,8	2,7	2,3	260	5	21,80	21,80
26753	200	8	4,2	3,0	2,5	290	5	22,90	22,90



Wiha. Premium Werkzeuge
für Profis.

Z 22 0 05

Water Pump Pliers Professional with Push Button Setting.



Standards	DIN ISO 8976.
Head shape	Extra narrow head, therefore also appropriate for work in difficult to access areas.
Design	Precision adjustment joint, box type, providing optimum adaptation to object to be gripped. Rapid and simple push button setting and locking. Long durability achieved by additional inductive hardening of gripper jaws to approx. 58 - 60 HRC. Finger jam protection in all settings ensures safe operation.
Material	Chrome vanadium tool steel, tempered.
Application	For gripping and holding pipes and angular profiles such as hex nuts in the installation area.

Order No.	mm	in	⌀	⌀	mm	mm	Gross	Net
26766	250	10	1 3/4	50	360	5	25,20	25,20

Z 21 0 01

Water Pump Pliers Basic, Box Type.



- Standards DIN ISO 8976.
- Head shape Narrow head, therefore also appropriate for work in small spaces.
- Design Precision adjustment joint, box type, providing optimum adaptation to object to be gripped.
Long durability achieved by additional inductive hardening of gripper jaws to approx. 58 - 60 HRC.
- Material Chrome vanadium tool steel, tempered.
- Application For gripping and holding pipes and angular profiles such as hex nuts in the installation area.

Order No.	mm	in	⌀	⌀	mm	mm	Gross	Net
26760	180	7	1	30	160	5	12,40	12,40
26761	250	10	1 3/4	50	305	5	13,10	13,10
26763	300	12	2	63	490	5	20,40	20,40