

130-588

Product Information



SCREEN-CLENE - Antistatic Screen & Filter Wipes

Product Code SCR 100T

Packaging 100 wipes per tub

Description

An anti-static screen cleaner developed for daily cleaning of VDU Screens and anti-glare filters.

Non-smearing and non-flammable impregnated wipes in 100 cloth roll.

Where to use

All VDU Screens and anti-glare filters (except mesh screens) OHP glass and lenses.

How to use

Remove lid and thread corner of first tissue from inside of roll through the centre hole. Replace lid and pull through gently. Wipe screen or filter thoroughly, applying light pressure only.

Does NOT require additional drying.

SELLING POINTS

1. Lint-free, tear resistant wipes.
2. Packaged in handy sized tub.
3. Suitable for use on all anti-glare filters (not mesh).
4. Tub made of environmentally friendly plastic (100% recyclable).
5. Requires no drying.

SAFETY DATA SHEET

PAGE: 1 of 3
PRINT DATE: 06/01/1998
REF: SCR100T

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND THE COMPANY/UNDERTAKING

SCREENCLENS TUB

Product name:

Product code:

AUTOMATION FACILITIES

Supplier:

H.K. Wentworth Ltd.,

Wentworth House, Blakes Road,

Wargrave, Berkshire, RG10 8AW, United Kingdom.

Fax No: 0118 9403084

Emergency telephone number:

0118 9404031

2. COMPOSITION/INFORMATION ON INGREDIENTS

Identification of the preparation	Chemical Name	CAS-No	EC-No	Class	Weight %
Cloth impregnated with fluid.	MONOPROPYLENE GLYCOL METHYL ETHER	107-98-2	603-064-00-3	R10	< 5
	METHANOL	67-56-1	200-659-6	F: R11 T; R23/25	< 2
NON HAZARDOUS CONSTITUENTS					> 90

3. HAZARDS IDENTIFICATION

Most important hazards:

Non hazardous

Specific hazards

Solvents may degrease the skin. Prolonged skin contact may cause skin irritation and/or dermatitis. Contact with eyes may cause irritation.

4. FIRST AID MEASURES

General advice:

Show this safety data sheet to the doctor in attendance. Move to fresh air in case of accidental inhalation of vapours. Wash off with soap and plenty of water.

Skin contact:

Flush eye(s) immediately with plenty of water if eye irritation persists, consult a specialist

Ingestion:

Clean mouth with water and drink afterwards plenty of water. Consult a physician if necessary

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media:

Extinguish with waterspray, dry chemical or alcohol foam

Extinguishing media which must not be used for safety reasons:

Not applicable

Specific hazards:

Standard procedure for chemical fires

Special protective equipment for firefighters:

Wear self contained breathing apparatus for fire fighting if necessary

Specific methods:

Not applicable

6. ACCIDENTAL RELEASE MEASURES

Personal precautions:

wear personal protective equipment

Environmental precautions:

Do not flush into surface water

Methods for cleaning up:

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust) After cleaning, flush away traces with water

7. HANDLING AND STORAGE

Handling:

When using, do not eat, drink or smoke. Avoid contact with the skin and the eyes. Keep containers tightly closed in a cool, well-ventilated place.

Storage:

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Chemical Name: MONOPROPYLENE GLYCOL METHYL ETHER
METHANOL

Long term (8 hrs) = 200ppm / 266mgm⁻³
Short term (15 min) = 250ppm / 333mgm⁻³

NON HAZARDOUS CONSTITUENTS

Engineering measures:

Ensure adequate ventilation

Personal protection equipment:

- Respiratory protection: No personal respiratory protective equipment normally required
- Hand protection: not required under normal use
- Eye protection: not required under normal use
- Skin and body protection: not required under normal use

Hygiene measures:

When using, do not eat, drink or smoke

9. PHYSICAL AND CHEMICAL PROPERTIES

Form:

Liquid

Colour:

colourless

Odour:

alcoholic

pH:

(20 °C)

Boiling point/range:

>100 °C

Melting point/range:

>0 °C

Decomposition temperature:

no data available

Flash point:

does not flash

Autoignition temperature:

no data available

Flammability (solid, gas):

Not applicable

Explosive properties:

Not applicable

Oxidizing properties:

no data available

Vapour pressure:

(20 °C)

hPa

Relative density:

(20 °C)
>= 0.997

Bulk density:

997

kg/m³

Solubility:

completely soluble

(g/l)

- fat solubility

no data available

Viscosity:

mPa.s

no data available

10. STABILITY AND REACTIVITY

Stability:

Stable at normal conditions

Conditions to avoid:

Not applicable

Materials to avoid:

oxidizing agents

Hazardous decomposition products:

None

11. TOXICOLOGICAL INFORMATION

Acute toxicity:

Not applicable

Local effects:

Solvents may degrease the skin

Sensitization:

Not applicable

Long term toxicity:

Prolonged skin contact may cause skin irritation and/or dermatitis

Chronic toxicity:

Not applicable

12. ECOLOGICAL INFORMATION

Mobility:

Persistence and degradability:

Readily biodegradable, according to appropriate OECD test

Bioaccumulation:

Not applicable

Ecotoxicity effects:

Not applicable

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products:

Flush into sewer with plenty of water. Do not contaminate ponds, waterways or ditches with chemical or used container

Contaminated packaging:

Can be offered for recycling, re-conditioning or puncture

14. TRANSPORT INFORMATION

Proper shipping name Not classified as dangerous in the meaning of transport regulations

15. REGULATORY INFORMATION

Classification according to European directive on classification of hazardous preparations 90/492/EEC

- Symbol(s):

- Contains: Not applicable

R-phrase(s):

S2 - Keep out of reach of children. S3 - Keep in a cool place.

16. OTHER INFORMATION

Recommended use:

Recommended restrictions:

Revision number:

0

Further information:

CN No. 34029010

Contact Name: Carolyn Booth

Department: Technical

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process unless specified in the text.