


125-759
105-760

HALL HANDIBURR




RETHREADERS

For cleaning out malformed or obstructed threads in electrical boxes.

Thread sizes available: M3.5, M4.0

- ★ Permanently fitted handle saves the cost and inconvenience of separate tapwrench.
- ★ Easy to use if box is close to a floor or corner
- ★ Quality High Speed Steel Ground Threads for longer life and ease of cutting
- ★ Ground lead on thread gives easy start
- ★ Not as easily lost as small individual taps
- ★ Handle marked with thread size



Rethreaders are part of the Hall 'Handiburr' range which also includes:

Chamferbits 12 4mm, 25mm

Pipe Reamer 10-34mm

Taper Reamers 3-12mm, 10-25mm



3 Flute 90° Head for chamfering or deburring



For deburring conduit, gas or copper pipe



For finishing, sizing or repairing holes in sheet

Other 'HALL' new products for 1987:

'Multicut' Step Drill
Size MC6M 6-18mm




Cutting diameters
6, 8, 10, 12, 14,
16, 18mm

Max material
thickness 5mm

Shank dia 10mm


This is an addition to the range of 'Multicut' Metric - and Inch - size Step Drills - Full range upon enquiry



'Multicut' Set Ref MCS1 contains tools No 1M (4-12mm), No 2M (10-20mm) and No 3M (20-30mm) plus cutting paste

'Conecut' and 'Conecut' Sets in Metal Cases

'Conecut' drills infinitely variable holes and is ideal for sheet steel up to 2mm thick, whilst 'Multicut' is designed to produce parallel-sided holes of specific diameter in slightly thicker materials.



'Conecut Set Ref CM210 contains tools No 0 (3-14mm), No 1 (6-20mm) and No 2 (16-30 5mm) plus cutting paste.

Made by

G&J HALL LTD

BURGESS ROAD, SHEFFIELD S9 3WD

Telephone: (0742) 440562 Telex: 54642

