## Primary lithium battery

## LS 14250

3.6 V Primary lithium-thionyl chloride (Li-SOCl<sub>2</sub>) High energy density ½ AA-size bobbin cell



#### **Benefits**

- High voltage response, stable during most of the lifetime of the application
- Wide operating temperature range (-60°C/+85°C)
- Low self-discharge rate (less than 1 % per year of storage at +20°C)
- Easy integration into compact systems
- Superior resistance to atmospheric corrosion

#### **Key features**

- Stainless steel container and end caps (low magnetic signature)
- Hermetic glass-to-metal sealing
- Non-flammable electrolyte
- Compliant with IEC 60086-4 safety standard and IEC 60079-11 intrinsic safety standard (class T4 assignment)
- Underwriters Laboratories (UL)
   Component Recognition
- Non-restricted for transport/ Non-assigned to Class 9 according to the UN Recommendations on the transport of dangerous goods
   Model Regulations
- · Manufactured in France, UK, China


#### **Main applications**

- Utility metering
- Automatic meter reading
- Alarms and security devices
- Tollgate systems
- Memory back-up
- Computer real-time clocks
- Tracking systems
- Automotive electronics
- Professional electronics

| Cell size refere   | ences   |  | ½ <b>R6</b> – ½ <b>AA</b>     |
|--|---|--|-------------------------------|
| Electrical characte  | eristics  |  |                               |
|  | to cells stored for one year or l   | ess at +30°C max.)   |                               |
|  | V cut-off. The capacity restored<br>drain, temperature and cut-off)   | by the cell varies   | 1.20 Ah                       |
| Open circuit voltage   | (at +20°C)  |  | 3.67 V                        |
| Nominal voltage  | (at 0.1 mA +20°C)   |  | 3.6 V                         |
| Nominal energy   |   |  | 4.32 Wh                       |
| undischarged cells with 3.0 V. The readings temperature, and the | ally up to 100 mA  If pulses, drained every 2 mn at  th 10 µA base current, yield volt  may vary according to the pulse  cell's previous history. Fitting th  d in severe conditions. Consult S | age readings above<br>characteristics, the<br>e cell with a capacitoi  | •                             |
|  | ded continuous current<br>possible, consult Saft)   |  | 35 mA                         |
| Storage  | (recommended)<br>(for more severe conditions, c   | onsult Saft)   | +30°C (+86°F) max             |
| • /  | e range<br>sient T may lead to reduced capa<br>s at the beginning of pulses. Cor  | ,  | -60°C/+85°C<br>(-76°F/+185°F) |
| Physical character   | ristics   |  |                               |
| Diameter (max)   |   |  | 14.55 mm (0.57 in)            |
| Height (max)   |   |  | 25.15 mm (0.99 in)            |
| Typical weight   |   |  | 8.9 g (O.3 oz)                |
| Li metal content   |   |  | approx. 0.3 g                 |
| Available termination  | suffix<br>CN, CNR<br>2 PF, 3 PF, 3 PF RP, 4 PF<br>CNA (AX)<br>FL  | radial tabs<br>radial pins<br>axial leads<br>flying leads <i>etc</i> . |                               |




## LS 14250



Dimensions in mm.

#### 3.7 3.6 3.5 30°C 3.4 voltage (V) 3.3 3.2 3.1 3.0 2.9 28 40% 2.7 2.6 2.5 0.01 0.1 10 100 Current (mA)

Voltage plateau versus Current and Temperature (at mid-discharge)




#### **S**torage

 The storage area should be clean, cool (preferably not exceeding +30°C), dry and ventilated.

#### Warning

- Fire, explosion and burn hazard.
- Do not recharge, short circuit, crush, disassemble, heat above 100°C (212°F), incinerate, or expose contents to water.
- Do not solder directly to the cell (use tabbed cell versions instead).

#### Restored Capacity versus Current and Temperature (2.0 V cut-off)



#### Saft Specialty Battery Group

12, rue Sadi Carnot 93170 Bagnolet - France Tel.: +33 (0)1 49 93 19 18

Fax: +33 (O)1 49 93 19 69

www.saftbatteries.com

#### Doc. Nº 31072-2-0909

Information in this document is subject to change without notice and becomes contractual only after written confirmation by Saft.

For more details on primary lithium technologies please refer to Primary Lithium Batteries Selector Guide Doc N $^\circ$  31048-2.

Published by the Communications Department.

Photo credit: Saft

Société anonyme au capital de 31 944 000  $\in$ 

RCS Bobigny B 383 703 873



## Primary lithium batteries

## Selector guide





## Saft lithium batteries

## meeting your needs...

For more than 32 years, Saft has pioneered the development and production of primary lithium cells and battery packs in Europe, North America and Asia/ Pacific.

Autonomy, power, voltage, shape, weight, service life, price... Saft knows how to tailor battery solutions you can Saft is a world specialist in the design and manufacture of hightech batteries for professional, industrial, space and military uses. With approximately 3,900 employees worldwide, Saft is present in 18 countries and operates two R&D centers.

Five manufacturing sites and an extensive sales network enable the Saft Lithium Battery Division to serve its customers worldwide with a product range that covers the three main primary lithium chemistries of today.


Among recognized characteristics of the Saft spirit worldwide are quality, performance, reliability, openness and an ability to meet the most demanding challenges. Take advantage of them for your applications!

Lithium power at your service Lithium is a light metal which exhibits Combining lithium with manganese dioxide (MnO<sub>2</sub>) powder or low-freezing point liquid cathode materials such as thionyl chloride (SOCl<sub>2</sub>) or sulfur dioxide (SO<sub>2</sub>), results in batteries with high energy, low weight, reduced selfdischarge rate, and ability to operate under extreme conditions.

#### Saft's lithium products

Three lithium chemistries are currently available:

- Lithium-thionyl chloride (Li-SOCl<sub>2</sub>) in LS/LSH 3.6 V cells,
- Lithium-sulfur dioxide (Li-SO<sub>2</sub>) in LO/G 3.0 V cells,
- Lithium-manganese dioxide (Li-MnO<sub>2</sub>) in LM/M 3.0 V cells.



## ...exceeding your expectations

The LS cells are *cylindrical* and based on the high-energy concentric "bobbin" electrode configuration. They are available in *standard* and "W" versions according to the elevated temperature characteristics of the envisioned applications.

The LSH, LO/G and LM/M cells are also *cylindrical* but use the power-optimized "coiled" and "spiral" electrode constructions. The Li-SO<sub>2</sub> cells are available in several versions: "SX" and "G" series, "SHX" high pulse capability series and "SXC" high capacity series.

Corrosion-proof containers, hermetic sealing based on rugged glass-to-metal seals and TIG or laser welds, built-in safety vents and individual protection fuses are design features common to most of Saft's lithium cells.

The LS, LSH, LO/G and LM/M cells are available as single units (with different optional finishes) or assembled within battery packs.

Whatever your application, you will probably find a Saft lithium battery able to meet your particular requirements. If not, custom-made solutions can be developed within your time-to-market constraints.



Glass-to-metal

## Saft primary lithium batteries: applications

|  | Memory<br>back-up | Real-time<br>clocks | Utility<br>metering<br>AMR | Security<br>Alarms | Electronic<br>toll<br>collection | Automotive electronics |   | Emergency<br>location<br>Buoys | Lighting<br>Night<br>vision | Medical<br>defibril-<br>lators | Downhole<br>logging | Meteor-<br>ology<br>Space | Profess-<br>ional<br>electron-<br>ics | GPS/GSM<br>tracking |
|--|-------------------|---------------------|----------------------------|--------------------|----------------------------------|------------------------|---|--------------------------------|-----------------------------|--------------------------------|---------------------|---------------------------|---------------------------------------|---------------------|
| LM/M spirals                           |                   |                     | 0                          | •                  |                                  | •                      | • | •                              | •                           | •                              |                     | •                         | •                                     | •                   |
| LS small bobbins<br>(½ AA, AA, ½ A, A) | •                 | •                   | •                          | •                  | •                                | •                      |   | •                              | •                           |                                | •                   |                           | •                                     | •                   |
| LS large bobbins<br>(C, D)             | •                 |                     | •                          | •                  |                                  | 0                      |   | •                              |                             |                                |                     | •                         | •                                     |                     |
| LSH spirals                            |                   |                     | 0                          | •                  |                                  | 0                      | • | •                              | •                           |                                | •                   | •                         | •                                     | •                   |
| LO/G spirals                           |                   |                     | 0                          | •                  |                                  | •                      | • | •                              | •                           | •                              |                     | •                         | •                                     | •                   |

# **Key features**

#### Primary cells and batteries are not rechargeable.

## High and stable operating voltage

- Above 3 V for LS and LSH cells.
- Above 2 V for LO/G and LM/M cells.

#### · Wide current capability range

From a few microamperes base current for the small LS cells to more than 10 A pulses for some LO/G and LM/M cells.

#### Wide operating temperature range

From –60°C up to +85°C (Standard cells) depending on cell type, current drain and environment conditions.

#### High operating temperature – spiral cell series

Operating safely and reliably up to  $150^{\circ}$ C.

#### · Long shelf life

Capacity loss in storage at +20°C below 1% (LS bobbins) and 3% (LSH, LO/G, LM/M spirals) per year.

#### · Extended operating life

Typically above 5 years, and up to 20 years for some applications.

#### • High energy densities

3-10 times greater than the non-lithium systems.

#### Excellent behavior in humid environments

Corrosion-free stainless steel cell envelopes.

#### Disposal

According to local regulations.

#### Adequate safety

Most of Saft's lithium cells are UL (Underwriters Laboratories) and IEC 60086-4 recognized, and non-restricted for transport. Most battery packs comply with European and US Army standards. Several LS cell models comply with the IEC 60079-11 "Intrinsic Safety" specification for ATEX applications.

#### Storage

The storage area should be clean, cool (preferably not exceeding +30°C), dry and ventilated.

#### • Logistic

The small LS cells are manufactured in France, UK and China.

#### Saft primary lithium chemistries: specific qualities

#### • Li-SOCI,

(LS, LSH cell series)

- Bobbin, coil or spiral construction
- Operating voltage > 3 V
- Ability to operate from60 to +85°C
- Non-flammable electrolyte
- Cells non-pressurized at room temperature
- Hermeticity guaranteed up to +120°C
- Unrivaled nominal capacities (LS)
- High temperature LSH cell series up to +150°C

#### • Li-SO<sub>2</sub>

(LO/G cell series)

- Spiral construction
- Non-flammable electrolyte
- Superior pulse capability
- Excellent capacity above 1 A
- Superior power at -40°C
- Hermeticity guaranteed up to +95°C
- Wide military acceptance

#### Li-MnO<sub>2</sub>

(LM/M cell series)

- Spiral construction
- Non-corrosive electrolyte
- Cells non-pressurized at room temperature
- Spiral cells with good pulse capability
- Minimal voltage delay
- Competitive capacity at high current and low temperature (-40°C)
- The LS "W" cell versions are recommended for use in applications with Widely fluctuating temperature (up to +95°C), such as electronic toll collection.
- ▶ The LO "SHX" cell versions offer superior pulse capability for discharges not exceeding the declared voltage cut-off.

## Saft lithium cell series: performance data

Enclosed data relates to batteries aged up to 12 months and properly stored. Consult Saft regarding specific pulse conditions or usage following prolonged storage and/or exposure to extreme temperatures.

- Nominal capacity at +20°C and 2 V discharge cut-off (continuous current).
- Maximum recommended pulse current: varies according to pulse characteristics (duration, frequency), temperature conditions, cell storage conditions prior to usage and the application's acceptable minimum voltage. The use of parallel capacitor to enhance the voltage at the beginning of pulses might be recommended. Consult Saft.
- Transport status: according to UN Model Regulations Ref. ST/SG/AC.10/1 Revision 15 (2007) and Manual of Tests and Criteria Ref. ST/SG/AC.10/11 Revision 4, 2003.

## Examples of standard individual cell tabbing arrangements



Other cell finishes are available upon request. Check availability and dimensions of tabbing arrangement for considered cell.

## Examples of standard battery packs configurations









## Primary lithium batteries Li-SOCI2 range



## Li-SOCl2 cells

|                | Production<br>site | Size  | Open<br>circuit<br>voltage | Nominal<br>voltage | Nominal capacity<br>(drain)<br>(2.0 V cut-off) | Maximum<br>recommended<br>continuous current | Operating<br>temperature<br>range | Outside<br>diameter<br>max. | Height<br>max. | Typical<br>weight | UL<br>recognition | Transport<br>status |
|----------------|--------------------|-------|----------------------------|--------------------|--|--|-----------------------------------|-----------------------------|----------------|-------------------|-------------------|---------------------|
| Small LS cells | 5                  |       |                            |                    |  |  |                                   |                             |                |                   |                   |                     |
| LS 14250       | UK-F-PRC           | ½ AA  | 3.67 V                     | 3.6 V              | 1.2 Ah (1 mA)                                  | 35 mA  | -60/+ 85°C*                       | 14.55 mm                    | 25.15 mm       | 8.9 g             | yes               | Non-restricted      |
| LS 14250W      | F-PRC              | ½ AA  | 3.67 V                     | 3.6 V              | 1.2 Ah (1 mA)                                  | 20 mA  | -60/+ 95°C*                       | 14.55 mm                    | 25.15 mm       | 8.9 g             | yes               | Non-restricted      |
| LS 14500       | UK-F-PRC           | АА    | 3.67 V                     | 3.6 V              | 2.6 Ah (2 mA)                                  | 50 mA  | -60/+ 85°C*                       | 14.55 mm                    | 50.30 mm       | 16.7 g            | yes               | Non-restricted      |
| LS 14500Ex     | UK-PRC             | АА    | 3.67 V                     | 3.6 V              | 2.6 Ah (2 mA)                                  | 50 mA  | -60/+ 85°C*                       | 14.55 mm                    | 50.30 mm       | 16.7 g            | yes               | Non-restricted      |
| LS 14500W      | F-PRC              | АА    | 3.67 V                     | 3.6 V              | 2.6 Ah (1 mA)                                  | 30 mA  | -60/+ 95°C*                       | 14.55 mm                    | 50.30 mm       | 16.7 g            | yes               | Non-restricted      |
| LS 17330       | UK                 | ²⁄₃ A | 3.67 V                     | 3.6 V              | 2.1 Ah (3 mA)                                  | 25 mA  | -60/+ 85°C*                       | 16.50 mm                    | 33.40 mm       | 14.4 g            | yes               | Non-restricted      |
| LS 17500       | F                  | А     | 3.67 V                     | 3.6 V              | 3.6 Ah (3 mA)                                  | 100 mA                                       | -60/+ 85°C*                       | 17.13 mm                    | 50.90 mm       | 21.9 g            | yes               | Non-restricted      |

<sup>\*</sup>Cells leakproof up to +120°C

#### Large LS cells

| LS 26500   | F | С | 3.67 V | 3.6 V | 7.7 Ah (4 mA)  | 150 mA | -60/+ 85°C* | 26.00 mm | 49.1 to 50.4 mm*** | 48 g | yes | Class 9 |
|------------|---|---|--------|-------|----------------|--------|-------------|----------|--------------------|------|-----|---------|
| LS 33600** | F | D | 3.67 V | 3.6 V | 17.0 Ah (5 mA) | 250 mA | -60/+ 85°C* | 33.40 mm | 60.2 to 61.6 mm*** | 90 g | yes | Class 9 |

<sup>\*</sup>Cells leakproof up to +120°C

#### LSH spiral cells

| LSH 14         | F | С  | 3.67 V | 3.6 V | 5.8 Ah (15 mA)      | 1.3 A  | -60/+ 85°C* | 26.00 mm | 50.40 mm | 51 g    | yes | Class 9        |
|----------------|---|----|--------|-------|---------------------|--------|-------------|----------|----------|---------|-----|----------------|
| LSH 14 "light" | F | С  | 3.67 V | 3.6 V | 3.6 Ah (15 mA)      | 1.3 A  | -60/+ 85°C  | 26.00 mm | 50.40 mm | 51 g    | -   | Non-restricted |
| LSH 20**       | F | D  | 3.67 V | 3.6 V | 13.0 Ah (15 mA)     | 1.8 A  | -60/+ 85°C* | 33.40 mm | 61.60 mm | 100 g   | yes | Class 9        |
| LSH 20-150     | F | D  | 3.67 V | 3.6 V | 14.0 Ah (300 mA)*** | 300 mA | -40/+ 150°C | 32.05 mm | 61.70 mm | 104.5 g | _   | Class 9        |
| LSH DD-150     | F | DD | 3.67 V | 3.6 V | 28.0 Ah (600 mA)*** | 600 mA | -40/+ 150°C | 33.0 mm  | 125.5 mm | 215 g   | _   | Class 9        |

<sup>\*</sup>Cells leakproof up to +120°C

Primary cells and batteries are not rechargeable.

Their internal impedance may rise versus time, especially in case of exposure at elevated temperature.



<sup>\*\*</sup>Low Magnetic cell versions available

<sup>\* \* \*</sup> Depending on cell finish

<sup>\*\*</sup>LSH 20 HTS cell version available All LSH cells are fitted with individual 5 Amp fuse protection

<sup>\* \* \*</sup> Nominal capacity at +150°C

## Li-SOCI<sub>2</sub> Military battery packs

|         | Cell<br>type<br>construction* | Open<br>circuit<br>voltage | Nominal<br>voltage | Voltage<br>cut-off | Rated<br>capacity | Maximum<br>dimensions  | Typical<br>weight | Safety<br>features | NATO<br>Stock Number<br>(NSN) | Typical<br>applications               |
|---------|-------------------------------|----------------------------|--------------------|--------------------|-------------------|------------------------|-------------------|--------------------|-------------------------------|---------------------------------------|
|         |                               |                            |                    |                    |                   |                        |                   |                    |                               |                                       |
| PS 40 A | 4s1p<br>LSH 14                | 14.7 V                     | 14.0 V             | 10.0 V             | 4.6 Ah            | 108 x 65 x 49 mm       | 285 g             | PTC 1.1 A**        | 6135-14-420-1760              | Radiocommunication<br>(TRPP 11/13)    |
| PS 42 A | 2s1p<br>LSH 20                | 7.3 V                      | 7.0 V              | 5.0 V              | 9.0 Ah            | 69.9 x 67.2 x 34 mm    | 230 g             | PTC 3.5 A**        | 6135-14-434-0766              | Radiocommunication<br>(TRPP 39)       |
| PS 48 B | 5s2p<br>LSH 20                | 18.3 V                     | 17.5 V             | 12.6 V             | 18.0 Ah           | 212.4 x 72.7 x 68.5 mm | 1150 g            | PTC 1.85 A**       | 6135-14-451-7198              | Radiocommunication<br>(TRC 350)       |
| PS 52 A | 2s1p<br>LSH 20                | 7.3 V                      | 7.2 V              | 5.0 V              | 12.5 Ah           | 77.5 x 63.5 x 34.6 mm  | 225 g             | PTC 2.0 A**        | 6135-14-459-9265              | Radiocommunication<br>(Portable PR4G) |

210.5 x 68.5 x 37.5 mm

15.0 V

12.5 Ah

720 g

PTC 2.5 A\*

6135-14-459-9266

## Li-SOCI<sub>2</sub> Civil battery packs

22.0 V

PS 53 B

| Cell<br>type<br>construct | Open<br>circuit<br>1* voltage | Nominal<br>voltage | Rated<br>capacity | Maximum<br>dimensions | Typical<br>weight | Typical<br>applications |
|---------------------------|-------------------------------|--------------------|-------------------|-----------------------|-------------------|-------------------------|
|---------------------------|-------------------------------|--------------------|-------------------|-----------------------|-------------------|-------------------------|

| LS 14250 MLB | 1s1p<br>LS 14250 | 3.67 V | 3.6 V  | 1.2 Ah | 16.8 x 28.6 mm        | 15 g | Metering,<br>professional electronics                               |
|--------------|------------------|--------|--------|--------|-----------------------|------|---|
| LS 9V        | 3s1p<br>LS 14250 | 11.0 V | 10.8 V | 1.2 Ah | 49.1 x 46.8 x 26.8 mm | 29 g | Memory back-up, metering, smoke detectors, professional electronics |
| Lithopack    | 2s1p<br>LS 14500 | 7.3 V  | 7.2 V  | 2.6 Ah | 56.6 x 31.6 x 17.3 mm | 34 g | Memory back-up, metering, professional electronics                  |

Primary cells and batteries are not rechargeable.

This data sheet is an insert part of the Primary lithium batteries Selector Guide (ref 31048-2), where complementary information and data on features, safety and storage can be found.

#### Saft **Specialty Battery Group**

12, rue Sadi Carnot 93170 Bagnolet - France Tel.:+33 (O)1 49 93 19 18 Fax:+33 (O)1 49 93 19 69 Doc Nº 31049-2-0710 Edition: July 2010

Data in this document is subject to change without notice and becomes contractual only after written confirmation. Single cells mentioned in this document may have their own specific data sheet with complementary data.

Please check website.

Published by the Communications Department.

Photo credit: Saft.

Société anonyme au capital de 31 944 000 € RCS Bobigny B 383 703 873

Produced by Arthur Associates Limited.



Radiocommunication

(Portable PR4G)

<sup>21.0</sup> V \* Xs Yp = Y parallel branches of X cells in series per branch

<sup>\* \*</sup> Maximum hold current

# Primary lithium batteries Li-SO<sub>2</sub> range



## Li-SO<sub>2</sub> cells

|             | Production<br>site | Size             | Open<br>circuit<br>voltage | Nominal<br>voltage | Nominal capacity<br>(drain)<br>(2.0 V cut-off) | Maximum<br>recommended<br>continuous current | Operating<br>temperature<br>range | Outside<br>diameter<br>max. | Height<br>max. | Weight | UL<br>recognition | Transport<br>status |
|-------------|--------------------|------------------|----------------------------|--------------------|--|--|-----------------------------------|-----------------------------|----------------|--------|-------------------|---------------------|
| G/LO spiral | cells              |                  |                            |                    |  |  |                                   |                             |                |        |                   |                     |
| G 04/3      | UK                 | ½ AA             | 3.0 V                      | 2.8 V              | 0.45 Ah (50 mA)                                | 0.25 A                                       | -60/+ 70°C*                       | 14.2 mm                     | 27.9 mm        | 8 g    | -                 | Non-restricted      |
| G 06/2      | UK                 | AA               | 3.0 V                      | 2.8 V              | 0.95 Ah (80 mA)                                | 0.5 A  | -60/+ 70°C*                       | 14.2 mm                     | 50.3 mm        | 15 g   | -                 | Non-restricted      |
| G 32/3      | UK                 | ²⁄₃ A            | 3.0 V                      | 2.8 V              | 0.8 Ah (80 mA)                                 | 0.75 A                                       | -60/+ 70°C*                       | 16.3 mm                     | 34.5 mm        | 12 g   | -                 | Non-restricted      |
| G 36/2      | UK                 | "long" A         | 3.0 V                      | 2.8 V              | 1.7 Ah (80 mA)                                 | 1.5 A  | -60/+ 70°C*                       | 16.3 mm                     | 57.7 mm        | 18 g   | -                 | Non-restricted      |
| LO 34 SX    | USA                | 1⁄3 С            | 3.0 V                      | 2.8 V              | 1.0 Ah (80 mA)                                 | 1.0 A  | -60/+ 70°C*                       | 25.9 mm                     | 20.3 mm        | 16 g   | yes               | Non-restricted      |
| LO 35 SX    | USA                | ²⁄₃ C            | 3.0 V                      | 2.8 V              | 2.2 Ah (650 mA)                                | 2.0 A  | -60/+ 70°C*                       | 25.9 mm                     | 35.9 mm        | 30 g   | yes               | Non-restricted      |
| G 52/3      | UK                 | С                | 3.0 V                      | 2.8 V              | 3.2 Ah (1.0 A)                                 | 2.5 A  | -60/+ 70°C*                       | 25.6 mm                     | 49.5 mm        | 47 g   | -                 | Class 9             |
| LO 29 SHX   | USA                | С                | 3.0 V                      | 2.8 V              | 3.75 Ah (O.25 A)                               | 2.5 A  | -60/+ 70°C*                       | 25.6 mm                     | 50.4 mm        | 40 g   | yes               | Class 9             |
| G 54/3      | UK                 | 5⁄4 C            | 3.0 V                      | 2.8 V              | 5.0 Ah (0.2 A)                                 | 2.5 A  | -60/+ 70°C*                       | 25.6 mm                     | 60.2 mm        | 58 g   | -                 | Class 9             |
| LO 43 SHX   | USA                | 5/4 C            | 3.0 V                      | 2.8 V              | 5.0 Ah (0.2 A)                                 | 2.5 A  | -60/+ 70°C*                       | 26.0 mm                     | 59.2 mm        | 53 g   | yes               | Class 9             |
| LO 40 SX    | USA                | ⅔ "Thin" D       | 3.0 V                      | 2.8 V              | 3.5 Ah (0.12 A)                                | 2.0 A  | -60/+ 70°C*                       | 28.95 mm                    | 42.29 mm       | 40 g   | yes               | Class 9             |
| LO 30 SHX   | USA                | "Thin" D         | 3.0 V                      | 2.8 V              | 5.75 Ah (O.2 A)                                | 3.0 A  | -60/+ 70°C*                       | 29.1 mm                     | 59.9 mm        | 63 g   | yes               | Class 9             |
| G 26        | UK                 | D                | 3.0 V                      | 2.8 V              | 7.75 Ah (O.25 A)                               | 2.5 A  | -60/+ 70°C*                       | 34.5 mm                     | 59.8 mm        | 85 g   | -                 | Class 9             |
| LO 26 SX    | USA                | D                | 3.0 V                      | 2.8 V              | 7.75 Ah (O.25 A)                               | 2.5 A  | -60/+ 70°C*                       | 34.2 mm                     | 59.3 mm        | 85 g   | yes               | Class 9             |
| LO 26 SXC   | USA                | D                | 3.0 V                      | 2.8 V              | 9.2 Ah (0.25 A)                                | 2.5 A  | -60/+ 70°C*                       | 34.2 mm                     | 59.3 mm        | 85 g   | -                 | Class 9             |
| LO 26 SHX   | USA                | D                | 3.0 V                      | 2.8 V              | 7.5 Ah (1.0 A)                                 | 4.0 A  | -60/+ 70°C*                       | 34.2 mm                     | 59.3 mm        | 85 g   | yes               | Class 9             |
| LO 25 SX    | USA                | "Fat" D          | 3.0 V                      | 2.8 V              | 8.0 Ah (0.27 A)                                | 2.5 A  | -60/+ 70°C*                       | 39.5 mm                     | 50.3 mm        | 96 g   | yes               | Class 9             |
| LO 39 SHX   | USA                | F                | 3.0 V                      | 2.8 V              | 11.5 Ah (1.0 A)                                | 3.0 A  | -60/+ 70°C*                       | 31.9 mm                     | 100.3 mm       | 125 g  | yes               | Class 9             |
| G 22/6      | UK                 | DD               | 3.0 V                      | 2.8 V              | 16.5 Ah (O.5 A)                                | 3.0 A  | -60/+ 70°C*                       | 33.3 mm                     | 120.6 mm       | 175 g  | -                 | Class 9             |
| G 62/1      | UK                 | "Long<br>Fat DD" | 3.0 V                      | 2.8 V              | 34.0 Ah (1.0 A)                                | 3.0 A  | -60/+ 70°C*                       | 41.7 mm                     | 141.0 mm       | 300 g  | -                 | Class 9             |

<sup>\*</sup> Cells leakproof up to +85°C

Primary cells and batteries are not rechargeable.

Their internal impedance may rise versus time, especially in case of exposure at elevated temperature.



## Li-SO<sub>2</sub> Military battery packs

|                                      | Cell<br>type<br>construction* | Open<br>circuit<br>voltage | Nominal<br>voltage | Voltage<br>cut-off | Rated capacity    | Maximum<br>dimensions   | Typical<br>weight | NATO<br>Stock Number<br>(NSN) | Typical<br>applications                                   |
|--------------------------------------|-------------------------------|----------------------------|--------------------|--------------------|-------------------|-------------------------|-------------------|-------------------------------|---|
|                                      |                               |                            |                    |                    |                   |                         |                   |                               |   |
| BA 5112 A/U                          | 4s1p<br>LO 35 SX              | 12.0 V                     | 11.2 V             | 8.0 V              | 2.3 Ah            | 77.8 x 57.2 x 39.1 mm   | 180 g             | 6135-01-235-4168              | Radiocommunication<br>(PRC 112)                           |
| BA 5557 A/U                          | 5s1p x 2<br>LO 35 SX          | 15.0 V/<br>30.0 V          | 14.0 V/<br>28.0 V  | 10.0 V/<br>20.0 V  | 4.4 Ah/<br>2.2 Ah | 100.1 x 106.3 x 37.3 mm | 500 g             | 6135-01-088-2707              | Radiocommunication  |
| BA 5567 A/U                          | 1s1p<br>LO 34 SX              | 3.0 V                      | 2.8 V              | 2.0 V              | 1.0 Ah            | 25.9 x 19.9 mm          | 20 g              | 6135-01-090-5363              | Night vision  |
| BA 5588 A/U                          | 5s1p<br>LO 40 SX              | 15.0 V                     | 13.5 V             | 11.0 V             | 3.5 Ah            | 96 x 90 x 31 mm         | 295 g             | 6135-00-088-2708              | Radiocommunication<br>(AN/PRC 128)                        |
| BA 5590 A/U                          | 5s1p x 2<br>LO 26 SX          | 15.0 V<br>30.0 V           | 13.5 V<br>27.0 V   | 10.0 V<br>20.0 V   | 15.0 Ah<br>7.5 Ah | 127 x 111.8 x 62.2 mm   | 1020 g            | 6135-01-523-3037              | Radiocommunication (with SOCI**) (AN/PRC/104/113/117/119) |
| BA 5590 B/U<br>(2 sets of terminals) | 5s1p x 2<br>LO 26 SX          | 15.0 V<br>30.0 V           | 13.5 V<br>27.0 V   | 10.0 V<br>20.0 V   | 15.0 Ah<br>7.5 Ah | 127 x 111.8 x 62.2 mm   | 1020 g            | 6135-01-036-3495              | Radiocommunication<br>(AN/PRC 104/119)                    |
| BA 5590 HC                           | 5s1p x 2<br>LO 26 SXC         | 15.0 V<br>30.0 V           | 13.5 V<br>27.0 V   | 10.0 V<br>20.0 V   | 18.2 Ah<br>9.1 Ah | 127 x 111.8 x 62.2 mm   | 1020 g            | TBD                           | Radiocommunication (AN/PRC 104/113/117/119)               |
| BA 5598 A/U                          | 5s1p<br>LO 25 SX              | 15.0 V                     | 13.5 V             | 10.0 V             | 7.5 Ah            | 120.7 x 92 x 54 mm      | 680 g             | 6135-01-034-2239              | Radiocommunication<br>(PRC 25/74/77)                      |
| BA 5599 A/U                          | 3s1p<br>LO 26 SX              | 9.0 V                      | 8.1 V              | 6.0 V              | 7.5 Ah            | 152 x 38 x 64 mm        | 450 g             | 6135-01-069-8575              | Radio tester  |
| BA 5600 A/U                          | 3s1p<br>LO 26 SX              | 9.0 V                      | 8.1 V              | 6.0 V              | 7.5 Ah            | 185.9 x 39.4 mm         | 360 g             | 6135-01-168-2944              | Communication terminal<br>AN/PSC 2/cap                    |
| BA 5800 A/U                          | 2s1p<br>LO 26 SX              | 6.0 V                      | 5.3 V              | 4.0 V              | 7.5 Ah            | 128.5 x 35.5 mm         | 220 g             | 6135-99-798-9851              | Compact Air Supply<br>Unit (CASU), GPS                    |
| BA 5847 B/U                          | 2s1p<br>LO 26 SX              | 6.0 V                      | 5.3 V              | 4.0 V              | 7.5 Ah            | 95 x 64.8 x 38 mm       | 220 g             | 6135-01-090-5364              | Radiocommunication<br>Mine detector                       |
| BT 5313                              | 9s1p<br>LO 26 SHX             | 27.0 V                     | 25.2 V             | 18.0 V             | 7.2 Ah            | Special                 | 1100 g            | N/A                           | Missile launcher  |
| BT 5790                              | 5s1p<br>LO 26 SX              | 15.0 V                     | 14.0 V             | 10.0 V             | 7.5 Ah            | 186.5 x 35.7 x 66.7 mm  | 630 g             | N/A                           | Radiocommunication  |
| BT 5791                              | 5s2p<br>LO 26 SX              | 15.0 V                     | 14.0 V             | 10.0 V             | 15.0 Ah           | 186.5 x 70.0 x 65.3 mm  | 1200 g            | N/A                           | Radiocommunication  |
| G 6-104<br>(/C,D,E,F,G,H)            | 2s1p<br>G20                   | 6.0 V                      | 5.6 V              | 4.0 V              | 7.5 Ah            | 128.5 x 35.5 mm         | 200 g             | -                             | CAM   |
| G 6-105                              | 2s1p<br>G52                   | 6.0 V                      | 5.6 V              | 4.0 V              | 3.2 Ah            | 55 x 28.1 x 56 mm       | 110 g             | 6135-99-658-9085              | Aircraft probe  |
| G 9-124                              | 3s1p<br>G20                   | 9.0 V                      | 8.4 V              | 6.0 V              | 7.5 Ah            | 110 x 42 x 83 mm        | 370 g             | 6135-14-383-9768              | Missile   |
| G 15-114                             | 5s2p<br>G06                   | 15.0 V                     | 14.0 V             | 9.6 V              | 1.9 Ah            | 90.6 x 40.3 x 71 mm     | 270 g             | 6135-99-795-4351              | Radiocommunication<br>+ other applications                |
| G 15-127                             | 2 x 5s1p<br>G62               | 2x15.0 V                   | 2x14.0 V           | 2x10.0 V           | 34 or<br>68 Ah    | 216 x 152 x 92 mm       | 3500 g            | 6135-99-794-2896              | Special forces  |
| G 18-115                             | 6s1p<br>G20                   | 18.0 V                     | 16.8 V             | 12.0 V             | 7.5 Ah            | 131.6 x 66.8 x 128 mm   | 850 g             | 6135-99-795-4350              | Radiocommunication<br>+ other applications                |
| G 30-101                             | 10s1p<br>G20                  | 30.0 V                     | 28.0 V             | 20.0 V             | 7.5 Ah            | 184.5 x 73.5 x 80 mm    | 1500 g            | 6135-99-747-4430              | Radiocommunication<br>+ other applications                |
| G 30-102/B                           | 10s1p<br>G22                  | 30.0 V                     | 28.0 V             | 20.0 V             | 16.0 Ah           | 184 x 72.5 x 133 mm     | 2500 g            | 6135-99-840-0109              | Radiocommunication<br>+ other applications                |
| Li/3                                 | 3s1p<br>LO 26 SX              | 9.0 V                      | 8.4 V              | 6.0 V              | 7.5 Ah            | 110 x 42 x 81 mm        | 450 g             | 6135-14-383-9768              | Missile launcher  |

<sup>\*</sup> Xs Yp = Y parallel branches of X cells in series per branch

Primary cells and batteries are not rechargeable.

This data sheet is an insert part of the Primary lithium batteries Selector Guide (ref 31048-2), where complementary information and data on features, safety and storage can be found.

#### Saft Specialty Battery Group

12, rue Sadi Carnot 93170 Bagnolet – France Tel.:+33 (0)1 49 93 19 18 Fax:+33 (0)1 49 93 19 69 Doc  $N^{\circ}$  31050-2-0909 Edition: September 2009

Data in this document is subject to change without notice and becomes contractual only after written confirmation. Single cells mentioned in this document may have their own specific data sheet with complementary data.

Please check website.

Published by the Communications Department.

Photo credit: Saft.

Société anonyme au capital de 31 944 000 €

RCS Bobigny B 383 703 873



<sup>\*\*</sup> SOCI: State of Charge Indicator

## Primary lithium batteries Li-MnO<sub>2</sub> range



## Li-MnO<sub>2</sub> cells

|           | _                  |           |                            |                    |  |  |                                   |                             |                |        |                   |                     |
|-----------|--------------------|-----------|----------------------------|--------------------|--|--|-----------------------------------|-----------------------------|----------------|--------|-------------------|---------------------|
|           | Production<br>site | Size      | Open<br>circuit<br>voltage | Nominal<br>voltage | Nominal capacity<br>(drain)<br>(2.0 V cut-off) | Maximum recommended continuous current | Operating<br>temperature<br>range | Outside<br>diameter<br>max. | Height<br>max. | Weight | UL<br>recognition | Transport<br>status |
| LM spiral | cells              |           |                            |                    |  |  |                                   |                             |                |        |                   |                     |
| LM 17130  | USA                | 1⁄3 Д     | 3.2 V                      | 3.0 V              | 0.5 Ah (4.5 mA)                                | 0.3 A                                  | -40/+ 70°C                        | 16.7 mm                     | 16.6 mm        | 8.0 g  | _                 | Non-restricted      |
| LM 22150  | USA                | ⅓ sub-C   | 3.2 V                      | 3.0 V              | 0.9 Ah (40 mA)                                 | 0.4 A                                  | -40/+ 70°C                        | 22.8 mm                     | 17.3 mm        | 15.0 g | -                 | Non-restricted      |
| LM 33550  | USA                | D         | 3.2 V                      | 3.0 V              | 12 Ah (250 mA)                                 | 4.0 A                                  | -40/+ 70°C                        | 34.2 mm                     | 61.4 mm        | 120 g  | _                 | Class 9             |
| М 49      | Germany*           | 3/4 sub-C | 3.2 V                      | 3.0 V              | 1.6 Ah (80 mA)                                 | 0.3 A                                  | -40/+ 70°C                        | 22.5 mm                     | 32.0 mm        | 24.0 g | -                 | Class 9             |
| M 52 HR   | Germany*           | С         | 3.2 V                      | 3.0 V              | 4.8 Ah (150 mA)                                | 2.0 A                                  | -40/+ 70°C                        | 26.2 mm                     | 51.5 mm        | 59.0 g | -                 | Class 9             |
| M 56      | Germany*           | 5/4 C     | 3.2 V                      | 3.0 V              | 6.7 Ah (150 mA)                                | 2.5 A                                  | -40/+ 70°C                        | 26.2 mm                     | 61.5 mm        | 70 g   | -                 | Class 9             |
| М 19      | Germany*           | "Short" D | 3.2 V                      | 3.0 V              | 9.5 Ah (150 mA)                                | 3.0 A                                  | -40/+ 70°C                        | 33.5 mm                     | 58.5 mm        | 105 g  | -                 | Class 9             |
| М 20      | Germany*           | D         | 3.2 V                      | 3.0 V              | 12.6 Ah (150 mA)                               | 3.5 A                                  | -40/+ 70°C                        | 34.2 mm                     | 61.5 mm        | 117 g  | -                 | Class 9             |
| M 20 HR   | Germany*           | D         | 3.2 V                      | 3.0 V              | 11.5 Ah (O.5 A)                                | 4.0 A                                  | -40/+ 70°C                        | 34.2 mm                     | 61.5 mm        | 117 g  | _                 | Class 9             |
| M 24 HR   | Germany*           | DD        | 3.2 V                      | 3.0 V              | 20.0 Ah (2.0 A)                                | 6.0 A                                  | -40/+ 70°C                        | 33.5 mm                     | 110.5 mm       | 201 g  | _                 | Class 9             |
| М 62      | Germany*           | "Big" DD  | 3.2 V                      | 3.0 V              | 33.0 Ah (1.6 A)                                | 6.0 A                                  | -40/+ 70°C                        | 42.5 mm                     | 133 mm         | 355 g  | _                 | Class 9             |

<sup>\*</sup> FRIWO cell series

Primary cells and batteries are not rechargeable.

Their internal impedance may rise versus time, especially in case of exposure at elevated temperature.



## Li-MnO<sub>2</sub> Military battery packs

|            | Cell<br>type<br>construction* | Open<br>circuit<br>voltage | Nominal<br>voltage | Voltage<br>cut-off | Nominal<br>capacity | Maximum<br>dimensions | Weight          | NATO<br>Stock Number<br>(NSN) | Typical<br>applications                                 |
|------------|-------------------------------|----------------------------|--------------------|--------------------|---------------------|-----------------------|-----------------|-------------------------------|---|
|            |                               |                            |                    |                    |                     |                       |                 |                               |   |
| BA 5368/U  | 4s1p<br>LM 22150              | 12.8 V                     | 12.0 V             | 9.0 V              | 0.9 Ah              | 76.2 x 26.9 mm        | 145 g           | 6135-01-455-7947              | Radiocommunication<br>(PRC-90-103-106-195)              |
| BA 5372/U  | 2s1p<br>LM 17130              | 6.4 V                      | 6.0 V              | 4.0 V              | 0.5 Ah              | 16.5 x 33.0 mm        | 20 g            | 6135-01-214-6441              | Radiocommunication<br>(SINCGARS)                        |
| BA 5390/U  | 5s1p x 2<br>LM 33550          | 16.5 V/33 V                | 15 V/30 V          | 10 V/20 V          | 24 Ah/12 Ah         | 127x111.8x62mm        | 1.41 kg/3.10 kg | 6135-01-036-3495              | Radiocommunication<br>(AN/PBC 104/113/117/119)          |
| 3.M20**    | 3s1p<br>M20                   | 9.9 V                      | 9.0 V              | 6.0 V              | 10.5 Ah             | 65 x 64 x 69 mm       | 360 g           | -                             | EPIRB   |
| 4.M52 HR** | 4s1p<br>M52 HR                | 13.2 V                     | 12.0 V             | 8.0 V              | 4.5 Ah              | 40 x 58.5 x 105 mm    | 270 g           | 6135-12-322-9102              | ABC protective equipment                                |
| 5.M20**    | 5s1p<br>M20                   | 16.5 V                     | 15.0 V             | 10.0 V             | 10.5 Ah             | 100 x 110 mm          | 740 g           | 6135-12-310-5164              | ABC protective equipment                                |
| 6.M20**    | 6s1p<br>M20                   | 19.8 V                     | 18.0 V             | 12.0 V             | 10.5 Ah             | 124 x 64 x 69 mm      | 710 g           | 6135-12-346-1035              | EPIRB   |
| 6.M20**    | 6s1p<br>M20                   | 19.8 V                     | 18.0 V             | 12.0 V             | 10.5 Ah             | 80 x 90 x 125 mm      | 950 g           | -                             | Military use  |
| 10.M20**   | 10s1p<br>M20                  | 33.0 V                     | 30.0 V             | 20.0 V             | 10.5 Ah             | 162 x 68 x 109 mm     | 1500 g          | 6135-12-339-0295              | ABC protective equipment                                |
| MIRA**     | 10s1p<br>M24 HR               | 33.0 V                     | 30.0 V             | 20.0 V             | 20.0 Ah             | 133 x 72 x 184 mm     | 2500 g          | 6135-12-329-3740              | Thermal sight system MIRA<br>(for missile system MILAN) |
| MR 506**   | 6s1p<br>M49                   | 19.8 V                     | 18.0 V             | 12.0 V             | 1.8 Ah              | 37 x 56 x 78 mm       | 200 g           | 6135-12-339-9599              | Emergency radio   |
| MR 509**   | 3s1p<br>M52 HR                | 9.9 V                      | 9.0 V              | 6.0 V              | 4.5 Ah              | 54 x 37 x 75 mm       | 180 g           | 6135-12-353-2558              | Emergency radio   |
| SEM 52**   | 3s1p<br>M52 HR                | 9.9 V                      | 9.0 V              | 6.0 V              | 4.5 Ah              | 65 x 33 x 78.5 mm     | 208 g           | 6135-12-308-9723              | Radiocommunication<br>(SEM 52)                          |
| SEM 70**   | 6s1p<br>M20                   | 19.8 V                     | 18.0 V             | 12.0 V             | 10.5 Ah             | 38 x 72 x 191 mm      | 750 g           | 6135-12-309-8604              | Radiocommunication<br>(SEM 70)                          |
| SEM91/93** | 3s1p<br>M52 HR                | 9.9 V                      | 9.0 V              | 6.0 V              | 4.5 Ah              | 65 x 33 x 78.5 mm     | 208 g           | 6135-12-355-0737              | Radiocommunication<br>(SEM 91/93)                       |

<sup>\*</sup> Xs Yp = Y parallel branches of X cells in series per branch

Primary cells and batteries are not rechargeable.

This data sheet is an insert part of the Primary lithium batteries Selector Guide (ref 31048-2), where complementary information and data on features, safety and storage can be found.

#### Saft **Specialty Battery Group**

12, rue Sadi Carnot 93170 Bagnolet - France Tel.:+33 (O)1 49 93 19 18 Fax:+33 (0)1 49 93 19 69 Doc Nº 31051-2-1109 Edition: November 2009

Data in this document is subject to change without notice and becomes contractual only after written confirmation. Single cells mentioned in this document may have their own specific data sheet with complementary data.

Please check website.

Published by the Communications Department.

Photo credit: Saft.

Société anonyme au capital de 31 944 000  $\mathop{\in}$  RCS Bobigny B 383 703 873



<sup>\*\*</sup> FRIWO batteries

## Serving your needs around the world

## Saft Specialty Battery Group sales network

#### Australia

Saft Batteries Pty Ltd. Unit 18/167 Prospect Highway Seven Hills, NSW 2147 Tel.: +61 2 9674 0700 Fax: +61 2 9620 9990

david.anderson@saftbatteries.com.au gary.piper@saftbatteries.com.au

#### China

Saft Hong Kong Ltd.
Unit 1107-9, 11/F, Westin Centre
26 Hung To Road,
Kwun Tong, Kowloon
Tel.: +852 3568 7066
Fax: +852 2798 0619
ivan.lam@saftbatteries.com

Saft Zhuhai Shanghai Office Room 2408, Lucky Mansion No. 660 Shangcheng Road Shanghai 200120, P. R. China Tel.: +86 21 5866 6405 Fax: +86 21 5866 6403 ben.li@saftbatteries.com

#### France Saft

12, rue Sadi Carnot 93170 Bagnolet

Tel.: +33 (O)1 49 93 19 18 Fax: +33 (O)1 49 93 19 69 lithiumsales.fr@saftbatteries.com

#### Germany

Saft Batterien GmbH Löffelholz Strasse, 20 90441 Nürnberg Tel.: +49 911 94174 20 Fax: +49 911 94174 25

ecaterina.hauser@saftbatteries.com

#### Israel

Saft
Vita Towers
11 Ben Gurion Street
Bnei Brack 51260
Tel.: +972 3 6160633
Fax: +972 3 6160635
amnon.dor@saftbatteries.com

#### Italy

Saft Batterie Italia S.r.I. Palazzo Cimabue, Via Cassanese, 224 20090 Segrate - Milano

Tel.: +39 O2 89 28 O7 45 Fax: +39 O2 89 28 O7 62 cesare.giuggioli@saftbatteries.com

#### Netherlands

Saft Batterijen B.V.
Achtseweg Zuid 151
5651 GW Eindhoven
Tel.: +31 40 272 1902
Fax: +31 40 272 1904
quido.jasper@saftbatteries.com

#### Norway Saft AS

Grini Naeringspark 1 N-1361 Osteraas Tel.: +47 6716 4161 Fax: +47 6716 4170 trond.beyer@saftbatteries.com

Russian Federation

ZAO Ancor (Saft) 21/3 Stanislavskogo St. Business Center "Stanislavkiy" 109004 Moscow

Russia

Tel.: +7495 788 52 04 Fax: +7495 788 52 04 dmitry.lozin@saftbatteries.com

#### Spain (+ Portugal)

Saft Baterias S.L.
Avda. Fuente Nueva 12, Nave 15
San Sebastian de los Reyes
28700 Madrid - Spain
Tel.: +34 916 593 482
Fax: +34 916 593 490
javier.sanchez@saftbatteries.com

#### Sweden

Saft AB (Civil Sales) Jungnergatan - Box 709 SE-572 28 Oskarshamn Tel.: +46 491 681 04 Fax: +46 491 680 85

christer.steen@saftbatteries.com

Saft AB (Military Business) Illervägen 6 SE-35245 Växjö Tel.: +46 470 452 47

Fax: +46 470 452 57 bengt.bengtsson@saftbatteries.com

#### UK (+ Ireland)

Saft Ltd. River Drive South Shields, Tyne & Wear NE33 2TR-UK

Tel.: +44 191 497 4703 Fax: +44 191 456 8256 lesley.lyons@saftbatteries.com

#### USA (+ Canada/Mexico)

Saft America Inc. 313, Crescent Street Valdese, NC 28690 - USA Tel.: +1 (828) 874 4111 Fax: +1 (828) 874 2431

lithiumsales.us@saftbatteries.com

## Saft Specialty Battery Group manufacturing sites

#### China Saft (Zhuhai Free Trade Zone)

Batteries Co. Ltd Lianfeng Rd Zhuhai 519030, Guangdong Province

Tel.: +86 756 881 9318 Fax: +86 756 881 9328 William.Fa@saftbatteries.com

lithiumsales.fr@saftbatteries.com

#### France

Saft Rue Georges Leclanché B.P. N° 1039 86060 Poitiers Cedex 09 Tel.: +33 (0)5 49 55 48 48 Fax: +33 (0)5 49 55 48 50

#### **Germany** FRIWO

Industriestrasse 22 D-63654 Büdingen Tel.: +49 911 94 174 22 Fax: +49 911 94 174 25 susan.mehnert@saftbatteries.com

#### United Kingdom

Saft Ltd.
River Drive
South Shields, Tyne & Wear
NE33 2TR
Tel.: +44 191 497 4703
Fax: +44 191 456 8256

lesley.lyons@saftbatteries.com

#### USA

Saft America Inc. 313, Crescent Street Valdese NC 28690

Tel.: +1 (828) 874 4111 Fax: +1 (828) 874 2431

lithiumsales.us@saftbatteries.com



## Saft Specialty Battery Group sales agents and distributors

Argentina

CH Sistemas Electronicos S.A.

Riobamba 350

1025 Ciudad Autónoma de Buenos Aires

Tel.: +54 11 4954 7200 Fax: +54 11 4954 7200 pilasch@ch-sistemas.com.ar ch@ch-sistemas.com.ar

Probattery

Baires Full Trading Paz Soldán 4960 C1427DSF

Buenos Aires

Tel.: +54 11 45 14 68 68 Fax: +54 11 45 14 68 66 gfreund@probattery.com.ar

Austria

Otto Sauseng GmbH Lienfeldergasse 32 A-1160 Wien

Tel.: +43 1 485 86 11 0 Fax: +43 1 485 86 11 21 vlado.bera@sauseng.at

Belgium (+ Luxembourg)

Helpelek

Avenue du Couronnement, 11 B-1200 Brussels - Belgium Tel.: +32 2 7 62 33 38 Fax: +32 2 7 62 37 01 joel.vanloocke@helpelek.be

Brazil

Barasch Sylmar R. Guaicurus 345 Agua Branca - Sao Paulo SP 05033-000

Tel.: +55 11 3864 63 66 Fax: +55 11 3864 63 66 barasch@barasch.com.br

Czech Republic

BATTEX spol.s r.o. Politických vězňů 1337 274 O1 Slaný

Tel.: +420 312 520116 Fax: +420 312 520117 vesely@battex.cz Denmark

Scansupply Energy A/S Topstykket 25 3460 Birkerød

Tel.: +45 45 82 50 90 Fax: +45 45 82 54 40 flemming@scansupply.dk

Egypt

47, Ahmed Taysir St.
Ramo Tower B#104
Heliopolis, 11341 Cairo
Tel.: +20 2 2621864
Fax: +20 2 4031195
info@elmetra-eg.com

Finland & Baltic countries

HansaBattery Oy Kilonkallio 3A O2610 Espoo

Tel.: +358 207 631 880 Fax: +358 207 631 889 hans.sandstrom@hansabattery.fi jon.sandstrom@hansabattery.fi

Hungary

Kapacitás Szentpetery u. 24-26 H-1115 Budapest Tel.: +36 1 463 08 80 Fax: +36 1 463 08 99 varga@akku.hu

Japan

Sumitomo Corporation Harumi Triton Square Office Tower Z 21F 1-8-12 Harumi, Chuo-Ku

Tokyo, 104-6222 Tel.: +81 3 5144 9081 Fax: +81 3 5144 9267

takahiro.shoji@sumitomocorp.co.jp

Korea

Cellcom Co Ltd. 1707, East Bldg, Hanshin Cylux 716, Suseo-Dong, Kangnam-Gu 135-884 Seoul

Tel.: +82 2 2149 0765 Fax: +82 2 2149 0766 djkim127@hotmail.com Poland

Wamtechnik Sp. z o.o. ul. Czajewicza 19 05-500 Piaseczno Tel.: +48 22 75 02 142 Fax: +48 22 75 02 139 p.wlodarczyk@wamtechnik.pl

Romania

Sprinter 2000 S.A. 60, Calea Feldioarei Brasov, 500483 Tel.: +40 268 472 333 Fax: +40 268 472 334

dan.chirila@sprinter-distribution.ro

Saudi Arabia & Arabic Gulf Countries

Dar Al Fursan PO Box 16221, Riyadh 11464 Tel.: +966 1 462 08 16 Fax: +966 1 462 08 16

Fax: +966 1 462 08 16 nader.altaher@daralfursan.com

Singapore

Powerpack Industries Pte Ltd 194 Pandan Loop O4-23 Singapore 128383 Tel.: +65 6872 0526 Fax: +65 6872 3041 sales@powerpack.com.sg

South Africa

Just Batteries 14, Railway Avenue Benoni 1501

Tel.: +27 11 421 7981 Fax: +27 11 421 7986 malcolm@justbatteries.co.za

Switzerland

Leclanché SA Avenue des Sports 42 1400 Yverdon-les-Bains Tel.: +41 24 424 6513 Fax: +41 24 424 6520 integration@leclanche.ch

Tunisia & Maghreb SFFFP

46 Av. de Madrid Tunis

Tel.: +216 71 342 602 Fax: +216 71 353 523

seep@gnet.tn

For other countries, please send your battery requests to lithiumsales.fr@saftbatteries.com

# **Saft Specialty Battery Group**12, rue Sadi Carnot

93170 Bagnolet - France Tel.: +33 (0)1 49 93 19 18 Fax: +33 (0)1 49 93 19 69 Doc N° 31052-2-0909 Edition: September 2009

Data in this document is subject to change without notice and becomes contractual only after written confirmation.

For more details on primary lithium technologies please refer to Primary Lithium Batteries Selector Guide Doc  $N^\circ$  31048-2.

Published by the Communications Department. Société anonyme au capital de 31 944 000 € RCS Bobigny B 383 703 873



#### Saft is committed to the highest standards of environmental stewardship.

Implementing this commitment to minimise the impact of its products and operations on the environment means that Saft gives priority to recycled over unrecycled raw materials, reduces its plant releases into the environment year after year, minimizes water usage, and ensures that its customers have recycling solutions for their batteries at the end of their lives. Regarding industrial Ni-Cd-batteries, Saft has had partnerships for many years with collection companies in most EU countries as well as in North America. This collection network receives and dispatches our customers' batteries at the end of their lives to fully approved recycling facilities, in compliance with the Laws governing transboundary waste shipments. Saft offers these services free of charge to its customers.

Please find a list of our collection points on our web site: www.saftbatteries.com

In other countries, Saft assists its customers in finding environmentally sound recycling solutions. Please contact your sales representative for further information.

Saft Specialty Battery Group

12, rue Sadi Carnot 93170 Bagnolet - France

Tel.: +33 (O)1 49 93 19 18 Fax: +33 (0)1 49 93 19 69

Doc N° 31048-2-0909 Edition: September 2009

Data in this document is subject to change without notice and becomes contractual only after written confirmation.

Published by the Communications Department.

Photo credit: ACR Electric, Berlin Heart AG, Creatas, Industrial Scientific, ©S. Laval, © Lockheed Martin, © MG International 2006, PhotoDisc, Program Executive Officer Soldier, © Courtesy of U.S. Army, Saft.

Société anonyme au capital de 31 944 000  $\in$  RCS Bobigny B 383 703 873

