


Power Management & Supply AC/DC Selection Guide



www.infineon.com/power



Never stop thinking

Introduction

TODAY'S MODERN LIFESTYLE leads to a fast-growing energy requirement as more and more people are able to afford electronic equipment. Consumers can select from an ever-growing range of cellular phones, PDAs, digital cameras, cordless phones, DVD players, VCRs, TV sets, LCD monitors, notebook and desktop computers, and home appliances, to mention only a few. The power consumption of these electronic devices continues to rise as a result of ever-increasing functions.

ENERGY GENERATION FREQUENTLY pollutes the environment through radioactive waste and CO₂. In order to compensate and reduce the pace of these overly proportional growing energy requirements, we must use energy more efficiently.

SWITCH MODE POWER SUPPLIES (SMPS) represent today's most efficient energy conversion approach for electronic equipment. Increasing the SMPS efficiency directly leads to energy savings during the equipment's operational time.

SOME ELECTRONIC DEVICES operate only for a few hours during the day, and are consequently in standby mode during the rest of the day. Lowering the standby power consumption will save a considerable amount of energy.

A CONTINUOUS TREND towards system miniaturization has accompanied the development of electronic equipment from the very beginning. Simultaneously, the power rating of the devices increases. This means more power in a smaller space – high-power density is the operative word.

THE "POWER & SUPPLY" group of Infineon Technologies focuses its R&D activities on cost effectiveness, low standby power consumption, high efficiency and power density. Today we are proud to serve our customers with technologically leading products in many areas of an off-line SMPS, power MOSFETs (CoolMOS™, OptiMOS®2), Silicon Carbide Schottky diodes (thinQ!™), IGBTs, intelligent SMPS and PFC control ICs, and CoolSET™ (SMPS control IC and CoolMOS™ in one package).



Applications, Requirements and Solutions

Charger

- Cost effectiveness
 - Integrated solution CoolSET™
- Low standby
 - Active burst mode of CoolSET

LCD Monitor

- High-power density
 - CoolMOS™ and CoolSET
- Low standby
 - Active burst mode of CoolSET and ICE3 series controller

Adapter

- High-power density
 - CoolMOS and CoolSET
- Low standby
 - Active burst mode of CoolSET and ICE3 series controller

Lamp Ballast

- Cost-effectiveness
 - TDA486x series
 - PFC controller
 - Integrated solution PFC CoolSET

Personal computer


- High-power density
 - CoolMOS
 - thinQ!™ Schottky diodes
 - OptiMOS®2
 - TDA16888
 - ICE1PC series PFC controller
- Low standby
 - Active burst mode of CoolSET and ICE3 series controller

Server

- Ultra-high-power density
 - CoolMOS
 - thinQ! Schottky diodes
 - OptiMOS®2
 - TDA16888
 - ICE1PC series PFC controller

TV, DVD, VCR, Set-top Box

- Cost-effectiveness
 - Integrated solution CoolSET
 - Charge pump PFC
 - Peak load function of ICE3 series
- Low standby
 - Active burst mode of ICE3 series
 - Frequency reduction of ICE1QS01
- Low EMI
 - Quasi-resonant switching





Contents

SMPS ICs

Fan Speed Controller	6
SMPS IC Overview	8
PWM Controller	10
Smart Ballast Controller	14
PFC and Combo Controller	16
CoolSET™	18
SMPS Topologies	20

Discretes

N-Channel MOSFETs, 500 to 800 V (CoolMOS™, Standard MOS)	22
Silicon Carbide Schottky Diodes (thinQ!™ Family)	30
Alphanumeric Listing	31
Packages	32

TDA21801 – Fan Speed Controller

WITH THE NEW fans speed controller TDA21801, essential system monitoring features of switched mode power supplies (SMPS) such as adjustable minimum fan speed, fan ON/OFF and over-temperature protection (OTP) can be easily implemented. Only few external components added to the IC are necessary for it.


THE TDA21801 is designed for applications using 3- or 4-wire fan solutions like PC silver boxes, Server silver box AC/DC converter and industrial/medical power supplies.

Benefits


- Full control over fan speed due to precision reference
- Low system cost when replacing 4-wire fans
- Reduced noise level
- Increased safety of power supplies

Features

- In combination with 2-wire fans same functionality as 4-wire fan solution
- Overtemperature protection feature to protect system and power supply
- Adjustable minimum fan speed (750 rpm to 4000 rpm)
- Fan speed can be increased by external PWM or analogue signal
- DSO-8 Package / ROHS compliant



Block Diagram



Typical Application Circuit

SMPS IC Overview


PWM Controller						
Quasiresonant			Fixed Frequency			
TDA4605-2 TDA4605-3	TDA16846 TDA16847	ICE1QS01 ICE1QS02	ICE2A(B)S01 ICE3A(B)S02 ICE3BS02L	ICE3DS01	TDA16850-2	
General purpose control IC	Universal, high performance control IC including low-power standby and power factor correction	PWM Control IC including advanced burst mode, PFC and frequency reduction for best-in-class efficiency ratings + active burst mode + start up cell	General purpose Control IC	General purpose Control IC with enhanced ICE2A(B)S01 features		Control with special features for CRT monitor applications
Typical Application	CVT, VCR, adapter	CTV, VCR, set-top-box, adapter	CTV, VCR, adapter	Applications exceeding the max. power range of CoolSET: charger, adapter, auxiliary power supplies, low end CTV, set-top-box, DVD	Applications exceeding the max. power range of CoolSET: charger, adapter, auxiliary power supplies, low end CTV, set-top-box, DVD, LCD	Monitors, CTVs, adapters, chargers
General Features						
Operating mode	Quasiresonant	Quasiresonant Fixed Frequency Synchronized	Quasiresonant	Fixed Frequency	Fixed Frequency	Fixed Frequency synchronized
Switching frequency	< 200 kHz	< 250 kHz adjustable in fixed frequency mode	< 250 kHz	100 kHz (67kHz)	110 kHz	60 kHz fixed < 130 kHz synchr.
Standby frequency	approx. 20 kHz	adjustable	20 kHz	21 kHz	–	20 kHz
Maximum duty cycle	unlimited	unlimited	unlimited	72%	72%	60%
Primary regulation without additional components	✓	✓	✓	–	–	–
Standby power	5 W / 400 mW	< 1 W / 400 mW	< 1 W / 400 mW	< 1 W / no load	100 mW / no load	< 1 W / no load
Low standby power mode active burst mode	–	–	–	–	480 mW / 300 mW	–
Soft switching for low EMI	–	–	–	✓	✓	✓
Maximum drain-source voltage @ 125°C T_j	*	*	*	*	*	–
Power range (85 ... 270 V) without heat sink	*	*	*	*	*	–
Power range (190 ... 270 V) without heat sink	–	–	–	–	–	–
Integrated auxiliary power supply	–	–	–	–	–	✓
Integrated 500V start-up cell	–	–	–	–	✓	–
PFC functionality	–	Charge Pump	Charge Pump	–	–	–
Protection Features						
Undervoltage lock-out	✓	✓	✓	✓	✓	✓
Overload and open loop correction	✓	✓	✓	✓	✓	✓
Overload protection	✓	✓	✓	✓	✓	–
Secondary undervoltage	✓	✓	✓	–	–	–
Cycle by cycle current limitation	✓	✓	✓	✓	✓	✓
Sophisticated power limitation management	✓	✓	✓	✓	✓	✓
Temporary high-power circuit	–	TDA16847	–	–	✓	–
Adjustable peak current limitation via external resistor	✓	✓	✓	✓	✓	✓
Current limitation via internal sense field	–	–	–	–	–	–
Demagnetization protection	✓	✓	✓	–	–	–
Thermal shut-down (with auto-restart)	–	–	–	✓	✓	✓
Auto restart mode for all protection features	✓	✓	✓	–	✓	–
Latch-off mode	–	–	–	–	✓	–
Brown out protection	–	–	–	–	–	–
Supply current with active gate (typ.)	11 mA	5 mA	10 mA	6.5 mA	7.2 mA	3 ... 10 mA
VCC operating range	7.5 ... 15.5 V	8 ... 16 V	9 ... 20 V	8.5 ... 21 V	8.5 ... 21 V	8.5 ... 22 V
DIP-package	DIP-8	DIP-14	DIP-8	DIP-8	DIP-8	DIP-8
SMD-package	–	DSO-14	DSO-8	DSO-8	DSO-8	–
ISODRAIN-package	–	–	–	–	–	–

* Depending on topology and switching transistor


** Only available in ISODRAIN package

Combo	PFC Controller		CoolSET™: Controller with CoolMOS™ in one Package					
PWM+CCM PFC	CCM	DCM	Fixed Frequency					
TDA16888	ICE1PCSo1 ICE1PCSo2	TDA4862 TDA4863 TDA4863-2	F3 Series ICE3A(B)0365 ICE3A(B)0565 ICE3A(B)1065 ICE3A(B)1565 ICE3A(B)2065 ICE3A(B)2565 ICE3A0365L ICE3A1065L ICE3A1565L	F3 Jitter Series ICE3B0365() ICE3B0565() ICE3B1065() ICE3B1565() ICE3B2065() ICE3B2565()	F3 Isodrain ICE3(B)2065P ICE3(B)3065P ICE3A(B)3565P ICE3(B)5065P ICE3A(B)5565P	F2 650V Series ICE2A(B)0565 ICE2A0565 ICE2A0565 ICE2A(B)165 ICE2A(B)265 ICE2A(B)365 ICE2A(B)765**	F2 800V Series ICE2A180 ICE2A280 ICE2A380**	
High performance power combi controller including PFC and PWM stage	Standalone PFC controller for boost topology with advanced diode protection	PFC Controller for high-power factor and active harmonic filter	Full protection features + low power standby mode and internal leading edge blanking + softstart + active burst mode + startup cell + built-in blanking window + latch-off mode	Full protection features + low power standby mode and internal leading edge blanking + softstart + active burst mode + startup cell + built-in blanking window + jittering	Full protection features + low power standby mode and internal leading edge blanking + softstart + active burst mode + startup cell + built-in blanking window	Full protection features + low power standby mode and internal leading edge blanking + softstart	Full protection features + low power standby mode and internal leading edge blanking + softstart	
Industrial aircon, motor drive, PC, server, adapter	Industrial, PC, motor drive, white goods	Ballast, CTV, PC monitor, adapter	Charger, auxiliary supplies, PC & Display standby supply, adapter,STB, DVD,VCR	Charger, auxiliary supplies, PC & Display standby supply, adapter,STB, DVD,VCR	Charger, auxiliary supplies, PC & Display standby supply, adapter,STB, DVD,VCR	Charger, auxiliary supplies, PC & Display standby supply, adapter,STB, DVD,VCR	Charger, auxiliary supplies, PC & Display standby supply, adapter,STB, DVD,VCR	
Fixed Frequency Continuous Conduction Mode	Fixed Frequency	Discontinuous Conduction Mode	Fixed Frequency	Fixed Frequency	Fixed Frequency	Fixed Frequency	Fixed Frequency	
up to 200 kHz	up to 250 kHz 67 kHz	Free-running 30 ... 300 kHz	100 kHz (67)	67 kHz	100 kHz (67)	100 kHz (67)	100 kHz	
PWM 0 kHz/PFC 50%	–	–	–	–	–	down to 21 kHz	down to 21 kHz	
PWM 50% /PFC 94%	95% @ 125 kHz	98%	50%	50%	72%	72%	72%	
–	–	–	–	–	–	–	–	
<1 W / no load	–	n/a	✓	✓	–	–	–	
–	–	✓	✓	✓	–	–	–	
✓	–	–	✓	✓	✓	✓	✓	
✓	–	–	650 V	650 V	650 V	650 V	800 V	
–	–	–	–	–	–	–	–	
–	–	–	–	–	–	–	–	
✓	–	–	650 V startup cell	650 V startup cell	650 V startup cell	–	–	
–	–	–	–	–	–	–	–	
✓	✓	✓	–	–	–	–	–	
✓	✓	✓	✓	✓	✓	✓	✓	
✓	✓	✓ **	✓	✓	✓	✓	✓	
✓	✓	✓	✓	✓	✓	✓	✓	
output undervoltage protection			✓	✓	✓	✓	✓	
PWM ✓ PFC ✓	✓	✓	✓	✓	✓	✓	✓	
–	✓	–	✓	✓	✓	✓	✓	
–	–	–	–	–	–	–	–	
✓	✓	✓	✓	✓	✓	✓	✓	
–	–	–	✓	✓	✓	–	–	
–	–	✓	–	–	–	–	–	
–	–	–	✓	✓	✓	✓	✓	
–	–	–	✓	✓	✓	✓	✓	
–	–	–	✓	✓	✓	✓	✓	
–	✓	–	–	–	–	–	–	
15 ... 40 mA	18 @ 125 kHz	4 mA	5.5 ... 8.1 mA	2.5 mA	5.7 ... 7.6 mA	5.3 ... 8.5 mA	6.5 ... 8.5 mA	
14 ... 19 V	10 ... 22 V	12.5 ... 20 V	8.5 ... 21 V	10.3 ... 261 V	8.5 ... 21 V	8.5 ... 21 V	8.5 ... 21 V	
DIP-20	DIP-8	DIP-8	DIP-8/DIP-7	DIP-8/DIP-7	–	DIP-8/DIP-7	DIP-7	
DSO-20	DSO-8	DSO-8	DSO-16-12	DSO-16-12	–	DSO-16/12	–	
–	–	–	–	–	TO220-6	–	TO220-6	

PWM Controller



Application Example: 80 W Demoboard with ICE1QSo1 and Primary Regulation



TDA4605-2 / TDA4605-3

Control IC for Switched-Mode Power Supplies
using MOS Transistor

- Fold-back characteristic protects external components
- Burst mode at secondary short-circuit
- Protection against open or a short of the control loop
- Mains undervoltage lock-out
- Soft-start for quiet start-up without noise
- Chip-over temperature protection
- Not for new designs, replaced by TDA16846

TDA16846 / TDA16847

SMPS Controller Supporting Low-power Standby and
Power Factor Correction

- Line current consumption with PFC
- Stable and adjustable standby frequency
- Very low start-up current
- Soft-start for quiet start-up
- Freely usable fault comparators
- Synchronization and fixed frequency facility
- Over and undervoltage lock-out
- Switch off at mains undervoltage
- Temporary high-power circuit (only TDA16847)
- Mains voltage dependent fold-back point correction
- Continuous frequency reduction with decreasing load
- Adjustable ringing suppression time

ICE1QSo1

SMPS Controller with very few peripheral components,
featuring Advanced Burst Mode, Frequency Reduction
and Power Factor Correction

- Line current consumption with PFC
- Stable standby frequency of 20 kHz
- Advanced burst mode < 1 W @ 350 mW sec. power
- Soft-start for noiseless start-up
- Digital frequency reduction for higher efficiency
and no-jitter designs
- Over and undervoltage protection
- Fold-back point correction for stable output power
independent of line voltage variations
- Ringing suppression time controlled by output power
- Additional fault comparator optionally useable

TDA16850-2

SMPS Controller for CRT Monitors

- Controller for fly-back topology
- Current mode PWM with spike blanking
- Leading edge triggered pulse with modulation
- Fast, soft switching totem pole gate drive (1 A)
- Soft-start management for safe start-up
- Off mode with power consumption less than 1 W
- Fast and slow peak current limitation
- All protection features available

PWM Controller

ICE2XSo1

Off-line SMPS Current Mode Controller

- PWM – Current Mode Controller
- 67 kHz and 100 kHz fixed frequency operation
- Max duty cycle up to 72%
- Frequency reduction for low standby
- Adjustable soft-start
- Propagation delay compensation
- Internal leading edge blanking
- Fully protected
- DIP-8 / DSO-8

ICE3DS01

Off-line SMPS Current Mode Controller

- PWM and 500 V start-up cell in one package
- Active burst mode for ultra-low standby power ($P_{IN} < 100 \text{ mW}$)
- Short-term overload function
- New protection: latched OFF or auto restart
- 100 kHz fixed frequency operation
- May duty cycle up to 72%
- Adjustable soft-start
- Propagation delay compensation
- Internal leading edge blanking
- Fully protected
- DIP-8 / DSO-8

ICE3AS02


Additional features to ICE3DS01

- 100 kHz

ICE3BS02

Additional features to ICE3DS01

- 67 kHz



Application Example: Circuit Diagram for PWM Fly-back Converter

Smart Ballast Controller

ICB1FL02G

Smart Ballast Controller ICB1FL02G is designed to control a Fluorescent Lamp Ballast including



- Discontinuous Conduction Mode
- Power Factor Correction (PFC)
- Lamp Inverter Control and
- High Voltage Level-Shift Half Bridge Driver with Coreless Transformer Technology in one package.

Product Highlights

- Critical conduction mode PFC with overcurrent and overvoltage protection and internal loop compensation
- End-of-life detection in multilamp topologies and detection of capacitive mode operation in T5 designs
- Improved reliability and minimized spread due to digital and optimized analog control functions


Short Form Data	min.	typ.	max.
Operating Voltage Range	10.5 V	–	17 V
Turn-on Threshold	–	14 V	–
Supply Current during UVLO and Fault Mode	–	–	150 µA
Operating Frequency of Inverter during Run Mode	20 kHz	–	100 kHz
Operating Frequency of Inverter during Preheating Mode	Run Frequency	–	150 kHz
Preheating Time	0	–	2000 ms
Dead Time between LS and HS Gate drive	–	1750 ns	–
Operating Voltage Range of floating HS Gate Drive	-900 V	–	+900 V
LS Current Limitation Threshold during Ignition	–	0.8 V	–
LS Current Protection Threshold	–	1.6 V	–
End-of-Life Detection Threshold	-230 µA	–	+230 µA
Amplitude Ratio for Detection of Rectifier Effect	0.85	–	1.15
Detection of non-ZVS Operation CapMode 1 & 2	–	–	–
PFC Preconverter control with critical and discontinuous CM	–	–	–
Maximum controlled on-time	–	23.5 µs	–
Hysteresis of Zero Current Detector	–	1 V	–
PFC current Limitation Threshold	–	1 V	–
Reference voltage for control of Bus Voltage	2.47 V	2.50 V	2.53 V
Overvoltage Detection Threshold	–	2.75 V	–
Undervoltage Detection Threshold	–	1.83 V	–
Open Loop Detection	–	0.375 V	–
Junction Operating Temperature Range	-25 °C	–	+125 °C
Pb-free Lead Plating; ROHS compliant	–	–	–

Due to a minimum number of external components necessary, system costs can be brought down significantly. ICB1FL02G can be used and designed easily and is therefore a basis for cost effective ballast solutions of the future.




Smart Ballast Controller – ICB1FL02G – Block Biagram

PFC and Combo Controller



Application Example: Circuit Diagram for PFC Boost Converter



ICE1PCSo1

Stand-alone Power Factor Correction (PFC) Controller in Continuous Conduction Mode

- Easy to use with very few external components
- Average current control
- Programmable operating frequency (50 to 250 kHz)
- Unique set of protection features including brown-out protection and boost diode protection
- Precise internal reference voltage
- Unique soft-start
- Enhanced dynamic response
- Leading edge modulation

ICE1PCSo2

Additional features to ICE1PCSo1

- Brown out protection
- Fixed Frequency 67 kHz

TDA4862

Power Factor Controller (PFC) IC for High-power Factor and Active Harmonic Filter

- IC for sinusoidal line-current consumption
- Power factor approaching 1
- Controls boost converter as an active harmonics filter
- Internal start-up with low current consumption
- Zero current detector for discontinuous operation mode
- High current totem pole gate driver
- Trimmed $\pm 1.4\%$ internal reference
- Undervoltage lock out with hysteresis
- Very low start-up current consumption
- Pin compatible with world standard
- Output overvoltage protection
- Current sense input with internal low pass filter
- Totem pole output with active shutdown during UVLO
- Junction temperature range -40°C to $+150^\circ\text{C}$
- Available in DIP-8 and DSO-8 packages

TDA4863 / TDA4863-2

Power Factor Controller IC for High-power Factor and Low THD

Additional Features to TDA4862

- Reduced tolerance of signal levels
- Improved light load behavior
- Open loop protection
- Current sense input with leading edge blanking LEB
- Undervoltage protection

ICE1PD265

PFC CoolSET™ version of TDA4863

- 650 V avalanche rugged CoolMOS™
- $R_{DS(on)} = 1.1 \Omega$
- DSO-16 package
- PFC output power
 - 55 W @ $V_{IN} = 90 \text{ V}$ ($T_A = 70^\circ\text{C}$)
 - 140 W @ $V_{IN} = 180 \text{ V}$ ($T_A = 70^\circ\text{C}$)
- Reduced size and assembling costs
- Highest efficiency due to lower power dissipation

TDA16888


High-performance Power Combi Controller
PFC Section

- IEC 1000-3 compliant
- Additional operation mode as auxiliary power supply
- Fast, soft switching totem pole gate drive (1 A)
- Leading edge triggered pulse width modulation
- Peak current limitation
- Continuous/discontinuous mode possible
- 94% maximum duty cycle


PWM Section

- Improved current mode control
- Fast, soft switching totem pole gate drive (1 A)
- Soft-start management
- Topologies are forward or fly back
- 50% maximum duty cycle

CoolSET™



Application Example: CoolSET™ for Off-line Switch Mode Power Supplies



ICE2Axxx / ICE2Bxxx

Off-line SMPS Controller with 650 V / 800 V CoolMOS™
on Board (High Protection & Energy Saving Solution)

- 650 V or 800 V avalanche rugged CoolMOS
- Typical $R_{DS(on)} = 0.45 \Omega \dots 4.7 \Omega$ at $T_j = 25^\circ\text{C}$

General Features

- Frequency reduction for lowest standby power
(below 1 W) to meet European requirements
100 kHz / 67 kHz switching frequency
- Internal leading edge blanking
- Modulated gate drive for soft switching
- High peak power accuracy
- DIP-7, DIP-8 or P-TO220-6, I²-PAK package

ICE3Axxxx / ICE3Bxxxx


Off-line SMPS Controller with 650 V CoolMOS on Board
(High Protection & Energy Saving Solution)

Additional Features to ICE2Axxx / ICE2Bxxx

- Startup cell
- Active burst mode
- Adjustable blanking window for load jump

SMPS Topologies

Boost Converter



Advantages

- Simple choke
- No problems with magnetic coupling
- Cheap solution


Disadvantages

- Power transistor drain-source voltage $V_{DS} = V_0 > V_I$
- No galvanic isolation between input and output voltage
- Medium loading of the output capacitor

Infineon Parts

TDA16888, TDA4862, TDA4863, TDA4863-2, CoolSET™, ICE1PD265, ICE1PCSO1, ICE2xSO1, ICE3DSO1

Fly-back Converter



Advantages

- Simple, low part count
- Several output voltages can be regulated simultaneously
- Wide control range for operating voltage changes

Disadvantages


- Power transistor drain-source voltage $V_{DS} = V_{IN} + nx(V_{OUT} + V_{D1S})$
- Heavy loading to output capacitor and diode

Infineon Parts

TDA16888, TDA16846, TDA16850, CoolSET™, ICE2xSO1, ICE3OSO1, ICE1QSO1

Forward Converter

Single Transistor Forward Converter Single-ended Forward Converter



Advantages

- Demagnetizing the core is no problem
- Simple circuitry

Disadvantages


- Power transistor drain-source voltage $V_{DS} > 2V_I$
- Demagnetizing winding is necessary
- Good magnetic coupling is necessary between primary and demagnetizing windings

Infineon Parts

TDA16888, TDA4916GG

Two-Transistor Forward Converter

Diagonal Half-bridge Converter Dual-ended Forward Converter



Advantages

- MOSFET drain-source voltage $V_{DS} = V_I$
- Core demagnetization is no problem
- The transformer may have a high level of stray inductance


Disadvantages

- Galvanic-isolated driving is necessary

Infineon Parts

TDA16888, TDA4916GG

Basic Non-isolated Sepic Converter



Advantages

- Transformer is replaced by two chokes
- Common ground connection
- No polarity inversion low voltage stress for the MOSFET
- Output voltage is above or below the input voltage


Disadvantages

- Voltage at the diode is $V_{IN} + V_{OUT} + V_{D1}$

Infineon Parts

TDA16888, CoolSET™, ICE2xS01, ICE3DS01

Buck-boost Converter Single Transistor Buck-boost Converter



Advantages

- Simple choke
- No problems with magnetic coupling


Disadvantages

- Power transistor drain-source voltage $V_{DS} = V_1 + V_0$
- No galvanic isolation between input and output voltage
- Heavy loading of output capacitor
- Input must "float"
- Output voltage negative in relation to input voltage

Infineon Parts

CoolSET™, ICE2xS01, ICE3DS01

Basic Non-isolated Cuk Converter



Advantages

- High efficiency
- Input / output current continuous
- Output voltage is inverse to input voltage

Disadvantages

- High peak currents in power components
- High ripple current in capacitor

Infineon Parts


TDA16888, CoolSET™, ICE2xS01, ICE3DS01

N-Channel MOSFETs

N-Channel 500 V CoolMOS™

Package	$R_{DS(on)\max.} [\Omega]$ @ $V_{GS} = 10 \text{ V}$	$V_{GS(\text{th})} [\text{V}]$	$I_D [\text{A}]$	typ. $Q_g [\text{nC}]$	Type
I ² -PAK	0.19	2.1 ... 3.9	21	95	SPI21N50C3
	0.28	2.1 ... 3.9	16	66	SPI16N50C3
	0.38	2.1 ... 3.9	11.6	49	SPI12N50C3
	0.6	2.1 ... 3.9	7.6	32	SPI08N50C3
TO247	0.07	2.1 ... 3.9	52	290	SPW52N50C3
	0.11	2.1 ... 3.9	32	170	SPW32N50C3
	0.19	2.1 ... 3.9	21	95	SPW21N50C3
	0.28	2.1 ... 3.9	16	66	SPW16N50C3
	0.38	2.1 ... 3.9	11.6	49	SPW12N50C3
D-PAK	0.6	2.1 ... 3.9	7.6	32	SPD08N50C3
	0.95	2.1 ... 3.9	4.5	22	SPD04N50C3
	1.4	2.1 ... 3.9	3.2	15	SPD03N50C3
	3	2.1 ... 3.9	1.8	9	SPD02N50C3
TO220 FullPAK	0.19	2.1 ... 3.9	21	95	SPA21N50C3
	0.28	2.1 ... 3.9	16	66	SPA16N50C3
	0.38	2.1 ... 3.9	11.6	49	SPA12N50C3
	0.6	2.1 ... 3.9	7.6	32	SPA08N50C3
	0.95	2.1 ... 3.9	4.5	22	SPA04N50C3
TO220 (3-leg)	0.19	2.1 ... 3.9	21	95	SPP21N50C3
	0.28	2.1 ... 3.9	16	66	SPP16N50C3
	0.38	2.1 ... 3.9	11.6	49	SPP12N50C3
	0.6	2.1 ... 3.9	7.6	32	SPP08N50C3
	0.95	2.1 ... 3.9	4.5	22	SPP04N50C3
D ² -PAK	0.19	2.1 ... 3.9	21	95	SPB21N50C3
	0.28	2.1 ... 3.9	16	66	SPB16N50C3
	0.38	2.1 ... 3.9	11.6	49	SPB12N50C3
	0.95	2.1 ... 3.9	4.5	22	SPB04N50C3
I-PAK Short Leads	0.95	2.1 ... 3.9	4.5	22	SPS04N50C3
	1.4	2.1 ... 3.9	3.2	15	SPS03N50C3
	3	2.1 ... 3.9	1.8	9	SPS02N50C3

For an overview about ROHS-compliant products please go to www.infineon.com/greenproducts



N-Channel 500 V CoolMOS™ CP Series

Package	$R_{DS(on)\max.} [\Omega]$ @ $V_{GS} = 10$ V	$V_{GS(th)}$ [V]	I_D [A]	typ. Q_g [nC]	Type
TO220 (3-leg)	0.520	2.5 ... 3.5	7	13	IPP50R520CP
	0.399	2.5 ... 3.5	9	17	IPP50R399CP
	0.350	2.5 ... 3.5	10	19	IPP50R350CP
	0.299	2.5 ... 3.5	12	23	IPP50R299CP
	0.250	2.5 ... 3.5	13	27	IPP50R250CP
	0.199	2.5 ... 3.5	17	34	IPP50R199CP
	0.140	2.5 ... 3.5	23	48	IPP50R140CP
TO220-FullPAK	0.520	2.5 ... 3.5	7	13	IPA50R520CP
	0.399	2.5 ... 3.5	9	17	IPA50R399CP
	0.350	2.5 ... 3.5	10	19	IPA50R350CP
	0.299	2.5 ... 3.5	12	23	IPA50R299CP
	0.250	2.5 ... 3.5	13	27	IPA50R250CP
	0.199	2.5 ... 3.5	17	34	IPA50R199CP
	0.140	2.5 ... 3.5	23	48	IPA50R140CP
TO247	0.199	2.5 ... 3.5	17	34	IPW50R199CP
	0.140	2.5 ... 3.5	23	48	IPW50R140CP
	0.450	2.5 ... 3.5	62	150	IPW50R045CP
D-PAK	0.520	2.5 ... 3.5	7	13	IPD50R520CP
	0.399	2.5 ... 3.5	9	17	IPD50R399CP
D ² -PAK	0.299	2.5 ... 3.5	12	23	IPB50R299CP
	0.250	2.5 ... 3.5	13	27	IPB50R250CP
	0.199	2.5 ... 3.5	17	34	IPB50R199CP
	0.140	2.5 ... 3.5	23	48	IPB50R140CP
I ² -PAK	0.399	2.5 ... 3.5	9	17	IPI50R399CP
	0.350	2.5 ... 3.5	10	19	IPI50R350CP
I-PAK Short Lead	0.520	2.5 ... 3.5	7	13	IPS50R520CP

For an overview about ROHS-compliant products please go to www.infineon.com/greenproducts

N-Channel 600 V CoolMOS™

Package	$R_{DS(on)\max.} [\Omega]$ @ $V_{GS} = 10$ V	$V_{GS(th)}$ [V]	I_D [A]	typ. Q_g [nC]	Type
I ² -PAK	0.19	2.1 ... 3.9	20.7	87	SPI20N60C3
	0.28	2.1 ... 3.9	15	63	SPI15N60C3
	0.38	3.5 ... 5.5	11	41.5	SPI11N60S5
	0.38	2.1 ... 3.9	11	45	SPI11N60C3
	0.6	3.5 ... 5.5	7.3	27	SPI07N60S5
	0.6	2.1 ... 3.9	7.3	21	SPI07N60C3
TO247	0.07	2.1 ... 3.9	47	252	SPW47N60C3
	0.10	2.1 ... 3.9	34.6	150	SPW35N60C3
	0.16	2.1 ... 3.9	24.3	104.9	SPW24N60C3
	0.19	3.5 ... 5.5	20	79	SPW20N60S5
	0.19	2.1 ... 3.9	20.7	87	SPW20N60C3
	0.28	2.1 ... 3.9	15	63	SPW15N60C3
	0.38	3.5 ... 5.5	11	41.5	SPW11N60S5
	0.38	2.1 ... 3.9	11	45	SPW11N60C3
D-PAK	0.60	2.1 ... 3.9	7.3	21	SPD07N60C3
	0.60	3.5 ... 5.5	7.3	27	SPD07N60S5
	0.75	2.1 ... 3.9	6.2	24	SPD06N60C3
	0.95	3.5 ... 5.5	4.5	17.6	SPD04N60S5
	0.95	2.1 ... 3.9	4.5	19	SPD4N60C3
	1.40	3.5 ... 5.5	3.2	12.4	SPD03N60S5
	1.40	2.1 ... 3.9	3.2	13	SPD03N60C3
	3	3.5 ... 5.5	1.8	7.3	SPD02N60S5
	3	2.1 ... 3.9	1.8	9.5	SPD02N60C3
	6	2.1 ... 3.9	0.8	3.9	SPD01N60C3
I-PAK	0.60	3.5 ... 5.5	7.3	27	SPU07N60S5
	0.95	3.5 ... 5.5	4.5	17.6	SPU04N60S5
	1.40	3.5 ... 5.5	3.2	12.4	SPU03N60S5
	3	3.5 ... 5.5	1.8	7.3	SPU02N60S5
	3	2.1 ... 3.9	1.8	9.5	SPU02N60C3
	6	2.1 ... 3.9	0.8	3.9	SPU01N60C3
SOT223	0.95	3.5 ... 5.5	0.8	17	SPN04N60S5
	1.40	3.5 ... 5.5	0.7	12.8	SPN03N60S5
	1.40	2.1 ... 3.9	0.7	13	SPN03N60C3
	3	3.5 ... 5.5	0.4	7.4	SPN02N60S5
	2.5	2.1 ... 3.9	0.4	10	SPN02N60C3
	6	2.1 ... 3.9	0.3	3.9	SPN01N60C3
I-PAK Short Leads	0.95	2.1...3.9	4.5	19	SPS04N60C3
	1.40	2.1...3.9	3.2	13	SPS03N60C3
	3	2.1...3.9	1.8	9.5	SPS02N60C3
	6	2.1...3.9	0.8	3.9	SPS01N60C3

For an overview about ROHS-compliant products please go to www.infineon.com/greenproducts

N-Channel 600 V CoolMOS™


Package	$R_{DS(on)\max.} [\Omega]$ @ $V_{GS} = 10$ V	$V_{GS(th)}$ [V]	I_D [A]	typ. Q_g [nC]	Type
TO220 FullPAK	0.19	2.1 ... 3.9	20.7	87	SPA20N60C3
	0.28	2.1 ... 3.9	15	63	SPA15N60C3
	0.38	2.1 ... 3.9	11	45	SPA11N60C3
	0.60	2.1 ... 3.9	7.3	21	SPA07N60C3
	0.75	2.1 ... 3.9	6.2	24	SPA06N60C3
	0.95	2.1 ... 3.9	4.5	19	SPA04N60C3
	1.40	2.1 ... 3.9	3.2	13	SPA03N60C3
TO220 (3-leg)	0.16	2.1...3.9	24.3	104.9	SPP24N60C3
	0.19	2.1...3.9	20.7	87	SPP20N60C3
	0.19	3.5 ... 5.5	20.7	79	SPP20N60S5
	0.28	2.1...3.9	15	63	SPP15N60C3
	0.38	2.1...3.9	11	45	SPP11N60C3
	0.38	3.5 ... 5.5	11	41.5	SPP11N60S5
	0.6	2.1...3.9	7.3	21	SPP07N60C3
	0.60	3.5 ... 5.5	7.3	27	SPP07N60S5
	0.75	2.1...3.9	6.2	24	SPP06N60C3
	0.95	2.1...3.9	4.5	19	SPP04N60C3
	0.95	3.5 ... 5.5	4.5	17.6	SPP04N60S5
	1.4	2.1...3.9	3.2	13	SPP03N60C3
	1.40	3.5 ... 5.5	3.2	12.4	SPP03N60S5
	3	2.1...3.9	1.8	9.5	SPP02N60C3
	3	3.5 ... 5.5	1.8	7.3	SPP02N60S5
D ² -PAK	0.19	3.5 ... 5.5	20.7	79	SPB20N60S5
	0.19	2.1...3.9	20.7	87	SPB20N60C3
	0.38	3.5 ... 5.5	11	41.5	SPB11N60S5
	0.38	2.1...3.9	11	45	SPB11N60C3
	0.60	3.5 ... 5.5	7.3	27	SPB07N60S5
	0.60	2.1...3.9	7.3	21	SPB07N60C3
	0.95	3.5 ... 5.5	4.5	17.6	SPB04N60S5
	0.95	2.1...3.9	4.5	19	SPB04N60C3
	1.40	3.5 ... 5.5	3.2	12.4	SPB03N60S5
	1.40	2.1...3.9	3.2	13	SPB03N60C3
	3	3.5 ... 5.5	1.8	7.3	SPB02N60S5
	3	2.1...3.9	1.8	9.5	SPB02N60C3

For an overview about ROHS-compliant products please go to www.infineon.com/greenproducts

N-Channel 600 V CoolMOS™ CP Series 600 V

Package	$R_{DS(on)\max.} [\Omega]$ @ $V_{GS} = 10$ V	$V_{GS(th)}$ [V]	I_D [A]	typ. Q_g [nC]	Type
TO220 (3-leg)	0.385	2.5 ... 3.5	9	17	IPP6oR385CP
	0.299	2.5 ... 3.5	11	22	IPP6oR299CP
	0.199	2.5 ... 3.5	16	33	IPP6oR199CP
	0.165	2.5 ... 3.5	21	39	IPP6oR165CP
	0.125	2.5 ... 3.5	25	53	IPP6oR125CP
	0.099	2.5 ... 3.5	31	60	IPP6oR099CP
TO247	0.299	2.5 ... 3.5	11	22	IPW6oR299CP
	0.199	2.5 ... 3.5	16	33	IPW6oR199CP
	0.165	2.5 ... 3.5	21	39	IPW6oR165CP
	0.125	2.5 ... 3.5	25	53	IPW6oR125CP
	0.099	2.5 ... 3.5	31	60	IPW6oR099CP
	0.045	2.5 ... 3.5	60	150	IPW6oR045CP
TO220 FullPAK	0.385	2.5 ... 3.5	9	17	IPA6oR385CP
	0.299	2.5 ... 3.5	11	22	IPA6oR299CP
	0.199	2.5 ... 3.5	16	33	IPA6oR199CP
	0.165	2.5 ... 3.5	21	39	IPA6oR165CP
	0.125	2.5 ... 3.5	25	53	IPA6oR125CP
I ² -PAK	0.385	2.5 ... 3.5	9	17	IP16oR385CP
	0.299	2.5 ... 3.5	11	22	IP16oR299CP
	0.199	2.5 ... 3.5	16	33	IP16oR199CP
D-PAK	0.385	2.5 ... 3.5	9	17	IPD6oR385CP
D ² -PAK	0.165	2.5 ... 3.5	21	39	IPB6oR165CP
	0.099	2.5 ... 3.5	31	60	IPB6oR099CP

For an overview about ROHS-compliant products please go to www.infineon.com/greenproducts



N-Channel 600 V CFD CoolMOS™ with Fast Body Diode

Package	$R_{DS(on)\max.} [\Omega]$ @ $V_{GS} = 10 \text{ V}$	$V_{GS(\text{th})} [\text{V}]$	$I_D [\text{A}]$	typ. $Q_g [\text{nC}]$	Type
TO220 (3-leg)	0.22	3.0 ... 5.0	20	95	SPP20N6oCFD
	0.44	3.0 ... 5.0	11	48	SPP11N6oCFD
TO247	0.08	3.0 ... 5.0	46	248	SPW47N6oCFD
	0.118	3.0 ... 5.0	34	163	SPW35N6oCFD
	0.22	3.0 ... 5.0	20	95	SPW20N6oCFD
	0.44	3.0 ... 5.0	11	48	SPW11N6oCFD

For an overview about ROHS-compliant products please go to www.infineon.com/greenproducts

N-Channel 650 V CoolMOS™

Package	$R_{DS(on)\max.} [\Omega]$ @ $V_{GS} = 10$ V	$V_{GS(th)}$ [V]	I_D [A]	typ. Q_g [nC]	Type
TO220 FullPAK	0.19	2.1 ... 3.9	20.7	87	SPA20N65C3
	0.38	2.1 ... 3.9	11	45	SPA11N65C3
	0.6	2.1 ... 3.9	7.3	21	SPA07N65C3
I ² -PAK	0.19	2.1 ... 3.9	20.7	87	SPI20N65C3
	0.38	2.1 ... 3.9	11	45	SPI11N65C3
	0.6	2.1 ... 3.9	7.3	21	SPI07N65C3
TO220 (3-leg)	0.19	2.1 ... 3.9	20.7	87	SPP20N65C3
	0.38	2.1 ... 3.9	11	45	SPP11N65C3
	0.6	2.1 ... 3.9	7.3	21	SPP07N65C3

N-Channel 800 V CoolMOS™

Package	$R_{DS(on)\max.} [\Omega]$ @ $V_{GS} = 10$ V	$V_{GS(th)}$ [V]	I_D [A]	typ. Q_g [nC]	Type
TO220 (3-leg)	0.29	2.1 ... 3.9	17	91	SPP17N80C3
	0.45	2.1 ... 3.9	11	50	SPP11N80C3
	0.65	2.1 ... 3.9	8	40	SPP08N80C3
	0.9	2.1 ... 3.9	6	27	SPP06N80C3
	1.3	2.1 ... 3.9	4	20	SPP04N80C3
	2.7	2.1 ... 3.9	2	9	SPP02N80C3
TO220 FullPAK	0.29	2.1 ... 3.9	17	91	SPA17N80C3
	0.45	2.1 ... 3.9	11	50	SPA11N80C3
	0.65	2.1 ... 3.9	8	40	SPA08N80C3
	0.9	2.1 ... 3.9	6	27	SPA06N80C3
	1.3	2.1 ... 3.9	4	20	SPA04N80C3
	2.7	2.1 ... 3.9	2	9	SPA02N80C3
D ² -PAK	0.29	2.1 ... 3.9	17	91	SPB17N80C3
TO247	0.29	2.1 ... 3.9	17	91	SPW17N80C3
	0.45	2.1 ... 3.9	11	58	SPW11N80C3
D-PAK	0.9	2.1 ... 3.9	6	27	SPD06N80C3
	1.3	2.1 ... 3.9	4	20	SPD04N80C3
	2.7	2.1 ... 3.9	2	9	SPD02N80C3
I ² -PAK	0.65	2.1 ... 3.9	8	40	SPI08N80C3

For an overview about ROHS-compliant products please go to www.infineon.com/greenproducts


N-Channel Enhancement

Package	V_{BRDSS} [V]	$R_{DS(on)\ max.}$ [Ω] @ $V_{GS} = 10$ V	$V_{GS(th)}$ [V]	I_D [A]	typ. Q_g [nC]	Type
SOT223	400	3	2.1 ... 4.0	0.36	–	BSP298
	400	25	1.5 ... 2.5	0.32	–	BSP324
	500	4	2.1 ... 4.0	0.4	–	BSP299
	600	45	1.5 ... 2.5	0.12	3.9	BSP125
SOT23	600	500	1.4 ... 2.6	0.023	1.4	BSS127
SOT89	600	45	1.3 ... 2.3	0.09	3.9	BSS225
SOT223	800	20	2.1 ... 4.0	0.19	–	BSP300

Standard N-Channel Depletion

Package	V_{DS} [V]	$R_{DS(on)}$ [Ω]	$V_{GS(th)}$ [V]	I_D [A]	Type
SOT23	60	8	-3.5 ... -2.4	0.230	BSS159N
	100	12	-2.9 ... -1.8	0.170	BSS169
	250	30	-2.1 ... -1.0	0.100	BSS139
	600	700	-2.7 ... -1.6	0.016	BSS126
SOT223	200	3.5	-2.1 ... -1.0	0.660	BSP149
	240	6	-2.1 ... -1.0	0.350	BSP129
	600	60	-2.1 ... -1.0	0.120	BSP135

For an overview about ROHS-compliant products please go to www.infineon.com/greenproducts



Silicon Carbide Schottky Diodes (thinQ!™ Family)

thinQ!™ 300 V

Package	V_{DC} [V]	I_F [A]	I_{FSM} [A]	Q_C [nC]	Type
D²-PAK	300	2 x 10	36	23	SDB20S30
TO220 (2-leg)	300	10	36	23	SDT10S30
TO220 (3-leg)	300	10	36	23	SDP10S30
	300	2 x 10	36	23	SDP20S30

thinQ!™ 600 V

Package	V_{DC} [V]	I_F [A]	I_{FSM} [A]	Q_C [nC]	Type
D²-PAK	600	6	21.5	21	SDB06S60
TO220 (2-leg)	600	4	12.5	13	SDT04S60
	600	5	18.5	14	SDT05S60
	600	6	21.5	21	SDT06S60
	600	2 x 6	36.0	30	SDT12S60
	600	8	26.0	24	SDT08S60
	600	2 x 5	31.0	29	SDT10S60
D-PAK	600	4	12.5	13	SDD04S60

thinQ!™ 2G 600 V









Package	V_{DC} [V]	I_F [A]	I_{FSM} [A]	typ. Q_C [nC]	Type
TO220 (2-leg)	600	4	32	8	IDT04S60C
	600	5	42	12	IDT05S60C
	600	2 x 5	84	24	IDT10S60C
	600	6	49	15	IDT06S60C
	600	2 x 6	98	30	IDT12S60C
	600	8	59	19	IDT08S60C
	600	2 x 8	118	38	IDT16S60C
D-PAK	600	4	32	8	IDD04S60C

For an overview about ROHS-compliant products please go to www.infineon.com/greenproducts

Alphanumeric Listing

Product Name	Product Description	Voltage Class	Page	Product Name	Product Description	Voltage Class	Page
BSP125	N-Channel Enhancement MOSFET	600 V	29	SPB07N6oC3	CoolMOS Transistor	600 V	25
BSP129	N-Channel Depletion MOSFET	240 V	29	SPB07N6oS5	CoolMOS Transistor	600 V	25
BSP135	N-Channel Depletion MOSFET	600 V	29	SPB11N6oC3	CoolMOS Transistor	600 V	25
BSP149	N-Channel Depletion MOSFET	200 V	29	SPB12N5oC3	CoolMOS Transistor	500 V	22
BSP298	N-Channel Enhancement MOSFET	400 V	29	SPB16N5oC3	CoolMOS Transistor	500 V	22
BSP299	N-Channel Enhancement MOSFET	500 V	29	SPB17N8oC3	CoolMOS Transistor	800 V	28
BSP300	N-Channel Enhancement MOSFET	800 V	29	SPB18N6oS5	CoolMOS Transistor	600 V	25
BSP324	N-Channel Enhancement MOSFET	400 V	29	SPB20N6oC3	CoolMOS Transistor	600 V	25
BSS126	N-Channel Depletion MOSFET	600 V	29	SPB20N6oS5	CoolMOS Transistor	600 V	25
BSS127	N-Channel Enhancement MOSFET	600 V	29	SPB21N5oC3	CoolMOS Transistor	500 V	22
BSS139	N-Channel Depletion MOSFET	250 V	29	SPD01N6oC3	CoolMOS Transistor	600 V	24
BSS159N	N-Channel Depletion MOSFET	60 V	29	SPD02N5oC3	CoolMOS Transistor	500 V	22
BSS169	N-Channel Depletion MOSFET	100 V	29	SPD02N6oC3	CoolMOS Transistor	600 V	24
BSS225	N-Channel Enhancement MOSFET	600 V	29	SPD02N6oS5	CoolMOS Transistor	600 V	24
IDD04S6oC	thinQ! 2G	600 V	30	SPD02N8oC3	CoolMOS Transistor	800 V	28
IDT04S6oC	thinQ! 2G	600 V	30	SPD03N5oC3	CoolMOS Transistor	500 V	22
IDT05S6oC	thinQ! 2G	600 V	30	SPD03N6oC3	CoolMOS Transistor	600 V	24
IDT06S6oC	thinQ! 2G	600 V	30	SPD03N6oS5	CoolMOS Transistor	600 V	24
IDT08S6oC	thinQ! 2G	600 V	30	SPD04N5oC3	CoolMOS Transistor	500 V	22
IDT10S6oC	thinQ! 2G	600 V	30	SPD04N6oS5	CoolMOS Transistor	600 V	24
IDT12S6oC	thinQ! 2G	600 V	30	SPD04N8oC3	CoolMOS Transistor	800 V	28
IDT16S6oC	thinQ! 2G	600 V	30	SPD06N6oC3	CoolMOS Transistor	600 V	24
IPA50R140CP	CoolMOS Transistor	500 V	23	SPD06N8oC3	CoolMOS Transistor	800 V	28
IPA50R199CP	CoolMOS Transistor	500 V	23	SPD07N6oC3	CoolMOS Transistor	600 V	24
IPA50R250CP	CoolMOS Transistor	500 V	23	SPD07N6oS5	CoolMOS Transistor	600 V	24
IPA50R299CP	CoolMOS Transistor	500 V	23	SPD08N5oC3	CoolMOS Transistor	500 V	22
IPA50R350CP	CoolMOS Transistor	500 V	23	SPD08N6oC3	CoolMOS Transistor	600 V	24
IPA50R399CP	CoolMOS Transistor	500 V	23	SPD09N6oC3	CoolMOS Transistor	600 V	24
IPA50R520CP	CoolMOS Transistor	500 V	23	SPD09N6oS5	CoolMOS Transistor	600 V	24
IPA60R125CP	CoolMOS Transistor	600 V	26	SPD09N75oC3	CoolMOS Transistor	650 V	28
IPA60R165CP	CoolMOS Transistor	600 V	26	SPD09N8oC3	CoolMOS Transistor	500 V	22
IPA60R199CP	CoolMOS Transistor	600 V	26	SPD09N8oC3	CoolMOS Transistor	800 V	28
IPA60R299CP	CoolMOS Transistor	600 V	26	SP11N6oC3	CoolMOS Transistor	600 V	24
IPA60R385CP	CoolMOS Transistor	600 V	26	SP11N6oS5	CoolMOS Transistor	600 V	24
IPB50R140CP	CoolMOS Transistor	500 V	23	SP11N65oC3	CoolMOS Transistor	650 V	28
IPB50R199CP	CoolMOS Transistor	500 V	23	SP12N5oC3	CoolMOS Transistor	500 V	22
IPB50R250CP	CoolMOS Transistor	500 V	23	SP11N6oC3	CoolMOS Transistor	600 V	24
IPB50R299CP	CoolMOS Transistor	500 V	23	SP16N5oC3	CoolMOS Transistor	500 V	22
IPB60R099CP	CoolMOS Transistor	600 V	26	SP12N6oC3	CoolMOS Transistor	600 V	24
IPB60R165CP	CoolMOS Transistor	600 V	26	SP12N6oC3	CoolMOS Transistor	650 V	28
IPD50R399CP	CoolMOS Transistor	500 V	23	SP12N5oC3	CoolMOS Transistor	500 V	22
IPD50R520CP	CoolMOS Transistor	500 V	23	SPN01N6oC3	CoolMOS Transistor	600 V	24
IPD60R385CP	CoolMOS Transistor	600 V	26	SPN02N6oC3	CoolMOS Transistor	600 V	24
IP150R350CP	CoolMOS Transistor	500 V	23	SPN02N6oS5	CoolMOS Transistor	600 V	24
IP150R399CP	CoolMOS Transistor	500 V	23	SPN03N6oC3	CoolMOS Transistor	600 V	24
IP160R199CP	CoolMOS Transistor	600 V	26	SPN03N6oS5	CoolMOS Transistor	600 V	24
IP160R299CP	CoolMOS Transistor	600 V	26	SPN04N6oC3	CoolMOS Transistor	600 V	24
IP160R385CP	CoolMOS Transistor	600 V	26	SPN04N6oS5	CoolMOS Transistor	600 V	24
IPPP50R140CP	CoolMOS Transistor	500 V	23	SPP02N6oS5	CoolMOS Transistor	600 V	25
IPPP50R199CP	CoolMOS Transistor	500 V	23	SPP02N8oC3	CoolMOS Transistor	800 V	28
IPPP50R250CP	CoolMOS Transistor	500 V	23	SPP03N6oC3	CoolMOS Transistor	600 V	25
IPPP50R299CP	CoolMOS Transistor	500 V	23	SPP03N6oS5	CoolMOS Transistor	600 V	25
IPPP60R099CP	CoolMOS Transistor	600 V	26	SPP03N6oC3	CoolMOS Transistor	600 V	24
IPPP60R125CP	CoolMOS Transistor	600 V	26	SPP06N6oC3	CoolMOS Transistor	600 V	25
IPPP60R165CP	CoolMOS Transistor	600 V	26	SPP06N8oC3	CoolMOS Transistor	800 V	28
IPPP60R199CP	CoolMOS Transistor	600 V	26	SPP07N65oC3	CoolMOS Transistor	650 V	28
IPPP60R299CP	CoolMOS Transistor	600 V	26	SPP07N6oC3	CoolMOS Transistor	600 V	25
IPPP60R385CP	CoolMOS Transistor	600 V	26	SPP07N6oS5	CoolMOS Transistor	600 V	25
IPPS50R520CP	CoolMOS Transistor	500 V	23	SPP08N5oC3	CoolMOS Transistor	500 V	22
IPW50R045CP	CoolMOS Transistor	500 V	23	SPP08N8oC3	CoolMOS Transistor	800 V	28
IPW50R140CP	CoolMOS Transistor	500 V	23	SPP11N6oC3	CoolMOS Transistor	600 V	25
IPW50R199CP	CoolMOS Transistor	500 V	23	SPP11N6oS5	CoolMOS Transistor	600 V	25
IPW60R045CP	CoolMOS Transistor	600 V	26	SPP11N6oCFD	CoolMOS Transistor	600 V	27
IPW60R099CP	CoolMOS Transistor	600 V	26	SPP11N65oC3	CoolMOS Transistor	650 V	28
IPW60R125CP	CoolMOS Transistor	600 V	26	SPP11N8oC3	CoolMOS Transistor	800 V	28
IPW60R165CP	CoolMOS Transistor	600 V	26	SPP12N5oC3	CoolMOS Transistor	500 V	22
IPW60R199CP	CoolMOS Transistor	600 V	26	SPP15N6oC3	CoolMOS Transistor	600 V	25
IPW60R299CP	CoolMOS Transistor	600 V	26	SPP16N5oC3	CoolMOS Transistor	500 V	22
SDB06S30	thinQ!	600 V	30	SPP17N8oC3	CoolMOS Transistor	800 V	28
SDB20S30	thinQ!	300 V	30	SPP20N6oCFD	CoolMOS Transistor	600 V	27
SDD04S6o	thinQ!	600 V	30	SPP20N6oC3	CoolMOS Transistor	600 V	25
SDP10S30	thinQ!	300 V	30	SPP20N6oS5	CoolMOS Transistor	600 V	25
SDP20S30	thinQ!	300 V	30	SPP20N5oC3	CoolMOS Transistor	650 V	28
SDT04S6o	thinQ!	600 V	30	SPP21N5oC3	CoolMOS Transistor	500 V	22
SDT05S6o	thinQ!	600 V	30	SPP24N6oC3	CoolMOS Transistor	600 V	25
SDT06S6o	thinQ!	600 V	30	SPS01N6oC3	CoolMOS Transistor	600 V	24
SDT08S6o	thinQ!	600 V	30	SPS02N5oC3	CoolMOS Transistor	500 V	22
SDT10S30	thinQ!	300 V	30	SPS02N6oC3	CoolMOS Transistor	600 V	24
SDT10S6o	thinQ!	600 V	30	SPS03N5oC3	CoolMOS Transistor	500 V	22
SDT12S6o	thinQ!	600 V	30	SPS03N6oC3	CoolMOS Transistor	600 V	24
SPA02N8oC3	CoolMOS Transistor	800 V	28	SPS04N5oC3	CoolMOS Transistor	500 V	22
SPA03N6oC3	CoolMOS Transistor	600 V	25	SPS04N6oC3	CoolMOS Transistor	600 V	24
SPA04N5oC3	CoolMOS Transistor	500 V	22	SPU01N6oC3	CoolMOS Transistor	600 V	24
SPA04N6oC3	CoolMOS Transistor	600 V	25	SPU02N6oC3	CoolMOS Transistor	600 V	24
SPA04N8oC3	CoolMOS Transistor	800 V	28	SPU02N6oS5	CoolMOS Transistor	600 V	24
SPA06N6oC3	CoolMOS Transistor	600 V	25	SPU03N6oS5	CoolMOS Transistor	600 V	24
SPA06N8oC3	CoolMOS Transistor	800 V	28	SPU04N6oS5	CoolMOS Transistor	600 V	24
SPA07N6oC3	CoolMOS Transistor	600 V	25	SPU07N6oS5	CoolMOS Transistor	600 V	24
SPA07N65oC3	CoolMOS Transistor	650 V	28	SPW11N6oC3	CoolMOS Transistor	600 V	24
SPA08N5oC3	CoolMOS Transistor	500 V	22	SPW11N6oCFD	CoolMOS Transistor	600 V	27
SPA08N8oC3	CoolMOS Transistor	800 V	28	SPW11N6oS5	CoolMOS Transistor	600 V	24
SPA11N6oC3	CoolMOS Transistor	600 V	25	SPW11N8oC3	CoolMOS Transistor	800 V	28
SPA11N65oC3	CoolMOS Transistor	650 V	28	SPW12N5oC3	CoolMOS Transistor	500 V	22
SPA11N8oC3	CoolMOS Transistor	800 V	28	SPW15N6oC3	CoolMOS Transistor	600 V	24
SPA12N5oC3	CoolMOS Transistor	500 V	22	SPW16N5oC3	CoolMOS Transistor	500 V	22
SPA15N6oC3	CoolMOS Transistor	600 V	25	SPW17N8oC3	CoolMOS Transistor	800 V	28
SPA16N5oC3	CoolMOS Transistor	500 V	22	SPW20N6oC3	CoolMOS Transistor	600 V	24
SPA17N8oC3	CoolMOS Transistor	800 V	28	SPW20N6oCFD	CoolMOS Transistor	600 V	27
SPA20N6oC3	CoolMOS Transistor	600 V	25	SPW20N6oS5	CoolMOS Transistor	600 V	24
SPA20N65oC3	CoolMOS Transistor	650 V	28	SPW21N5oC3	CoolMOS Transistor	500 V	22
SPA21N5oC3	CoolMOS Transistor	500 V	22	SPW24N6oC3	CoolMOS Transistor	600 V	24
SPB02N6oC3	CoolMOS Transistor	600 V	25	SPW32N5oC3	CoolMOS Transistor	500 V	22
SPB02N6oS5	CoolMOS Transistor	600 V	25	SPW35N6oC3	CoolMOS Transistor	600 V	24
SPB03N6oC3	CoolMOS Transistor	600 V	25	SPW35N6oCFD	CoolMOS Transistor	600 V	27
SPB03N6oS5	CoolMOS Transistor	600 V	25	SPW47N6oC3	CoolMOS Transistor	600 V	24
SPB04N5oC3	CoolMOS Transistor	500 V	22	SPW47N6oCFD	CoolMOS Transistor	600 V	27
SPB04N6oC3	CoolMOS Transistor	600 V	25	SPW52N5oC3	CoolMOS Transistor	500 V	22

Packages


D-PAK	D ² -PAK	DIP-7	DIP-8
			
DIP-14	DIP-20	DSO-8	DSO-14
			
DSO-16/12	DSO-16	DSO-18	DSO-20
			
I-PAK	I-PAK Short Leads	I ² -PAK (TO262)	SOT23
			
SOT223	TO220 (2-leg)	TO220 (3-leg)	TO220 FullPAK
			
TO220-6-46	TO220-6-47	TO247	
			

More Detailed Information on Power Management and Supply is Available

On our website:

www.infineon.com/power

- Data sheets
- Application notes
- Technical articles
- Simulation models
- Literature order codes



Edition May 2006

Published by
Infineon Technologies AG
81726 München, Germany

© Infineon Technologies AG 2006.
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

INFINEON TECHNOLOGIES SALES OFFICES WORLDWIDE*

(COUNTRY/AREA)

Australia

Infineon Technologies Australia Pty. Ltd.
885 Mountain Highway
Bayswater, Victoria 3153
☎ (+61) 3 - 97 21 88 88
Fax (+61) 3 - 97 21 88 08

Austria

Infineon Technologies Austria AG
Operngasse 20b/31
1040 Wien
☎ (+43) 0-51 77 71 11 00
Fax (+43) 0-51 77 71 15 00

Belgium/Luxembourg

Netherlands

Infineon Technologies Holding B.V.
Sales Division
Westblaak 32
3012 KM Rotterdam
☎ (+31) 10-2 17 68 00
Fax (+31) 10-2 17 68 19

Brazil

Infineon Technologies
South America Ltda.
Avenida Ermanno Marchetti,
1435 - 4º andar
05038-001 Águia Branca São Paulo-SP
☎ (+55) 11-39 08 25 64
Fax (+55) 11-39 08 25 64

Canada

Infineon Technologies
North America Corp.
340 March Road, Suite 301
Kanata, Ontario K2K 2E2
☎ (+1) 6 13-5 91 38 35
Fax (+1) 6 13-5 91 89 54

China

Infineon Technologies
International Trade (Shanghai) Co., Ltd.
Beijing Representative Office
12th Floor, Quantum Plaza
No.27 Zhi Chun Road
Haidian District
Beijing 100083
People's Republic of China
☎ (+86) 10 - 82 35 61 18
Fax (+86) 10 - 82 35 54 74

Infineon Technologies
International Trade (Shanghai) Co., Ltd.
No. 7 & 8, Lane 647, Song Tao Road
Zhang Jian Hi-Tech Park
Shanghai 201203, China
☎ (+86) 21-61 01 90 00
Fax (+86) 21-50 80 62 04

Infineon Technologies
International Trade (Shanghai) Co., Ltd.
Shenzhen Office
Room 1502, Block A
Tian An International Building
Renmin Nan Road
Shenzhen 518 001
☎ (+86) 7 55-82 28 91 04
Fax (+86) 7 55-82 28 02 17

Infineon Technologies
Taiwan Ltd.
12F-1, No. 3-2 Yuan Qu Street,
Nan Kang Software Park
Taipei 115
☎ (+8 86) 2-26 55 75 00
Fax (+8 86) 2-2 65 57 50 18

Denmark

Infineon Technologies
Hong Kong Ltd.
Hong Kong Office
Suite 302, Level 3 Festival Walk
80 Tat Chee Avenue
Kowloon Tong,
Hong Kong
☎ (+8 52) 28 - 32 05 00
Fax (+8 52) 28 - 27 97 62

Finland

Infineon Technologies Nordic A/S
Hérlev Hovedgade 201A
2730 Herlev
☎ (+45) 44-50 77 00
Fax (+45) 44-50 77 01

Infineon Technologies Nordic OY
Visitor's Address Upseerinkatu 1
P.O. Box 276
02601 Espoo
☎ (+3 58) 10-6 80 84 00
Fax (+3 58) 10-6 80 84 01

France

Infineon Technologies France S.A.S
Industrial Sales
2 ter, rue Marcel Doret
Burlaines II
31700 Blagnac
Phone (+33) 5-34 55 13 30
Fax (+33) 5-34 55 13 34

Infineon Technologies France S.A.S.
39 - 47, Boulevard Ornano
93527 Saint-Denis CEDEX 2
☎ (+33) 1-48 09 72 00
Fax (+33) 1-48 09 72 90

Germany

Infineon Technologies AG
Siemensstraße 31 - 33
71254 Ditzingen/Stuttgart
☎ (+49) 71 56 - 17 91 90
Fax (+49) 71 54 - 1 79 19 90

Infineon Technologies AG
Düsseldorfer Landstraße 401,
47259 Duisburg
☎ (+49) 20 3 - 7 29 87 11
Fax (+49) 20 3 - 7 29 87 60

Infineon Technologies AG
Naegelsbacherstraße 26
91052 Erlangen
☎ (+49) 91 31 - 97 00 10
Fax (+49) 91 31 - 9 70 01 99

Infineon Technologies AG
Paderborner Straße 1
30539 Hannover
☎ (+49) 511-8 76 56 20
Fax (+49) 5 11-87 65 62 90

Infineon Technologies AG
Am Campeone 1 - 12
8126 Munich
☎ (+49) 89-23 40
Fax (+49) 89-23 42 46 94

Infineon Technologies AG
Südwestpark 65
90449 Nuremberg
☎ (+49) 9 11-25 29 30
Fax (+49) 9 11-2 52 93 93

Infineon Technologies AG
Industrial Sales
Max-Planck-Str. 5
59581 Warstein
Phone (+49) 29 02 - 764 - 0
Fax (+49) 29 02 - 764 - 11 02

India

Infineon Technologies
India Pvt. Ltd.
13th Floor, Discoverer Building
International Technology Park
Whitefield Road
Bangalore 560 066
☎ (+91) 80-51 39 20 00
Fax (+91) 80-51 39 23 33

Ireland

Infineon Technologies Ireland Ltd.
69 Fitzwilliam Lane
Dublin 2
☎ (+3 53) 1-7 99 95 00
Fax (+3 53) 1-7 99 95 01

Israel

Nisko Ltd.
2, Habarzel Street
Tel Aviv 69710
☎ (+9 72) 3-7 65 73 00
Fax (+9 72) 3-7 65 73 33

Italy

Infineon Technologies Italia S.r.l.
Via Vipiteno, 4
20128 Milano
☎ (+39) 02 - 25 20 41
Fax (+39) 02 - 52 04 43 95

Japan

Infineon Technologies Japan K.K.
Maruyama Nissei Building 14F
2-14-21 Nishiki, Naka-ku
Nagoya-shi, Aichi 460-0003
☎ (+81) 52 - 2 23 15 70
Fax (+81) 52 - 2 23 14 61

Infineon Technologies Japan K.K.
ORIX-Dojima Building 8F
2-1-31, Dojima, Kita-ku
Osaka-shi,
Osaka 530-0003
☎ (+81) 6 - 47 97 44 60
Fax (+81) 6 - 47 97 44 62

Infineon Technologies Japan K.K.
Takanawa Park Tower
8Fl/9Fl/10Fl/12Fl/17Fl
3-20-14, Higashi-Gotanda,
Shinagawa-ku,
Tokyo 141-0022
☎ (+81) 3 - 54 49 64 11
Fax (+81) 3 - 54 49 64 01

Korea

Infineon Technologies Korea Co., Ltd.
4th floor Sigma Tower
7-19 Shinchon-dong Songpa-gu
Seoul 138-734
☎ (+82) 2-34 60 09 00
Fax (+82) 2-34 60 09 01

Malaysia

Infineon Technologies
Malaysia SDN BHD
Krystal Point II
1-4/11/12, Lebuh Bukit Kecil 6
11900 Bayan Lepas
Penang, Malaysia
☎ (+60) 4-6 44 77 66
Fax (+60) 4-6 41 48 72

Mexico

Turkey

Infineon Technologies
Everest Sales & Solutions
Av. Manuel Acuña 2674-101
Col. Ladron de Guevara
44680 Guadalajara
☎ (+52) 33 - 36 42 21 01
Fax (+52) 33 - 36 40 65 62

Poland

Siemens Sp. z.o.o.
Ul. Zupnicka 11
03-821 Warszawa
☎ (+48) 22-8 70 91 50
Fax (+48) 22-8 70 91 59

Portugal

Infineon Technologies F.S.,
Portugal, S.A.
Avenida 1º de Maio, 801
Mindela
4485-629 Vila do Conde
☎ (+3 51) 2 52-24 60 00
Fax (+3 51) 2 52-24 60 01

Russia

Infineon Technologies RUS LLC
Leninsky prospect 113/1
117198 Moscow
☎ (+7) 495 956 5195
Fax (+7) 495 956 5195

Singapore

Infineon Technologies Asia
Pacific Pte. Ltd.
8 Kallang Sector
Singapore 349 282
☎ (+65) 68-76 28 88
Fax (+65) 68-76 31 22

South Africa

Siemens Components
P.O. Box 3438
Halfway House 1680
2146 Sandton
☎ (+27) 11 - 6 52 20 00
Fax (+27) 11 - 6 52 26 14

Spain

Siemens, S.A.
División Componentes
Ronda de Europa, 5
28760 Tres Cantos-Madrid
☎ (+34) 91-5 14 71 55
Fax (+34) 91-5 14 70 14

Sweden

Infineon Technologies Sweden AB
Isafjordsgatan 16
164 81 Kista
☎ (+46) 8-57 50 00
Fax (+46) 8-57 46 12

Switzerland

Infineon Technologies
Schweiz AG
Badenerstrasse 623
P.O. Box 1570
8048 Zürich
☎ (+41) 44 - 4 97 80 40
Fax (+41) 44 - 4 97 80 50

Infineon Technologies
North America Corp.
1901 N. Roselle Rd., Suite 1020
Schaumburg, IL 60195
☎ (+1) 8 47 - 8 84 70 09
Fax (+1) 8 47 - 8 84 75 99

Infineon Technologies
North America Corp.
238 Littleton Rd, Suite 200
Westford, MA 01886
☎ (+1) 9 78 - 6 92 05 50
Fax (+1) 9 78 - 6 92 23 09

* and representative offices