



K320QVG-V1-F

Product

Standard LCD Module 240 x RGB x 320 Dots 3.2" TFT LCD Wide temperature With LED backlight With Touch Panel

Kentec Electronics (Displays) Limited URL: http://www.kentecdisplay.com.hk

E-mail: t.liang@kentecdisplay.com.hk; mf.zou@kentecdisplay.com.hk

CONTENTS

		Page No.
1.	DOCUMENT REVISION HISTORY	3
2.	GENERAL DESCRIPTION	4
3.	MECHANICAL SPECIFICATIONS	4
4.	INTERFACE SIGNALS	6
5.	ABSOLUTE MAXIMUM RATINGS	7
6.	ELECTRICAL SPECIFICATIONS	7
7.	OPTICAL CHARACTERISTICS	8
8.	TIMING CHARACTERISTICS	10
9.	RELIABILITY TEST ITEM	10
10.	SUGGESTIONS FOR USING LCD MODULES	10
11.	INSPECTION STANDARD	13
12.	PACKING(REFERENCE ONLY)	18



FS-K320QVG-V1-F 10/Oct/2011 **PAGE 3 OF 18**

1. Docume	1. Document revision history :							
DOCUMENT REVISION	DATE	DESCRIPTION	PREPARED BY	APPROVED BY				
01	2011.10.10	First Release.	XW Li					
	<u> </u>							



2. General Description

- 3.2"(diagonal), 240 x RGB x 320 dots, 262k colors, Transmissive, TFT LCD module.
- Viewing Direction: 9 o'clock.
- Driving IC: ILI9325D or equivalent TFT controller/driver.
- 16-bits/8-bit data bus (I80 system interface).
- Logic voltage: 2.8V (typ.).
- Touch panel.

3. Mechanical Specifications

The mechanical detail is shown in Fig. 1 and summarized in Table 1 below.

Table 1

Par	rameter	Specifications	Unit
Outline dimensions		55.04W) x 77.7(H) x 3.5(D) (Exclude FPC, cables of touch panel and backlight)	mm
	View area	50.6(W) x 66.8 (H)	mm
	TP active area	49.6(W) x 65.8(H)	mm
Color TFT	LCD active area	48.6(W) x 64.7(H)	mm
240xRGBx320	Display format	240 x RGB x 320	dots
	Color configuration	RGB stripes	-
	Dot pitch	0.2025(RGB)(W) x 0.2025(H)	mm
Weight		TBD	grams






Figure 1: Outline Drawing



4. Interface signals

Table 2: Pin assignment

D: 37	Table 2: Pin assignment								
Pin No.	Symbol		Description						
1-2	LED_K	Power supply for	Power supply for LED backlight						
3-4	LED_A	11 7							
5	GND	Power supply (s	system	ground)				
6	XR								
7	YD	Terminal of touc	ch pane	el.					
8	XL		P						
9	YU								
10	GND	Power supply (s	system	ground))				
11-13	NC	No connection							
14	RESET	System reset pir	1						
15	CS	Chip select pin							
16	NC	No connection							
17	SDI	Data input pin o							
18	SDO	Data output pin	of seri	al interf	face				
19-20	NC	No connection							
21-25	DB[0-4]	Bi-directional d	ata bus	(Bit0-b	pit4)				
26-27	NC	No connection							
28-30	DB[5-7]	Bi-directional d	ata bus	(Bit5-b	pit7)				
31	NC	No connection							
32-33	DB[8-9]	Bi-directional d	ata bus	(Bit8-b	pit9)				
34-35	NC	No connection							
36-41	DB[10-15]	Bi-directional d	ata bus	(Bit10-	-bit15)				
42	HSYNC	Line synchroniz	zation s	ignal in	put				
43	VSYNC	Frame /Ram syr	nchroni	zation	signal input				
44	DCLK	Dot clock signa	1						
45-46	VCC	Supply voltage	for log	ic and lo	ed driving				
47-48	IOVCC	Supply voltage			-				
49	DC	Data/Command	select						
50	RD	I80 system: Ser	ves as a	a read si	gnal and reads data at the low level				
5.1	WD/CCI	I80 system: Ser	ves as a	a write	signal and writes data at the rising edge				
51	WR/SCL	SPI: Serves as s	erial cl	lock sig	nal				
		Interface selecti							
		IM3 IM2	IM1	IM0	Interface mode				
		0 0	1	0	16-bit 8080 parallel interface, D[17:10]&D[8:1]				
52-55	IM[0:3]	0 0	1	1	8-bit 8080 parallel interface, D[8:1]				
		0 1	0	ID	Serial Peripheral Interface (SPI)				
		0 1	1	0	9-bit 3 wires Serial Peripheral Interface				
		0 1 1 8-bit 4 wires Serial Peripheral Interface							
56	FMARK	Output a frame head pulse signal							
57	NC	No connection							
58	DE	Data enable signal for RGB interface operation							
59-60	GND	Power supply (s	Power supply (system ground)						



5. Absolute Maximum Ratings

5.1 Electrical Maximum Ratings

<u>Table 3: Electrical Maximum Ratings – for IC</u>

Parameter	Symbol	Min.	Max.	Unit	Note
Power supply voltage (VDD)	VCC	-0.3	+4.6	V	1

Note:

- 1.VCC, GND must be maintained.
- 2. The modules may be destroyed if they are used beyond the absolute maximum ratings.

5.2 Environmental Condition

Table 4

Item	Operat tempera (Top	nture	Stor tempe (Ts (Not	Remark	
	Min.	Max.	Min.	Max.	
Ambient temperature	-20°C	+70°C	-30°C	+80°C	Dry
Humidity (Note 1)	80	No			
Humidity (Note 1)	< 50% RH for 40°	$C < Ta \le Maxin$	mum operating	temperature	condensation

Note 1: Product cannot sustain at extreme storage conditions for long time.

6. Electrical Specifications

Typical Electrical Characteristics

At Ta = 25 °C, VCC=IOVCC= 2.2V to 3.3V, GND=0V.

Table 5

Parameter	Symbol Conditions		Min.	Typ.	Max.	Unit
Supply voltage (logic)	VDD-GND		2.6	2.8	3.3	V
Supply current (Logic & LCD)	ICC	VDD=2.8V	-	1	10	mA
Supply current of white LED backlight	ILED	Forward voltage =18~22V	-	15	20	mA
Luminance (on the module surface)		Number of LED dies = 6 serial	-	150	1	cd/m ²



7. Optical Characteristics

Table 7: Optical specifications

Items		Symbol	Condition	Specifications			Unit		
nems		Symbol	Condition	Min.	Typ.	Max.	Omi		
Contrast Ra	atio	CR		1	300	-	ı		
Response T	ima	T_R		-	10	20	ms		
Response 1	me	T_{F}		-	15	20	ms		
	Red	X_R		0.627	0.642	0.657	-		
	Red	Y_R		0.315	0.330	0.345	1		
	Green	X_{G}		0.264 0.279	0.294	ı			
Chromaticity		Y_{G}	0.556 0.571 0.586 - 0.121 0.136 0.151 - 0.083 0.098 0.113 - 0.293 0.308 0.323 -	0.556	0.571	0.586	ı	Note	
Cinomaticity	Blue	X_{B}		-	11010				
		Y_B		0.083	0.098	0.113	-		
	White	X_{W}		-					
	Wille	Y_{W}		0.308	0.323	0.338	-		
	Hor.	\$\phi 1(3 o'clock)		50	60	-			
Viewing angle		φ2(9 o'clock)	Center	30	40	-	deg.		
	Ver.	θ2(12 o'clock)	CR=10	50	60	-	ueg.		
	ver.	θ1(6 o'clock)		50	60	-			
NTSC ratio					61.5		%		

Note 1: Definition of Contrast Ratio (CR):

The contrast ratio can be calculated by the following expression.

Contrast Ratio (CR) = L63 / L0

L63: Luminance of gray level 63

L0: Luminance of gray level 0

CR = CR (10)

CR (X) is corresponding to the Contrast Ratio of the point X at Figure in Note 5.

Note 2: Definition of Response Time (TR, TF):




Figure 3

Note 3: Viewing Angle




Figure 4

The above "Viewing Angle" is the measuring position with Largest Contrast Ratio; not for good image quality. View Direction for good image quality is 6 O'clock. Module maker can increase the "Viewing Angle" by applying Wide View Film.

Note 4: Measurement Set-Up:

The LCD module should be stabilized at a given temperature for 20 minutes to avoid abrupt temperature change during measuring. In order to stabilize the luminance, the measurement should be executed after lighting Backlight for 20 minutes in a windless room.




Figure 5



8. Timing Characteristics Please refer ILI9325 datasheet.

9. Reliability Test Item

Test Item	Sample Type	Test Condition	Test result determinant gist
High temperature	Normal temperature	70±3 ;96Н	the inspection of
storage	Wide temperature	80±3 ;96H	appearance and function
Low temperature	Normal temperature	-20±3 ;120H	character.
storage	Wide temperature	-30±3 ;120H	
High temperature	Normal temperature	50 ±3 ,90%±3%RH;96H	
/humidity storage	Wide temperature	60 ±3 ,90%±3%RH;96H	
High temperature	Normal temperature	60±3 ;96H	no objection of the function
operation	Wide temperature	70±3 ;96H	character; no fatal objection of
Low temperature	Normal temperature	0±3 ;96H	the appearance.
operation	Wide temperature	-20±3 ;96H	
High temperature	Normal temperature	40 ±3 ,90%±3%RH;96H	
/humidity operation	Wide temperature	50 ±3 ,90%±3%RH;96H	
Temperature Shock	Normal temperature	-20±3 ,30min? 70±3 ,30	inspect the objections
		min;10cycle	appearance, function & the
			whole structure
	Wide temperature	-30±3 ,30min	The inspection of appearance,
		80±3,30min;10cycle	function & the whole structure

10. Suggestions for using LCD modules

10.1 Handling of LCM

- 1. The LCD screen is made of glass. Don't give excessive external shock, or drop from a high place.
- 2. If the LCD screen is damaged and the liquid crystal leaks out, do not lick and swallow. When the liquid is attach to your hand, skin, cloth etc, wash it off by using soap and water thoroughly and immediately.
- 3. Don't apply excessive force on the surface of the LCM.
- 4. If the surface is contaminated ,clean it with soft cloth. If the LCM is severely contaminated , use Isopropyl alcohol/Ethyl alcohol to clean. Other solvents may damage the polarizer . The following solvents is especially prohibited: water , ketone Aromatic solvents etc.



- 5. Exercise care to minimize corrosion of the electrode. Corrosion of the electrodes is accelerated by water droplets, moisture condensation or a current flow in a high-humidity environment.
- 6. Install the LCD Module by using the mounting holes. When mounting the LCD module make sure it is free of twisting, warping and distortion. In particular, do not forcibly pull or bend the I/O cable or the backlight cable.
- 7. Don't disassemble the LCM.
- 8. To prevent destruction of the elements by static electricity, be careful to maintain an optimum work environment.
 - Be sure to ground the body when handling the LCD modules.
 - Tools required for assembling, such as soldering irons, must be properly grounded.
 - To reduce the amount of static electricity generated, do not conduct assembling and other work under dry conditions.
 - The LCD module is coated with a film to protect the display surface. Exercise care when peeling off this protective film since static electricity may be generated.
- 9. Do not alter, modify or change the the shape of the tab on the metal frame.
- 10. Do not make extra holes on the printed circuit board, modify its shape or change the positions of components to be attached.
- 11. Do not damage or modify the pattern writing on the printed circuit board.
- 12. Absolutely do not modify the zebra rubber strip (conductive rubber) or heat seal connector
- 13. Except for soldering the interface, do not make any alterations or modifications with a soldering iron.
- 14. Do not drop, bend or twist LCM.


10.2 Cautions for installing and assemabling if the module has Touch Panel

- 1. Use a buffer material (Gasket) between the touch panel and Front-case to protect damage and wrong operating. The dimension of the buffer material's edge between the TP V.A. edge is Min. 0.3mm.
- 2. We recommend to design a case that it can't over the boundary of the active area Max. 0.5mm in order



to prevent an operation at outside of the active area which can't guarantee the specified durability, because operation at the outside of the active area cause serious damage of a transparent.

- 3. When design case for installing Module, you would consider give a distance about 0.2 ± 0.15 mm between the module edge to case inside.
- 4. The corners of the product are not chamfered. When positioning and fixing the product on the case, we sugguest that you would provide a R part on the conner of the case so as not to apply load on the corner of the transparent module.



10.3 Storage

- 1. Store in an ambient temperature of 5 to 45 °C, and in a relative humidity of 40% to 60%. Don't expose to sunlight or fluorescent light.
- 2. Storage in a clean environment, free from dust, active gas, and solvent.
- 3. Store in antistatic container.



11. Inspection Standard

This specification is made to be used as the standard acceptance/rejection criteria for Color mobile phone LCM with touch pannel.

11.1 Sample plan and Inspection condition


11.1.1 Sample plan

Sampling plan according to MIL-STD-105E, normal level 2 and based on:

Major defect: AQL 0.65; Minor defect: AQL 1.5. 11.1.2 Inspection condition

Viewing distance for cosmetic inspection is about 30cm with bare eyes, and under an environment of 20~40W light intensity, all directions for inspecting the sample should be within 45 against perpendicular line.

11.2 Definition of inspection zone in LCD



Inspection zones in an LCD

Zone A: character/Digit area;

Zone B: viewing area except Zone A (ZoneA+ZoneB=minimum Viewing area);

Zone C: Outside viewing area (invisible area after assembly in customer's product);

Note: As a general rule, visual defects in Zone C are permissible, when it is no trouble for quality and assembly of customer's product. Defects are classified as major defects and minor defects according to the degree of defectiveness defined herein.

11.3 Major defects and Minor defects

11.3.1 Major defects

A major defect is a defect that is likely to result in failure, or to reduce the usability of the product for its intended purpose.


11.3.1.1 Abnormal operation: modules cannot display normally;



- 11.3.1.2 Line defect;
- 11.3.1.3 There is serious distortion or sharp burr on mechanical housing;
- 11.3.1.4 Glass breakage.
- 11.3.2 Minor defects:

A minor defect is a defect that is not likely to reduce the usability of the product for its intended purpose.

- 11.3.2.1 Dot defect:
 - 11.3.2.1.1 Inspection pattern: Full white, full black, red, green and blue screens;
 - 11.3.2.1.2 Criteria:(acceptable);




- Note: 1. Dot defect is defined as the defective area of the dot area is larger than 50% of the dot area . And the bright dot defect must be visible through 5% ND filter.
 - 2. Except for the allowed numbers of adjacent dots, the distance between dot defects should be more than 3mm apart.
- 11.3.2.1.3 The definitions of the inner display area and outer display area.

11.4 Inspection standards table:

11.4.1 Major defect

Item No.	Items to be	Inspection Standard	Classification of defects	
11.4.1.1	All functional defects	 No display Display abnormally Missing vertical/horizontal segment Short circuit Back-light no lighting, flickering and abnormal lighting. 	Major	
11.4.1.2	Missing	Missing component		
11.4.1.3	Outline dimension	Overall outline dimension beyond the drawing is not allowed.		
11.4.1.4	linearity	No more than 1.5%		





11.4.2 Cosmetic Defect (spot defect)

Item No	Itemsto be	Inspection Standard	·					
	Clear Spots Black and white	For dark/white spot, as $F = (x + y)/2$	sizeF is defined	Ç Ç Ç Ç Ç Ç Ç Ç Ç Ç Ç Ç Ç Ç Ç Ç Ç Ç Ç	Minor			
11 4 2 1	Spot defect	Zone		table Qty				
11.4.2.1	Pinhole, Foreign	Size(mm)	A B	С				
	Particle,	F=0.1	Ignore		Minor			
	polarizer	0.10< F=0.15	2	Ignore	1411101			
	Dirt	0.15< F=0.20	1					
	Dirt	F > 0.20	0					
		Zone	Acceptable Qty					
	Clear Spots TP Dirt	Size(mm)	A B	C				
11.4.2.2		F=0.1	Ignore		Minor			
11.4.2.2		0.10< F=0.15	2	Ignoro				
		0.15< F=0.25	1	Ignore				
		F > 0.25	0					
	Dim Spots	Zone	Acceptable Qty					
	Circle	Size(mm)	A B	C				
	shaped and	F=0.2	Ignore					
11.4.2.3	dim edged	0.20< F=0.4	2		Minor			
	defects	0.4< F=0.6	1	Ignore				
		F > 0.6	0					
		dot =sub-pixel			'			
			Accept	able Qty				
			I	II				
11.4.2.4	Dot defect	Bright dot	0	2	Minor			
		Dark dot 1 2 The distance of two point >5mm						
11 12 0		The distance of two p	JOHN >JHIII					

11.4.3 Cosmetic Defect (linear defect)

Item No	Items to be		Inspection Standard					
	Line defect Black line, White line, Foreign	Si	ze(mm)	Ac	cceptable Q	ty		
		Black line, L(Length)	W(Width)	zone				
				A	В	C		
11.4.3.1		Ignore	W=0.02	Ignore		Minor	Minor	
	material on	L=3.0	0.02< W=0.03	2				
	polarizer	L=2.0	0.03< W=0.05 1 Ignore		1			
			W> 0.05	Define as spot defect				




FS-K320QVG-V1-F 10/Oct/2011 PAGE 16 OF 18

		The line can b	e seen at	fter mobile	phone in the	e operatin	ng cond	lition:	
11.4.3.2	Foreign Material on TP film	Size(mm)			Acceptable Qty				
		L(Length)	W(Width)	zone					
				A		В	С	Minor	
		Ignore	W=0.0	03	Ignore				
		L=3.0	0.03 < W=0.05		3		Ignore		
			W> 0	.05	Define as spot defect]		
	Dim line defect Polarizer &BL scratch TP film scratch	If the scratch can be seen after mobile phone cover assembling or in the operating condition, judge by the line defect of 11.4.3.1. If the scratch can be seen only in non-operating condition or some special angle, judge by the following.							
		Size(mm)		Acceptable Qty			ty	Minor	
11.4.3.3		I (I anath)	W(Width)		zone				
11.4.3.3		tch L(Length)			A]	В	С	WIIIOI
		Ignore	W=0.0)2	Ignore				
		L=3.0	0.02<	W=0.03 2			Ignore		
		L=2.0	0.03<	W=0.05		1	Ignore		
			W> 0	.05	Define	as spot d	lefect		
		Air bubbles between glass & polarizer							
11.4.3.4	Polarize Air bubble	Acceptable Qty							
			A			В		C	
		F=0.2		Ignore			Minor		
		0.20< F=0.3		2				Ignore	
		0.3< F=0.5			1				
		F> 0.5			0				

11.4.4 Chipping Defect

Item No	Items to be	Inspection Standard				Classification of defects
11.4.4.1	Glass defect	Chips on corner A:LCD Glass defect Notes: S=contact pad length Chips on the corner of terminal shall not ITO pad or expose perimeter seal. B:TP Glass defect	$\begin{bmatrix} X \\ =0.2 \end{bmatrix}$ to be allowed $\begin{bmatrix} X \\ =3.0 \end{bmatrix}$	Y =S ed to extend Y =3.0	Z	Minor

FS-K320QVG-V1-F 10/Oct/2011 PAGE 17 OF 18



11.4.5 Parts Defect

11. 7 .J 1 ai	is Defect			
Item No Items to be		Inspection Standard	Classification	
			of defects	
	Douts contro	1. Not allow IC and FPC/heat-seal lead width is more than 50% beyond lead pattern.		
11.4.5.1	Parts contra position	2. Not allow chip or solder component is off center more than	Major	
	position	50% of the pad outline.		
	SMT	According to the <acceptability electronic<="" of="" td=""><td></td></acceptability>		
11.4.5.2		assemblies>IPC-A-610C class 2 standard. Component missing	Major	
		or function defect are Major defect, the others are Minor defect.		
		1. Pattern font:		
		Pattern fonts are clear and symmetrical, pattern fonts filter		
	TP Defect	lightly are allowed; The fort line is not allow to thinner or		
		thicker than 1/3 of normal size, and swing is not more than		
		0.1mm. the line is smooth and not broken.		
11.4.5.3			Major	
		Pattern font		
		2、The wing forward in the side of Visual Area:		
		The length of wing forward inside of the Visual Area:		
		n=0.2mm; Not excess 3 point, and the distance D=20mm _o		

FS-K320QVG-V1-F 10/Oct/2011 PAGE 18 OF 18

11.4.5.5	Soldering	1 No unmelted solder paste may be present on the FPC 2 No cold solder joints, missing solder connections, oxidation	Major
11.4.5.4	Backlight elements	1 Illumination source flickers when lit. 2 Spots or scratches that appear when lit must be judged using LCD spot, lines and contamination standards. 3 Backlight doesn't light or color is wrong	Major
		Burr 3, Film impression: With operation, must be invisibility. 4, Touch panel knob: if writing function normally, it could be allowed.	

12. Packing T.B.D.