


## DC Film Capacitors MKT Radial Potted Type



### APPLICATIONS

Blocking and coupling, bypass and energy reservoir

### REFERENCE STANDARDS

IEC 60384-2

### MARKING

C-value; tolerance; rated voltage; manufacturer's symbol; year and week of manufacturer; manufacturer's type

### DIELECTRIC

Polyester film

### ELECTRODES

Metallized

### CONSTRUCTION

Mono construction

### RATED (DC) VOLTAGE 371

63 V, 100 V, 250 V, 400 V

### RATED (DC) VOLTAGE 372

100 V, 250 V, 400 V, 630 V

### RATED (DC) VOLTAGE 373

100 V, 250 V, 400 V, 630 V

### RATED (AC) VOLTAGE 371

40 V, 63 V, 160 V, 220 V

### RATED (AC) VOLTAGE 372

63 V, 160 V, 220 V, 250 V

### RATED (AC) VOLTAGE 373

63 V, 160 V, 220 V, 250 V

### FEATURES

- 371: 7.62 mm lead pitch. Supplied loose in box and taped on reel or ammpack
- 372: 10 mm lead pitch. Supplied loose in box and taped on reel or ammpack
- 373: 15 mm to 27.5 mm lead pitch. Supplied loose in box and taped on reel
- Compliant to RoHS Directive 2002/95/EC



**RoHS**  
COMPLIANT

### ENCAPSULATION

Flame retardant plastic case and epoxy resin (UL-class 94 V-0)

### CLIMATIC TESTING CLASS ACC. TO IEC 60068-1

55/105/56

### CAPACITANCE RANGE (E12 SERIES)

**371:** 0.0039  $\mu$ F to 1.5  $\mu$ F

**372:** 0.0047  $\mu$ F to 0.68  $\mu$ F

**373:** 0.047  $\mu$ F to 15  $\mu$ F

### CAPACITANCE TOLERANCE

$\pm 10\%$ ,  $\pm 5\%$

### LEADS

Tinned wire

### RATED TEMPERATURE

85 °C

### MAXIMUM APPLICATION TEMPERATURE

105 °C

### PERFORMANCE GRADE


Grade 1 (long life)

### DETAIL SPECIFICATION

For more detailed data and test requirements contact:  
[dc-film@vishay.com](mailto:dc-film@vishay.com)



## COMPOSITION OF CATALOG NUMBER: 371



| TYPE         | PACKAGING                | LEAD CONFIGURATION                                 | PREFERRED TYPES |      |       |       |       |
|--------------|--------------------------|--|-----------------|------|-------|-------|-------|
|              |                          |  | C-TOL.          | 63 V | 100 V | 250 V | 400 V |
| 371          | Loose in box             | Lead length  | ± 10 %          | 11   | 21    | 41    | 51    |
|              |                          | 4.0 mm + 1.0 mm/- 0.5 mm                           | ± 5 %           | 12   | 22    | 42    | 52    |
|              |                          | Lead length  | ± 10 %          | 15   | 25    | 45    | 55    |
|              | Taped on reel (1)        | 26.0 ± 2.0 mm                                      | ± 5 %           | 16   | 26    | 46    | 56    |
|              |                          | H (1) = 18.5 mm                                    | ± 10 %          | 35   | 65    | 75    | 85    |
|              |                          | P <sub>0</sub> = 12.7 mm<br>Reel diameter = 356 mm | ± 5 %           | 36   | 66    | 76    | 86    |
| Ammopack (1) | H (1) = 18.5 mm          | ± 10 %   | 38              | 68   | 78    | 88    |       |
|              | P <sub>0</sub> = 12.7 mm | ± 5 %  | 39              | 69   | 79    | 89    |       |

**Note**

(1) For detailed tape specifications refer to packaging information: [www.vishay.com/doc?28139](http://www.vishay.com/doc?28139)

## SPECIFIC REFERENCE DATA

| DESCRIPTION   | VALUE                   |                          |                          |                     |
|---|-------------------------|--------------------------|--------------------------|---------------------|
|   | at 1 kHz                | at 10 kHz                | at 100 kHz               |                     |
| Tangent of loss angle:  |                         |                          |                          |                     |
| C ≤ 0.1 μF  | ≤ 75 x 10 <sup>-4</sup> | ≤ 130 x 10 <sup>-4</sup> | ≤ 250 x 10 <sup>-4</sup> |                     |
| 0.1 μF < C ≤ 0.47 μF  | ≤ 75 x 10 <sup>-4</sup> | ≤ 130 x 10 <sup>-4</sup> | ≤ 250 x 10 <sup>-4</sup> |                     |
| 0.47 μF < C ≤ 1.5 μF  | ≤ 75 x 10 <sup>-4</sup> | ≤ 130 x 10 <sup>-4</sup> | -                        |                     |
| Rated voltage pulse slope (dU/dt) <sub>R</sub> at                           | 63 V <sub>DC</sub>      | 100 V <sub>DC</sub>      | 250 V <sub>DC</sub>      | 400 V <sub>DC</sub> |
|   | 18 V/μs                 | 36 V/μs                  | 70 V/μs                  | 190 V/μs            |
| R between leads, for C ≤ 0.33 μF  |                         |                          |                          |                     |
| at 10 V; 1 min  | > 15 000 MΩ             |                          |                          |                     |
| at 100 V; 1 min   |                         | > 15 000 MΩ              | > 30 000 MΩ              | > 30 000 MΩ         |
| RC between leads, for C > 0.33 μF   |                         |                          |                          |                     |
| at 10 V; 1 min  | > 5000 s                |                          |                          |                     |
| at 100 V; 1 min   |                         | > 5000 s                 | -                        | -                   |
| R between interconnecting leads and case (foil method)                      | > 30 000 MΩ             |                          |                          |                     |
| Withstanding (DC) voltage (cut off current 10 mA) (1); rise time ≤ 1000 V/s | 100 V; 1 min            | 160 V; 1 min             | 400 V; 1 min             | 640 V; 1 min        |
| Withstanding (DC) voltage between leads and case                            | 200 V; 1 min            | 20 V; 1 min              | 500 V; 1 min             | 800 V; 1 min        |
| Maximum application temperature   | 105 °C                  |                          |                          |                     |

**Note**

(1) See "Voltage Proof Test for Metallized Film Capacitors": [www.vishay.com/doc?28169](http://www.vishay.com/doc?28169)

U<sub>RDC</sub> = 63 V; U<sub>RAC</sub> = 40 V

| C<br>(µF)   | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 371 XXYYY AND PACKAGING  |                   |                                      |                   |  |                   |  |                   |  |  |
|---|---------------------------------|----------------------------|--|-------------------|--------------------------------------|-------------------|--|-------------------|--|-------------------|--|--|
|   |                                 |                            | LOOSE IN BOX                                 |                   |                                      |                   | AMMOPACK <sup>(2)</sup>                  |                   | REEL <sup>(1)(2)</sup>                   |                   | C-VALUE                                |  |
|   |                                 |                            | l <sub>t</sub> = 4.0 mm<br>+ 1.0 mm/- 0.5 mm |                   | l <sub>t</sub> = 26.0 mm<br>± 2.0 mm |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   |  |  |
|   |                                 |                            | C-tol. =<br>± 10 %                           | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                   | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % |  |  |
| XX<br>(SPQ)   | XX<br>(SPQ)                     | XX<br>(SPQ)                | XX<br>(SPQ)                                  | XX<br>(SPQ)       | XX<br>(SPQ)                          | XX<br>(SPQ)       | XX<br>(SPQ)                              | XX<br>(SPQ)       | XX<br>(SPQ)                              | ..YYY             |  |  |
| Pitch = 7.62 mm + 0.30 mm/- 0.40 mm; d <sub>t</sub> = 0.50 mm ± 0.05 mm |                                 |                            |  |                   |                                      |                   |  |                   |  |                   |  |  |
| 0.056<br>0.068<br>0.082<br>0.1  | 2.5 x 6.5 x 10.0                | 0.24                       | 11...<br>(1000)                              | 12...<br>(1000)   | 15...<br>(1000)                      | 16...<br>(1000)   | 38...<br>(2000)                          | 39...<br>(2000)   | 35...<br>(2000)                          | 36...<br>(2000)   | 563<br>683<br>823<br>104               |  |
| 0.12<br>0.15<br>0.18<br>0.22  | 3.0 x 8.0 x 10.0                | 0.34                       | 11...<br>(1000)                              | 12...<br>(1000)   | 15...<br>(1000)                      | 16...<br>(1000)   | 38...<br>(1500)                          | 39...<br>(1500)   | 35...<br>(1500)                          | 36...<br>(1500)   | 124<br>154<br>184<br>224               |  |
| 0.27<br>0.33<br>0.39<br>0.47<br>0.56<br>0.68                            | 4.0 x 9.0 x 10.0                | 0.51                       | 11...<br>(1000)                              | 12...<br>(1000)   | 15...<br>(1000)                      | 16...<br>(1000)   | 38...<br>(1000)                          | 39...<br>(1000)   | 35...<br>(1500)                          | 36...<br>(1500)   | 274<br>334<br>394<br>474<br>564<br>684 |  |
| 0.82<br>1.0   | 5.0 x 10.5 x 10.0               | 0.73                       | 11...<br>(1000)                              | 12...<br>(1000)   | 15...<br>(1000)                      | 16...<br>(1000)   | 38...<br>(1000)                          | 39...<br>(1000)   | 35...<br>(1000)                          | 36...<br>(1000)   | 824<br>105                             |  |
| 1.2<br>1.5  | 6.0 x 11.5 x 10.0               | 1.0                        | 11...<br>(750)                               | 12...<br>(750)    | 15...<br>(1000)                      | 16...<br>(1000)   | 38...<br>(500)                           | 39...<br>(500)    | 35...<br>(500)                           | 36...<br>(500)    | 125<br>155                             |  |

**Notes**

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- (2) H = In-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"
- (3) Weight for short lead product only

U<sub>RDC</sub> = 100 V; U<sub>RAC</sub> = 63 V

| C<br>(µF)   | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 371 XXYYY AND PACKAGING  |                   |                                      |                   |  |                   |  |                   |  |  |
|---|---------------------------------|----------------------------|--|-------------------|--------------------------------------|-------------------|--|-------------------|--|-------------------|--|--|
|   |                                 |                            | LOOSE IN BOX                                 |                   |                                      |                   | AMMOPACK <sup>(2)</sup>                  |                   | REEL <sup>(1)(2)</sup>                   |                   | C-VALUE                                |  |
|   |                                 |                            | l <sub>t</sub> = 4.0 mm<br>+ 1.0 mm/- 0.5 mm |                   | l <sub>t</sub> = 26.0 mm<br>± 2.0 mm |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   |  |  |
|   |                                 |                            | C-tol. =<br>± 10 %                           | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                   | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % |  |  |
| XX<br>(SPQ)   | XX<br>(SPQ)                     | XX<br>(SPQ)                | XX<br>(SPQ)                                  | XX<br>(SPQ)       | XX<br>(SPQ)                          | XX<br>(SPQ)       | XX<br>(SPQ)                              | XX<br>(SPQ)       | XX<br>(SPQ)                              | ..YYY             |  |  |
| Pitch = 7.62 mm + 0.30 mm/- 0.40 mm; d <sub>t</sub> = 0.50 mm ± 0.05 mm |                                 |                            |  |                   |                                      |                   |  |                   |  |                   |  |  |
| 0.018<br>0.022<br>0.027<br>0.033<br>0.039<br>0.047                      | 2.5 x 6.5 x 10.0                | 0.24                       | 21...<br>(1000)                              | 22...<br>(1000)   | 25...<br>(1000)                      | 26...<br>(1000)   | 68...<br>(2000)                          | 69...<br>(2000)   | 65...<br>(2000)                          | 66...<br>(2000)   | 183<br>223<br>273<br>333<br>393<br>473 |  |
| 0.056<br>0.068<br>0.082<br>0.1  | 3.0 x 8.0 x 10.0                | 0.34                       | 21...<br>(1000)                              | 22...<br>(1000)   | 25...<br>(1000)                      | 26...<br>(1000)   | 68...<br>(1500)                          | 69...<br>(1500)   | 65...<br>(1500)                          | 66...<br>(1500)   | 563<br>683<br>823<br>104               |  |
| 0.12<br>0.15<br>0.18<br>0.22  | 4.0 x 9.0 x 10.0                | 0.51                       | 21...<br>(1000)                              | 22...<br>(1000)   | 25...<br>(1000)                      | 26...<br>(1000)   | 68...<br>(1000)                          | 69...<br>(1000)   | 65...<br>(1500)                          | 66...<br>(1500)   | 124<br>154<br>184<br>224               |  |
| 0.27<br>0.33<br>0.39<br>0.47  | 5.0 x 10.5 x 10.0               | 0.73                       | 21...<br>(1000)                              | 22...<br>(1000)   | 25...<br>(1000)                      | 26...<br>(1000)   | 68...<br>(1000)                          | 69...<br>(1000)   | 65...<br>(1000)                          | 66...<br>(1000)   | 274<br>334<br>394<br>474               |  |

**Notes**

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- (2) H = In-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"
- (3) Weight for short lead product only



U<sub>RDC</sub> = 250 V; U<sub>RAC</sub> = 160 V

| C<br>(µF)   | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 371 XYYYY AND PACKAGING  |                   |                                      |                   |  |                   |  |                   |  |  |
|---|---------------------------------|----------------------------|--|-------------------|--------------------------------------|-------------------|--|-------------------|--|-------------------|--|--|
|   |                                 |                            | LOOSE IN BOX                                 |                   |                                      |                   | AMMOPACK <sup>(2)</sup>                  |                   | REEL <sup>(1)(2)</sup>                   |                   | C-VALUE<br>..YYY                       |  |
|   |                                 |                            | l <sub>t</sub> = 4.0 mm<br>+ 1.0 mm/- 0.5 mm |                   | l <sub>t</sub> = 26.0 mm<br>± 2.0 mm |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   |  |  |
|   |                                 |                            | C-tol. =<br>± 10 %                           | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                   | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % |  |  |
| XX<br>(SPQ)   | XX<br>(SPQ)                     | XX<br>(SPQ)                | XX<br>(SPQ)                                  | XX<br>(SPQ)       | XX<br>(SPQ)                          | XX<br>(SPQ)       | XX<br>(SPQ)                              |                   |  |                   |  |  |
| Pitch = 7.62 mm + 0.30 mm/- 0.40 mm; d <sub>t</sub> = 0.50 mm ± 0.05 mm |                                 |                            |  |                   |                                      |                   |  |                   |  |                   |  |  |
| 0.082<br>0.01<br>0.012<br>0.015   | 2.5 x 6.5 x 10.0                | 0.24                       | 41...<br>(1000)                              | 42...<br>(1000)   | 45...<br>(1000)                      | 46...<br>(1000)   | 78...<br>(2000)                          | 79...<br>(2000)   | 75...<br>(2000)                          | 76...<br>(2000)   | 822<br>103<br>123<br>153               |  |
| 0.018<br>0.022<br>0.027<br>0.033<br>0.039<br>0.047                      | 3.0 x 8.0 x 10.0                | 0.34                       | 41...<br>(1000)                              | 42...<br>(1000)   | 45...<br>(1000)                      | 46...<br>(1000)   | 78...<br>(1500)                          | 79...<br>(1500)   | 75...<br>(1500)                          | 76...<br>(1500)   | 183<br>223<br>273<br>333<br>393<br>473 |  |
| 0.056<br>0.068<br>0.082<br>0.1  | 4.0 x 9.0 x 10.0                | 0.51                       | 41...<br>(1000)                              | 42...<br>(1000)   | 45...<br>(1000)                      | 46...<br>(1000)   | 78...<br>(1000)                          | 79...<br>(1000)   | 75...<br>(1500)                          | 76...<br>(1500)   | 563<br>683<br>823<br>104               |  |
| 0.12  | 5.0 x 10.5 x 10.0               | 0.73                       | 41...<br>(1000)                              | 42...<br>(1000)   | 45...<br>(1000)                      | 46...<br>(1000)   | 78...<br>(1000)                          | 79...<br>(1000)   | 75...<br>(1000)                          | 76...<br>(1000)   | 124                                    |  |

**Notes**

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- (2) H = In-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"
- (3) Weight for short lead product only


U<sub>RDC</sub> = 400 V; U<sub>RAC</sub> = 220 V

| C<br>(µF)   | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(1)</sup> | CATALOG NUMBER BFC2 371 XYYYY AND PACKAGING   |                   |                                      |                   |  |                   |  |                   |                                 |  |
|---|---------------------------------|----------------------------|---|-------------------|--------------------------------------|-------------------|--|-------------------|--|-------------------|---------------------------------|--|
|   |                                 |                            | LOOSE IN BOX                                  |                   |                                      |                   | AMMOPACK <sup>(2)</sup>                  |                   | REEL <sup>(1)(2)</sup>                   |                   | C-VALUE<br>..YYY                |  |
|   |                                 |                            | l <sub>t</sub> = 4.0 mm + 1.0 mm/<br>- 0.5 mm |                   | l <sub>t</sub> = 26.0 mm<br>± 2.0 mm |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   |                                 |  |
|   |                                 |                            | C-tol. =<br>± 10 %                            | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                   | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % |                                 |  |
| XX<br>(SPQ)   | XX<br>(SPQ)                     | XX<br>(SPQ)                | XX<br>(SPQ)                                   | XX<br>(SPQ)       | XX<br>(SPQ)                          | XX<br>(SPQ)       | XX<br>(SPQ)                              |                   |  |                   |                                 |  |
| Pitch = 7.62 mm + 0.30 mm/- 0.40 mm; d <sub>t</sub> = 0.50 mm ± 0.05 mm |                                 |                            |   |                   |                                      |                   |  |                   |  |                   |                                 |  |
| 0.0039<br>0.0047<br>0.0056<br>0.0068                                    | 2.5 x 6.5 x 10.0                | 0.24                       | 51...<br>(1000)                               | 52...<br>(1000)   | 55...<br>(1000)                      | 56...<br>(1000)   | 88...<br>(2000)                          | 89...<br>(2000)   | 85...<br>(2000)                          | 86...<br>(2000)   | 392<br>472<br>562<br>682        |  |
| 0.0082<br>0.01  | 3.0 x 8.0 x 10.0                | 0.34                       | 51...<br>(1000)                               | 52...<br>(1000)   | 55...<br>(1000)                      | 56...<br>(1000)   | 88...<br>(1500)                          | 89...<br>(1500)   | 85...<br>(1500)                          | 86...<br>(1500)   | 822<br>103                      |  |
| 0.012<br>0.015  | 4.0 x 9.0 x 10.0                | 0.51                       | 51...<br>(1000)                               | 52...<br>(1000)   | 55...<br>(1000)                      | 56...<br>(1000)   | 88...<br>(1000)                          | 89...<br>(1000)   | 85...<br>(1500)                          | 86...<br>(1500)   | 123<br>153                      |  |
| 0.018<br>0.022<br>0.027<br>0.033<br>0.039                               | 5.0 x 10.5 x 10.0               | 0.73                       | 51...<br>(1000)                               | 52...<br>(1000)   | 55...<br>(1000)                      | 56...<br>(1000)   | 88...<br>(1000)                          | 89...<br>(1000)   | 85...<br>(1000)                          | 86...<br>(1000)   | 183<br>223<br>273<br>333<br>393 |  |

**Notes**

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- (2) H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"
- (3) Weight for short lead products only

## COMPOSITION OF CATALOG NUMBER: 372



| TYPE | PACKAGING         | LEAD CONFIGURATION  | PREFERRED TYPES |       |       |       |       |
|------|-------------------|---|-----------------|-------|-------|-------|-------|
|      |                   |   | C-TOL.          | 100 V | 250 V | 400 V | 630 V |
| 372  | Loose in box      | Lead length<br>4.0 mm + 1.0 mm/- 0.5 mm                               | ± 10 %          | 21    | 41    | 51    | 61    |
|      |                   |   | ± 5 %           | 22    | 42    | 52    | 62    |
|      | Taped on reel (1) | H (1) = 18.5 mm<br>P <sub>0</sub> = 12.7 mm<br>Reel diameter = 356 mm | ± 10 %          | 25    | 45    | 55    | 65    |
|      |                   |   | ± 5 %           | 26    | 46    | 56    | 66    |
|      | Ammopack (1)      | H (1) = 18.5 mm<br>P <sub>0</sub> = 12.7 mm                           | ± 10 %          | 28    | 48    | 58    | 68    |
|      |                   |   | ± 5 %           | 29    | 49    | 59    | 69    |

**Note**

(1) For detailed tape specifications refer to packaging information: [www.vishay.com/doc?28139](http://www.vishay.com/doc?28139)

## SPECIFIC REFERENCE DATA

| DESCRIPTION  | VALUE                   |                     |                          |                     |                          |  |
|--|-------------------------|---------------------|--------------------------|---------------------|--------------------------|--|
| Tangent of loss angle:<br>C ≤ 0.1 μF<br>0.1 μF < C ≤ 0.68 μF                   | at 1 kHz                |                     | at 10 kHz                |                     | at 100 kHz               |  |
|  | ≤ 75 x 10 <sup>-4</sup> |                     | ≤ 130 x 10 <sup>-4</sup> |                     | ≤ 250 x 10 <sup>-4</sup> |  |
|  | ≤ 75 x 10 <sup>-4</sup> |                     | ≤ 130 x 10 <sup>-4</sup> |                     | ≤ 250 x 10 <sup>-4</sup> |  |
| Rated voltage pulse slope (dU/dt) <sub>R</sub> at                              | 100 V <sub>DC</sub>     | 250 V <sub>DC</sub> | 400 V <sub>DC</sub>      | 630 V <sub>DC</sub> |                          |  |
|  | 34 V/μs                 | 50 V/μs             | 80 V/μs                  | 120 V/μs            |                          |  |
| R between leads, for C ≤ 0.33 μF<br>at 10 V; 1 min<br>at 100 V; 1 min          | > 15 000 MΩ             | > 15 000 MΩ         | > 30 000 MΩ              | > 30 000 MΩ         |                          |  |
| RC between leads, for C > 0.33 μF at 100 V; 1 min                              | > 5000 s                |                     |                          |                     |                          |  |
| R between interconnecting leads and case (foil method)                         | > 30 000 MΩ             |                     |                          |                     |                          |  |
| Withstanding (DC) voltage (cut off current 10 mA) (1);<br>rise time ≤ 1000 V/s | 160 V; 1 min            | 400 V; 1 min        | 640 V; 1 min             | 1008 V; 1 min       |                          |  |
| Withstanding (DC) voltage between leads and case                               | 200 V; 1 min            | 500 V; 1 min        | 800 V; 1 min             | 1260 V; 1 min       |                          |  |
| Maximum application temperature  | 105 °C                  |                     |                          |                     |                          |  |

**Note**

(1) See "Voltage Proof Test for Metallized Film Capacitors": [www.vishay.com/doc?28169](http://www.vishay.com/doc?28169)



U<sub>RDC</sub> = 100 V; U<sub>RAC</sub> = 63 V

| C<br>( $\mu$ F)  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 372 XYYYY AND PACKAGING |                       |  |                       |  |                       | C-VALUE                                       |
|--|---------------------------------|----------------------------|---|-----------------------|--|-----------------------|--|-----------------------|---|
|  |                                 |                            | LOOSE IN BOX                                |                       | REEL <sup>(1)(2)</sup>                   |                       | AMMOPACK <sup>(2)</sup>                  |                       |   |
|  |                                 |                            | l <sub>t</sub> = 4.0 mm + 1.0 mm/- 0.5 mm   |                       | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                       | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                       |   |
|  |                                 |                            | C-tol. =<br>$\pm$ 10 %                      | C-tol. =<br>$\pm$ 5 % | C-tol. =<br>$\pm$ 10 %                   | C-tol. =<br>$\pm$ 5 % | C-tol. =<br>$\pm$ 10 %                   | C-tol. =<br>$\pm$ 5 % |   |
|  |                                 |                            | XX<br>(SPQ)                                 | XX<br>(SPQ)           | XX<br>(SPQ)                              | XX<br>(SPQ)           | XX<br>(SPQ)                              | XX<br>(SPQ)           | ..YYY   |
| Pitch = 10.0 mm $\pm$ 0.4 mm; d <sub>t</sub> = 0.60 mm $\pm$ 0.06 mm |                                 |                            |   |                       |  |                       |  |                       |   |
| 0.1<br>0.12<br>0.15<br>0.18<br>0.22<br>0.27<br>0.33                  | 4.0 x 10.0 x 12.5               | 0.65                       | 21...<br>(1000)                             | 22...<br>(1000)       | 25...<br>(1400)                          | 26...<br>(1400)       | 28...<br>(750)                           | 29...<br>(750)        | 104<br>124<br>154<br>184<br>224<br>274<br>334 |
| 0.39<br>0.47   | 5.0 x 11.0 x 12.5               | 0.87                       | 21...<br>(1000)                             | 22...<br>(1000)       | 25...<br>(1100)                          | 26...<br>(1100)       | 28...<br>(600)                           | 29...<br>(600)        | 394<br>474                                    |
| 0.56<br>0.68   | 6.0 x 12.0 x 12.5               | 1.15                       | 21...<br>(750)                              | 22...<br>(750)        | 25...<br>(900)                           | 26...<br>(900)        | 28...<br>(500)                           | 29...<br>(500)        | 564<br>684                                    |

**Notes**

• SPQ = Standard Packing Quantity

(1) Reel diameter = 356 mm is available on request

(2) H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"

(3) Weight for short lead product only

U<sub>RDC</sub> = 250 V; U<sub>RAC</sub> = 160 V

| C<br>( $\mu$ F)  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 372 XYYYY AND PACKAGING |                       |  |                       |  |                       | C-VALUE                         |
|--|---------------------------------|----------------------------|---|-----------------------|--|-----------------------|--|-----------------------|---------------------------------|
|  |                                 |                            | LOOSE IN BOX                                |                       | REEL <sup>(1)(2)</sup>                   |                       | AMMOPACK <sup>(2)</sup>                  |                       |                                 |
|  |                                 |                            | l <sub>t</sub> = 4.0 mm + 1.0 mm/- 0.5 mm   |                       | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                       | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                       |                                 |
|  |                                 |                            | C-tol. =<br>$\pm$ 10 %                      | C-tol. =<br>$\pm$ 5 % | C-tol. =<br>$\pm$ 10 %                   | C-tol. =<br>$\pm$ 5 % | C-tol. =<br>$\pm$ 10 %                   | C-tol. =<br>$\pm$ 5 % |                                 |
|  |                                 |                            | XX<br>(SPQ)                                 | XX<br>(SPQ)           | XX<br>(SPQ)                              | XX<br>(SPQ)           | XX<br>(SPQ)                              | XX<br>(SPQ)           | ..YYY                           |
| Pitch = 10.0 mm $\pm$ 0.4 mm; d <sub>t</sub> = 0.60 mm $\pm$ 0.06 mm |                                 |                            |   |                       |  |                       |  |                       |                                 |
| 0.047<br>0.056<br>0.068<br>0.082<br>0.1                              | 4.0 x 10.0 x 12.5               | 0.65                       | 41...<br>(1000)                             | 42...<br>(1000)       | 45...<br>(1400)                          | 46...<br>(1400)       | 48...<br>(750)                           | 49...<br>(750)        | 473<br>563<br>683<br>823<br>104 |
| 0.12<br>0.15   | 5.0 x 11.0 x 12.5               | 0.87                       | 41...<br>(1000)                             | 42...<br>(1000)       | 45...<br>(1100)                          | 46...<br>(1100)       | 48...<br>(600)                           | 49...<br>(600)        | 124<br>154                      |
| 0.18<br>0.22   | 6.0 x 12.0 x 12.5               | 1.15                       | 41...<br>(750)                              | 42...<br>(750)        | 45...<br>(900)                           | 46...<br>(900)        | 48...<br>(500)                           | 49...<br>(500)        | 184<br>224                      |

**Notes**

• SPQ = Standard Packing Quantity

(1) Reel diameter = 356 mm is available on request

(2) H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"

(3) Weight for short lead product only

U<sub>RDC</sub> = 400 V; U<sub>RAC</sub> = 220 V

| C<br>(μF)  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 372 XXYYY AND PACKAGING |                   |  |                   |  |                   | C-VALUE<br><br>..YYY  |
|--|---------------------------------|----------------------------|---|-------------------|--|-------------------|--|-------------------|---|
|  |                                 |                            | LOOSE IN BOX                                |                   | REEL <sup>(1)(2)</sup>                   |                   | AMMOPACK <sup>(2)</sup>                  |                   |   |
|  |                                 |                            | l <sub>t</sub> = 4.0 mm + 1.0 mm/- 0.5 mm   |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   |   |
|  |                                 |                            | C-tol. =<br>± 10 %                          | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % |   |
|  |                                 |                            |   | XX<br>(SPQ)       | XX<br>(SPQ)                              | XX<br>(SPQ)       | XX<br>(SPQ)                              |                   |   |
| <b>Pitch = 10.0 mm ± 0.4 mm; d<sub>t</sub> = 0.60 mm ± 0.06 mm</b>                                 |                                 |                            |   |                   |  |                   |  |                   |   |
| 0.0047<br>0.0056<br>0.0068<br>0.0082<br>0.01<br>0.012<br>0.015<br>0.018<br>0.022<br>0.027<br>0.033 | 4.0 x 10.0 x 12.5               | 0.65                       | 51...<br>(1000)                             | 52...<br>(1000)   | 55...<br>(1400)                          | 56...<br>(1400)   | 58...<br>(750)                           | 59...<br>(750)    | 472<br>562<br>682<br>822<br>103<br>123<br>153<br>183<br>223<br>273<br>333 |
| 0.039<br>0.047<br>0.056  | 5.0 x 11.0 x 12.5               | 0.87                       | 51...<br>(1000)                             | 52...<br>(1000)   | 55...<br>(1100)                          | 56...<br>(1100)   | 58...<br>(600)                           | 59...<br>(600)    | 393<br>473<br>563   |
| 0.068<br>0.082   | 6.0 x 12.0 x 12.5               | 1.15                       | 51...<br>(750)                              | 52...<br>(750)    | 55...<br>(900)                           | 56...<br>(900)    | 58...<br>(500)                           | 59...<br>(500)    | 683<br>823  |

**Notes**

- SPQ = Standard Packing Quantity
- <sup>(1)</sup> Reel diameter = 356 mm is available on request
- <sup>(2)</sup> H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to “Packaging Information”
- <sup>(3)</sup> Weight for short lead product only

U<sub>RDC</sub> = 630 V; U<sub>RAC</sub> = 250 V


| C<br>(μF)  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 372 XXYYY AND PACKAGING |                   |  |                   |  |                   | C-VALUE<br><br>..YYY            |
|--|---------------------------------|----------------------------|---|-------------------|--|-------------------|--|-------------------|---------------------------------|
|  |                                 |                            | LOOSE IN BOX                                |                   | REEL <sup>(1)(2)</sup>                   |                   | AMMOPACK <sup>(2)</sup>                  |                   |                                 |
|  |                                 |                            | l <sub>t</sub> = 4.0 mm + 1.0 mm/- 0.5 mm   |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   |                                 |
|  |                                 |                            | C-tol. =<br>± 10 %                          | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % |                                 |
|  |                                 |                            |   | XX<br>(SPQ)       | XX<br>(SPQ)                              | XX<br>(SPQ)       | XX<br>(SPQ)                              |                   |                                 |
| <b>Pitch = 10.0 mm ± 0.4 mm; d<sub>t</sub> = 0.60 mm ± 0.06 mm</b> |                                 |                            |   |                   |  |                   |  |                   |                                 |
| 0.01<br>0.012<br>0.015<br>0.018<br>0.022                           | 4.0 x 10.0 x 12.5               | 0.65                       | 61...<br>(1000)                             | 62...<br>(1000)   | 65...<br>(1400)                          | 66...<br>(1400)   | 68...<br>(750)                           | 69...<br>(750)    | 103<br>123<br>153<br>183<br>223 |
| 0.027<br>0.033   | 5.0 x 11.0 x 12.5               | 0.87                       | 61...<br>(1000)                             | 62...<br>(1000)   | 65...<br>(1100)                          | 66...<br>(1100)   | 68...<br>(600)                           | 69...<br>(600)    | 273<br>333                      |
| 0.039<br>0.047   | 6.0 x 12.0 x 12.5               | 1.15                       | 61...<br>(750)                              | 62...<br>(750)    | 65...<br>(900)                           | 66...<br>(900)    | 68...<br>(500)                           | 69...<br>(500)    | 393<br>473                      |

**Notes**

- SPQ = Standard Packing Quantity
- <sup>(1)</sup> Reel diameter = 356 mm is available on request
- <sup>(2)</sup> H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to “Packaging Information”
- <sup>(3)</sup> Weight for short lead product only



**COMPOSITION OF CATALOG NUMBER: 373**



| TYPE            | PACKAGING         | LEAD CONFIGURATION  | PREFERRED TYPES |       |       |       |       |
|-----------------|-------------------|---|-----------------|-------|-------|-------|-------|
|                 |                   |   | C-TOL.          | 100 V | 250 V | 400 V | 630 V |
| 373<br>compact  | Loose in box      | Lead length<br>5.0 mm ± 1.0 mm  | ± 10 %          | 23    | 43    | 53    | 63    |
|                 |                   |   | ± 5 %           | 24    | 44    | 54    | 64    |
|                 | Taped on reel (1) | H (1) = 18.5 mm<br>P <sub>0</sub> = 12.7 mm<br>Reel diameter = 356 mm | ± 10 %          | 27    | 47    | 57    | 67    |
| 373<br>standard | Loose in box      | Lead length<br>5.0 mm ± 1.0 mm  | ± 10 %          | 21    | 41    | 51    | -     |
|                 |                   |   | ± 5 %           | 22    | 42    | 52    |       |
|                 | Taped on reel (1) | H (1) = 18.5 mm<br>P <sub>0</sub> = 12.7 mm<br>Reel diameter = 356 mm | ± 10 %          | 25    | 45    | 55    |       |
|                 |                   |   | ± 5 %           | 26    | 46    | 56    |       |

**Note**

(1) For detailed tape specifications refer to packaging information: [www.vishay.com/doc?28139](http://www.vishay.com/doc?28139)

**SPECIFIC REFERENCE DATA**

| DESCRIPTION   | VALUE                   |                          |                          |                     |
|---|-------------------------|--------------------------|--------------------------|---------------------|
|   | at 1 kHz                | at 10 kHz                | at 100 kHz               |                     |
| Tangent of loss angle:  |                         |                          |                          |                     |
| C ≤ 0.1 μF  | ≤ 75 x 10 <sup>-4</sup> | ≤ 130 x 10 <sup>-4</sup> | ≤ 250 x 10 <sup>-4</sup> |                     |
| 0.1 μF < C ≤ 0.47 μF  | ≤ 75 x 10 <sup>-4</sup> | ≤ 130 x 10 <sup>-4</sup> | ≤ 300 x 10 <sup>-4</sup> |                     |
| 0.47 μF < C ≤ 1.0 μF  | ≤ 75 x 10 <sup>-4</sup> | ≤ 130 x 10 <sup>-4</sup> | -                        |                     |
| 1.0 μF < C ≤ 10 μF  | ≤ 75 x 10 <sup>-4</sup> | ≤ 150 x 10 <sup>-4</sup> | -                        |                     |
| C > 10 μF   | ≤ 75 x 10 <sup>-4</sup> | -                        | -                        |                     |
| Rated voltage pulse slope (dU/dt) <sub>R</sub> at                           | 100 V <sub>DC</sub>     | 250 V <sub>DC</sub>      | 400 V <sub>DC</sub>      | 630 V <sub>DC</sub> |
| P = 15 mm   | 14 V/μs                 | 16 V/μs                  | 34 V/μs                  | 90 V/μs             |
| P = 22.5 mm   | 5 V/μs                  | 7 V/μs                   | 14 V/μs                  | 35 V/μs             |
| P = 27.5 mm   | 4 V/μs                  | 6 V/μs                   | 12 V/μs                  | 30 V/μs             |
| R between leads, for C ≤ 0.33 μF  |                         |                          |                          |                     |
| at 100 V; 1 min   | > 15 000 MΩ             | > 15 000 MΩ              | > 30 000 MΩ              | > 30 000 MΩ         |
| at 500 V; 1 min   |                         |                          |                          |                     |
| RC between leads, for C > 0.33 μF   |                         |                          |                          |                     |
| at 100 V; 1 min   | > 5000 s                | > 10 000 s               | > 10 000 s               | > 10 000 s          |
| at 500 V; 1 min   |                         |                          |                          |                     |
| R between interconnecting leads and case (foil method)                      | > 30 000 MΩ             |                          |                          |                     |
| Withstanding (DC) voltage (cut off current 10 mA) (1); rise time ≤ 1000 V/s | 160 V; 1 min            | 400 V; 1 min             | 640 V; 1 min             | 1008 V; 1 min       |
| Withstanding (DC) voltage between leads and case                            | 200 V; 1 min            | 500 V; 1 min             | 800 V; 1 min             | 1260 V; 1 min       |
| Maximum application temperature   | 105 °C                  |                          |                          |                     |

**Note**

(1) See "Voltage Proof Test for Metallized Film Capacitors": [www.vishay.com/doc?28169](http://www.vishay.com/doc?28169)



$U_{RDC} = 100\text{ V}$ ;  $U_{RAC} = 63\text{ V}$  (compact size)

| C<br>( $\mu\text{F}$ )   | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 373 XXYYY AND PACKAGING |                       |  |                       | C-VALUE<br><br>..YYY   |
|--|---------------------------------|----------------------------|---|-----------------------|--|-----------------------|--|
|  |                                 |                            | LOOSE IN BOX                                |                       | REEL <sup>(1)(2)</sup>                   |                       |  |
|  |                                 |                            | $l_t = 5.0\text{ mm} \pm 1.0\text{ mm}$     |                       | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                       |  |
|  |                                 |                            | C-tol. =<br>$\pm 10\%$                      | C-tol. =<br>$\pm 5\%$ | C-tol. =<br>$\pm 10\%$                   | C-tol. =<br>$\pm 5\%$ |  |
|  |                                 |                            | XX<br>(SPQ)                                 | XX<br>(SPQ)           | XX<br>(SPQ)                              | XX<br>(SPQ)           |  |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.60\text{ mm} \pm 0.06\text{ mm}</math></b> |                                 |                            |   |                       |  |                       |  |
| 0.33<br>0.39<br>0.47<br>0.56<br>0.68<br>0.82<br>1<br>1.2<br>1.5<br>1.8                               | 5.0 x 11.0 x 17.5               | 1.1                        | 23...<br>(1000)                             | 24...<br>(1000)       | 27...<br>(1100)                          | 28...<br>(1100)       | 334<br>394<br>474<br>564<br>684<br>824<br>105<br>125<br>155<br>185 |
| 2.2  | 6.0 x 12.0 x 17.5               | 1.5                        | 23...<br>(1000)                             | 24...<br>(1000)       | 27...<br>(900)                           | 28...<br>(900)        | 225  |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b> |                                 |                            |   |                       |  |                       |  |
| 2.7<br>3.3   | 7.0 x 13.5 x 17.5               | 2.0                        | 23...<br>(1000)                             | 24...<br>(1000)       | 27...<br>(800)                           | 28...<br>(800)        | 275<br>335   |
| 3.9<br>4.7   | 8.5 x 15.0 x 17.5               | 2.7                        | 23...<br>(1000)                             | 24...<br>(1000)       | 27...<br>(650)                           | 28...<br>(650)        | 395<br>475   |

**Notes**

• SPQ = Standard Packing Quantity

<sup>(1)</sup> Reel diameter = 356 mm is available on request

<sup>(2)</sup> H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"

<sup>(3)</sup> Weight for short lead products only

$U_{RDC} = 250\text{ V}$ ;  $U_{RAC} = 160\text{ V}$  (compact size)

| C<br>( $\mu\text{F}$ )  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 373 XXYYY AND PACKAGING |                       |  |                       | C-VALUE<br><br>..YYY            |
|---|---------------------------------|----------------------------|---|-----------------------|--|-----------------------|---------------------------------|
|   |                                 |                            | LOOSE IN BOX                                |                       | REEL <sup>(1)(2)</sup>                   |                       |                                 |
|   |                                 |                            | $l_t = 5.0\text{ mm} \pm 1.0\text{ mm}$     |                       | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                       |                                 |
|   |                                 |                            | C-tol. =<br>$\pm 10\%$                      | C-tol. =<br>$\pm 5\%$ | C-tol. =<br>$\pm 10\%$                   | C-tol. =<br>$\pm 5\%$ |                                 |
|   |                                 |                            | XX<br>(SPQ)                                 | XX<br>(SPQ)           | XX<br>(SPQ)                              | XX<br>(SPQ)           |                                 |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.40 mm; <math>d_t = 0.60\text{ mm} \pm 0.06\text{ mm}</math></b> |                                 |                            |   |                       |  |                       |                                 |
| 0.15<br>0.18<br>0.22<br>0.27<br>0.32  | 5.0 x 11.0 x 17.5               | 1.1                        | 43...<br>(1000)                             | 44...<br>(1000)       | 47...<br>(1100)                          | 48...<br>(1100)       | 154<br>184<br>224<br>274<br>334 |
| 0.39<br>0.47  | 6.0 x 12.0 x 17.5               | 1.5                        | 43...<br>(1000)                             | 44...<br>(1000)       | 47...<br>(900)                           | 48...<br>(900)        | 394<br>474                      |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.40 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b> |                                 |                            |   |                       |  |                       |                                 |
| 0.56<br>0.68  | 7.0 x 13.5 x 17.5               | 2.0                        | 43...<br>(1000)                             | 44...<br>(1000)       | 47...<br>(800)                           | 48...<br>(800)        | 564<br>684                      |
| 0.82<br>1.0   | 8.5 x 15.0 x 17.5               | 2.7                        | 43...<br>(1000)                             | 44...<br>(1000)       | 47...<br>(650)                           | 48...<br>(650)        | 824<br>105                      |
| 1.2   | 10.0 x 16.5 x 17.5              | 3.5                        | 43...<br>(500)                              | 44...<br>(500)        | 47...<br>(600)                           | 48...<br>(600)        | 125                             |
| <b>Pitch = 22.5 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b>  |                                 |                            |   |                       |  |                       |                                 |
| 1.5<br>1.8  | 8.5 x 18.0 x 26.0               | 4.5                        | 43...<br>(200)                              | 44...<br>(200)        | 47...<br>(450)                           | 48...<br>(450)        | 155<br>185                      |
| 2.2<br>2.7  | 10.0 x 19.5 x 26.0              | 5.7                        | 43...<br>(200)                              | 44...<br>(200)        | 47...<br>(350)                           | 48...<br>(350)        | 225<br>275                      |



| C<br>( $\mu$ F)  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(1)</sup> | CATALOG NUMBER BFC2 373 XXYYY AND PACKAGING |                        |  |                        | C-VALUE<br><br>..YYY |
|--|---------------------------------|----------------------------|---|------------------------|--|------------------------|----------------------|
|  |                                 |                            | LOOSE IN BOX                                |                        | REEL <sup>(1)(2)</sup>                   |                        |                      |
|  |                                 |                            | $l_t = 5.0 \text{ mm} \pm 1.0 \text{ mm}$   |                        | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                        |                      |
|  |                                 |                            | C-tol. =<br>$\pm 10 \%$                     | C-tol. =<br>$\pm 5 \%$ | C-tol. =<br>$\pm 10 \%$                  | C-tol. =<br>$\pm 5 \%$ |                      |
|  |                                 |                            | XX<br>(SPQ)                                 | XX<br>(SPQ)            | XX<br>(SPQ)                              | XX<br>(SPQ)            |                      |
| <b>Pitch = 27.5 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.80 mm <math>\pm</math> 0.08 mm</b> |                                 |                            |   |                        |  |                        |                      |
| 3.3  | 11.0 x 21.0 x 31.0              | 8.2                        | 43...<br>(100)                              | 44...<br>(100)         | -  | -                      | 335                  |
| 3.9<br>4.7   | 13.0 x 23.0 x 31.0              | 10.2                       | 43...<br>(100)                              | 44...<br>(100)         | -  | -                      | 395<br>475           |

**Notes**

• SPQ = Standard Packing Quantity

<sup>(1)</sup> Reel diameter = 356 mm is available on request

<sup>(2)</sup> H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"

<sup>(3)</sup> Weight for short lead product only

**U<sub>RDC</sub> = 400 V; U<sub>RAC</sub> = 220 V (compact size)**

| C<br>( $\mu$ F)  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 373 XXYYY AND PACKAGING |                        |  |                        | C-VALUE<br><br>..YYY                          |
|--|---------------------------------|----------------------------|---|------------------------|--|------------------------|---|
|  |                                 |                            | LOOSE IN BOX                                |                        | REEL <sup>(1)(2)</sup>                   |                        |   |
|  |                                 |                            | $l_t = 5.0 \text{ mm} \pm 1.0 \text{ mm}$   |                        | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                        |   |
|  |                                 |                            | C-tol. =<br>$\pm 10 \%$                     | C-tol. =<br>$\pm 5 \%$ | C-tol. =<br>$\pm 10 \%$                  | C-tol. =<br>$\pm 5 \%$ |   |
|  |                                 |                            | XX<br>(SPQ)                                 | XX<br>(SPQ)            | XX<br>(SPQ)                              | XX<br>(SPQ)            |   |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.60 mm <math>\pm</math> 0.06 mm</b> |                                 |                            |   |                        |  |                        |   |
| 0.047<br>0.056<br>0.068<br>0.082<br>0.1<br>0.12<br>0.15  | 5.0 x 11.0 x 17.5               | 1.1                        | 53...<br>(1000)                             | 54...<br>(1000)        | 57...<br>(1100)                          | 58...<br>(1100)        | 473<br>563<br>683<br>823<br>104<br>124<br>154 |
| 0.18<br>0.22   | 6.0 x 12.0 x 17.5               | 1.5                        | 53...<br>(1000)                             | 54...<br>(1000)        | 57...<br>(900)                           | 58...<br>(900)         | 184<br>224                                    |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.80 mm <math>\pm</math> 0.08 mm</b> |                                 |                            |   |                        |  |                        |   |
| 0.27<br>0.33   | 7.0 x 13.5 x 17.5               | 2.0                        | 53...<br>(1000)                             | 54...<br>(1000)        | 57...<br>(800)                           | 58...<br>(800)         | 274<br>334                                    |
| 0.39<br>0.47   | 8.5 x 15.0 x 17.5               | 2.7                        | 53...<br>(1000)                             | 54...<br>(1000)        | 57...<br>(650)                           | 58...<br>(650)         | 394<br>474                                    |
| 0.56   | 10.0 x 16.5 x 17.5              | 3.5                        | 53...<br>(500)                              | 54...<br>(500)         | 57...<br>(600)                           | 58...<br>(600)         | 564   |
| <b>Pitch = 22.5 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.80 mm <math>\pm</math> 0.08 mm</b> |                                 |                            |   |                        |  |                        |   |
| 0.68<br>0.82   | 8.5 x 18.0 x 26.0               | 4.5                        | 53...<br>(200)                              | 54...<br>(200)         | 57...<br>(450)                           | 58...<br>(450)         | 684<br>824                                    |
| 1<br>1.2   | 10.0 x 19.5 x 26.0              | 5.7                        | 53...<br>(200)                              | 54...<br>(200)         | 57...<br>(350)                           | 58...<br>(350)         | 105<br>125                                    |
| <b>Pitch = 27.5 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.80 mm <math>\pm</math> 0.08 mm</b> |                                 |                            |   |                        |  |                        |   |
| 1.5  | 11.0 x 21.0 x 31.0              | 8.2                        | 53...<br>(100)                              | 54...<br>(100)         | -  | -                      | 155   |
| 1.8<br>2.2   | 13.0 x 23.0 x 31.0              | 10.2                       | 53...<br>(100)                              | 54...<br>(100)         | -  | -                      | 185<br>225                                    |

**Notes**

• SPQ = Standard Packing Quantity

<sup>(1)</sup> Reel diameter = 356 mm is available on request

<sup>(2)</sup> H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"

<sup>(3)</sup> Weight for short lead product only

$U_{RDC} = 630\text{ V}$ ;  $U_{RAC} = 250\text{ V}$  (compact size)

| C<br>( $\mu\text{F}$ )   | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 373 XXYYY AND PACKAGING |                       |  |                       |            |
|--|---------------------------------|----------------------------|---|-----------------------|--|-----------------------|------------|
|  |                                 |                            | LOOSE IN BOX                                |                       | REEL <sup>(1)(2)</sup>                 |                       | C-VALUE    |
|  |                                 |                            | $l_t = 5.0\text{ mm} \pm 1.0\text{ mm}$     |                       | H = 18.5 mm;<br>$P_0 = 12.7\text{ mm}$ |                       |            |
|  |                                 |                            | C-tol. =<br>$\pm 10\%$                      | C-tol. =<br>$\pm 5\%$ | C-tol. =<br>$\pm 10\%$                 | C-tol. =<br>$\pm 5\%$ |            |
|  |                                 |                            | XX<br>(SPQ)                                 | XX<br>(SPQ)           | XX<br>(SPQ)                            | XX<br>(SPQ)           | ..YYY      |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.60\text{ mm} \pm 0.06\text{ mm}</math></b> |                                 |                            |   |                       |  |                       |            |
| 0.047<br>0.056   | 5.0 x 11.0 x 17.5               | 1.1                        | 63...<br>(1000)                             | 64...<br>(1000)       | 67...<br>(1100)                        | 68...<br>(1100)       | 473<br>563 |
| 0.068<br>0.082   | 6.0 x 12.0 x 17.5               | 1.5                        | 63...<br>(1000)                             | 64...<br>(1000)       | 67...<br>(900)                         | 68...<br>(900)        | 683<br>823 |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b> |                                 |                            |   |                       |  |                       |            |
| 0.1<br>0.12  | 7.0 x 13.5 x 17.5               | 2.0                        | 63...<br>(1000)                             | 64...<br>(1000)       | 67...<br>(800)                         | 68...<br>(800)        | 104<br>124 |
| 0.15<br>0.18   | 8.5 x 15.0 x 17.5               | 2.7                        | 63...<br>(1000)                             | 64...<br>(1000)       | 67...<br>(650)                         | 68...<br>(650)        | 154<br>184 |
| 0.22   | 10.0 x 16.5 x 17.5              | 3.5                        | 63...<br>(500)                              | 64...<br>(500)        | 67...<br>(600)                         | 68...<br>(600)        | 224        |
| <b>Pitch = 22.5 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b> |                                 |                            |   |                       |  |                       |            |
| 0.27<br>0.33   | 8.5 x 18.0 x 26.0               | 4.5                        | 63...<br>(200)                              | 64...<br>(200)        | 67...<br>(450)                         | 68...<br>(450)        | 274<br>334 |
| 0.39<br>0.47   | 10.0 x 19.5 x 26.0              | 5.7                        | 63...<br>(200)                              | 64...<br>(200)        | 67...<br>(350)                         | 68...<br>(350)        | 394<br>474 |
| <b>Pitch = 27.5 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b> |                                 |                            |   |                       |  |                       |            |
| 0.56   | 11.0 x 21.0 x 31.0              | 8.2                        | 63...<br>(100)                              | 64...<br>(100)        | -                                      | -                     | 564        |
| 0.68<br>0.82   | 13.0 x 23.0 x 31.0              | 10.2                       | 63...<br>(100)                              | 64...<br>(100)        |  |                       | 684<br>824 |
| 1.00   | 15.0 x 25.0 x 31.5              | 13.4                       | 63...<br>(100)                              | 64...<br>(100)        |  |                       | 105        |

### Notes

• SPQ = Standard Packing Quantity

<sup>(1)</sup> Reel diameter = 356 mm is available on request

<sup>(2)</sup> H = in-tape height;  $P_0$  = Sprocket hole distance; for detailed specifications refer to "Packaging Information"

<sup>(3)</sup> Weight for short lead product only



U<sub>RDC</sub> = 100 V; U<sub>RAC</sub> = 63 V (standard size)

| C<br>( $\mu$ F)  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 373 XYYY AND PACKAGING |                       |                 |  |                                 |         |
|--|---------------------------------|----------------------------|--|-----------------------|-----------------|--|---------------------------------|---------|
|  |                                 |                            | LOOSE IN BOX                               |                       |                 | REEL <sup>(1)(2)</sup>                   |                                 | C-VALUE |
|  |                                 |                            | l <sub>t</sub> = 5.0 mm $\pm$ 1.0 mm       |                       |                 | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                                 |         |
|  |                                 |                            | C-tol. =<br>$\pm$ 10 %                     | C-tol. =<br>$\pm$ 5 % | SPQ             | C-tol. =<br>$\pm$ 10 %                   | C-tol. =<br>$\pm$ 5 %           |         |
| XX<br>(SPQ)  | XX<br>(SPQ)                     | XX<br>(SPQ)                | XX<br>(SPQ)                                | XX<br>(SPQ)           | ..YYY           |  |                                 |         |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.60 mm <math>\pm</math> 0.06 mm</b> |                                 |                            |  |                       |                 |  |                                 |         |
| 0.33<br>0.39<br>0.47<br>0.56<br>0.68   | 5.0 x 11.0 x 17.5               | 1.1                        | 21...<br>(1000)                            | 22...<br>(1000)       | 25...<br>(1100) | 26...<br>(1100)                          | 334<br>394<br>474<br>565<br>684 |         |
| 0.82<br>1  | 6.0 x 12.0 x 17.5               | 1.5                        | 21...<br>(1000)                            | 22...<br>(1000)       | 25...<br>(900)  | 26...<br>(900)                           | 824<br>105                      |         |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.80 mm <math>\pm</math> 0.08 mm</b> |                                 |                            |  |                       |                 |  |                                 |         |
| 1.2<br>1.5   | 7.0 x 13.5 x 17.5               | 2.0                        | 21...<br>(1000)                            | 22...<br>(1000)       | 25...<br>(800)  | 26...<br>(800)                           | 125<br>155                      |         |
| 1.8<br>2.2   | 8.5 x 15.0 x 17.5               | 2.7                        | 21...<br>(1000)                            | 22...<br>(1000)       | 25...<br>(650)  | 26...<br>(650)                           | 185<br>225                      |         |
| <b>Pitch = 22.5 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.80 mm <math>\pm</math> 0.08 mm</b> |                                 |                            |  |                       |                 |  |                                 |         |
| 2.7<br>3.3   | 8.5 x 18.0 x 26.0               | 4.5                        | 21...<br>(200)                             | 22...<br>(200)        | 25...<br>(450)  | 26...<br>(450)                           | 275<br>335                      |         |
| 3.9<br>4.7   | 10.0 x 19.5 x 26.0              | 5.7                        | 21...<br>(200)                             | 22...<br>(200)        | 25...<br>(350)  | 26...<br>(350)                           | 395<br>475                      |         |
| <b>Pitch = 27.5 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.80 mm <math>\pm</math> 0.08 mm</b> |                                 |                            |  |                       |                 |  |                                 |         |
| 5.6<br>6.8   | 11.0 x 21.0 x 31.0              | 8.2                        | 21...<br>(100)                             | 22...<br>(100)        | -               | -  | 565<br>685                      |         |
| 8.2<br>10  | 13.0 x 23.0 x 31.0              | 10.2                       | 21...<br>(100)                             | 22...<br>(100)        | -               | -  | 825<br>106                      |         |
| 12<br>15   | 18.0 x 28.0 x 31.5              | 18.4                       | 21...<br>(100)                             | 22...<br>(100)        | -               | -  | 126<br>156                      |         |

**Notes**

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- (2) H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"
- (3) Weight for short lead product only

**Available on request**

| C<br>( $\mu$ F)  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 373 XYYY AND PACKAGING |                       |     |                        |                       |     |
|--|---------------------------------|----------------------------|--|-----------------------|-----|------------------------|-----------------------|-----|
|  |                                 |                            | LOOSE IN BOX                               |                       |     | REEL <sup>(1)(2)</sup> |                       |     |
|  |                                 |                            | l <sub>t</sub> = 5.0 mm $\pm$ 1.0 mm       |                       |     | H = 18.5 mm            |                       |     |
|  |                                 |                            | C-tol. =<br>$\pm$ 10 %                     | C-tol. =<br>$\pm$ 5 % | SPQ | C-tol. =<br>$\pm$ 10 % | C-tol. =<br>$\pm$ 5 % | SPQ |
| <b>Pitch = 22.5 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.80 mm <math>\pm</math> 0.08 mm</b> |                                 |                            |  |                       |     |                        |                       |     |
| 1.5  | 6.0 x 15.5 x 26.0               | 2.7                        | 90012                                      | 90013                 | 300 | 90018                  | 90019                 | 600 |
| 1.8<br>2.2   | 7.0 x 16.5 x 26.0               | 3.3                        | 90022<br>90002                             | 90023<br>90003        | 200 | 90028<br>90008         | 90029<br>90009        | 550 |
| <b>Pitch = 27.5 mm <math>\pm</math> 0.4 mm; d<sub>t</sub> = 0.80 mm <math>\pm</math> 0.08 mm</b> |                                 |                            |  |                       |     |                        |                       |     |
| 4.7  | 9.0 x 19.0 x 31.0               | 6.1                        | 90032                                      | 90033                 | 100 | -                      |                       |     |

**Notes**

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- (2) H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"
- (3) Weight for short lead product only

U<sub>RDC</sub> = 250 V; U<sub>RAC</sub> = 160 V (standard size)

| C<br>(µF)  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 373 XXYYY AND PACKAGING |                   |  |                   |         |
|--|---------------------------------|----------------------------|---|-------------------|--|-------------------|---------|
|  |                                 |                            | LOOSE IN BOX                                |                   | REEL <sup>(1)(2)</sup>                   |                   |         |
|  |                                 |                            | l <sub>t</sub> = 5.0 mm ± 1.0 mm            |                   | H = 18.5 mm;<br>P <sub>0</sub> = 12.7 mm |                   |         |
|  |                                 |                            | C-tol. =<br>± 10 %                          | C-tol. =<br>± 5 % | C-tol. =<br>± 10 %                       | C-tol. =<br>± 5 % | C-VALUE |
|  |                                 |                            | XX<br>(SPQ)                                 | XX<br>(SPQ)       | XX<br>(SPQ)                              | XX<br>(SPQ)       | ..YYY   |
| <b>Pitch = 15.0 mm ± 0.4 mm; d<sub>t</sub> = 0.60 mm ± 0.06 mm</b> |                                 |                            |   |                   |  |                   |         |
| 0.15   | 5.0 x 11.0 x 17.5               | 1.1                        | 41...                                       | 42...             | 45...                                    | 46...             | 154     |
| 0.18   |                                 |                            | (1000)                                      | (1000)            | (1100)                                   | (1100)            | 184     |
| 0.22   |                                 |                            |   |                   |  |                   | 224     |
| 0.27   | 6.0 x 12.0 x 17.5               | 1.5                        | 41...                                       | 42...             | 45...                                    | 46...             | 274     |
| 0.33   |                                 |                            | (1000)                                      | (1000)            | (900)                                    | (900)             | 334     |
| 0.39   |                                 |                            |   |                   |  |                   | 394     |
| 0.47   |                                 |                            |   |                   |  |                   | 474     |
| <b>Pitch = 15.0 mm ± 0.4 mm; d<sub>t</sub> = 0.80 mm ± 0.08 mm</b> |                                 |                            |   |                   |  |                   |         |
| 0.56   | 7.0 x 13.5 x 17.5               | 2.0                        | 41...                                       | 42...             | 45...                                    | 46...             | 564     |
| 0.68   |                                 |                            | (1000)                                      | (1000)            | (800)                                    | (800)             | 684     |
| 0.82   | 8.5 x 15.0 x 17.5               | 2.7                        | 41...                                       | 42...             | 45...                                    | 46...             | 824     |
| 1  |                                 |                            | (1000)                                      | (1000)            | (650)                                    | (650)             | 105     |
| <b>Pitch = 22.5 mm ± 0.4 mm; d<sub>t</sub> = 0.80 mm ± 0.08 mm</b> |                                 |                            |   |                   |  |                   |         |
| 1.2  | 8.5 x 18.0 x 26.0               | 4.5                        | 41...                                       | 42...             | 45...                                    | 46...             | 125     |
| 1.5  |                                 |                            | (200)                                       | (200)             | (450)                                    | (450)             | 155     |
| 1.8  | 10.0 x 19.5 x 26.0              | 5.7                        | 41...                                       | 42...             | 45...                                    | 46...             | 185     |
| 2.2  |                                 |                            | (200)                                       | (200)             | (350)                                    | (350)             | 225     |
| <b>Pitch = 27.5 mm ± 0.4 mm; d<sub>t</sub> = 0.80 mm ± 0.08 mm</b> |                                 |                            |   |                   |  |                   |         |
| 2.7  | 13.0 x 23.0 x 31.0              | 10.2                       | 41...                                       | 42...             |  |                   | 275     |
| 3.3  |                                 |                            | (100)                                       | (100)             |  |                   | 335     |
| 3.9  | 15.0 x 28.0 x 31.5              | 13.4                       | 41...                                       | 42...             |  |                   | 395     |
| 4.7  |                                 |                            | (100)                                       | (100)             |  |                   | 475     |

**Notes**

• SPQ = Standard Packing Quantity

(1) Reel diameter = 356 mm is available on request

(2) H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"

(3) Weight for short lead product only

**Available on request**

| C<br>(µF)  | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 373 XXYYY AND PACKAGING |                   |     |                        |                   |     |
|--|---------------------------------|----------------------------|---|-------------------|-----|------------------------|-------------------|-----|
|  |                                 |                            | LOOSE IN BOX                                |                   |     | REEL <sup>(1)(2)</sup> |                   |     |
|  |                                 |                            | l <sub>t</sub> = 5.0 mm ± 1.0 mm            |                   |     | H = 18.5 mm            |                   |     |
|  |                                 |                            | C-tol. =<br>± 10 %                          | C-tol. =<br>± 5 % | SPQ | C-tol. =<br>± 10 %     | C-tol. =<br>± 5 % | SPQ |
| <b>Pitch = 22.5 mm ± 0.4 mm; d<sub>t</sub> = 0.80 mm ± 0.08 mm</b> |                                 |                            |   |                   |     |                        |                   |     |
| 0.47   | 6.0 x 15.5 x 26.0               | 2.7                        | 90042                                       | 90046             | 300 | 90048                  | 90049             | 600 |
| 0.56   |                                 |                            | 90052                                       | 90053             |     | 90058                  | 90059             |     |
| 0.67   |                                 |                            | 90062                                       | 90063             |     | 90068                  | 90069             |     |
| 0.85   | 7.0 x 16.5 x 26.0               | 3.3                        | 90072                                       | 90073             | 200 | 90078                  | 90079             | 550 |
| 1  |                                 |                            | 90082                                       | 90083             |     | 90088                  | 90089             |     |
| <b>Pitch = 27.5 mm ± 0.4 mm; d<sub>t</sub> = 0.80 mm ± 0.08 mm</b> |                                 |                            |   |                   |     |                        |                   |     |
| 1.2  | 9.0 x 19.0 x 31.5               | 6.1                        | 90172                                       | 90173             | 100 |                        |                   |     |
| 1.5  |                                 |                            | 90092                                       | 90093             |     |                        |                   |     |
| 1.8  | 9.0 x 21.0 x 31.0               | 8.2                        | 90102                                       | 90103             | 100 |                        |                   |     |
| 2.2  |                                 |                            | 90112                                       | 90113             |     |                        |                   |     |

**Notes**

• SPQ = Standard Packing Quantity

(1) Reel diameter = 356 mm is available on request

(2) H = in-tape height; P<sub>0</sub> = Sprocket hole distance; for detailed specifications refer to "Packaging Information"

(3) Weight for short lead product only



# MKT371, MKT372, MKT373

DC Film Capacitors  
MKT Radial Potted Type

Vishay BCcomponents

$U_{RDC} = 400\text{ V}$ ;  $U_{RAC} = 220\text{ V}$  (standard size)

| C<br>( $\mu\text{F}$ )   | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 373 XXYYY AND PACKAGING |                       |                 |  |                                 | C-VALUE<br>..YYY |
|--|---------------------------------|----------------------------|---|-----------------------|-----------------|--|---------------------------------|------------------|
|  |                                 |                            | LOOSE IN BOX                                |                       |                 | REEL <sup>(1)(2)</sup>                           |                                 |                  |
|  |                                 |                            | $l_t = 5.0\text{ mm} \pm 1.0\text{ mm}$     |                       |                 | $H = 18.5\text{ mm}$ ;<br>$P_0 = 12.7\text{ mm}$ |                                 |                  |
|  |                                 |                            | C-tol. =<br>$\pm 10\%$                      | C-tol. =<br>$\pm 5\%$ | SPQ             | C-tol. =<br>$\pm 10\%$                           | C-tol. =<br>$\pm 5\%$           |                  |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.60\text{ mm} \pm 0.06\text{ mm}</math></b> |                                 |                            |   |                       |                 |  |                                 |                  |
| 0.047<br>0.056<br>0.068<br>0.082<br>0.1  | 5.0 x 11.0 x 17.5               | 1.1                        | 51...<br>(1000)                             | 52...<br>(1000)       | 55...<br>(1100) | 56...<br>(1100)                                  | 473<br>563<br>683<br>823<br>104 |                  |
| 0.12<br>0.15   | 6.0 x 12.0 x 17.5               | 1.5                        | 51...<br>(1000)                             | 52...<br>(1000)       | 55...<br>(900)  | 56...<br>(900)                                   | 124<br>154                      |                  |
| <b>Pitch = 15.0 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b> |                                 |                            |   |                       |                 |  |                                 |                  |
| 0.18<br>0.22   | 7.0 x 13.5 x 17.5               | 2.0                        | 51...<br>(1000)                             | 52...<br>(1000)       | 55...<br>(800)  | 56...<br>(800)                                   | 184<br>224                      |                  |
| 0.27<br>0.33   | 8.5 x 15.0 x 17.5               | 2.7                        | 51...<br>(1000)                             | 52...<br>(1000)       | 55...<br>(650)  | 56...<br>(650)                                   | 274<br>334                      |                  |
| <b>Pitch = 22.5 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b> |                                 |                            |   |                       |                 |  |                                 |                  |
| 0.39<br>0.47   | 8.5 x 18.0 x 26.0               | 4.5                        | 51...<br>(200)                              | 52...<br>(200)        | 55...<br>(450)  | 56...<br>(450)                                   | 394<br>474                      |                  |
| 0.56<br>0.68   | 10.0 x 19.5 x 26.0              | 5.7                        | 51...<br>(200)                              | 52...<br>(200)        | 55...<br>(350)  | 56...<br>(350)                                   | 564<br>684                      |                  |
| <b>Pitch = 27.5 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b> |                                 |                            |   |                       |                 |  |                                 |                  |
| 0.82<br>1  | 13.0 x 23.0 x 31.0              | 10.2                       | 51...<br>(100)                              | 52...<br>(100)        | -               | -  | 824<br>105                      |                  |
| 1.2<br>1.5   | 15.0 x 25.0 x 31.5              | 13.4                       | 51...<br>(100)                              | 52...<br>(100)        | -               | -  | 125<br>155                      |                  |

**Notes**

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- (2) H = in-tape height;  $P_0$  = Sprocket hole distance; for detailed specifications refer to "Packaging Information"
- (3) Weight for short lead product only

**Available on request**

| C<br>( $\mu\text{F}$ )   | DIMENSIONS<br>w x h x l<br>(mm) | MASS<br>(g) <sup>(3)</sup> | CATALOG NUMBER BFC2 373 XXYYY AND PACKAGING |                       |     |                        |                       |     |
|--|---------------------------------|----------------------------|---|-----------------------|-----|------------------------|-----------------------|-----|
|  |                                 |                            | LOOSE IN BOX                                |                       |     | REEL <sup>(1)(2)</sup> |                       |     |
|  |                                 |                            | $l_t = 5.0\text{ mm} \pm 1.0\text{ mm}$     |                       |     | $H = 18.5\text{ mm}$   |                       |     |
|  |                                 |                            | C-tol. =<br>$\pm 10\%$                      | C-tol. =<br>$\pm 5\%$ | SPQ | C-tol. =<br>$\pm 10\%$ | C-tol. =<br>$\pm 5\%$ | SPQ |
| <b>Pitch = 22.5 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b> |                                 |                            |   |                       |     |                        |                       |     |
| 0.22   | 6.0 x 15.5 x 26.0               | 2.7                        | 90122                                       | 90123                 | 300 | 90128                  | 90129                 | 600 |
| 0.27<br>0.33   | 7.0 x 16.5 x 26.0               | 3.3                        | 90132<br>90142                              | 90133<br>90143        | 200 | 90138<br>90148         | 90139<br>90149        | 550 |
| <b>Pitch = 27.5 mm <math>\pm</math> 0.4 mm; <math>d_t = 0.80\text{ mm} \pm 0.08\text{ mm}</math></b> |                                 |                            |   |                       |     |                        |                       |     |
| 0.68   | 9.0 x 19.0 x 31.5               | 6.1                        | 90152                                       | 90153                 | 100 | -                      | -                     | -   |

**Notes**

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- (2) H = in-tape height;  $P_0$  = Sprocket hole distance; for detailed specifications refer to "Packaging Information"
- (3) Weight for short lead product only

## MOUNTING

### Normal Use

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoliers are designed for mounting in printed-circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to packaging information: [www.vishay.com/doc?28139](http://www.vishay.com/doc?28139)

### Specific Method of Mounting to Withstand Vibration and Shock

In order to withstand vibration and shock tests, it must be ensured that stand-off pips are in good contact with the printed-circuit board:


- For pitches  $\leq 15$  mm capacitors shall be mechanically fixed by the leads
- For larger pitches the capacitors shall be mounted in the same way and the body clamped

### Space Requirements On Printed-Circuit Board

The maximum space for length ( $l_{max.}$ ), width ( $W_{max.}$ ) and height ( $h_{max.}$ ) of film capacitors to take in account on the printed-circuit board is shown in the drawing:

- For products with pitch  $\leq 15$  mm,  $\Delta w = \Delta l = 0.3$  mm and  $\Delta h = 0.1$  mm
- For products with  $15$  mm  $<$  pitch  $\leq 27.5$  mm,  $\Delta w = \Delta l = 0.5$  mm and  $\Delta h = 0.1$  mm

Eccentricity defined as in drawing. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.



## SOLDERING

For general soldering conditions and wave soldering profile, we refer to the application note:

“Soldering Guidelines for Film Capacitors”: [www.vishay.com/doc?28171](http://www.vishay.com/doc?28171)

### Storage Temperature

- Storage temperature:  $T_{stg} = -25$  °C to  $+40$  °C with RH maximum 80 % without condensation

### Ratings and Characteristics Reference Conditions


Unless otherwise specified, all electrical values apply to an ambient free air temperature of  $23$  °C  $\pm 1$  °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of  $50$  %  $\pm 2$  %.

For reference testing, a conditioning period shall be applied over  $96$  h  $\pm 4$  h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.




### CHARACTERISTICS


371, 372, 373 - Capacitance as a function of frequency




371 - Capacitance as a function of ambient temperature




372, 373 - Capacitance as a function of ambient temperature




371, 372, 373 - Max. DC and AC Voltage as a function of temperature



371 - Impedance as a function of frequency




372 - Impedance as a function of frequency







373 - Impedance as a function of frequency




371 - Max. AC voltage as a function of frequency




371 - Max. AC voltage as a function of frequency



371 - Max. AC voltage as a function of frequency




371 - Max. AC voltage as a function of frequency







371 - Max. AC voltage as a function of frequency




371 - Max. AC voltage as a function of frequency




371 - Max. AC voltage as a function of frequency




371 - Max. AC voltage as a function of frequency




372 - Max. AC voltage as a function of frequency




372 - Max. AC voltage as a function of frequency




372 - Max. AC voltage as a function of frequency




372 - AC voltage as a function of frequency




372 - AC voltage as a function of frequency




372 - AC voltage as a function of frequency



372 - AC voltage as a function of frequency




372 - AC voltage as a function of frequency







373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency



373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency






373 - Max. AC voltage as a function of frequency




373 - Max. AC voltage as a function of frequency




**Maximum RMS current (sinewave) as a function of frequency**

$U_{AC}$  is the maximum AC voltage depending on the ambient temperature in the curves "Max. RMS voltage and AC current as a function of frequency".


371, 372, 373 - Tangent of loss angle as a function of frequency



371, 372, 373 - Insulation resistance as a function of the ambient temperature (typical curve)



371, 372, 373 - Maximum allowed component temperature rise ( $\Delta T$ ) as a function of the ambient temperature  $T_{amb}$  (°C)



**HEAT CONDUCTIVITY (G) AS A FUNCTION OF (ORIGINAL) PITCH AND CAPACITOR BODY THICKNESS IN mW/°C**

| W <sub>max.</sub><br>(mm) | HEAT CONDUCTIVITY (mW/°C) |               |               |               |               |
|---------------------------|---------------------------|---------------|---------------|---------------|---------------|
|                           | PITCH 7.62 mm             | PITCH 10.0 mm | PITCH 15.0 mm | PITCH 22.5 mm | PITCH 27.5 mm |
| 2.5                       | 3                         | -             | -             | -             | -             |
| 3.0                       | 4                         | -             | -             | -             | -             |
| 3.5                       | -                         | -             | -             | -             | -             |
| 4.0                       | 5                         | 6.0           | -             | -             | -             |
| 4.5                       | -                         | -             | -             | -             | -             |
| 5.0                       | 6                         | 7.5           | 10            | -             | -             |
| 6.0                       | 7                         | 9.0           | 11            | 19            | -             |
| 7.0                       | -                         | -             | 12            | 21            | -             |
| 8.5                       | -                         | -             | 16            | 25            | -             |
| 10.0                      | -                         | -             | 18            | 28            | -             |
| 11.0                      | -                         | -             | -             | -             | 36            |
| 13.0                      | -                         | -             | -             | -             | 42            |
| 15.0                      | -                         | -             | -             | -             | 48            |
| 18.0                      | -                         | -             | -             | -             | 57            |

**POWER DISSIPATION AND MAXIMUM COMPONENT TEMPERATURE RISE**

The power dissipation must be limited in order not to exceed the maximum allowed component temperature rise as a function of the free ambient temperature.


The power dissipation can be calculated according type detail specification “HQN-384-01/101: Technical Information Film Capacitors”.

The component temperature rise ( $\Delta T$ ) can be measured (see section “Measuring the component temperature” for more details) or calculated by  $\Delta T = P/G$ :

- $\Delta T$  = Component temperature rise (°C)
- P = Power dissipation of the component (mW)
- G = Heat conductivity of the component (mW/°C)

**MEASURING THE COMPONENT TEMPERATURE**

A thermocouple must be attached to the capacitor body as in:



The temperature is measured in unloaded ( $T_{amb}$ ) and maximum loaded condition ( $T_C$ ).

The temperature rise is given by  $\Delta T = T_C - T_{amb}$ .

To avoid radiation or convection, the capacitor should be tested in a wind-free box.



### APPLICATION NOTE AND LIMITING CONDITIONS

These capacitors are not suitable for mains applications as across-the-line capacitors without additional protection, as described hereunder. These mains applications are strictly regulated in safety standards and therefore electromagnetic interference suppression capacitors conforming the standards must be used.

For capacitors connected in parallel, normally the proof voltage and possibly the rated voltage must be reduced. For information depending of the capacitance value and the number of parallel connections contact: [dc-film@vishay.com](mailto:dc-film@vishay.com)

To select the capacitor for a certain application, the following conditions must be checked:

1. The peak voltage ( $U_P$ ) shall not be greater than the rated DC voltage ( $U_{RDC}$ )
2. The peak-to-peak voltage ( $U_{P-P}$ ) shall not be greater than  $2\sqrt{2} \times U_{RAC}$  to avoid the ionisation inception level
3. The voltage peak slope ( $dU/dt$ ) shall not exceed the rated voltage pulse slope in an RC-circuit at rated voltage and without ringing. If the pulse voltage is lower than the rated DC voltage, the rated voltage pulse slope may be multiplied by  $U_{Rdc}$  and divided by the applied voltage.

For all other pulses following equation must be fulfilled:

$$2 \times \int_0^T \left(\frac{dU}{dt}\right)^2 \times dt < U_{Rdc} \times \left(\frac{dU}{dt}\right)_{rated}$$

T is the pulse duration.

4. The maximum component surface temperature rise must be lower than the limits (see graph Max. Allowed Component Temperature Rise).
5. Since in circuits used at voltages over 280 V peak-to-peak the risk for an intrinsically active flammability after a capacitor breakdown (short circuit) increases, it is recommended that the power to the component is limited to 100 times the values mentioned in the table: "Heat Conductivity"
6. When using these capacitors as across-the-line capacitor in the input filter for mains applications or as series connected with an impedance to the mains the applicant must guarantee that the following conditions are fulfilled in any case (spikes and surge voltages from the mains included).

#### Voltage Conditions for 6 Above

| ALLOWED VOLTAGES                             | $T_{amb} \leq 85 \text{ }^\circ\text{C}$ | $85 \text{ }^\circ\text{C} < T_{amb} \leq 105 \text{ }^\circ\text{C}$ |
|--|--|---|
| Maximum continuous RMS voltage               | $U_{RAC}$                                | See "Max. AC Voltage as Function of Temperature" per characteristics  |
| Maximum temperature RMS-overvoltage (< 24 h) | $1.25 \times U_{RAC}$                    | $U_{RAC}$   |
| Maximum peak voltage ( $V_{O-P}$ ) (< 2 s)   | $1.6 \times U_{RDC}$                     | $1.3 \times U_{RDC}$  |

#### EXAMPLE

C = 330 nF - 63 V used for the voltage signal shown in next drawing.

$U_{P-P} = 40 \text{ V}$ ;  $U_P = 35 \text{ V}$ ;  $T_1 = 100 \text{ } \mu\text{s}$ ;  $T_2 = 200 \text{ } \mu\text{s}$


The ambient temperature is  $35 \text{ }^\circ\text{C}$

Checking conditions:

1. The peak voltage  $U_P = 35 \text{ V}$  is lower than  $63 \text{ V}_{DC}$
2. The peak-to-peak voltage  $40 \text{ V}$  is lower than  $2\sqrt{2} \times 40 \text{ V}_{AC} = 113 \text{ V}_{P-P}$
3. The voltage pulse slope ( $dU/dt$ ) =  $40 \text{ V}/100 \text{ } \mu\text{s} = 0.4 \text{ V}/\mu\text{s}$   
This is lower than  $60 \text{ V}/\mu\text{s}$  (see specific reference data for each version)
4. The dissipated power is  $16.2 \text{ mW}$  as calculated with fourier terms  
The temperature rise for  $W_{max.} = 3.5 \text{ mm}$  and pitch =  $5 \text{ mm}$  will be  $16.2 \text{ mW}/3.0 \text{ mW}/^\circ\text{C} = 5.4 \text{ }^\circ\text{C}$   
This is lower than  $15 \text{ }^\circ\text{C}$  temperature rise at  $35 \text{ }^\circ\text{C}$ , according figure max. allowed component temperature rise
5. Not applicable
6. Not applicable



## Voltage Signal



## INSPECTION REQUIREMENTS

### General Notes:

1. Sub-clause numbers of tests and performance requirements refer to the "Sectional Specification, Publication IEC 60384-2 and Specific Reference Data".

### Group C Inspection Requirements

| SUB-CLAUSE NUMBER AND TEST                          | CONDITIONS   | PERFORMANCE REQUIREMENTS  |
|---|--|---|
| <b>SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1</b> |  |   |
| 4.1 Dimensions (detail)                             |  | As specified in chapters "General Data" of this specification   |
| 4.3.1 Initial measurements                          | Capacitance<br>Tangent of loss angle:<br>For $C \leq 470$ nF at 100 kHz<br>for $470$ nF < $C \leq 10$ $\mu$ F at 10 kHz<br>for $C > 10$ $\mu$ F at 1 kHz |   |
| 4.3 Robustness of terminations                      | Tensile and bending  | No visible damage   |
| 4.4 Resistance to soldering heat                    | Method: 1A<br>Solder bath: $280$ °C $\pm$ $5$ °C<br>Duration: 10 s   |   |
| 4.14 Component solvent resistance                   | Isopropylalcohol at room temperature<br>Method: 2<br>Immersion time: 5 min $\pm$ 0.5 min<br>Recovery time: Min. 1 h, max. 2 h                            |   |
| 4.4.2 Final measurements                            | Visual examination<br><br>Capacitance<br><br>Tangent of loss angle   | No visible damage<br>Legible marking<br><br>$ \Delta C/C  \leq 2\%$ of the value measured initially<br><br>Increase of $\tan \delta$<br>$\leq 0.005$ for: $C \leq 100$ nF or<br>$\leq 0.010$ for: $100$ nF < $C \leq 220$ nF or<br>$\leq 0.015$ for: $220$ nF < $C \leq 470$ nF and<br>$\leq 0.003$ for: $C > 470$ nF<br>Compared to values measured in 4.3.1 |



| SUB-CLAUSE NUMBER AND TEST   | CONDITIONS  | PERFORMANCE REQUIREMENTS   |
|--|---|--|
| <b>SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1</b>                        |   |  |
| 4.6.1 Initial measurements   | Capacitance<br>Tangent of loss angle:<br>For $C \leq 470$ nF at 100 kHz<br>for $470$ nF < $C \leq 10$ $\mu$ F at 10 kHz<br>for $C > 10$ $\mu$ F at 1 kHz  | No visible damage  |
| 4.6 Rapid change of temperature  | $\theta A = -55$ °C<br>$\theta B = +105$ °C<br>5 cycles<br>Duration $t = 30$ min  |  |
| 4.7 Vibration  | Visual examination<br>Mounting:<br>See section "Mounting" of this specification<br>Procedure B4<br>Frequency range: 10 Hz to 55 Hz<br>Amplitude: 0.75 mm or<br>Acceleration 98 m/s <sup>2</sup><br>(whichever is less severe)<br>Total duration 6 h | No visible damage  |
| 4.7.2 Final inspection   | Visual examination  | No visible damage  |
| 4.9 Shock  | Mounting:<br>See section "Mounting" of this specification<br>Pulse shape: Half sine<br>Acceleration: 490 m/s <sup>2</sup><br>Duration of pulse: 11 ms   |  |
| 4.9.3 Final measurements   | Visual examination<br>Capacitance<br>Tangent of loss angle<br><br>Insulation resistance   | No visible damage<br>$ \Delta C/C  \leq 3$ % of the value measured in 4.6.1<br>Increase of $\tan \delta$<br>$\leq 0.010$ (370 and 371)<br>$\leq 0.005$ (372 and 373) for: $C \leq 100$ nF or<br>$\leq 0.010$ for: $100$ nF < $C \leq 220$ nF or<br>$\leq 0.015$ for: $220$ nF < $C \leq 470$ nF and<br>$\leq 0.003$ for: $C > 470$ nF<br>Compared to values measured in 4.6.1<br>As specified in section "Insulation Resistance" of this specification   |
| <b>SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B</b> |   |  |
| 4.10 Climatic sequence   |   |  |
| 4.10.2 Dry heat  | Temperature: + 105 °C<br>Duration: 16 h   |  |
| 4.10.3 Damp heat cyclic<br>Test Db, first cycle                            |   |  |
| 4.10.4 Cold  | Temperature: - 55 °C<br>Duration: 2 h   |  |
| 4.10.6 Damp heat cyclic<br>Test Db, remaining cycles                       |   |  |
| 4.10.6.2 Final measurements  | Voltage proof = $U_{RDC}$ for 1 min within 15 min after removal from test chamber<br>Visual examination<br><br>Capacitance<br><br>Tangent of loss angle<br><br>Insulation resistance  | No breakdown of flash-over<br><br>No visible damage<br>Legible marking<br>$ \Delta C/C  \leq 3$ % of the value measured in 4.4.2 or 4.9.3<br>Increase of $\tan \delta$<br>$\leq 0.010$ (370 and 371)<br>$\leq 0.005$ (372 and 373) for: $C \leq 100$ nF or<br>$\leq 0.010$ for: $100$ nF < $C \leq 220$ nF or<br>$\leq 0.015$ for: $220$ nF < $C \leq 470$ nF and<br>$\leq 0.005$ for: $C > 470$ nF<br>Compared to values measured in 4.3.1 or 4.6.1<br>$\geq 50$ % of values specified in section "Insulation Resistance" of this specification |

| SUB-CLAUSE NUMBER AND TEST  | CONDITIONS   | PERFORMANCE REQUIREMENTS  |
|---|--|---|
| <b>SUB-GROUP C2</b>   |  |   |
| 4.11 Damp heat steady state<br>4.11.1 Initial measurements<br>4.11.3 Final measurements | 56 days, 40 °C, 90 % to 95 % RH<br>Capacitance<br>Tangent of loss angle at 1 kHz<br>Voltage proof = $U_{RDC}$ for 1 min within 15 min after removal from testchamber<br>Visual examination<br><br>Capacitance<br>Tangent of loss angle<br>Insulation resistance  | No breakdown of flash-over<br><br>No visible damage<br>Legible marking<br>$ \Delta C/C  \leq 5\%$ of the value measured in 4.11.1.<br>Increase of $\tan \delta \leq 0.005$<br>Compared to values measured in 4.11.1<br>$\geq 50\%$ of values specified in section "Insulation Resistance" of this specification   |
| <b>SUB GROUP C3</b>   |  |   |
| 4.12 Endurance<br>4.12.1 Initial measurements<br>4.12.5 Final measurements              | Duration: 2000 h<br>1.25 x $U_{RDC}$ at 85 °C<br>0.8 x 1.25 $U_{RDC}$ at 105 °C<br>Capacitance<br>Tangent of loss angle:<br>For $C \leq 470$ nF at 100 kHz<br>for $470$ nF < $C \leq 10$ $\mu$ F at 10 kHz<br>for $C > 10$ $\mu$ F at 1 kHz<br>Visual examination<br><br>Capacitance<br>Tangent of loss angle<br><br>Insulation resistance         | No visible damage<br>Legible marking<br>$ \Delta C/C  \leq 5\%$ compared to values measured in 4.12.1<br>Increase of $\tan \delta$<br>$\leq 0.005$ at 85 °C (370 and 371)<br>$\leq 0.010$ at 100 °C (370 and 371)<br>$\leq 0.005$ (372 and 373) for: $C \leq 100$ nF or<br>$\leq 0.010$ for: $100$ nF < $C \leq 220$ nF or<br>$\leq 0.015$ for: $220$ nF < $C \leq 470$ nF and<br>$\leq 0.003$ for: $C > 470$ nF<br>Compared to values measured in 4.12.1<br>$\geq 50\%$ of values specified in section "Insulation Resistance" of this specification |
| <b>SUB-GROUP C4</b>   |  |   |
| 4.13 Charge and discharge<br>4.13.1 Initial measurements<br>4.13.3 Final measurements   | 10 000 cycles<br>Charged to $U_{RDC}$<br>Discharge resistance:<br>$R = \frac{U_R}{C \times 2.5 \times (dU/dt)_R}$<br>Capacitance<br>Tangent of loss angle:<br>For $C \leq 470$ nF at 100 kHz<br>for $470$ nF < $C \leq 10$ $\mu$ F at 10 kHz<br>for $C > 10$ $\mu$ F at 1 kHz<br>Capacitance<br>Tangent of loss angle<br><br>Insulation resistance | $ \Delta C/C  \leq 3\%$ compared to values measured in 4.13.1<br>Increase of $\tan \delta$<br>$\leq 0.005$ for: $C \leq 100$ nF or<br>$\leq 0.010$ for: $100$ nF < $C \leq 220$ nF or<br>$\leq 0.015$ for: $220$ nF < $C \leq 470$ nF and<br>$\leq 0.003$ for: $C > 470$ nF<br>Compared to values measured in 4.13.1<br>$\geq 50\%$ of values specified in section "Insulation Resistance" of this specification  |



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**