

Octal channel high-side driver

Datasheet - production data



- Protection against loss of ground
- Very low standby current
- Compliance to 61000-4-4 IEC test up to 4 kV

Description


The VN808-32-E is a monolithic device designed in STMicroelectronics VIPower M0-3 technology, intended to drive any kind of load with one side connected to ground. Active current limitation combined with thermal shutdown and automatic restart, protect the device against overload. In overload condition, the channel turns off and on again automatically so to maintain the junction temperature between T_{TSD} and T_R . If this condition makes case temperature reach T_{CSD} , overloaded channels are turned off and restart only when the case temperature decreases down to T_{CR} . Non-overloaded channels continue to operate normally. Device automatically turns off in case of ground pin disconnection. This device is especially suitable for industrial applications conform to IEC 61131.

Features

| Type | $R_{DS(on)}$ | I_{out} | V_{CC} |
|------------|----------------|-----------|----------|
| VN808-32-E | 150 m Ω | 1 A | 45 V |

- $V_{CC}/2$ compatible input
- Junction overtemperature protection
- Case overtemperature protection for thermal independence of the channels
- Current limitation
- Shorted load protection
- Undervoltage shutdown

Figure 1. Internal schematic



Contents

| | | |
|----------|--|-----------|
| 1 | Maximum ratings | 3 |
| 2 | Electrical characteristics | 4 |
| 3 | Pin connections | 6 |
| 4 | Current, voltage conventions and internal diagram | 8 |
| 5 | Switching time waveforms | 10 |
| 6 | Reverse polarity protection | 13 |
| 7 | Package mechanical data | 14 |
| | 7.1 Footprint recommended data | 16 |
| | 7.2 Tube shipment information | 17 |
| | 7.3 Tape and reel shipment information | 18 |
| 8 | Ordering information | 20 |
| 9 | Revision history | 21 |

1 Maximum ratings

Table 1. Absolute maximum ratings

| Symbol | Parameter | Value | Unit |
|------------|---|--------------------|------------------|
| V_{CC} | DC supply voltage | 45 | V |
| $-I_{GND}$ | DC ground pin reverse current TRAN ground pin reverse current (pulse duration < 1 ms) | -250 -6 | mA A |
| I_{OUT} | DC output current | Internally limited | A |
| $-I_{OUT}$ | Reverse DC output current | -2 | A |
| I_{IN} | DC Input current | ± 10 | mA |
| V_{IN} | Input voltage range | $-3/+V_{CC}$ | V |
| V_{ESD} | Electrostatic discharge (R = 1.5 k Ω ; C = 100 pF) | 2000 | V |
| P_{TOT} | Power dissipation at $T_C = 25\text{ }^\circ\text{C}$ | 96 | W |
| L_{MAX} | Max. inductive load ($V_{CC} = 24\text{ V}$, $R_{LOAD} = 48\text{ }\Omega$, $T_A = 100\text{ }^\circ\text{C}$) | 2 | H |
| T_J | Junction operating temperature | Internally limited | $^\circ\text{C}$ |
| T_C | Case operating temperature | Internally limited | $^\circ\text{C}$ |
| T_{STG} | Storage temperature | -40 to 150 | $^\circ\text{C}$ |

Table 2. Thermal data

| Symbol | Parameter | Value | Unit |
|--------------|--|----------|--------------------|
| $R_{th(JC)}$ | Thermal resistance junction-case | Max. 1.3 | $^\circ\text{C/W}$ |
| $R_{th(JA)}$ | Thermal resistance junction-ambient ⁽¹⁾ | Max. 50 | $^\circ\text{C/W}$ |

1. When mounted on FR4 printed circuit board with 0.5 cm² of copper area (at least 35 μm thick) connected to all TAB pins.

2 Electrical characteristics

($10.5\text{ V} < V_{CC} < 32\text{ V}$; $-40\text{ °C} < T_J < 125\text{ °C}$; unless otherwise specified)

Table 3. Power section

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|-----------------|---|---|------|------|------------|----------|
| V_{CC} | Operating supply voltage | | 10.5 | | 45 | V |
| V_{USD} | Undervoltage shutdown | | 7 | | 10.5 | V |
| R_{ON} | On state resistance | $I_{OUT} = 0.5\text{ A}$; $T_J = 25\text{ °C}$ $I_{OUT} = 0.5\text{ A}$ | | 150 | 185 280 | mΩ mΩ |
| I_S | Supply current | OFF state; $V_{CC} = 24\text{ V}$ $T_{CASE} = 25\text{ °C}$ ON state (all channels ON) $V_{CC} = 24\text{ V}$, $T_{CASE} = 100\text{ °C}$ | | | 150 12 | μA mA |
| I_{LGND} | Output current at turn-off | $V_{CC} = V_{STAT} = V_{IN} = V_{GND} = 24\text{ V}$ $V_{OUT} = 0\text{ V}$ | | | 1 | mA |
| $I_{L(off)}$ | OFF state output current | $V_{IN} = V_{OUT} = 0\text{ V}$ | 0 | | 5 | μA |
| $V_{OUT(off)}$ | OFF state output voltage | $V_{IN} = 0\text{ V}$, $I_{OUT} = 0\text{ A}$ | | | 3 | V |
| $t_d(V_{CCon})$ | Power-on delay time from V_{CC} rising edge | see Figure 7 | | 1 | | ms |

Table 4. Switching ($V_{CC} = 24\text{ V}$)

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|--------------------|------------------------|---|------|------|------|------|
| t_{ON} | Turn-on time | $R_L = 48\text{ Ω}$ from 80% V_{OUT} (see Figure 6) | | 50 | 100 | μs |
| t_{OFF} | Turn-off time | $R_L = 48\text{ Ω}$ to 10% V_{OUT} (see Figure 6) | | 75 | 150 | μs |
| $dV_{OUT}/dt(on)$ | Turn-on voltage slope | $R_L = 48\text{ Ω}$ from $V_{OUT} = 2.4\text{ V}$ to $V_{OUT} = 19.2\text{ V}$ (see Figure 6) | | 0.7 | | V/μs |
| $dV_{OUT}/dt(off)$ | Turn-off voltage slope | $R_L = 48\text{ Ω}$ from $V_{OUT} = 21.6\text{ V}$ to $V_{OUT} = 2.4\text{ V}$ (see Figure 6) | | 1.5 | | V/μs |

Table 5. Input pin

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|---------------|--------------------------|-------------------------------------|--------------|------|--------------|---------------|
| V_{INL} | Input low level | | | | $V_{CC}/2-1$ | V |
| I_{INL} | Low level input current | $V_{IN} = V_{CC} / 2 - 1 \text{ V}$ | 80 | | 650 | μA |
| V_{INH} | Input high level | | $V_{CC}/2+1$ | | | V |
| I_{INH} | High level input current | $V_{IN} = V_{CC} / 2 + 1 \text{ V}$ | | 150 | 260 | μA |
| $V_{I(HYST)}$ | Input hysteresis voltage | | | 0.6 | | V |
| I_{IN} | Input current | $V_{IN} = V_{CC} = 32 \text{ V}$ | | | 300 | μA |

Table 6. Protection

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|-------------|-------------------------------|--|-------------|-------------|-------------|--------------------|
| T_{CSD} | Case shutdown temperature | | 125 | 130 | 135 | $^{\circ}\text{C}$ |
| T_{CR} | Case reset temperature | | 110 | | | $^{\circ}\text{C}$ |
| T_{CHYST} | Case thermal hysteresis | | 7 | 15 | | $^{\circ}\text{C}$ |
| T_{TSD} | Junction shutdown temperature | | 150 | 175 | 200 | $^{\circ}\text{C}$ |
| T_R | Junction reset temperature | | 135 | | | $^{\circ}\text{C}$ |
| T_{HYST} | Junction thermal hysteresis | | 7 | 15 | | $^{\circ}\text{C}$ |
| I_{lim} | DC short-circuit current | $V_{CC} = 24 \text{ V}; R_{LOAD} = 10 \text{ m}\Omega$ | 1 | | 1.7 | A |
| V_{demag} | Turn-off output clamp voltage | $I_{OUT} = 0.5 \text{ A}; L = 6 \text{ mH}$ | $V_{CC}-57$ | $V_{CC}-52$ | $V_{CC}-47$ | V |

Table 7. Status pin

| Symbol | Parameter | Test conditions | Min. | Typ. | Max. | Unit |
|--------------|---------------------------|---|------|-------------|------|---------------|
| I_{HSTAT} | High level output current | $V_{CC} = 18...32 \text{ V}; R_{STAT} = 1 \text{ k}\Omega$ (fault condition) | 2 | 3 | 4 | mA |
| I_{LSTAT} | Leakage current | Normal operation; $V_{CC} = 32 \text{ V}$ | | | 0.1 | μA |
| V_{CLSTAT} | Clamp voltage | $I_{STAT} = 1 \text{ mA}$ $I_{STAT} = -1 \text{ mA}$ | 6.0 | 6.8 -0.7 | 8.0 | V V |

3 Pin connections

Figure 2. Connection diagram (top view)



Table 8. Pin functions

| Pin N° | Symbol | Function |
|----------------|-----------------|---|
| TAB | V _{CC} | Positive power supply voltage |
| 1 | V _{CC} | Positive power supply voltage |
| 2,3,4,5 | NC | Not connected |
| 6 | Input 1 | Input of channel 1 |
| 7 | Input 2 | Input of channel 2 |
| 8 | Input 3 | Input of channel 3 |
| 9 | Input 4 | Input of channel 4 |
| 10 | Input 5 | Input of channel 5 |
| 11 | Input 6 | Input of channel 6 |
| 12 | Input 7 | Input of channel 7 |
| 13 | Input 8 | Input of channel 8 |
| 14,15,16,17,18 | NC | Not connected |
| 19 | GND | Logic ground |
| 20 | STATUS | Common open source diagnostic for overtemperature |
| 21,22 | Output 8 | High-side output of channel 8 |
| 23,24 | Output 7 | High-side output of channel 7 |
| 25,26 | Output 6 | High-side output of channel 6 |

Table 8. Pin functions (continued)

| Pin N° | Symbol | Function |
|--------|----------|-------------------------------|
| 27,28 | Output 5 | High-side output of channel 5 |
| 29,30 | Output 4 | High-side output of channel 4 |
| 31,32 | Output 3 | High-side output of channel 3 |
| 33,34 | Output 2 | High-side output of channel 2 |
| 35,36 | Output 1 | High-side output of channel 1 |

4 Current, voltage conventions and internal diagram

Figure 3. Current and voltage conventions




Figure 4. Equivalent internal block diagram (same structure for all channels)




Figure 5. Application example




Table 9. Truth table

| Conditions | INPUTn | OUTPUTn | STATUS |
|--|--------|---------|--------|
| Normal operation | L | L | L |
| | H | H | L |
| Current limitation | L | L | L |
| | H | X | L |
| Overtemperature (see waveforms 3, 4 Figure 8) -> $T_J > T_{TSD}$ | L | L | L |
| | H | L | H |
| Undervoltage | L | L | X |
| | H | L | X |

5 Switching time waveforms

Figure 6. Turn-on and turn-off




Figure 7. V_{CC} turn-on




Figure 8. Waveforms





Figure 9. Waveforms (continued)



6 Reverse polarity protection

This schematic can be used with any type of load.

The following is an indication on how to dimension the R_{GND} resistor.

$$R_{GND} = (-V_{CC}) / (-I_{GND})$$


where $-I_{GND}$ is the DC reverse ground pin current and can be found in [Section 1: Maximum ratings](#) of this datasheet.

Power dissipation in R_{GND} (when $V_{CC} < 0$: during reverse polarity situations) is:

$$PD = (-V_{CC})^2 / R_{GND}$$

Note: In normal condition (no reverse polarity) due to the diode there is a voltage drop between GND of the device and GND of the system.

Figure 10. Reverse polarity protection




7 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

Table 10. PowerSO-36 mechanical data

| Dim. | mm | | |
|--------|-------|-------|-------|
| | Min. | Typ. | Max. |
| A | | | 3.60 |
| a1 | 0.10 | | 0.30 |
| a2 | | | 3.30 |
| a3 | 0 | | 0.10 |
| b | 0.22 | | 0.38 |
| c | 0.23 | | 0.32 |
| D (1) | 15.80 | | 16.00 |
| D1 | 9.40 | | 9.80 |
| E | 13.90 | | 14.50 |
| E1 (1) | 10.90 | | 11.10 |
| E2 | | | 2.90 |
| E3 | 5.8 | | 6.2 |
| e | | 0.65 | |
| e3 | | 11.05 | |
| G | 0 | | 0.10 |
| H | 15.50 | | 15.90 |
| h | | | 1.10 |
| L | 0.80 | | 1.10 |
| N | | | 10° |
| S | 0° | | 8° |

Figure 11. PowerSO-36 drawings



7.1 Footprint recommended data

Figure 12. Footprint recommended data




Table 11. Footprint data

| Dim. | mm |
|------|-----------|
| A | 9.5 |
| B | 14.7-15.0 |
| C | 12.5-12.7 |
| D | 6.3 |
| E | 0.42 |
| G | 0.65 |

7.2 Tube shipment information

Figure 13. Tube shipment information




Table 12. Tube mechanical data

| Dim. | mm |
|------|------------|
| A | 18.80 |
| B | 17.2 ±0.2 |
| C | 8.20 ±0.2 |
| D | 10.90 ±0.2 |
| E | 2.90 ±0.2 |
| F | 0.40 |
| G | 0.80 |
| H | 6.30 |
| I | 4.30 ±0.2 |
| J | 3.7 ±0.2 |
| K | 9.4 |
| L | 0.40 |
| M | 0.80 |
| N | 3.50 ±0.2 |

Base quantity 31 pcs.

Bulk quantity 310 pcs.

7.3 Tape and reel shipment information

Figure 14. Tape specifications




Table 13. Tape mechanical data

| Dim. | mm |
|------------|----------------------|
| D | 1.50 +0.1/0 |
| E | 1.75 ±0.1 |
| Po | 4.00 ±0.1 |
| T max. | 0.40 |
| D1 min. | 1.50 |
| F | 11.5 ±0.05 |
| K max. | 6.50 |
| P2 | 2.00 ±0.1 |
| R | 50 |
| W | 24.00 ±0.30 |
| P1 | 24.00 |
| Ao, Bo, Ko | 0.05 min to 1.0 max. |

Base quantity 600 pcs.

Bulk quantity 600 pcs.

Figure 15. Reel specifications




Table 14. Reel mechanical data

| Dim. | mm |
|-----------|------------|
| Tape size | 24.0 ±0.30 |
| A max. | 330.0 |
| B min. | 1.5 |
| C | 13.0 ±0.20 |
| D min. | 20.2 |
| N min. | 60 |
| G | 24.4 +2/-0 |
| T max. | 30.4 |

8 Ordering information

Table 15. Order code

| Order code | Package | Packaging |
|-------------------|----------------|------------------|
| VN808-32-E | PowerSO-36 | Tube |
| VN808TR-32-E | PowerSO-36 | Tape and reel |

9 Revision history

Table 16. Document revision history

| Date | Revision | Changes |
|-------------|----------|---|
| 25-Jan-2008 | 1 | Initial release |
| 07-Jul-2008 | 2 | Added Section 6 on page 13 |
| 04-Aug-2008 | 3 | Added: Figure 12: Footprint recommended data |
| 25-Aug-2009 | 4 | Updated Section 6: Reverse polarity protection |
| 24-Feb-2010 | 5 | Updated Section 7: Package mechanical data |
| 07-Dec-2012 | 6 | Added max. value to I_{INL} parameter in Table 5 . Minor text changes. |
| 01-Jul-2013 | 7 | Updated Section 7.1: Footprint recommended data . |

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

ST PRODUCTS ARE NOT AUTHORIZED FOR USE IN WEAPONS. NOR ARE ST PRODUCTS DESIGNED OR AUTHORIZED FOR USE IN: (A) SAFETY CRITICAL APPLICATIONS SUCH AS LIFE SUPPORTING, ACTIVE IMPLANTED DEVICES OR SYSTEMS WITH PRODUCT FUNCTIONAL SAFETY REQUIREMENTS; (B) AERONAUTIC APPLICATIONS; (C) AUTOMOTIVE APPLICATIONS OR ENVIRONMENTS, AND/OR (D) AEROSPACE APPLICATIONS OR ENVIRONMENTS. WHERE ST PRODUCTS ARE NOT DESIGNED FOR SUCH USE, THE PURCHASER SHALL USE PRODUCTS AT PURCHASER'S SOLE RISK, EVEN IF ST HAS BEEN INFORMED IN WRITING OF SUCH USAGE, UNLESS A PRODUCT IS EXPRESSLY DESIGNATED BY ST AS BEING INTENDED FOR "AUTOMOTIVE, AUTOMOTIVE SAFETY OR MEDICAL" INDUSTRY DOMAINS ACCORDING TO ST PRODUCT DESIGN SPECIFICATIONS. PRODUCTS FORMALLY ESCC, QML OR JAN QUALIFIED ARE DEEMED SUITABLE FOR USE IN AEROSPACE BY THE CORRESPONDING GOVERNMENTAL AGENCY.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2013 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com