www.ti.com

SCES156H-DECEMBER 1998-REVISED SEPTEMBER 2008

### 16-BIT TRANSPARENT D-TYPE LATCH WITH 3-STATE OUTPUTS


#### **FEATURES**

- Member of the Texas Instruments Widebus™ Family
- EPIC<sup>™</sup> (Enhanced-Performance Implanted CMOS) Submicron Process
- DOC<sup>™</sup> (Dynamic Output Control) Circuit Dynamically Changes Output Impedance, Resulting in Noise Reduction Without Speed Degradation
- Dynamic Drive Capability Is Equivalent to Standard Outputs With I<sub>OH</sub> and I<sub>OL</sub> of ±24 mA at 2.5-V V<sub>CC</sub>

- Overvoltage-Tolerant Inputs/Outputs Allow Mixed-Voltage-Mode Data Communications
- I<sub>off</sub> Supports Partial-Power-Down Mode Operation
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- Package Options Include Plastic Thin Shrink Small-Outline (DGG) and Thin Very Small-Outline (DGV) Packages

### **DESCRIPTION**

A Dynamic Output Control (DOC<sup>TM</sup>) circuit is implemented, which, during the transition, initially lowers the output impedance to effectively drive the load and, subsequently, raises the impedance to reduce noise. Figure 1 shows typical  $V_{OL}$  vs  $I_{OL}$  and  $V_{OH}$  vs  $I_{OH}$  curves to illustrate the output impedance and drive capability of the circuit. At the beginning of the signal transition, the DOC circuit provides a maximum dynamic drive that is equivalent to a high-drive standard-output device. For more information, refer to the TI application reports, *AVC Logic Family Technology and Applications*, literature number SCEA006, and *Dynamic Output Control (DOC*<sup>TM</sup>) *Circuitry Technology and Applications*, literature number SCEA009.






Figure 1. Output Voltage vs Output Current

This 16-bit transparent D-type latch is operational at 1.2-V to 3.6-V  $V_{CC}$ , but is designed specifically for 1.65-V to 3.6-V  $V_{CC}$  operation.

The SN74AVC16373 is particularly suitable for implementing buffer registers, I/O ports, bidirectional bus drivers, and working registers. This device can be used as two 8-bit latches or one 16-bit latch. When the latch-enable (LE) input is high, the Q outputs follow the data (D) inputs. When LE is taken low, the Q outputs are latched at the levels set up at the D inputs.

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Widebus, EPIC, DOC are trademarks of Texas Instruments.



### **DESCRIPTION (CONTINUED)**

A buffered output-enable  $(\overline{OE})$  input can be used to place the eight outputs in either a normal logic state (high or low logic levels) or the high-impedance state. In the high-impedance state, the outputs neither load nor drive the bus lines significantly. The high-impedance state and the increased drive provide the capability to drive bus lines without need for interface or pullup components.  $\overline{OE}$  does not affect internal operations of the latch. Old data can be retained or new data can be entered while the outputs are in the high-impedance state.

To ensure the high-impedance state during power up or power down,  $\overline{OE}$  should be tied to  $V_{CC}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.

This device is fully specified for partial-power-down applications using I<sub>off</sub>. The I<sub>off</sub> circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.

The SN74AVC16373 is characterized for operation from -40°C to 85°C.

#### **TERMINAL ASSIGNMENTS**

#### DGG OR DGV PACKAGE (TOP VIEW) 10E [ 48 **∏** 1LE 1Q1 **[**] 2 47 ¶ 1D1 1Q2 **∏**3 46 1D2 GND 4 45 GND 1Q3 🛮 5 44 1 1D3 1Q4 [ 43 ¶ 1D4 6 $V_{CC}$ 42 V<sub>CC</sub> 1Q5 **∏**8 41 **1** 1D5 1Q6 **9** 40 1D6 39 [] GND GND 10 38 **∏** 1D7 107 ∏ 11 1Q8 12 37 ¶ 1D8 2Q1 Π 36 2D1 13 2Q2 **∏**14 35 T 2D2 GND II 15 34 **∏** GND 2Q3 **∏** 33 T 2D3 16 2Q4 **∏**17 32 T 2D4 Vcc [ 18 31 V<sub>CC</sub> 2Q5 **∏** 19 30 T 2D5 2Q6 ∏20 29 ¶ 2D6 GND ∏21 28 | GND 2Q7 **∏** 22 27 2D7 2Q8 **1**23 26 2D8 2<del>0E</del> **□** 25 1 2LE 24

### GQL/ZQL PACKAGE (TOP VIEW)

|   |          | 1          | 2  | 3  | 4  | 5  | 6          |    |
|---|----------|------------|----|----|----|----|------------|----|
| Α | /        | $\bigcirc$ | () | () | () | () | $\bigcirc$ | )  |
| В |          | ()         | () | () | () | () | ()         |    |
| С |          | ()         | () | () | () | () | ()         |    |
| D |          | ()         | () | () | () | () | ()         |    |
| Е |          | ()         | () |    |    | () | ()         | -  |
| F |          | ()         | () |    |    | () | ()         |    |
| G |          | ()         | () | () | () | () | ()         | -  |
| Н |          | ()         | () | () | () | () | ()         |    |
| J |          | ()         | () | () | () | () | ()         |    |
| K |          | ()         | () | () | () | () | ()         |    |
|   | <b>√</b> |            |    |    |    |    |            | _/ |

# TERMINAL ASSIGNMENTS (56-Ball GQL/ZQL Package)<sup>(1)</sup>

|   | 1    | 2   | 3         | 4         | 5   | 6               |
|---|------|-----|-----------|-----------|-----|-----------------|
| Α | 1DIR | NC  | NC        | NC        | NC  | 1 <del>OE</del> |
| В | 1B2  | 1B1 | GND       | GND       | 1A1 | 1A2             |
| С | 1B4  | 1B3 | $V_{CCB}$ | $V_{CCA}$ | 1A3 | 1A4             |
| D | 1B6  | 1B5 | GND       | GND       | 1A5 | 1A6             |
| E | 1B8  | 1B7 |           |           | 1A7 | 1A8             |
| F | 2B1  | 2B2 |           |           | 2A2 | 2A1             |
| G | 2B3  | 2B4 | GND       | GND       | 2A4 | 2A3             |
| Н | 2B5  | 2B6 | $V_{CCB}$ | $V_{CCA}$ | 2A6 | 2A5             |
| J | 2B7  | 2B8 | GND       | GND       | 2A8 | 2A7             |
| K | 2DIR | NC  | NC        | NC        | NC  | 2 <del>OE</del> |


(1) NC - No internal connection



## FUNCTION TABLE (EACH 8-BIT LATCH)


|    | INPUTS | OUTPUT |       |
|----|--------|--------|-------|
| OE | LE     | Q      |       |
| L  | Н      | Н      | Н     |
| L  | Н      | L      | L     |
| L  | L      | X      | $Q_0$ |
| Н  | X      | Χ      | Z     |


### LOGIC SYMBOL<sup>(1)</sup>



(1) This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

### **LOGIC DIAGRAM (POSITIVE LOGIC)**





To Seven Other Channels



### Absolute Maximum Ratings(1)

over operating free-air temperature range (unless otherwise noted)

|                  |  |                                    | MIN  | MAX                   | UNIT |
|------------------|--|------------------------------------|------|-----------------------|------|
| V <sub>CC</sub>  | Supply voltage range                                   |                                    | -0.5 | 4.6                   | V    |
| $V_{I}$          | Input voltage range (2)                                |                                    | -0.5 | 4.6                   | V    |
| Vo               | Voltage range applied to any output in the high        | n-impedance or power-off state (2) | -0.5 | 4.6                   | V    |
| Vo               | Voltage range applied to any output in the high        | n or low state <sup>(2)(3)</sup>   | -0.5 | V <sub>CC</sub> + 0.5 | V    |
| I <sub>IK</sub>  | Input clamp current                                    | V <sub>I</sub> < 0                 |      | -50                   | mA   |
| I <sub>OK</sub>  | Output clamp current                                   | V <sub>O</sub> < 0                 |      | -50                   | mA   |
| Io               | Continuous output current                              | ·                                  |      | ±50                   | mA   |
|                  | Continuous current through each V <sub>CC</sub> or GND |                                    |      | ±100                  | mA   |
|                  |  | DGG package                        |      | 70                    |      |
| $\theta_{JA}$    | Package thermal impedance (4)                          | DGV package                        |      | 58                    | °C/W |
|                  |  | GQL/ZQL package                    |      | 42                    |      |
| T <sub>stg</sub> | Storage temperature range                              |                                    | -65  | 150                   | °C   |

<sup>(1)</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

<sup>(2)</sup> The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.

<sup>3)</sup> The output positive-voltage rating may be exceeded up to 4.6 V maximum if the output current rating is observed.

<sup>(4)</sup> The package thermal impedance is calculated in accordance with JESD 51.

www.ti.com

## Recommended Operating Conditions<sup>(1)</sup>

|                  |  |  | MIN                    | MAX                    | UNIT |
|------------------|--|--|------------------------|------------------------|------|
| .,               | Complexialtage                                 | Operating                                    | 1.4                    | 3.6                    | V    |
| $V_{CC}$         | Supply voltage                                 | Data retention only                          | 1.2                    |                        | V    |
|                  |  | V <sub>CC</sub> = 1.2 V                      | V <sub>CC</sub>        |                        |      |
|                  |  | V <sub>CC</sub> = 1.4 V to 1.6 V             | 0.65 × V <sub>CC</sub> |                        |      |
| $V_{IH}$         | High-level input voltage                       | $V_{CC} = 1.65 \text{ V to } 1.95 \text{ V}$ | 0.65 × V <sub>CC</sub> |                        | V    |
|                  |  | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$   | 1.7                    |                        |      |
|                  |  | V <sub>CC</sub> = 3 V to 3.6 V               | 2                      |                        |      |
|                  |  | V <sub>CC</sub> = 1.2 V                      |                        | GND                    |      |
|                  |  | V <sub>CC</sub> = 1.4 V to 1.6 V             |                        | 0.35 × V <sub>CC</sub> |      |
| $V_{IL}$         | Low-level input voltage                        | V <sub>CC</sub> = 1.65 V to 1.95 V           |                        | 0.35 × V <sub>CC</sub> | V    |
|                  |  | V <sub>CC</sub> = 2.3 V to 2.7 V             |                        | 0.7                    |      |
|                  |  | V <sub>CC</sub> = 3 V to 3.6 V               |                        | 0.8                    |      |
| VI               | Input voltage                                  |  | 0                      | 3.6                    | V    |
| .,               | Output valtage                                 | Active state                                 | 0                      | V <sub>CC</sub>        | V    |
| V <sub>O</sub>   | Output voltage                                 | 3-state                                      | 0                      | 3.6                    | V    |
|                  |  | V <sub>CC</sub> = 1.4 V to 1.6 V             |                        | -2                     |      |
|                  | Static high-level output current (2)           | V <sub>CC</sub> = 1.65 V to 1.95 V           |                        | -4                     | A    |
| I <sub>OHS</sub> | Static high-level output current               | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$   |                        | -8                     | mA   |
|                  |  | V <sub>CC</sub> = 3 V to 3.6 V               |                        | -12                    |      |
|                  |  | V <sub>CC</sub> = 1.4 V to 1.6 V             |                        | 2                      |      |
|                  | Chatia lave lavel autout average (2)           | V <sub>CC</sub> = 1.65 V to 1.95 V           |                        | 4                      | A    |
| I <sub>OLS</sub> | Static low-level output current <sup>(2)</sup> | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$   |                        | 8                      | mA   |
|                  |  | $V_{CC} = 3 \text{ V to } 3.6 \text{ V}$     |                        | 12                     |      |
| Δt/Δν            | Input transition rise or fall rate             | V <sub>CC</sub> = 1.4 V to 3.6 V             |                        | 5                      | ns/V |
| T <sub>A</sub>   | Operating free-air temperature                 |  | -40                    | 85                     | °C   |

All unused inputs of the device must be held at  $V_{CC}$  or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004. Dynamic drive capability is equivalent to standard outputs with  $I_{OH}$  and  $I_{OL}$  of  $\pm 24$  mA at 2.5-V  $V_{CC}$ . See Figure 1 for  $V_{OL}$  vs  $I_{OL}$  and  $V_{OH}$  vs  $I_{OH}$  characteristics. Refer to the TI application reports, AVC Logic Family Technology and Applications, literature number SCEA066, and Dynamic Output Control (DOCTM) Circuitry Technology and Applications, literature number SCEA009.



### **Electrical Characteristics**

over recommended operating free-air temperature range (unless otherwise noted)

|                  | PARAMETER      | TEST                           | CONDITIONS               | V <sub>cc</sub> | MIN TYP(1)            | MAX  | UNIT |
|------------------|----------------|--------------------------------|--------------------------|-----------------|-----------------------|------|------|
|                  |                | $I_{OHS} = -100 \mu\text{A}$   |                          | 1.4 V to 3.6 V  | V <sub>CC</sub> - 0.2 |      |      |
|                  |                | $I_{OHS} = -2 \text{ mA},$     | V <sub>IH</sub> = 0.91 V | 1.4 V           | 1.05                  |      |      |
| $V_{OH}$         |                | $I_{OHS} = -4 \text{ mA},$     | V <sub>IH</sub> = 1.07 V | 1.65 V          | 1.2                   |      | V    |
|                  |                | $I_{OHS} = -8 \text{ mA},$     | V <sub>IH</sub> = 1.7 V  | 2.3 V           | 1.75                  |      |      |
|                  |                | $I_{OHS} = -12 \text{ mA},$    | V <sub>IH</sub> = 2 V    | 3 V             | 2.3                   |      |      |
|                  |                | $I_{OLS} = 100 \mu A$          |                          | 1.4 V to 3.6 V  |                       | 0.2  |      |
|                  |                | $I_{OLS} = 2 \text{ mA},$      | V <sub>IL</sub> = 0.49 V | 1.4 V           |                       | 0.4  |      |
| $V_{OL}$         |                | $I_{OLS} = 4 \text{ mA},$      | V <sub>IL</sub> = 0.57 V | 1.65 V          |                       | 0.45 | V    |
|                  |                | $I_{OLS} = 8 \text{ mA},$      | V <sub>IL</sub> = 0.7 V  | 2.3 V           |                       | 0.55 |      |
|                  |                | I <sub>OLS</sub> = 12 mA,      | V <sub>IL</sub> = 0.8 V  | 3 V             |                       | 0.7  |      |
| I <sub>I</sub>   |                | $V_I = V_{CC}$ or GND          |                          | 3.6 V           |                       | ±2.5 | μΑ   |
| I <sub>off</sub> |                | $V_I$ or $V_O = 3.6 \text{ V}$ |                          | 0               |                       | ±10  | μΑ   |
| l <sub>OZ</sub>  |                | $V_O = V_{CC}$ or GND          |                          | 3.6 V           |                       | ±10  | μΑ   |
| Icc              |                | $V_I = V_{CC}$ or GND,         | I <sub>O</sub> = 0       | 3.6 V           |                       | 40   | μΑ   |
|                  | Control innuts | V V or CND                     |                          | 2.5 V           | 3                     |      |      |
| ^                | Control inputs | $V_I = V_{CC}$ or GND          |                          | 3.3 V           | 3                     |      | F    |
| Ci               | Data innuta    | V V as CND                     |                          | 2.5 V           | 2.5                   |      | pF   |
|                  | Data inputs    | $V_I = V_{CC}$ or GND          |                          | 3.3 V           | 2.5                   |      |      |
| <u></u>          | Outouto        | V V or CND                     |                          | 2.5 V           | 6.5                   |      | ~F   |
| C <sub>o</sub>   | Outputs        | $V_O = V_{CC}$ or GND          |                          | 3.3 V           | 6.5                   |      | pF   |

<sup>(1)</sup> Typical values are measured at  $V_{CC}$  = 2.5 V and 3.3 V,  $T_A$  = 25°C.

### **Timing Requirements**

over recommended operating free-air temperature range (unless otherwise noted) (see Figure 2 through Figure 5)

|                |                             | V <sub>CC</sub> = | V <sub>CC</sub> = 1.2 V |     | V <sub>CC</sub> = 1.5 V<br>± 0.1 V |     | V <sub>CC</sub> = 1.8 V<br>± 0.15 V |     | 2.5 V<br>2 V | V <sub>CC</sub> = 3.3 V<br>± 0.3 V |     | UNIT |
|----------------|-----------------------------|-------------------|-------------------------|-----|------------------------------------|-----|-------------------------------------|-----|--------------|------------------------------------|-----|------|
|                |                             | MIN               | MAX                     | MIN | MAX                                | MIN | MAX                                 | MIN | MAX          | MIN                                | MAX |      |
| t <sub>w</sub> | Pulse duration, LE high     |                   |                         |     |                                    | 2.2 |                                     | 2   |              | 1.8                                |     | ns   |
| $t_{su}$       | Setup time, data before LE↓ | 1.7               |                         | 1.2 |                                    | 1.1 |                                     | 0.9 |              | 0.8                                |     | ns   |
| t <sub>h</sub> | Hold time, data after LE↓   | 2                 |                         | 1.1 |                                    | 1.1 |                                     | 1.1 |              | 1                                  |     | ns   |

### **Switching Characteristics**

over recommended operating free-air temperature range (unless otherwise noted) (see Figure 2 through Figure 5)

| PARAMETER        | FROM<br>(INPUT) | TO<br>(OUTPUT) | V <sub>CC</sub> = 1.2 V | 1.2 V $V_{CC} = 1.5 V$<br>$\pm 0.1 V$ |     | V <sub>CC</sub> = 1.8 V<br>± 0.15 V |     | V <sub>CC</sub> = 2.5 V<br>± 0.2 V |     | V <sub>CC</sub> = 3.3 V<br>± 0.3 V |     | UNIT |
|------------------|-----------------|----------------|-------------------------|---------------------------------------|-----|-------------------------------------|-----|------------------------------------|-----|------------------------------------|-----|------|
|                  | (INFOT)         | (001701)       | TYP                     | MIN                                   | MAX | MIN                                 | MAX | MIN                                | MAX | MIN                                | MAX |      |
| 4                | D               | Q              | 5.8                     | 1.2                                   | 6.8 | 1                                   | 5.7 | 0.8                                | 3.3 | 0.7                                | 2.8 | 20   |
| t <sub>pd</sub>  | LE              | Q              | 7.2                     | 1.4                                   | 8.3 | 1.1                                 | 6.6 | 0.8                                | 4   | 0.7                                | 3.2 | ns   |
| t <sub>en</sub>  | ŌĒ              | Q              | 7.4                     | 1.6                                   | 8.8 | 1.6                                 | 6.7 | 1.4                                | 4.3 | 0.7                                | 3.4 | ns   |
| t <sub>dis</sub> | ŌĒ              | Q              | 8.4                     | 2.5                                   | 9.4 | 2.3                                 | 7.8 | 1.3                                | 4.2 | 1.2                                | 3.9 | ns   |

Submit Documentation Feedback



www.ti.com


## **Operating Characteristics**

 $T_A = 25^{\circ}C$ 

|     | PARAMETER         |                  | TEST CONDITIONS                  | V <sub>CC</sub> = 1.8 V<br>TYP | V <sub>CC</sub> = 2.5 V<br>TYP | V <sub>CC</sub> = 3.3 V<br>TYP | UNIT |
|-----|-------------------|------------------|----------------------------------|--------------------------------|--------------------------------|--------------------------------|------|
| C   | Power dissipation | Outputs enabled  | $C_1 = 0$ . $f = 10 \text{ MHz}$ | 40                             | 43                             | 47                             | ρF   |
| Cpd | capacitance       | Outputs disabled | $C_L = 0$ , $f = 10 \text{ MHz}$ | 20                             | 22                             | 24                             | рг   |



## PARAMETER MEASUREMENT INFORMATION $V_{CC} = 1.2 \text{ V AND } 1.5 \text{ V } \pm 0.1 \text{ V}$




- NOTES: A. C<sub>L</sub> includes probe and jig capacitance.
  - B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  - C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_O = 50~\Omega$ ,  $t_f \leq$  2 ns,  $t_f \leq$  2 ns.
  - D. The outputs are measured one at a time, with one transition per measurement.
  - E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - F. t<sub>PZL</sub> and t<sub>PZH</sub> are the same as t<sub>en</sub>.
  - G. t<sub>PLH</sub> and t<sub>PHL</sub> are the same as t<sub>pd</sub>.

Figure 2. Load Circuit and Voltage Waveforms



# PARAMETER MEASUREMENT INFORMATION $V_{CC} = 1.8 \text{ V} \pm 0.15 \text{ V}$




- NOTES: A. C<sub>L</sub> includes probe and jig capacitance.
  - B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  - C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_Q = 50 \ \Omega$ ,  $t_f \leq 2 \ ns$ ,  $t_f \leq 2 \ ns$ .
  - D. The outputs are measured one at a time, with one transition per measurement.
  - E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - F.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
  - G. t<sub>PLH</sub> and t<sub>PHL</sub> are the same as t<sub>pd</sub>.

Figure 3. Load Circuit and Voltage Waveforms



## PARAMETER MEASUREMENT INFORMATION $V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V}$




- NOTES: A. C<sub>L</sub> includes probe and jig capacitance.
  - B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  - C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_O$  = 50  $\Omega$ ,  $t_f \leq$  2 ns.
  - D. The outputs are measured one at a time, with one transition per measurement.
  - E. t<sub>PLZ</sub> and t<sub>PHZ</sub> are the same as t<sub>dis</sub>.
  - F. t<sub>PZI</sub> and t<sub>PZH</sub> are the same as t<sub>en</sub>.
  - G.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .

Figure 4. Load Circuit and Voltage Waveforms



## PARAMETER MEASUREMENT INFORMATION $V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V}$



- NOTES: A. C<sub>I</sub> includes probe and jig capacitance.
  - B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  - C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_O = 50~\Omega$ ,  $t_f \leq$  2 ns,  $t_f \leq$  2 ns.
  - D. The outputs are measured one at a time, with one transition per measurement.
  - E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - F. t<sub>PZL</sub> and t<sub>PZH</sub> are the same as t<sub>en</sub>.
  - G. t<sub>PLH</sub> and t<sub>PHL</sub> are the same as t<sub>pd</sub>.

Figure 5. Load Circuit and Voltage Waveforms





www.ti.com 20-Aug-2011

#### **PACKAGING INFORMATION**

| Orderable Device | Status (1) | Package Type               | Package<br>Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup>    | Lead/<br>Ball Finish | MSL Peak Temp <sup>(3)</sup> | Samples<br>(Requires Login) |
|------------------|------------|----------------------------|--------------------|------|-------------|----------------------------|----------------------|------------------------------|-----------------------------|
| 74AVC16373DGGRG4 | ACTIVE     | TSSOP                      | DGG                | 48   | 2000        | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-1-260C-UNLIM           |                             |
| 74AVC16373DGVRE4 | ACTIVE     | TVSOP                      | DGV                | 48   | 2000        | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-1-260C-UNLIM           |                             |
| 74AVC16373DGVRG4 | ACTIVE     | TVSOP                      | DGV                | 48   | 2000        | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-1-260C-UNLIM           |                             |
| SN74AVC16373DGGR | ACTIVE     | TSSOP                      | DGG                | 48   | 2000        | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-1-260C-UNLIM           |                             |
| SN74AVC16373DGVR | ACTIVE     | TVSOP                      | DGV                | 48   | 2000        | Green (RoHS<br>& no Sb/Br) | CU NIPDAU            | Level-1-260C-UNLIM           |                             |
| SN74AVC16373ZQLR | ACTIVE     | BGA<br>MICROSTAR<br>JUNIOR | ZQL                | 56   | 1000        | Green (RoHS<br>& no Sb/Br) | SNAGCU               | Level-1-260C-UNLIM           |                             |

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.



### PACKAGE OPTION ADDENDUM

20-Aug-2011


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## PACKAGE MATERIALS INFORMATION


www.ti.com 14-Jul-2012

### TAPE AND REEL INFORMATION

### **REEL DIMENSIONS**



### **TAPE DIMENSIONS**



| A0 | Dimension designed to accommodate the component width     |
|----|---|
| В0 | Dimension designed to accommodate the component length    |
| K0 | Dimension designed to accommodate the component thickness |
| W  | Overall width of the carrier tape                         |
| P1 | Pitch between successive cavity centers                   |

## TAPE AND REEL INFORMATION

### \*All dimensions are nominal

| Device           | Package<br>Type                  | Package<br>Drawing |    | SPQ  | Reel<br>Diameter<br>(mm) | Reel<br>Width<br>W1 (mm) | A0<br>(mm) | B0<br>(mm) | K0<br>(mm) | P1<br>(mm) | W<br>(mm) | Pin1<br>Quadrant |
|------------------|----------------------------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| SN74AVC16373DGGR | TSSOP                            | DGG                | 48 | 2000 | 330.0                    | 24.4                     | 8.6        | 15.8       | 1.8        | 12.0       | 24.0      | Q1               |
| SN74AVC16373DGVR | TVSOP                            | DGV                | 48 | 2000 | 330.0                    | 16.4                     | 7.1        | 10.2       | 1.6        | 12.0       | 16.0      | Q1               |
| SN74AVC16373ZQLR | BGA MI<br>CROSTA<br>R JUNI<br>OR | ZQL                | 56 | 1000 | 330.0                    | 16.4                     | 4.8        | 7.3        | 1.5        | 8.0        | 16.0      | Q1               |

www.ti.com 14-Jul-2012




\*All dimensions are nominal

| Device           | Package Type            | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------------|-------------------------|-----------------|------|------|-------------|------------|-------------|
| SN74AVC16373DGGR | TSSOP                   | DGG             | 48   | 2000 | 367.0       | 367.0      | 45.0        |
| SN74AVC16373DGVR | TVSOP                   | DGV             | 48   | 2000 | 367.0       | 367.0      | 38.0        |
| SN74AVC16373ZQLR | BGA MICROSTAR<br>JUNIOR | ZQL             | 56   | 1000 | 333.2       | 345.9      | 28.6        |

## ZQL (R-PBGA-N56)

### PLASTIC BALL GRID ARRAY



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.

- B. This drawing is subject to change without notice.
- C. Falls within JEDEC MO-285 variation BA-2.
- D. This package is Pb-free. Refer to the 56 GQL package (drawing 4200583) for tin-lead (SnPb).

MicroStar Junior is a trademark of Texas Instruments



### DGV (R-PDSO-G\*\*)

### **24 PINS SHOWN**

### **PLASTIC SMALL-OUTLINE**



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15 per side.

D. Falls within JEDEC: 24/48 Pins – MO-153 14/16/20/56 Pins – MO-194

### DGG (R-PDSO-G\*\*)

### PLASTIC SMALL-OUTLINE PACKAGE

#### **48 PINS SHOWN**



NOTES: A. All linear dimensions are in millimeters.

B. This drawing is subject to change without notice.

C. Body dimensions do not include mold protrusion not to exceed 0,15.

D. Falls within JEDEC MO-153

#### IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46C and to discontinue any product or service per JESD48B. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components which meet ISO/TS16949 requirements, mainly for automotive use. Components which have not been so designated are neither designed nor intended for automotive use; and TI will not be responsible for any failure of such components to meet such requirements.

| roducts | Applications       |               |  |
|---------|--------------------|---------------|--|
| udia    | ununu ti oom/oudio | Automotive on |  |

Audio Automotive and Transportation www.ti.com/automotive www.ti.com/audio www.ti.com/communications **Amplifiers** amplifier.ti.com Communications and Telecom **Data Converters** dataconverter.ti.com Computers and Peripherals www.ti.com/computers **DLP® Products** Consumer Electronics www.ti.com/consumer-apps www.dlp.com DSP dsp.ti.com **Energy and Lighting** www.ti.com/energy Clocks and Timers www.ti.com/clocks Industrial www.ti.com/industrial Interface interface.ti.com Medical www.ti.com/medical Logic logic.ti.com Security www.ti.com/security

Power Mgmt power.ti.com Space, Avionics and Defense www.ti.com/space-avionics-defense

Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

OMAP Mobile Processors www.ti.com/omap TI E2E Community e2e.ti.com

Wireless Connectivity www.ti.com/wirelessconnectivity

www.ti-rfid.com

Pr