

LIN Transceiver with Voltage Regulator

Features:

- The MCP2021/2/1P/2P are Compliant with LIN Bus Specifications 1.3, 2.0, and 2.1 and are Compliant to SAE J2602
- Support Baud Rates up to 20 kBaud with LIN-compatible Output Driver
- 43V Load Dump Protected
- Very Low EMI Meets Stringent OEM Requirements
- Wide Supply Voltage, 6.0V 18.0V Continuous:
 Maximum Input Voltage of 30V
- Extended Temperature Range: -40 to +125°C
- Interface to PIC[®] EUSART and Standard USARTs
- Local Interconnect Network (LIN) Bus Pin:
 - Internal Pull-up Resistor and Diode
 - Protected Against Ground Shorts
 - Protected Against Loss of Ground
 - High-Current Drive
- Automatic Thermal Shutdown
- On-Chip Voltage Regulator:
 - Output Voltage of 5.0V with Tolerances of ±3% Overtemperature Range
 - Available with Alternate Output Voltage of 3.3V with Tolerances of ±3% Overtemperature Range
 - Maximum Continuous Input Voltage of 30V
 - Internal Thermal Overload Protection
 - Internal Short Circuit Current Limit
 - External Components Limited to Filter Capacitor Only and Load Capacitor
- Two Low-Power Modes:
 - Receiver On, Transmitter Off, Voltage Regulator On (\cong 85 µA)
 - Receiver Monitoring Bus, Transmitter Off, Voltage Regulator Off (\cong 16 µA)

Description:

The MCP2021/2/1P/2P provides a bidirectional, halfduplex communication physical interface to automotive and industrial LIN systems that meets the LIN bus specification Revision 2.0. The devices incorporate a voltage regulator with 5V at 50 mA or 3.3V at 50 mA regulated power-supply outputs.

The regulator is short-circuit protected, and is protected by an internal thermal shutdown circuit. The device has been specifically designed to operate in the automotive operating environment and will survive all specified transient conditions while meeting all of the stringent quiescent current requirements.

The MCP2021/2/1P/2P family of devices includes the following packages.

8-pin PDIP, DFN and SOIC packages:


- MCP2021-330, LIN-compatible driver, 8-pin, 3.3V regulator, wake up on dominant level of LBUS
- MCP2021-500, LIN-compatible driver, 8-pin, 5.0V regulator, wake up on dominant level of LBUS
- MCP2021P-330, LIN-compatible driver, 8-pin, 3.3V regulator, wake up at falling edge of LBUS voltage
- MCP2021P-500, LIN-compatible driver, 8-pin, 5.0V regulator, wake up at falling edge of LBUS voltage

14-pin PDIP, TSSOP and SOIC packages with RESET output:


- MCP2022-330, LIN-compatible driver, 14-pin, 3.3V regulator, RESET output, wake up on dominant level of LBUS
- MCP2022-500, LIN-compatible driver, 14-pin, 5.0V regulator, RESET output, wake up on dominant level of LBUS
- MCP2022P-330, LIN-compatible driver, 14-pin, 3.3V regulator, RESET output, wake up at falling edge of LBUS voltage
- MCP2022P-500, LIN-compatible driver, 14-pin, 5.0V regulator, RESET output, wake up at falling edge of LBUS voltage




Package Types



MCP2021/2 Block Diagram



MCP2021P/2P Block Diagram



NOTES:

1.0 DEVICE OVERVIEW

The MCP2021/2/1P/2P provides a physical interface between a microcontroller and a LIN half-duplex bus. It is intended for automotive and industrial applications with serial bus speeds up to 20 Kbaud.

The MCP2021/2/1P/2P provides a half-duplex, bidirectional communications interface between a microcontroller and the serial network bus. This device will translate the CMOS/TTL logic levels to LIN-level logic, and vice versa.

The LIN specification 2.0 requires that the transceiver(s) of all nodes in the system be connected via the LIN pin, referenced to ground, and with a maximum external termination resistance load of 510Ω from LIN bus to battery supply. The 510Ω corresponds to one Master and sixteen Slave nodes.

The MCP2021/2/1P/2P-500 provides a +5V, 50 mA, regulated power output. The regulator uses an LDO design, is short-circuit protected, and will turn the regulator output off if it falls below 3.5V.

The MCP2021/2/1P/2P also includes thermalshutdown protection.

The regulator is specifically designed to operate in the automotive environment and will survive +43V load dump transients, double-battery jumps, and reverse battery connections when a reverse blocking diode is used. The other members of the MCP2021/2/1P/2P-330 family output +3.3V at 50 mA with a turn-off voltage of 2.5V. (See Section 1.6 "Internal Voltage Regulator").

MCP2021/2 wakes from Power-Down mode on a dominant level on LBUS. MCP2021P/2P wakes at a transition from recessive level to dominant level on LBUS.

1.1 Optional External Protection

1.1.1 REVERSE BATTERY PROTECTION

An external reverse-battery-blocking diode should be used to provide polarity protection (see Figure 1-6).

1.1.2 TRANSIENT VOLTAGE PROTECTION (LOAD DUMP)

An external 43V transient suppressor (TVS) diode, between VBB and ground, with a 50Ω transient protection resistor (RTP) in series with the battery supply and the VBB pin, protect the device from power transients (see Figure 1-6) and ESD events. While this protection is optional, it is considered good engineering practice. The resistor value is chosen according to Equation 1-1.

EQUATION 1-1:

 $RTP <= (VBB_{min} - 5.5) / 250 \text{ mA.}$ 5.5V = VUVLO + 1.0V, 250 mA is the peak current at Power-On whenVBB = 5.5V

1.2 Internal Protection

1.2.1 ESD PROTECTION

For component-level ESD ratings, please refer to the **Section 2.1 "Absolute Maximum Ratings†"**.

1.2.2 GROUND LOSS PROTECTION

The LIN Bus specification states that the LIN pin must transition to the recessive state when ground is disconnected. Therefore, a loss of ground effectively forces the LIN line to a hi-impedance level.

1.2.3 THERMAL PROTECTION

The thermal protection circuit monitors the die temperature and is able to shut down the LIN transmitter and voltage regulator if it detects a thermal overload.

There are three causes for a thermal overload. A thermal shut down can be triggered by any one, or a combination of, the following thermal overload conditions:

- Voltage regulator overload
- LIN bus output overload
- Increase in die temperature due to increase in environmental temperature

Driving the TXD and checking the RXD pin makes it possible to determine whether there is a bus contention (i.e., Rx = low, Tx = high) or a thermal overload condition (i.e., Rx = high, Tx = low).




FIGURE 1-1: Thermal Shutdown State Diagrams.

1.3 Modes of Operation

For an overview of all operational modes, please refer to Table 1-1.

1.3.1 POWER-ON RESET MODE

Upon application of VBB, the device enters Power-On Reset mode (POR). During this mode, the part maintains the digital section in a Reset mode and waits until the voltage on pin VBB rises above the "ON" threshold (typically 5.75V) to enter to the Ready mode. If during the operation, the voltage on pin VBB falls below the "OFF" threshold (typically 4.25V), the part comes back to the POR mode.

1.3.2 POWER-DOWN MODE

In Power-Down mode, the transmitter and the voltage regulator are off. Only the receiver wake-up from the LIN bus section, and the CS/LWAKE pin wake-up circuits, are in operation. This is the lowest power mode.

If pin CS/LWAKE goes to a high level during Power-Down mode, the device immediately enters Ready mode and enables the voltage regulator; and after the output has stabilized (approximately 0.3 ms to 1.2 ms), the device goes to Operation mode or Transmitter-Off mode (see Figure 1-2 for MCP2021/2 and Figure 1-3 for MCP2021P/2P).

Note: The above time interval <1.2 ms assumes 12V VBB input and no thermal shutdown event.

LIN bus activity will also change the device from Power-Down mode to Ready mode. MCP2021/2 wakes up on the dominant level of the LIN bus, and MCP2021P/2P on a falling edge that follows a dominant level lasting 20 μ s of time.

The Power-Down mode can be reached through either Operation mode or Transmitter-Off mode.

1.3.3 READY MODE

Upon entering Ready mode, the voltage regulator and receiver-threshold-detect circuit are powered up. The transmitter remains in an off state. The device is ready to receive data as soon as the regulator is stabilized, but not to transmit. If a microcontroller is being driven by the voltage regulator output, it will go through a POR and initialization sequence. The LIN pin is in the recessive state for MCP2021/2 and in floating state for MCP2021P/2P.

The device will stay in Ready mode until the output of the voltage regulator has stabilized and the CS/LWAKE pin is true ('1'). After VREG is stable and CS/LWAKE is high, MCP2021/2 will enter Operation mode; and MCP2021P/2P will enter either Operation mode or Transmitter-Off mode, depending on the level of the FAULT/TXE pin (refer to Figure 1-3).

1.3.4 OPERATION MODE

In this mode, all internal modules are operational.

The device will go into the Power-Down mode on the falling edge of CS/LWAKE.

For the MCP2021P/2P devices, the pull-up resistor is switched on only in this mode.

1.3.5 TRANSMITTER-OFF MODE

Whenever the FAULT/TXE signal is low, or permanent dominant on TXD/LBUS is detected, the LBUS transmitter is off.

The transmitter may be re-enabled whenever the FAULT/TXE signal returns high, either by removing the internal fault condition or when the CPU returns the FAULT/TXE high. The transmitter will not be enabled if the FAULT/TXE pin is brought high when the internal fault is still present.

If TX-OFF mode is caused by TXD/LBUS permanent dominant level, the transmitter can recover when the permanent dominant status disappears.

The transmitter is also turned off whenever the voltage regulator is unstable or recovering from a fault. This prevents unwanted disruption of the bus during times of uncertain operation.

1.3.6 WAKE-UP

The Wake-Up sub-module observes the LBUS in order to detect bus activity. Bus activity is detected when the voltage on the LBUS stays below a threshold of approximately 0.4 VBB for a typical duration of at least 20 µs. The MCP2021/2 device is level sensitive to LBUS. Dominant level longer than 20 µs will cause the device to leave the Power-Down mode. The MCP2021P/2P device is falling-edge sensitive to LBUS. Only the LBUS transition from recessive to dominant, followed by at least 20 µs dominant level, can wake up the device. Putting CS/LWAKE to high level also wakes up the device. Refer to Figure 1-2 and Figure 1-3.

1.3.7 DIFFERENCE DETAILS BETWEEN MCP2021/2 AND MCP2021P/2P

The MCP202XP is a minor variation of the MCP202X device that adds improved state machine control, as well as the ability to disconnect the internal $30k\Omega$ pullup between LIN and VBB in all modes except normal operation. These changes allow the system designer to better handle fault conditions and reduce the overall system current consumption. The differences between the two device versions are as follows:

1. Switchable LIN-VBB Pull-Up Resistor:

On the MCP202XP device, the internal $30k\Omega$ pull-up resistor is disconnected in all modes except Operation mode. On the MCP202X device, this pull-up resistor is always connected. (See the MCP2021/2 Block Diagram and the MCP2021P/2P Block Diagram for details.)

2. Power Down Wake-up on LIN Traffic:


The MCP202XP device requires a LIN falling edge to generate a valid Wake condition, due to bus traffic. The MCP202X device will generate a Wake anytime LIN is at a valid dominant level. Because of this, if the LIN bus becomes permanently shorted, it becomes impossible to place the MCP202X in a low-power state.


3. State Machine Options:


The MCP202XP device is able to enter Transmitter Off mode from Ready mode without transitioning through Operation mode. The MCP202X device must enter Operation mode from Ready mode. (see State Machine Diagrams, Figure 1-2 and Figure 1-3 for details). This capability allows the system designer to monitor the bus in Ready mode to determine if the system should transition to normal operation and connect the internal pullup, or if Ready mode was reached due to an invalid condition. In the case of an invalid condition, the MCP202XP device can be placed into Power-Down mode without connecting the internal pull-up and waking other nodes on the LIN Bus network.


Note:	To enter Transmitter Off, the system must
	set TXE 'low' before pulling CS high (see
	Figure 1-5). Otherwise, if CS is pulled high
	first, the MCP202XP will enter Operation
	mode due to the internal pull-up on TXE.


To properly take advantage of the device differences, the system designer is required to implement some microcontroller code to the power-up routine. This code will monitor the status of the LIN bus to determine how to respond to the dominant signal. It will also determine if the local LIN node needs to respond or can 'Listen Only'. If the local LIN node does not need to respond, it can enter Transmitter Off mode, disconnecting the $30k\Omega$ pull-up, reducing module current while still maintaining the ability to properly receive all valid LIN messages.

















FIGURE 1-5: Forced Power-Down Mode Sequence for MCP2021P/2P.

	Transmitter Dessiver Voltage Onerstien							
State	Transmitter	Receiver	Regulator	Operation	Comments			
POR	OFF	OFF	OFF	Read VBB; if VBB>5.75V, enter Ready mode				
Ready	OFF	ON	ON	MCP2021/2: If CS/LWAKE is high level, then Operation mode. MCP2021P/2P: If CS/LWAKE is high level and FAULT/TXE is high level, then Operation mode. If CS/LWAKE is high level and FAULT/TXE is low level, then TXOFF mode.	E			
Operation	ON	ON	ON	If CS/LWAKE is low level, then Power- Down mode. If FAULT/TXE is low level or TXD/LBUS permanent dominant is detected, then Transmitter-Off mode.	Normal Operation mode			
Power-Down	OFF	Activity Detect	OFF	On LIN bus falling, go to Ready mode. On CS/LWAKE high level, go through Ready mode; then, to either operation or Transmitter-Off mode (refer to Figure 1-2 and Figure 1-3).	Low-Power mode			
Transmitter-Off	OFF	ON	ON	If CS/LWAKE is low level, then Power- Down mode. If FAULT/TXE is high, then Operation mode.				

TABLE 1-1: OVERVIEW OF OPERATIONAL MODES

1.4 Pin Descriptions

	Dev	ices		Function				
Pin Name	8-Pin DFN, PDIP, SOIC	14-Pin PDIP, SOIC, TSSOP	Pin Type	Normal Operation				
Vreg	3	3	0	Power Output				
Vss	5	11	Р	Ground				
VBB	7	13	Р	Battery Supply				
TXD	4	4	I	Transmit Data Input (TTL)				
RXD	1	1	0	Receive Data Output (CMOS)				
LBUS	6	12	I/O	LIN bus (Bidirectional)				
CS/LWAKE	2	2	TTL	Chip Select (TTL)				
FAULT/TXE	8	14	OD	Fault Detect Output, Transmitter Enable (OD)				
RESET		5	OD	RESET signal Output (OD)				

Legend: O = Output, P = Power, I = Input, TTL = TTL input buffer, OD = Open-Drain output

1.4.1 POWER OUTPUT (VREG)

Positive Supply Voltage Regulator Output pin.

1.4.2 GROUND (Vss)

Ground pin.

1.4.3 BATTERY (VBB)

Battery Positive Supply Voltage pin. This pin is also the input for the internal voltage regulator.

1.4.4 TRANSMIT DATA INPUT (TXD)

The Transmit Data Input pin has an internal pull-up to VREG. The LIN pin is low (dominant) when TXD is low, and high (recessive) when TXD is high.

For extra bus security, TXD is internally forced to '1' when VREG is less than 1.8V (typical).

If the thermal protection detects an overtemperature condition while the signal TXD is low, the transmitter is shut down. The recovery from the thermal shutdown is equal to adequate cooling time.

1.4.5 RECEIVE DATA OUTPUT (RXD)

The Receive Data Output pin is a standard CMOS output and follows the state of the LIN pin.

1.4.6 LIN BUS

The bidirectional LIN bus Interface pin is the driver unit for the LIN pin and is controlled by the signal TXD. LIN has an open collector output with a current limitation. To reduce EMI, the edges during the signal changes are slope-controlled. To further reduce radiated emissions, the LBUS pin has corner-rounding control for both falling and rising edges. The internal LIN receiver observes the activities on the LIN bus, and generates output signal RXD that follows the state of the LBUS. A 1st degree with 1 μ S time constant (160KhZ), low-pass input filter is placed to maintain EMI immunity.

1.4.7 CS/LWAKE

Chip Select Input pin. A internal pull-down resistor will keep the CS/LWAKE pin low. This is done to ensure that no disruptive data will be present on the bus while the microcontroller is executing a POR and I/O initialization sequence. The pin must see a high level to activate the transmitter.

If CS/LWAKE= '0' when the VBB supply is turned on, the device stays in Ready mode (Low-Power mode). In Ready mode, both the receiver and the voltage regulator are on and the LIN transmitter driver is off.

If CS/LWAKE = '1' when the VBB supply is turned on, the device will proceed to either Operation or Transmitter-Off mode (refer to Figure 1-2 and Figure 1-3) after the VREG output has stabilized.

This pin may also be used as a local wake-up input (see Figure 1-6). In this implementation, the microcontroller will set the I/O pin that controls the CS/LWAKE as an high-impedance input. The internal pull-down resistor will keep the input low. An external switch, or other source, can then wake up the transceiver and the microcontroller.

Note: CS/LWAKE should not be tied directly to VREG as this could force the MCP202X into Operation mode before the microcontroller is initialized.

1.4.8 FAULT/TXE

Fault Detect Output and Transmitter Enable Input bidirectional pin.

This pin is an open-drain output. Its state is defined as shown in Table 1-2. The transmitter driver is disabled whenever this pin is low ('0'), either from an internal fault condition or by external drive. This allows the transmitter to be placed in an off state and still allow the voltage regulator to operate. Refer to Table 1-1.

The FAULT/TXE also signals a mismatch between the TXD input and the LBUS level. This can be used to detect a bus contention. Since the bus exhibits a propagation delay, the sampling of the internal compare is debounced to eliminate false faults.

This pin has an internal pull-up resistor of approximately 750 k Ω . The internal pull-up resistor is too weak. We recommend adding a 10 kOhm external pull-up resistor to ensure a logic high level.

- **Note 1:** The FAULT/TXE pin is true (0) whenever the internal circuits have detected a short or thermal excursion and have disabled the LBUS output driver.
 - 2: FAULT/TXE is true (0) when VREG not OK and has disabled the LBUS output driver.

The FAULT/TXE pin sampled at a rate faster than every 10 $\mu s.$

тхр	RXD	LINBUS	Thermal	FAULT/TXE						
In	Out	I/O	Override	External Input	Driven Output	Definition				
L	Н	Vbb	OFF	Н	L	FAULT , TXD driven low, LINBUS shorted to VBB (Note 1)				
Н	Н	VBB	OFF	Н	Н	ок				
L	L	GND	OFF	Н	Н	ок				
Н	L	GND	OFF	Н	Н	OK, data is being received from the LINBUS				
х	х	VBB	ON	Н	L	FAULT, transceiver in thermal shutdown				
x	х	Vbb	x	L	х	NO FAULT , the CPU is commanding the transceiver to turn off the transmitter driver				

TABLE 1-2:FAULT/TXE TRUTH TABLE

Legend: x = don't care

1.4.9 RESET

RESET is an open-drain output pin. This pin reflects an internal signal that tracks the internal system voltage has reached a valid, stable level.

As long as the internal voltage is valid, this pin will keep high impedance. When the system voltage drops below the minimum required, the voltage regulator will shut down and immediately convert the RESET output to short to GND. A pull-up resistor is needed to change the output to high/low voltage. When connected to a microcontroller input, this can provide a warning that the voltage regulator is shutting down (see Figure 1-2).

Alternately, it <u>can act</u> as an external brown-out by connecting the RESET output to MCLR (see Figure 1-<u>2)</u>. In addition to monitoring the internal voltage, RESET is asserted immediately upon entering the Power-Down mode.

Note 1: The FAULT/TXE is valid after approximately 25 µs after TXD falling edge. This is to eliminate false fault reporting during bus propagation delays.

1.5 Typical Applications







FIGURE 1-6: Typical MCP2021/MCP2021P Application.









1.6 Internal Voltage Regulator

1.6.1 5.0V REGULATOR

The MCP2021 has a low-drop-out voltage, positive regulator capable of supplying 5.00 VDC \pm 3% at up to 50 mA of load current, over the entire operating temperature range of -40°C to +125°C. With a load current of 50 mA, the minimum input to output voltage differential required for the output to remain in regulation is typically +0.5V (+1V maximum over the full operating temperature range). Quiescent current is less than 100 µA with a full 50 mA load current when the input to output voltage differential is greater than +3.00V.

The regulator requires an external output bypass capacitor for stability. See Figure 2-3 for correct capacity and ESR for stable operation.

Designed for automotive applications, the regulator will protect itself from double-battery jumps and up to +43V load dump transients. The voltage regulator has both short-circuit and thermal-shut-down protection built in.

Regarding the correlation between VBB, VREG and IDD, please refer to Figure 1-10 — Figure 1-12. When the input voltage (VBB) drops below the differential needed to provide stable regulation, the output VREG will track the input down to approximately 3.5V, at which point the regulator will turn off. This will allow microcontrollers with internal POR circuits to generate a clean arm-

ing of the POR trip point. The MCP2021 will then monitor VBB and turn on the regulator when VBB rises above 5.75, again.

When the input voltage (VBB) drops below the differential needed to provide stable regulation, the output VREG) will track the input down to approximately +4.25V. The regulator will turn off the output at this point. This will allow PIC microcontrollers with internal POR circuits to generate a clean arming of the POR trip point. The regulator output will stay off until VBB is above +5.75 V_{DC}.

In the start phase, the device must detect at least 5.75V to initiate operation during power up. In the Power-Down mode, the VBB monitor will be turned off.

The regulator has a thermal shutdown. If the thermal protection circuit detects an overtemperature condition, and the signals TxD and RXD are LOW, or TxD is HIGH, the regulator will shut down. The recovery from the thermal shutdown is equal to adequate cooling time.




FIGURE 1-9:


Voltage Regulator Block Diagram.


Note: The regulator has an overload current limiting of approximately 100 mA. During a short circuit, the VREG is monitored. If VREG is lower than 3.5V, the VREG will turn off. After a recovery time of about three milliseconds, the VREG will be checked again. If there is no short circuit (VREG >3.5V), the VREG will be switched back on.

1.6.2 3.3V REGULATOR

A metal option provides for a alternate $3.30 \text{ VDC} \pm 3\%$ at up to 50 mA of load current over the entire operating temperature range of -40° C to $+125^{\circ}$ C. All specifications given above for the 5.0V operation apply except for any difference noted here.


The same input tracking of 4.25V applies the 3.3V regulator.







Voltage Regulator Output on POR.






FIGURE 1-12: Voltage Regulator Output on Overcurrent Situation.

1.7 ICSP[™] Considerations

The following should be considered when the MCP2021/2/1P/2P is connected to pins supporting in-circuit programming:

- Power used for programming the microcontroller can be supplied from the programmer or from the MCP2021/2/1P/2P.
- The voltage on VREG should not exceed the maximum output voltage of VREG.

NOTES:

2.0 ELECTRICAL CHARACTERISTICS

2.1 Absolute Maximum Ratings†

VIN DC Voltage on RXD and TXD	-0.3 to VREG+0.3V
VIN DC Voltage on FAULT and RESET	
VIN DC Voltage on CS/LWAKE	0.3 to +43V
VBB Battery Voltage, non-operating (LIN bus recessive, no regulator load, t < 60s)	0.3 to +43V
VBB Battery Voltage, transient ISO 7637 Test 1	200V
VBB Battery Voltage, transient ISO 7637 Test 2a	+150V
VBB Battery Voltage, transient ISO 7637 Test 3a	300V
VBB Battery Voltage, transient ISO 7637 Test 3b	+200V
VBB Battery Voltage, continuous	-0.3 to +30V
VLBUS Bus Voltage, continuous	18 to +30V
VLBUS Bus Voltage, transient (Note 1)	27 to +43V
ILBUS Bus Short Circuit Current Limit	200 mA
ESD protection on LIN, Vвв (IEC 61000-4-2, 330 Ohm, 150 pF) (Note 3)	minimum ±9 kV
ESD protection on LIN, VBB (Charge Device Model) (Note 2)	±1500V
ESD protection on LIN, VBB (Human Body Model, 1 kOhm, 100 pF) (Note 4)	<u>+</u> 8 kV
ESD protection on LIN, VBB (Machine Model) (Note 2)	±800V
ESD protection on all other pins (Human Body Model) (Note 2)	> 4 kV
Maximum Junction Temperature	150°C
Storage Temperature	55 to +150°C

Note 1: ISO 7637/1 load dump compliant (t < 500 ms).

- 2: According to JESD22-A114-B.
- 3: According to IBEE, without bus filter.
- 4: Limited by Test Equipment.

† NOTICE: Stresses above those listed under "Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

2.2 DC Specifications

DC Specifications	Electrical Char Unless otherwis VBB = 6.0V to 1 TA = -40°C to + ⁻ CLOADREG = 10	e indicated, all 8.0V I25°C	limits a	are specified fo	or:	
Parameter	Sym	Min	Тур	Max	Units	Conditions
Power						
VBB Quiescent Operating Current	IBBQ		115	210	μA	IOUT = 0 mA, LBUS recessive
			120	215	μA	VOUT = 3.3V
VBB Transmitter-Off Current	Іввто	_	90	190	μA	With V _{REG} on, t <u>ransmitter</u> off, receiver on, FAULT/TXE = VIL, CS = VIH
			95	210	μA	VOUT = 3.3V
VBB Power-Down Current	IBBPD	_	16	26	μA	With VREG powered-off, receiver on and transmitter off, FAULT/TXE = VIH, TXD = VIH, CS = VIL)
VBB Current with Vss Floating	IBBNOGND	-1		1	mA	VBB = 12V, GND to VBB, VLIN = 0-18V
Microcontroller Interface						
High-L <u>evel In</u> put Voltage (TXD, FAULT/TXE)	Viн	2.0 or (0.25 VREG + 0.8)		Vreg +0.3	V	
Low-Level Input Voltage (TXD, FAULT/TXE)	Vil	-0.3	—	0.15 VREG	V	
High-Level Input Current (TXD, FAULT/TXE)	Ін	-2.5	_	_	μA	Input voltage = 0.8*VREG
Low-Level Input Current (TXD, FAULT/TXE)	lı∟	-10			μA	Input voltage = 0.2*VREG
Pull-up Current on Input (TXD)	IPUTXD	-3.0	_		μA	~800 k Ω internal pull-up to VREG @ VIH = 0.7*VREG
High-Level Input Voltage (CS/LWAKE)	Vін	0.7 VREG	_	VBB	V	Through a current-limiting resistor
Low-Level Input Voltage (CS/LWAKE)	VIL	-0.3	—	0.3Vreg	V	
High-Level Input Current (CS/LWAKE)	Ін	_	—	7.0	μA	Input voltage = 0.8*VREG
Low-Level Input Current (CS/LWAKE)	lı∟	—	—	3.0	μA	Input voltage = 0.2*VREG
Pull-down Current on Input (CS/LWAKE)	IPDCS	_	—	6.0	μA	~1.3M Ω internal pull-down to Vss @ VIH = 3.5V

Note 1: Internal current limited. 2.0 ms maximum recovery time (RLBUS = 0Ω , TX = 0.4 VREG, VLBUS = VBB).

2: For design guidance only, not tested.

3: Node has to sustain the current that can flow under this condition; bus must be operational under this condition.

2.2 DC Specifications (Continued)

	-									
	Electrical Chara									
DC Creatifications	Unless otherwise indicated, all limits are specified for: $V_{BB} = 6.0V$ to 18.0V									
DC Specifications										
	TA = -40° C to $+125^{\circ}$ C CLOADREG = 10μ F									
			_			• •••				
Parameter	Sym	Min	Тур	Мах	Units	Conditions				
Bus Interface										
High-Level Input Voltage	VIH(LBUS)	0.6 Vвв	_	18	V	Recessive state				
Low-Level Input Voltage	VIL(LBUS)	-8		0.4 Vвв	V	Dominant state				
Input Hysteresis	VHYS	_		0.175 Vвв	V	VIH(LBUS) - VIL(LBUS)				
Low-Level Output Current	IOL(LBUS)	40		200	mA	Output voltage = 0.1 VBB, VBB = 12V				
Pull-up Current on Input	IPU(LBUS)	5		180	μA	~30 kΩ internal pull-up @ VIH (LBUS) = 0.7 VBB				
Short Circuit Current Limit	Isc	50	_	200	mA	(Note 1)				
High-Level Output Voltage	Voh(Lbus)	0.8 Vbb		VBB	V	VOH(LBUS) must be at least 0.8 VBB				
Low-Level Output Voltage	Vollo (Lbus)	—		0.2 Vвв	V					
Input Leakage Current (at the receiver during dominant bus level)	IBUS_PAS_DOM	-1			mA	Driver off, VBUS = 0V, VBAT = 12V				
Leakage Current (disconnected from ground)	IBUS_NO_GND	-1		+1	mA	GNDDEVICE = VBAT, 0V < VBUS < 18V, VBAT = 12V				
Leakage Current (disconnected from VBAT)	IBUS	_		10	μA	VBAT = GND, 0 < VBUS < 18V, TA = -40°C to +85°C (Note 3)				
				50	μA	TA = +85°C to +125°C				
Receiver Center Voltage	VBUS_CNT	0.475 Vвв	0.5 Vвв	0.525 Vвв	V	VBUS_CNT = (VIL (LBUS) + VIH (LBUS))/2				
Slave Termination	Rslave	20	30	47	kΩ					

Note 1: Internal current limited. 2.0 ms maximum recovery time (RLBUS = 0Ω , TX = 0.4 VREG, VLBUS = VBB).

2: For design guidance only, not tested.

3: Node has to sustain the current that can flow under this condition; bus must be operational under this condition.


2.2 DC Specification (Continued)

DC Specifications	Electrical Characteristics: Unless otherwise indicated, all limits are specified for: $V_{BB} = 6.0V$ to $18.0V$ $T_A = -40^{\circ}C$ to $+125^{\circ}C$ $C_{LOADREG} = 10 \mu F$								
Parameter	Sym	Min	Тур	Max	Units	Conditions			
Voltage Regulator - 5.0V									
Output Voltage	Vout	4.85	5.00	5.15	V	0 mA < IOUT < 50 mA,			
Load Regulation	ΔVουτ2	_	10	50	mV	5 mA < IOUT < 50 mA refer to Section 1.6 "Internal Voltage Regulator"			
Quiescent Current	Ivrq	—	—	25	μA	IOUT = 0 mA, (Note 2)			
Power Supply Ripple Reject	PSRR	_	—	50	dB	1 VPP @10-20 kHz Cload = 10 μf, Iload = 50 mA			
Output Noise Voltage	eN	_	—	100	µVrms	10 Hz – 40 MHz CFILTER = 10 μ f, CBP = 0.1 μ f, CLOAD 10 μ f, ILOAD = 50 mA			
Shutdown Voltage	Vsd	3.5	—	4.0	V	See Figure 1-8			
Input Voltage to Maintain Regulation	VBB	6.0	_	18.0	V				
Input Voltage to Turn Off Output	Voff	4.0	_	4.5	V				
Input Voltage to Turn On Output	Von	5.5	—	6.0	V				

Note 1: Internal current limited. 2.0 ms maximum recovery time (RLBUS = 0Ω , TX = 0.4 VREG, VLBUS = VBB).

2: For design guidance only, not tested.

3: Node has to sustain the current that can flow under this condition; bus must be operational under this condition.




•		-					
DC Specifications	Electrical Characteristics: Unless otherwise indicated, all limits are specified for: VBB = $6.0V$ to $18.0V$ TA = $-40^{\circ}C$ to $+125^{\circ}C$ CLOADREG = $10 \ \mu$ F						
Parameter	Sym	Min	Тур	Max	Units	Conditions	
Voltage Regulator - 3.3V							
Output Voltage	Vout	3.20	3.30	3.40	V	0 mA < IOUT < 50 mA	
Line Regulation	ΔVουτ1	_	10	50	mV	IOUT = 1 mA, 6.0V < VBB < 18V	
Load Regulation	ΔVουτ2	—	10	50	mV	5 mA < IOUT < 50 mA Refer to Section 1.6 "Internal Voltage Regulator"	
Quiescent Current	Ivrq			25	μA	IOUT = 0 mA, (Note 2)	
Power Supply Ripple Reject	PSRR	_	_	50	dB	1 VPP @10-20 kHz Cload = 10 μf, Iload = 50 mA	
Output Noise Voltage	eN	_	_	100	µVrms /√Hz	10 Hz – 40 MHz CFILTER = 10 μf, CBP = 0.1 μf CLOAD = 10 μf, ILOAD = 50 mA	
Shutdown Voltage	Vsd	2.5	—	2.7	V	See Figure 1-8	
Input Voltage to Maintain Regulation	VBB	6.0	_	18.0	V		
Input Voltage to Turn Off Output	Voff	4.0	—	4.5	V		
Input Voltage to Turn On Output	Von	5.5	—	6.0	V		

2.2 DC Specification (Continued)

Note 1: Internal current limited. 2.0 ms maximum recovery time (RLBUS = 0Ω , TX = 0.4 VREG, VLBUS = VBB).

2: For design guidance only, not tested.

3: Node has to sustain the current that can flow under this condition; bus must be operational under this condition.



© 2005-2013 Microchip Technology Inc.




FIGURE 2-3: ESR Curves for Load Capacitor Selection.

2.3 AC Specification

AC CHARACTERISTICS	VBB = 6.0V to	o 18.0V; Ta	$c = -40^{\circ}C$ to	o +125°C		
Parameter	Sym	Min	Тур	Max	Units	Test Conditions
Bus Interface - Constant Slo	ope Time Para	ameters				
Slope rising and falling edges	tSLOPE	3.5	_	22.5	μs	7.3V <= VBB <= 18V
Propagation Delay of Transmitter	t TRANSPD	_	_	4.0	μs	tTRANSPD = max (tTRANSPDR or tTRANSPDF)
Propagation Delay of Receiver	trecpd	—	_	6.0	μs	tRECPD = max (tRECPDR or tRECPDF)
Symmetry of Propagation Delay of Receiver rising edge w.r.t. falling edge	tRECSYM	-2.0	_	2.0	μs	tRECSYM = max (tRECPDF - tRECPDR)
Symmetry of Propagation Delay of Transmitter rising edge w.r.t. falling edge	ttranssym	-2.0	_	2.0	μs	ttranssym = max (ttranspdf - ttranspdr)
Time to sample of FAULT/ TXE for bus conflict reporting	t FAULT	—	_	32.5	μs	tFAULT = max (tTRANSPD + tSLOPE + tRECPD)
Duty Cycle 1 @20.0 kbit/sec		39.6		_	%tBIT	$\begin{array}{l} \mbox{CBUS;RBUS conditions:} \\ 1 \ nF; \ 1 \ k\Omega \mid 6.8 \ nF; \ 660\Omega \mid \\ 10 \ nF; \ 500\Omega \\ THREC(MAX) = 0.744 \ x \ VBB, \\ THDOM(MAX) = 0.581 \ x \ VBB, \\ VBB = 7.0V - 18V; \ tBIT = 50 \ \mu s. \\ D1 = tBUS_REC(MIN) / 2 \ x \ tBIT) \end{array}$
Duty Cycle 2 @20.0 kbit/sec		_	_	58.1	%tBIT	$\begin{array}{l} C\text{BUS}; R\text{BUS conditions:} \\ 1 \text{ nF}; 1 \text{k}\Omega \mid 6.8 \text{nF}; 660\Omega \mid \\ 10 \text{ nF}; 500\Omega \\ \text{THREC}(\text{MAX}) = 0.284 \text{ x } \text{VBB}, \\ \text{THDOM}(\text{MAX}) = 0.422 \text{ x } \text{VBB}, \\ \text{VBB} = 7.6\text{V} - 18\text{V}; \text{tBIT} = 50 \text{\mus}. \\ \text{D2} = \text{tBUS}_{\text{REC}}(\text{MAX}) / 2 \text{ x } \text{tBIT} \end{array}$
Duty Cycle 3 @10.4 kbit/sec		41.7		_	%tBIT	$\begin{array}{l} \mbox{CBUS;RBUS conditions:} \\ 1 \ nF; \ 1 \ k\Omega \mid 6.8 \ nF; \ 660\Omega \mid \\ 10 \ nF; \ 500\Omega \\ THREC(MAX) = 0.778 \ x \ VBB, \\ THDOM(MAX) = 0.616 \ x \ VBB, \\ VBB = 7.0V \ - \ 18V; \ tBIT = 96 \ \mu s. \\ D3 = \ tBUS_REC(MIN) \ / \ 2 \ x \ tBIT) \end{array}$
Duty Cycle 4 @10.4 kbit/sec		_		59.0	%tBIT	$\begin{array}{l} \mbox{CBUS;RBUS conditions:} \\ 1 \ nF; \ 1 \ k\Omega \mid 6.8 \ nF; \ 660\Omega \mid \\ 10 \ nF; \ 500\Omega \\ THREC(MAX) = 0.251 \ x \ VBB, \\ THDOM(MAX) = 0.389 \ x \ VBB, \\ VBB = 7.6V \ - \ 18V; \ tBIT = 96 \ \mu s. \\ D4 = tBUS_REC(MAX) \ / \ 2 \ x \ tBIT) \end{array}$

2.3 AC Specification (Continued)

AC CHARACTERISTICS	VBB = 6.0V to	o 18.0V; Ta	. = -40°C to) +125°C		
Parameter	Sym	Min	Тур	Max	Units	Test Conditions
Voltage Regulator			_	_		
Bus Activity Debounce Time	tBDB	5	10	20	μs	Bus debounce time
Bus Activity to Voltage Regulator Enabled	t BACTVE	100	250	500	μs	After bus debounce time
Voltage Regulator Enabled to Ready	tvevr	_	—	1200	μs	(Note 1)
Chip Select to Operation Ready	tCSOR	_	_	500	μs	(Note 1, 2)
Chip Select to Power-Down	tCSPD	_	_	80	μs	
Short-Circuit to Shut-Down	tSHUTDOWN	20	_	100	μs	
RESET Timing						
VREG OK Detect to RESET	tRPU	—	—	10.0	μs	
VREG OK Detect to RESET Active	tRPD	—	_	10.0	μs	

Note 1: Time depends on external capacitance and load.


2: Design guidance only, not tested.

2.4 Thermal Specifications

THERMAL CHARACTERISTICS


Parameter	Symbol	Тур	Max	Units	Test Conditions
Recovery Temperature	θRECOVERY	+140	—	°C	
Shutdown Temperature	0SHUTDOWN	+150	—	°C	
Short Circuit Recovery Time	t THERM	1.5	5.0	ms	
Thermal Package Resistances	•				
Thermal Resistance, 8L-DFN	θJA	35.7	_	°C/W	
Thermal Resistance, 8L-PDIP	θJA	89.3	—	°C/W	
Thermal Resistance, 8L-SOIC	θJA	149.5	—	°C/W	
Thermal Resistance, 14L-PDIP	θJA	70	—	°C/W	
Thermal Resistance, 14L-SOIC	θJA	95.3	—	°C/W	
Thermal Resistance, 14L-TSSOP	θJA	100	—	°C/W	

Note 1: The maximum power dissipation is a function of TJMAX, Θ JA and ambient temperature T_A. The maximum allowable power dissipation at an ambient temperature is PD = (TJMAX - TA) Θ JA. If this dissipation is exceeded, the die temperature will rise above 150°C and the MCP2021 will go into thermal shutdown.



2.5 Timing Diagrams and Specifications







Regulator CS/LWAKE Timing Diagram.




FIGURE 2-6: Regulator BUS WAKE Timing Diagram.




FIGURE 2-7: RESET Timing Diagram.




FIGURE 2-8:

CS/LWAKE to RESET Timing Diagram.






FIGURE 2-9:

Typical I_{BBQ} vs. Temperature.










FIGURE 2-11: Typical I_{BBPD} vs. Temperature.


3.0 PACKAGING INFORMATION

3.1 Package Marking Information




3.1 Package Marking Information (Continued)





MCP2021	MCP2021P
2021500E	2021P50E


E	kar	nple	
202 SN		500 103	
\bigcirc	Š	25	6



Legend:	Υ	Customer-specific information Year code (last digit of calendar year)
	ΥY	Year code (last 2 digits of calendar year)
	WW	Week code (week of January 1 is week '01')
	NNN	Alphanumeric traceability code
	(e3)	Pb-free JEDEC designator for Matte Tin (Sn)
	*	This package is Pb-free. The Pb-free JEDEC designator ((e_3)) can be found on the outer packaging for this package.
		nt the full Microchip part number cannot be marked on one line, it will dover to the next line, thus limiting the number of available
		s for customer-specific information.

3.1 Package Marking Information (Continued)

14-Lead TSSOP (4.4 mm)



MCP2022	MCP2022P
2022500E	2022P50E


2/10	linpio
2022	2500E
	1033
	256

Example

d: XXX	Customer-specific information
Y	Year code (last digit of calendar year)
ΥY	Year code (last 2 digits of calendar year)
WW	Week code (week of January 1 is week '01')
NNN	Alphanumeric traceability code
(e3)	Pb-free JEDEC designator for Matte Tin (Sn)
*	This package is Pb-free. The Pb-free JEDEC designator ($_{(e3)}$)
	can be found on the outer packaging for this package. \smile
In the eve	nt the full Microchip part number cannot be marked on one line, it will
	d over to the next line, thus limiting the number of available s for customer-specific information.
	WW NNN e3 *

8-Lead Plastic Dual Flat, No Lead Package (MD) – 4x4x0.9 mm Body [DFN]


Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing C04-131E Sheet 1 of 2

8-Lead Plastic Dual Flat, No Lead Package (MD) – 4x4x0.9 mm Body [DFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units MILLIMETERS			S
Dimension	Limits	MIN	NOM	MAX
Number of Pins	Ν		8	
Pitch	е		0.80 BSC	
Overall Height	А	0.80	0.90	1.00
Standoff	A1	0.00	0.02	0.05
Contact Thickness	A3	0.20 REF		
Overall Length	D	4.00 BSC		
Exposed Pad Width	E2	2.60 2.70 2.80		
Overall Width	Е	4.00 BSC		
Exposed Pad Length	D2	3.40	3.50	3.60
Contact Width	b	0.25	0.30	0.35
Contact Length	L	0.30 0.40 0.50		
Contact-to-Exposed Pad	К	0.20	-	-

Notes:


- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Package may have one or more exposed tie bars at ends.
- 3. Package is saw singulated
- 4. Dimensioning and tolerancing per ASME Y14.5M
 - BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-131E Sheet 2 of 2

8-Lead Plastic Dual Flat, No Lead Package (MD) - 4x4x0.9 mm Body [DFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Units		MILLIMETERS		
Dimensio	Dimension Limits		NOM	MAX	
Contact Pitch	E		0.80 BSC		
Optional Center Pad Width	W2	3.6			
Optional Center Pad Length	T2			2.50	
Contact Pad Spacing	C1		4.00		
Contact Pad Width (X8)	X1			0.35	
Contact Pad Length (X8)	Y1			0.75	
Distance Between Pads	G	0.45			

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2131C

8-Lead Plastic Dual Flat, No Lead Package (MF) – 6x5 mm Body [DFN-S]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		MILLIMETERS	
	Dimension Limits	MIN	NOM	MAX
Number of Pins	N		8	
Pitch	e		1.27 BSC	
Overall Height	А	0.80	0.85	1.00
Standoff	A1	0.00	0.01	0.05
Contact Thickness	A3	0.20 REF		
Overall Length	D	5.00 BSC		
Overall Width	E	6.00 BSC		
Exposed Pad Length	D2	3.90	4.00	4.10
Exposed Pad Width	E2	2.20	2.30	2.40
Contact Width	b	0.35	0.40	0.48
Contact Length	L	0.50	0.60	0.75
Contact-to-Exposed Pad	К	0.20	_	_

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Package may have one or more exposed tie bars at ends.

- 3. Package is saw singulated.
- 4. Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.


REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-122B

NOTE

8-Lead Plastic Dual Flat, No Lead Package (MF) - 6x5 mm Body [DFN-S]

For the most current package drawings, please see the Microchip Packaging Specification located at Note: http://www.microchip.com/packaging



NOTE: THIS PACKAGE MAY ALSO BE USED WITH THE 8L SOIC (3.90 mm LAND PATTERN

n)	

Units		MILLIMETERS		
Dimension	Dimension Limits		NOM	MAX
Contact Pitch	E			
Optional Center Pad Width	W2	2.4		
Optional Center Pad Length	T2	4.		4.10
Contact Pad Spacing	С	5.60		
Contact Pad Width (X8)	X1			0.45
Contact Pad Length (X8)	Y1	1.10		

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2122A

8-Lead Plastic Dual In-Line (P) – 300 mil Body [PDIP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		INCHES	
Dimensio	n Limits	MIN	NOM	MAX
Number of Pins	Ν		8	
Pitch	е		.100 BSC	
Top to Seating Plane	Α	-	-	.210
Molded Package Thickness	A2	.115	.130	.195
Base to Seating Plane	A1	.015	-	-
Shoulder to Shoulder Width	Е	.290	.310	.325
Molded Package Width	E1	.240	.250	.280
Overall Length	D	.348	.365	.400
Tip to Seating Plane	L	.115	.130	.150
Lead Thickness	С	.008	.010	.015
Upper Lead Width	b1	.040	.060	.070
Lower Lead Width	b	.014	.018	.022
Overall Row Spacing §	eB	-	-	.430

Notes:

1. Pin 1 visual index feature may vary, but must be located with the hatched area.

2. § Significant Characteristic.

3. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed .010" per side.


4. Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-018B

8-Lead Plastic Small Outline (SN) - Narrow, 3.90 mm Body [SOIC]


Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing No. C04-057C Sheet 1 of 2

8-Lead Plastic Small Outline (SN) - Narrow, 3.90 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS			
Dimensior	Dimension Limits		NOM	MAX
Number of Pins	N		8	
Pitch	е		1.27 BSC	
Overall Height	Α	-	-	1.75
Molded Package Thickness	A2	1.25	-	-
Standoff §	A1	0.10	-	0.25
Overall Width	Е	6.00 BSC		
Molded Package Width	E1	3.90 BSC		
Overall Length	D	4.90 BSC		
Chamfer (Optional)	h	0.25	-	0.50
Foot Length	L	0.40	-	1.27
Footprint	L1		1.04 REF	
Foot Angle	φ	0° - 8°		
Lead Thickness	с	0.17 - 0.25		
Lead Width	b	0.31 - 0.51		
Mold Draft Angle Top	α	5° - 15°		
Mold Draft Angle Bottom	β	5°	-	15°

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. § Significant Characteristic

3. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15mm per side.

4. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing No. C04-057C Sheet 2 of 2

8-Lead Plastic Small Outline (SN) – Narrow, 3.90 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX	
Contact Pitch	E	1.27 BSC			
Contact Pad Spacing	С		5.40		
Contact Pad Width (X8)	X1			0.60	
Contact Pad Length (X8)	Y1			1.55	

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2057A

14-Lead Plastic Dual In-Line (P) – 300 mil Body [PDIP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		INCHES	
Dimensior	n Limits	MIN	NOM	MAX
Number of Pins	Ν		14	
Pitch	е		.100 BSC	
Top to Seating Plane	Α	-	-	.210
Molded Package Thickness	A2	.115	.130	.195
Base to Seating Plane	A1	.015	_	-
Shoulder to Shoulder Width	E	.290	.310	.325
Molded Package Width	E1	.240	.250	.280
Overall Length	D	.735	.750	.775
Tip to Seating Plane	L	.115	.130	.150
Lead Thickness	С	.008	.010	.015
Upper Lead Width	b1	.045	.060	.070
Lower Lead Width	b	.014	.018	.022
Overall Row Spacing §	eB	_	_	.430

Notes:

1. Pin 1 visual index feature may vary, but must be located with the hatched area.


- 2. § Significant Characteristic.
- 3. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed .010" per side.
- 4. Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.


Microchip Technology Drawing C04-005B


14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging




TOP VIEW











14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging





VIEW C

Units		MILLIMETERS			
Dimension Limits		MIN	NOM	MAX	
Number of Pins	N		14		
Pitch	е		1.27 BSC		
Overall Height	A	-	-	1.75	
Molded Package Thickness	A2	1.25	-	-	
Standoff §	A1	0.10	-	0.25	
Overall Width	E	6.00 BSC			
Molded Package Width	E1	3.90 BSC			
Overall Length	D	8.65 BSC			
Chamfer (Optional)	h	0.25 0.50			
Foot Length	L	0.40	-	1.27	
Footprint	L1		1.04 REF		
Lead Angle	Θ	0°	-	-	
Foot Angle	φ	0° - 8°			
Lead Thickness	С	0.10 - 0.25			
Lead Width	b	0.31	-	0.51	
Mold Draft Angle Top	α	5° - 15°			
Mold Draft Angle Bottom	β	5°	-	15°	

Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. § Significant Characteristic

 Dimension D does not include mold flash, protrusions or gate burrs, which shall not exceed 0.15 mm per end. Dimension E1 does not include interlead flash or protrusion, which shall not exceed 0.25 mm per side.

4. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances. REF: Reference Dimension, usually without tolerance, for information purposes only.

5. Datums A & B to be determined at Datum H.

Microchip Technology Drawing No. C04-065C Sheet 2 of 2

14-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

	Units	N	S	
Dimension	Dimension Limits		NOM	MAX
Contact Pitch	E	1.27 BSC		
Contact Pad Spacing	С	5.40		
Contact Pad Width	Х	0.6		0.60
Contact Pad Length	Y	1.50		
Distance Between Pads	Gx	0.67		
Distance Between Pads	G	3.90		

Notes:


1. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2065A

14-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging






Microchip Technology Drawing C04-087C Sheet 1 of 2

14-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Units		MILLIMETERS			
Dimension Limits		MIN	NOM	MAX	
Number of Pins	N	14			
Pitch	е	0.65 BSC			
Overall Height	А	-	-	1.20	
Molded Package Thickness	A2	0.80	1.00	1.05	
Standoff	A1	0.05	-	0.15	
Overall Width	E	6.40 BSC			
Molded Package Width	E1	4.30	4.40	4.50	
Molded Package Length	D	4.90	5.00	5.10	
Foot Length	L	0.45	0.60	0.75	
Footprint	(L1)	1.00 REF			
Foot Angle	φ	0°	-	8°	
Lead Thickness	С	0.09	-	0.20	
Lead Width	b	0.19	-	0.30	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15mm per side.

3. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing No. C04-087C Sheet 2 of 2

14-Lead Plastic Thin Shrink Small Outline (ST) - 4.4 mm Body [TSSOP]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E		0.65 BSC	
Contact Pad Spacing	C1		5.90	
Contact Pad Width (X14)	X1			0.45
Contact Pad Length (X14)	Y1			1.45
Distance Between Pads	G	0.20		

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2087A

MCP2021/2/1P/2P

NOTES:

APPENDIX A: REVISION HISTORY

Revision G (July 2013)

The following has been modified:

- 1. Added Note 2 in Section 2.3 "AC Specification".
- 2. Added pull up to nFAULT/TXE pin in Section 1.4 "Pin Descriptions" and Section 1.5 "Typical Applications".

Revision F (January 2012)

The following has been modified:

1. Added the MCP2021P and MCP2022P options and related information throughout the document.

Revision E (February 2009)

The following is the list of modifications:

- 1. Added Example 1-7 and Example 1-8.
- 2. Updated Section 1.4.9 "RESET".
- 3. Updated Section 1.7 "ICSP™ Considerations".
- 4. Updated Section 2.1 "Absolute Maximum Ratings†".
- 5. Updated Section 2.2 "DC Specifications" and Section 2.3 "AC Specification".
- 6. Added FIGURE 2-3: "ESR Curves for Load Capacitor Selection.".
- 7. Updated the Product Identification System section.

Revision D (July 2008)

The following is the list of modifications:

- 1. Updated ESD specs under 'Absolute DC'.
- 2. Updated notes in Example 1-1.
- 3. Updated Package Outline Drawings.

Revision C (April 2008)

The following is the list of modifications:

- 1. Added LIN2.1 and J2602 compliance statement to Features section.
- 2. Added recommended RC network for CS/ LWAKE in Example 1-1.
- 3. Updated **2.1 "Absolute Maximum Ratings†"** to reflect current test results.
- Updated 2.2 "DC Specifications" and 2.3 "AC Specification" 2.3 AC Specifications to reflect current production device.
- 5. Added 8-Lead SOIC Landing Pattern Outline drawing.

Revision B (August 2007)

The following is the list of modifications:

- 1. Modified Block Diagram on page 2.
- 2. Section 1.3.5 "Transmitter-OFF Mode": Deleted text in 1st paragraph.
- 3. Example 1-6: Removed +5V notation.
- 4. Section 1.4 "Pin Descriptions": Removed 10pin DFN, MSOP column from table.
- 5. Section 1.4.8 "Fault/TXE": Deleted text from 2nd paragraph.
- Section 3.0 "Packaging Information": Added 8-lead 4x4 and 6x5 DFN and 14-lead TSSOP packages. Updated package outline drawings and added drawings for 8-lead DFN and 14-lead TSSOP drawings.

Revision A (November 2005)

Original Release of this Document.

MCP2021/2/1P/2P

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NOX /XX		Examples:
Device	Temperature Range Package MCP2021: LIN Transceiver with Voltage Regulator; wakes dominant level of LIN bus. MCP2021T: LIN Transceiver with Voltage Regulator; wakes	f) MCP2021-500E/P: 5.0V, 8L-PDIP pkg.
	MCP2022: LIN Transceiver with Voltage Regulator, and RE pin; wakes up on dominant level of LIN bus. MCP2022: LIN Transceiver with Voltage Regulator, and RE pin; wakes up on dominant level of LIN bus. MCP2022T: LIN Transceiver with Voltage Regulator, and RE pin; wakes up on dominant level of LIN bus. (Tape and Reel) (SOIC only)	set 3.3V, 8L-SOIC pkg. h) MCP2021T-500E/MD: Tape and Reel, 5.0V, 8L-DFN pkg. iii) MOD0004T E00E/(Nh)
Temperature Range:	 MCP2021P: LIN Transceiver with Voltage Regulator; wakes falling edge of LIN bus level. MCP2021PT: LIN Transceiver with Voltage Regulator; wakes falling edge of LIN bus level (Tape and Reel) (SOIC only) MCP2022P: LIN Transceiver with Voltage Regulator, and RE pin; wakes up at a falling edge of LIN bus level. MCP2022PT: LIN Transceiver with Voltage Regulator, and RE pin; wakes up at a falling edge of LIN bus level. MCP2022PT: LIN Transceiver with Voltage Regulator, and RE pin; wakes up at a falling edge of LIN bus level. (Tape and Reel) (SOIC only) E = -40°C to +125°C 	b) MCP2022-330E/P: 3.3V, 14L-PDIP pkg. up at a c) MCP2022-500E/SL: 5.0V, 14L-SOIC pkg. d) MCP2022-500E/P: 5.0V, 14L-PDIP pkg. sET e) MCP2022T-330E/SL: Tape and Reel, 3.3V, 14L-SOIC pkg. 3.3V, 14L-SOIC pkg. 3.3V, 14L-SOIC pkg.
Package:	MD = Plastic Micro Small Outline (4x4), 8-lead MF = Plastic Micro Small Outline (6x5), 8-lead P = Plastic DIP (300 mil Body), 8-lead, 14-lead SN = Plastic SOIC, (150 mil Body), 8-lead SL = Plastic SOIC, (150 mil Body), 14-lead ST = Plastic Thin Shrink Small Outline, 14-lead	

MCP2021/2/1P/2P

NOTES:

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

Trademarks

The Microchip name and logo, the Microchip logo, dsPIC, FlashFlex, KEELOQ, KEELOQ logo, MPLAB, PIC, PICmicro, PICSTART, PIC³² logo, rfPIC, SST, SST Logo, SuperFlash and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

FilterLab, Hampshire, HI-TECH C, Linear Active Thermistor, MTP, SEEVAL and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

Analog-for-the-Digital Age, Application Maestro, BodyCom, chipKIT, chipKIT logo, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, dsSPEAK, ECAN, ECONOMONITOR, FanSense, HI-TIDE, In-Circuit Serial Programming, ICSP, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, mTouch, Omniscient Code Generation, PICC, PICC-18, PICDEM, PICDEM.net, PICkit, PICtail, REAL ICE, rfLAB, Select Mode, SQI, Serial Quad I/O, Total Endurance, TSHARC, UniWinDriver, WiperLock, ZENA and Z-Scale are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

GestIC and ULPP are registered trademarks of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2005-2013, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

Rinted on recycled paper.

ISBN: 978-1-62077-345-1

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and mulfacture of development systems is ISO 9001:2000 certified.



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Cleveland Independence, OH Tel: 216-447-0464 Fax: 216-447-0643

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Farmington Hills, MI Tel: 248-538-2250 Fax: 248-538-2260

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

Santa Clara Santa Clara, CA Tel: 408-961-6444 Fax: 408-961-6445

Toronto Mississauga, Ontario, Canada Tel: 905-673-0699 Fax: 905-673-6509

ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway Harbour City, Kowloon Hong Kong Tel: 852-2401-1200 Fax: 852-2401-3431 Australia - Sydney

Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

China - Beijing Tel: 86-10-8569-7000 Fax: 86-10-8528-2104

China - Chengdu Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Chongqing Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

China - Hangzhou Tel: 86-571-2819-3187 Fax: 86-571-2819-3189

China - Hong Kong SAR Tel: 852-2943-5100

Fax: 852-2401-3431 China - Nanjing

Tel: 86-25-8473-2460 Fax: 86-25-8473-2470 **China - Qingdao** Tel: 86-532-8502-7355

Fax: 86-532-8502-7205 China - Shanghai

Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

China - Shenzhen Tel: 86-755-8864-2200 Fax: 86-755-8203-1760

China - Wuhan Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

China - Xian Tel: 86-29-8833-7252 Fax: 86-29-8833-7256

China - Xiamen Tel: 86-592-2388138 Fax: 86-592-2388130

China - Zhuhai Tel: 86-756-3210040 Fax: 86-756-3210049

ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4123

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-2566-1512 Fax: 91-20-2566-1513

Japan - Osaka Tel: 81-6-6152-7160 Fax: 81-6-6152-9310

Japan - Tokyo Tel: 81-3-6880- 3770 Fax: 81-3-6880-3771

Korea - Daegu Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

Malaysia - Penang Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

Singapore Tel: 65-6334-8870 Fax: 65-6334-8850

Taiwan - Hsin Chu Tel: 886-3-5778-366 Fax: 886-3-5770-955

Taiwan - Kaohsiung Tel: 886-7-213-7828 Fax: 886-7-330-9305

Taiwan - Taipei Tel: 886-2-2508-8600 Fax: 886-2-2508-0102

Thailand - Bangkok Tel: 66-2-694-1351 Fax: 66-2-694-1350

EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4450-2828

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Fax: 45-4485-2829

Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

UK - Wokingham Tel: 44-118-921-5869 Fax: 44-118-921-5820