

# **TPS54528EVM-052, 5-A, SWIFT™ Regulator Evaluation Module**

This user's guide contains information for the TPS54528 as well as support documentation for the TPS54528EVM-052 evaluation module. Included are the performance specifications, schematic, and the bill of materials of the TPS54528EVM-052.

## **Contents**

1	Introduction .....	3
2	Performance Specification Summary .....	3
3	Modifications .....	3
3.1	Output Voltage Setpoint .....	3
3.2	Output Filter and Closed-Loop Response .....	4
4	Test Setup and Results .....	4
4.1	Input/Output Connections .....	4
4.2	Start-Up Procedure .....	5
4.3	Efficiency .....	5
4.4	Load Regulation .....	6
4.5	Line Regulation .....	6
4.6	Load Transient Response .....	7
4.7	Output Voltage Ripple .....	8
4.8	Input Voltage Ripple .....	9
4.9	Start-Up .....	10
5	Board Layout .....	11
5.1	Layout .....	12
6	Schematic, Bill of Materials, and Reference .....	14
6.1	Schematic .....	14
6.2	Bill of Materials .....	15
6.3	Reference .....	15

## **List of Figures**

1	TPS54528EVM-052 Efficiency .....	5
2	TPS54528EVM-052 Light-Load Efficiency.....	5
3	TPS54528EVM-052 Load Regulation, $V_{IN} = 5\text{ V}$ and $V_{IN} = 12\text{ V}$ .....	6
4	TPS54528EVM-052 Line Regulation.....	6
5	TPS54528EVM-052 Load Transient Response, 1.25 A to 3.75 A .....	7
6	TPS54528EVM-052 Load Transient Response, 0 A to 2.5 A.....	7
7	TPS54528EVM-052 Output Voltage Ripple .....	8
8	TPS54528EVM-052 Start of Eco-mode™ Output Voltage Ripple.....	8
9	TPS54528EVM-052 Eco-mode™ Output Voltage Ripple .....	9
10	TPS54528EVM-052 Input Voltage Ripple .....	9
11	TPS54528EVM-052 Start-Up Relative to $V_{IN}$ With SS.....	10
12	TPS54528EVM-052 Start-Up Relative to $V_{IN}$ With VREG5 .....	10
13	TPS54528EVM-052 Start-Up Relative to EN With SS .....	11
14	TPS54528EVM-052 Start-Up Relative to EN With VREG5.....	11

SWIFT, Eco-mode, D-CAP2 are trademarks of Texas Instruments.

15	Top Assembly .....	12
16	Top Layer .....	12
17	Internal Layer 1 .....	13
18	Internal Layer 2 .....	13
19	Bottom Layer .....	14
20	TPS54528EVM-052 Schematic Diagram .....	14

#### List of Tables

1	Input Voltage and Output Current Summary .....	3
2	TPS54528EVM-052 Performance Specifications Summary .....	3
3	Output Voltages .....	4
4	Connection and Test Points .....	4
5	Bill of Materials .....	15

## 1 Introduction

The TPS54528 is a single, adaptive on-time, D-CAP2™-mode, synchronous buck converter requiring a low, external component count. The D-CAP2™ control circuit is optimized for low-ESR output capacitors such as POSCAP, SP-CAP, or ceramic types and features fast transient response with no external compensation. The switching frequency is internally set at a nominal 650 kHz. The high-side and low-side switching MOSFETs are incorporated inside the TPS54528 package along with the gate drive circuitry. The low drain-to-source on resistance of the MOSFETs allows the TPS54528 to achieve high efficiencies and helps keep the junction temperature low at high-output currents. The TPS54528 also features auto-skip Eco-mode™ operation for improved light-load efficiency. The TPS54528 dc/dc synchronous converter is designed to provide up to a 5-A output from an input voltage source of 4.5 V to 18 V. The output voltage range is from 0.76 V to 6 V. Rated input voltage and output current range for the evaluation module are given in [Table 1](#).

The TPS54528EVM-052 evaluation module is a single, synchronous buck converter providing 1.05 V at 5 A from 4.5-V to 18-V input. This user's guide describes the TPS54528EVM-052 performance.

**Table 1. Input Voltage and Output Current Summary**

EVM	Input Voltage Range	Output Current Range
TPS54528EVM-052	$V_{IN} = 4.5 \text{ V to } 18 \text{ V}$	0 A to 5 A

## 2 Performance Specification Summary

A summary of the TPS54528EVM-052 performance specifications is provided in [Table 2](#). Specifications are given for an input voltage of  $V_{IN} = 12 \text{ V}$  and an output voltage of 1.05 V, unless otherwise noted. The ambient temperature is 25°C for all measurement, unless otherwise noted.

**Table 2. TPS54528EVM-052 Performance Specifications Summary**

Specifications	Test Conditions	Min	Typ	Max	Unit
Input voltage range ( $V_{IN}$ )		4.5	12	18	V
Output voltage			1.05		V
Operating frequency	$V_{IN} = 12 \text{ V}, I_O = 2 \text{ A}$		650		kHz
Output current range		0		5	A
Line regulation	$I_O = 2.5 \text{ A}$		+/- 0.33		%
Load regulation	$V_{IN} = 12 \text{ V}$		+0.9/- 0.1		%
Overcurrent limit	$V_{IN} = 12 \text{ V}, L_O = 1.5 \mu\text{H}$	5.6	6.4	7.9	A
Output ripple voltage	$V_{IN} = 12 \text{ V}, I_O = 5 \text{ A}$		15		mV <sub>PP</sub>
Maximum efficiency	$V_{IN} = 5 \text{ V}, I_O = 0.7 \text{ A}$		87.8		%

## 3 Modifications

These evaluation modules are designed to provide access to the features of the TPS54528. Some modifications can be made to this module.

### 3.1 Output Voltage Setpoint

To change the output voltage of the EVMs, it is necessary to change the value of resistor R1. Changing the value of R1 can change the output voltage above 0.765 V. The value of R1 for a specific output voltage can be calculated using [Equation 1](#).

For output voltage from 0.76 V to 6 V:

$$VO = 0.765 \times \left( 1 + \frac{R1}{R2} \right) \quad (1)$$

Table 3 lists the R1 values for some common output voltages. For higher output voltages of 1.8 V or above, a feedforward capacitor (C4) may be required to improve phase margin. Pads for this component (C4) are provided on the printed-circuit board. Note that the resistor values given in Table 3 are standard values and not the exact value calculated using Equation 1.

**Table 3. Output Voltages**

Output Voltage (V)	R1 (k $\Omega$ )	R2 (k $\Omega$ )	C4 (pF)	L1 ( $\mu$ H)	C9, C10, C11 Total Capacitance ( $\mu$ F)
1	6.81	22.1		1 - 1.5	22 - 68
1.05	8.25	22.1		1 - 1.5	22 - 68
1.2	12.7	22.1		1 - 1.5	22 - 68
1.5	21.5	22.1		1.5	22 - 68
1.8	30.1	22.1	5 - 22	1.5	22 - 68
2.5	49.9	22.1	5 - 22	2.2	22 - 68
3.3	73.2	22.1	5 - 22	2.2	22 - 68
5	124	22.1	5 - 22	3.3	22 - 68

### 3.2 Output Filter and Closed-Loop Response

The TPS54528 relies on the output filter characteristics to ensure stability of the control loop. The recommended output filter components for common output voltages are given in Table 3. It may be possible for other output filter component values to provide acceptable closed-loop characteristics. R3 and TP4 are provided for convenience in breaking the control loop and measuring the closed-loop response.

## 4 Test Setup and Results

This section describes how to properly connect, set up, and use the TPS54528EVM-052. It also includes test results typical for the evaluation module and efficiency, output load regulation, output line regulation, load transient response, output voltage ripple, input voltage ripple, start-up, and switching frequency.

### 4.1 Input/Output Connections

Table 4 shows the input/output connectors and test points of TPS54528EVM-052. Connect a power supply capable of supplying 2 A to J1 through a pair of 20 AWG wires. Connect the load to J2 through a pair of 20 AWG wires. The maximum load current capability is 5 A. Minimize wire lengths to reduce losses in the wires. Test point TP1 provides a place to monitor the input voltages ( $V_{IN}$ ) with TP2 providing a convenient ground reference. Use TP8 to monitor the output voltage with TP9 as the ground reference.

**Table 4. Connection and Test Points**


Reference Designator	Function
J1	$V_{IN}$ (See Table 1 for $V_{IN}$ range.)
J2	$V_{OUT}$ , 1.05 V at 5 A maximum
JP1	EN control. Connect EN to OFF to disable, connect EN to ON to enable
TP1	$V_{IN}$ test point at $V_{IN}$ connector
TP2	GND test point at $V_{IN}$
TP3	EN test point
TP4	Loop response measurement test point
TP5	VREG5 test point
TP6	Switch node test point
TP7	Analog ground test point
TP8	Output voltage test point
TP9	Ground test point at output connector

## 4.2 Start-Up Procedure

1. Ensure that the jumper at JP1 (Enable control) is set from EN to OFF.
2. Apply appropriate  $V_{IN}$  voltage to VIN and PGND terminals at J1.
3. Move the jumper at JP1 (Enable control) to cover EN and ON. The EVM enables the output voltage.

## 4.3 Efficiency


Figure 1 shows the efficiency for the TPS54528EVM-052 at an ambient temperature of 25°C.



G001

**Figure 1. TPS54528EVM-052 Efficiency**

Figure 2 shows the efficiency at light loads for the TPS54528EVM-052 at an ambient temperature of 25°C.




G002

**Figure 2. TPS54528EVM-052 Light-Load Efficiency**

## 4.4 Load Regulation

The load regulation for the TPS54528EVM-052 is shown in Figure 3.




G003

Figure 3. TPS54528EVM-052 Load Regulation,  $V_{IN} = 5\text{ V}$  and  $V_{IN} = 12\text{ V}$

## 4.5 Line Regulation

The line regulation for the TPS54528EVM-052 is shown in Figure 4.




G004


Figure 4. TPS54528EVM-052 Line Regulation

## 4.6 Load Transient Response

The TPS54528EVM-052 response to load transient steps are shown in Figure 5 and Figure 6. Total peak-to-peak voltage variation is as shown.




**Figure 5. TPS54528EVM-052 Load Transient Response, 1.25 A to 3.75 A**



**Figure 6. TPS54528EVM-052 Load Transient Response, 0 A to 2.5 A**


## 4.7 Output Voltage Ripple

The TPS54528EVM-052 output voltage ripple is shown in Figure 7. The output current is the rated full load of 5 A.



**Figure 7. TPS54528EVM-052 Output Voltage Ripple**


The TPS54528EVM-052 output voltage ripple during the start of Eco-mode™ operation is shown in Figure 8. The output current is 30 mA.



**Figure 8. TPS54528EVM-052 Start of Eco-mode™ Output Voltage Ripple**




The TPS54528EVM-052 output voltage ripple during Eco-mode™ operation is shown in Figure 9. The output current is 2.1 mA.



**Figure 9. TPS54528EVM-052 Eco-mode™ Output Voltage Ripple**

#### 4.8 Input Voltage Ripple


The TPS54528EVM-052 input voltage ripple is shown in Figure 10. The output current is the rated full load of 5 A.




**Figure 10. TPS54528EVM-052 Input Voltage Ripple**

## 4.9 Start-Up

The TPS54528EVM-052 start-up waveforms relative to  $V_{IN}$  are shown in [Figure 11](#) and [Figure 12](#).




**Figure 11. TPS54528EVM-052 Start-Up Relative to  $V_{IN}$  With SS**




**Figure 12. TPS54528EVM-052 Start-Up Relative to  $V_{IN}$  With VREG5**

The TPS54528EVM-052 start-up waveforms relative to enable (EN) are shown in [Figure 13](#) and [Figure 14](#).



**Figure 13. TPS54528EVm-052 Start-Up Relative to EN With SS**



**Figure 14. TPS54528EVm-052 Start-Up Relative to EN With VREG5**

## 5 Board Layout

This section provides description of the TPS54528EVm-052, board layout, and layer illustrations.

## 5.1 Layout

The board layout for the TPS54528EVM-052 is shown in Figure 15 through Figure 19. The top layer contains the main power traces for VIN, VO, and ground. Also on the top layer are connections for the pins of the TPS54528 and a large area filled with ground. Many of the signal traces also are located on the top side. The input decoupling capacitors are located as close to the IC as possible. The input and output connectors, test points, and all of the components are located on the top side. An analog ground (GND) area is provided on the top side. Analog ground (GND) and power ground (PGND) are connected at a single point on the top layer near C6. The bottom layer is primarily power ground but also has a trace to connect VIN to the enable jumper, a trace to connect VREG5 to TP5, and the feedback trace from VOUT to the voltage setpoint divider network.




Figure 15. Top Assembly






Figure 16. Top Layer



**Figure 17. Internal Layer 1**



**Figure 18. Internal Layer 2**




Figure 19. Bottom Layer

## 6 Schematic, Bill of Materials, and Reference

### 6.1 Schematic

Figure 20 is the schematic for the TPS54528EVM-052.




Figure 20. TPS54528EVM-052 Schematic Diagram

## 6.2 Bill of Materials

**Table 5. Bill of Materials**

RefDes	Qty	Value	Description	Size	Part Number	MFR
C1, C2	2	10uF	Capacitor, Ceramic, 25V, X5R, 20%	1210	Std	Std
C11	0	Open	Capacitor, Ceramic	1206	Std	Std
C3, C7	2	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	Std	Std
C4, C8	1	Open	Capacitor, Ceramic	0603	Std	Std
C5	1	1.0uF	Capacitor, Ceramic, 16V, X7R, 10%	0603	Std	Std
C6	1	8200pF	Capacitor, Ceramic, 25V, X7R, 10%	0603	Std	Std
C9, C10	2	22uF	Capacitor, Ceramic, 6.3V, X5R, 20%	1206	C3216X5R0J226M	TDK
J1, J2	2	ED555/2DS	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25 inch	ED555/2DS	Sullins
JP1	1	PEC03SAAN	Header, Male 3-pin, 100mil spacing	0.100 inch x 3	PEC03SAAN	Sullins
L1	1	1.5uH	Inductor, SMT, 11 A, 9.7 mΩ	0.256 x 0.280 inch	SPM6530T-1R5M100	TDK
R1	1	8.25k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
R2	1	22.1k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
R3	1	0	Resistor, Chip, 1/16W, 1%	0603	Std	Std
R4	1	10.0k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
R5	0	Open	Resistor, Chip, 1/16W, 1%	0603	Std	Std
TP1, TP3, TP4, TP5, TP6, TP8	3	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
TP2, TP7, TP9	3	5001	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone
U1	1	TPS54528DDA	IC, 5-A Output Single Sync. Step-Down	SO8[DDA]	TPS54528DDA	TI
–	1		Shunt, 100-mil, Black	0.100	929950-00	3M
–	1		PCB, 2.76 In x 1.97 In x 0.062 In		PWR052	Any

## 6.3 Reference

1. *TPS54528, 4.5V to 18V Input, 5-A Synchronous Step-Down SWIFT™ Converter With Eco-mode™* data sheet ([SLVSAY4](#))

## Evaluation Board/Kit Important Notice

Texas Instruments (TI) provides the enclosed product(s) under the following conditions:

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. Persons handling the product(s) must have electronics training and observe good engineering practice standards. As such, the goods being provided are not intended to be complete in terms of required design-, marketing-, and/or manufacturing-related protective considerations, including product safety and environmental measures typically found in end products that incorporate such semiconductor components or circuit boards. This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and therefore may not meet the technical requirements of these directives or other related directives.

Should this evaluation board/kit not meet the specifications indicated in the User's Guide, the board/kit may be returned within 30 days from the date of delivery for a full refund. THE FOREGOING WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE.

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user indemnifies TI from all claims arising from the handling or use of the goods. Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge.

EXCEPT TO THE EXTENT OF THE INDEMNITY SET FORTH ABOVE, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

TI currently deals with a variety of customers for products, and therefore our arrangement with the user **is not exclusive**.

TI assumes **no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein**.

Please read the User's Guide and, specifically, the Warnings and Restrictions notice in the User's Guide prior to handling the product. This notice contains important safety information about temperatures and voltages. For additional information on TI's environmental and/or safety programs, please contact the TI application engineer or visit [www.ti.com/esh](http://www.ti.com/esh).

No license is granted under any patent right or other intellectual property right of TI covering or relating to any machine, process, or combination in which such TI products or services might be or are used.

## FCC Warning

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. It generates, uses, and can radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment in other environments may cause interference with radio communications, in which case the user at his own expense will be required to take whatever measures may be required to correct this interference.

## EVM Warnings and Restrictions

It is important to operate this EVM within the input voltage range of 4.5 V to 18 V and the output voltage range of 0.76 V to 6 V .

Exceeding the specified input range may cause unexpected operation and/or irreversible damage to the EVM. If there are questions concerning the input range, please contact a TI field representative prior to connecting the input power.

Applying loads outside of the specified output range may result in unintended operation and/or possible permanent damage to the EVM. Please consult the EVM User's Guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative.

During normal operation, some circuit components may have case temperatures greater than 85°C. The EVM is designed to operate properly with certain components above 85°C as long as the input and output ranges are maintained. These components include but are not limited to linear regulators, switching transistors, pass transistors, and current sense resistors. These types of devices can be identified using the EVM schematic located in the EVM User's Guide. When placing measurement probes near these devices during operation, please be aware that these devices may be very warm to the touch.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated



## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
Wireless	<a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated