


<b>Specification</b>				
<b>Part Number:</b>	MCT062A6W640320LWL			
<b>Version:</b>	1			
<b>Date:</b>	25/02/2015			
<b>Revision</b>				
<b>No.</b>	<b>Date</b>	<b>Description</b>	<b>Item</b>	<b>Page</b>
				

# Contents

	Page
2. General Specification	4
3. Module Classification Information	5
4. Interface Pin Function	6
5. Mechanical Drawing	7
6. Block Diagram	8
7. Absolute Maximum Ratings	9
8. Electrical Characteristics	10
9. DC Characteristics	10
10. Interface Timing	11
11. Optical Characteristics	15
12. Reliability	17
13. Package Specification	18
14. Initial Code For Reference	20

MIDAS

design • manufacture • supply

## 2. General Specification

- Resolution: 640 x 320
- Module dimension: 170.32 x 88.3 x 5.3mm
- Active Area : 140.0 x 70.0 mm
- Dot pitch: 0.21875 x 0. 21875 mm
- LCD type: TFT, Negative , Transmissive
- View direction: Wide View
- Backlight Type: LED, Normally Black

\*Color tone slight changed by temperature and driving voltage.

MIDAS  
design • manufacture • supply



## 4. Interface Pin Function

### 4.1. LCM PIN Definition

Pin	Symbol	Function	Remark
1	GND	System ground	
2	VDD	Power Supply : +3.3V	
3	NC	No connect	
4	A0	Data/Command select	
5	/WR(R/W)	Write strobe signal	
6	/RD(E)	Read strobe signal	
7	DB0	Data bus	
8	DB1	Data bus	
9	DB2	Data bus	
10	DB3	Data bus	
11	DB4	Data bus	
12	DB5	Data bus	
13	DB6	Data bus	
14	DB7	Data bus	
15	/CS	Chip select	
16	/RESET(RSTB)	Hardware reset	
17	IF0	Mode select	Note1
18	IF1		
19	NC	No connect	
20	NC	No connect	
21	NC	No connect	
22	NC	No connect	

Note1:

Setting		MCU Type	Interface Pin Function				
IF1	IF0		CSB	A0	RWR	ERD	D[7:0]
L	L	Parallel 8080 series MCU	CSB	A0	/WR	/RD	D[7:0]
L	H	Parallel 6800 series MCU			R/W	E	
H	H	Serial 4-Line series MCU			-	-	D7=SCL, D0=SDA, D[6:1] are not used
H	L	Serial 3-Line series MCU			-	-	


The un-used pins are marked as “-” and should be connected to “H” by VDDI.

### 4.2. Backlight Unit Section(CN2)


LED Light Bar connector is used for the the integral backlight system. The recommended model is “JST XH-3” manufactured by JST.

Pin No.	Symbol	I/O	Function	Remark
1	V <sub>LED+</sub>	P	Power for LED backlight anode (A)	Red
3	V <sub>LED-</sub>	P	Power for LED backlight cathode (K)	Black

# 5. Mechanical Drawing



## 6. Block Diagram




## 7. Absolute Maximum Ratings

Item	Symbol	Min	Typ	Max	Unit
Operating Temperature	TOP	-20	—	+70	°C
Storage Temperature	TST	-30	—	+80	°C

Note: Device is subject to be damaged permanently if stresses beyond those absolute maximum ratings listed above

1. Temp.  $\leq 60^{\circ}\text{C}$ , 90% RH MAX. Temp.  $> 60^{\circ}\text{C}$ , Absolute humidity shall be less than 90% RH at  $60^{\circ}\text{C}$



MIDAS

design • manufacture • supply



## 8. Electrical Characteristics


### 8.1. Operating conditions:

Item	Symbol	Condition	Min	Typ	Max	Unit	Remark
Supply Voltage For LCM	VDD	—	3.0	3.3	3.6	V	
Supply Current For LCM	IDD	—	—	25	38	mA	Note1
Power Consumption	—	—	—	83	137	mW	

Note1: This value is test for VDD=3.3V only

### 8.2 LED driving conditions

Parameter	Symbol	Min.	Typ.	Max.	Unit	Remark
LED current		-	160	-	mA	
Power Consumption		1392	-	1680	mW	
LED voltage	A-K	8.7	9.6	10.5	V	Note 1
LED Life Time		-	20,000	-	Hr	Note 2,3,4



Note 1 : Power supply the back light specification

Note 2 :  $T_a = 25^\circ\text{C}$

Note 3 : Brightness to be decreased to 50% of the initial value


Note 4 : The single LED lamp case

## 9. DC Characteristics

Parameter	Symbol	Rating			Unit	Condition
		Min	Typ	Max		
Low level input voltage	$V_{IL}$	0	-	0.3VDD	V	
High level input voltage	$V_{IH}$	0.7VDD	-	VDD	V	

# 10. AC Characteristics

## 10.1 System Bus Timing for 6800 Series MPU




Item	Signal	Symbol	Condition	Min	Max	Unit
Address setup time	A0	tAW6	-	10	-	ns
Address hold time	A0	tAH6	-	0	-	
System cycle time		tCYC6	-	200	-	
Enable L pulse width (WRITE)	E	tEHLW	-	100	-	
Enable H pulse width (WRITE)	E	tEHLR	-	100	-	
Enable L pulse width (READ)	E	tEHWL	-	130	-	
Enable H pulse width (READ)	E	tEHWL	-	130	-	
CSB setup time	CSB	tCSS6	-	100	-	
CSB hold time	CSB	tCSH6	-	100	-	
Write data setup time	D[7:0]	tDS6	-	70	-	
Write data hold time	D[7:0]	tDH6	-	20	-	
Read data access time	D[7:0]	tACC6	CL = 100 pF	-	80	
Read data output disable time	D[7:0]	tOH6	CL = 100 pF	15	80	

Note:

1. The input signal rise time and fall time (tr, tf) is specified at 15 ns or less. When the system cycle time is extremely fast,  $(tr + tf) \leq (tCYC6 - tCCLW - tCCHW)$  for  $(tr + tf) \leq (tCYC6 - tCCLR - tCCHR)$  are specified.
2. All timing is specified using 20% and 80% of VDDI as the reference.
3. tCCLW and tCCLR are specified as the overlap between CSB being "L" and /WR and /RD being at the "L" level. CSB and /WR (or /RD) cannot act at the same time and CSB should be 100ns wider than /WR (or /RD).

## 10.2 System Bus Timing for 8080 Series MPU




Item	Signal	Symbol	Condition	Min	Max	Unit
Address setup time	A0	tAW8	-	10	-	ns
Address hold time		tAH8	-	0	-	
System cycle time		tCYC8	-	200	-	
/WR L pulse width (WRITE)	/WR	tCCLW	-	100	-	
/WR H pulse width (WRITE)		tCCHW	-	100	-	
/RD L pulse width (READ)	/RD	tCCLR	-	120	-	
/RD H pulse width (READ)		tCCHR	-	120	-	
CSB setup time	CSB	tCSS8	-	100	-	
CSB hold time		tCSH8	-	100	-	
Write data setup time	D[7:0]	tDS8	-	70	-	
Write data hold time		tDH8	-	20	-	
Read data access time		tACC8	CL = 100 pF	-	80	
Read data output disable time		tOH8	CL = 100 pF	15	80	

Note:

- The input signal rise time and fall time ( $t_r$ ,  $t_f$ ) is specified at 15 ns or less. When the system cycle time is extremely fast,  $(t_r + t_f) \leq (t_{CYC8} - t_{CCLW} - t_{CCHW})$  for  $(t_r + t_f) \leq (t_{CYC8} - t_{CCLR} - t_{CCHR})$  are specified.
- All timing is specified using 20% and 80% of VDDI as the reference.
- $t_{CCLW}$  and  $t_{CCLR}$  are specified as the overlap between CSB being "L" and /WR and /RD being at the "L" level. CSB and /WR (or /RD) cannot act at the same time and CSB should be 100ns wider than /WR (or /RD).

### 10.3 System Bus Timing for 4-Line Serial Interface




Item	Signal	Symbol	Condition	Min	Max	Unit
Serial clock period		tSCYC	-	80	-	ns
SCL "H" pulse width	SCL	tSHW	-	40	-	
SCL "L" pulse width	SCL	tSLW	-	40	-	
Address setup time	A0	tSAS	-	40	-	
Address hold time	A0	tSAH	-	40	-	
Data setup time	SDA	tSDS	-	15	-	
Data hold time	SDA	tSDH	-	20	-	
CSB-SCL time		tCSS	-	40	-	
CSB-SCL time	CSB	tCSH	-	40	-	
CSB "H" pulse width	CSB	tCSW	-	15	-	

Note:

1. The input signal rise and fall time ( $t_r$ ,  $t_f$ ) are specified at 15 ns or less.
2. All timing is specified using 20% and 80% of VDDI as the standard.

### 10.4 System Bus Timing for 3-Line Serial Interface



Item	Signal	Symbol	Condition	Min	Max	Unit
Serial clock period		$t_{SCYC}$	-	80	-	ns
SCL "H" pulse width	SCL	$t_{SHW}$	-	40	-	
SCL "L" pulse width	SCL	$t_{SLW}$	-	40	-	
Data setup time	SDA	$t_{SDS}$	-	15	-	
Data hold time	SDA	$t_{SDH}$	-	20	-	
CSB-SCL time		$t_{CSS}$	-	40	-	
CSB-SCL time	CSB	$t_{CSH}$	-	40	-	
CSB "H" pulse width	CSB	$t_{CSW}$	-	15	-	

Note:

1. The input signal rise and fall time ( $t_r$ ,  $t_f$ ) are specified at 15 ns or less.
2. All timing is specified using 20% and 80% of  $V_{DDI}$  as the standard.

# 11. Optical Characteristic

Item	Symbol	Temp	Condition.	Min	Typ.	Max.	Unit	Remark
Response time	Tr	25°C	$\theta=0^\circ, \phi=0^\circ$	-	8	-	.ms	Note 3
	Tf	25°C		-	12	-		
Contrast ratio	CR	25°C	At optimized viewing angle	-	800	-	-	Note 4
Viewing angle	Hor.	$\Theta_R$	25°C	$CR \geq 10$	80		Deg.	Note 1 Note 2
		$\Theta_L$	25°C		80			
	Ver.	$\Phi_B$	25°C		80			
		$\Phi_T$	25°C		80			
Brightness	-	25°C	-	500	600	-	cd/m <sup>2</sup>	Center of display

Ta=25±2°C, IL=160mA

Note 1: Definition of viewing angle range




Fig. 11-1 Definition of viewing angle

Note 2: Test equipment setup: After stabilizing and leaving the panel alone at a driven temperature for 10 minutes, the measurement should be executed. Measurement should be executed in a stable, windless, and dark room. Optical specifications are measured by Topcon BM-7(BM-5) luminance meter 1.0° field of view at a distance of 50cm and normal direction.





Fig. 11-2 Optical measurement system setup


Note 3: Definition of Response time: Definition of response time : The response time is defined as the time interval between the 10% and 90% amplitudes.



Note 4: Definition of contrast ratio : The contrast ratio is defined as the following expression.

$$\text{Contrast ratio (CR)} = \frac{\text{Luminance measured when LCD on the "White" state}}{\text{Luminance measured when LCD on the "Black" state}}$$

Note 8: Uniformity (U) =  $\frac{\text{Brightness}(\text{min})}{\text{Brightness}(\text{max})} \times 100\%$



## 12. Reliability

Content of Reliability Test (Wide temperature, -20°C~70°C)


Environmental Test			
Test Item	Content of Test	Test Condition	Note
High Temperature storage	Endurance test applying the high storage temperature for a long time.	80°C 200hrs	2
Low Temperature storage	Endurance test applying the low storage temperature for a long time.	-30°C 200hrs	1,2
High Temperature Operation	Endurance test applying the electric stress (Voltage & Current) and the thermal stress to the element for a long time.	70°C 200hrs	—
Low Temperature Operation	Endurance test applying the electric stress under low temperature for a long time.	-20°C 200hrs	1
High Temperature/ Humidity Operation	The module should be allowed to stand at 60°C,90%RH max For 96hrs under no-load condition excluding the polarizer, Then taking it out and drying it at normal temperature.	60°C,90%RH 96hrs	1,2
Thermal shock resistance	The sample should be allowed stand the following 10 cycles of operation  <div style="text-align: center;"> <p style="margin: 0;">-20°C      25°C      70°C</p> <p style="margin: 0;">30min    5min    30min</p> <p style="margin: 0;">1 cycle</p> </div>	-20°C/70°C 10 cycles	—
Vibration test	Endurance test applying the vibration during transportation and using.	Total fixed amplitude : 15mm Vibration Frequency : 10~55Hz One cycle 60 seconds to 3 directions of X,Y,Z for Each 15 minutes	3
Static electricity test	Endurance test applying the electric stress to the terminal.	VS=800V, RS=1.5kΩ CS=100pF 1 time	—

Note1: No dew condensation to be observed.

Note2: The function test shall be conducted after 4 hours storage at the normal Temperature and humidity after remove from the test chamber.

Note3: The packing have to including into the vibration testing.





MIDAS

design • manufacture • supply

## 14. Initial Code For Reference

```
void Initial_code()
{
    Write_Command(0xae);
    Write_Data(0xa5);

    Write_Command(0x61);
    Write_Data(0x0f);
    Write_Data(0x04);
    Write_Data(0x02);
    Write_Data(0xa5);

    Write_Command(0x62);
    Write_Data(0x00);
    Write_Data(0x3b);
    Write_Data(0x1b);
    Write_Data(0xa5);

    Write_Command(0x63);
    Write_Data(0x05);
    Write_Data(0x0f);
    Write_Data(0xa5);
    Write_Data(0xa5);

    Write_Command(0x24);
    Write_Data(0x01);
    Write_Data(0xa5);
    Write_Data(0xa5);
    Write_Data(0xa5);

    Write_Command(0x22);
    Write_Data(0x02);
    Write_Data(0xa5);
    Write_Data(0xa5);
    Write_Data(0xa5);

    Write_Command(0x91);
    Write_Data(0x00);
```

Write\_Data(0x21);  
Write\_Data(0x23);  
Write\_Data(0x24);

Write\_Command(0x92);  
Write\_Data(0x27);  
Write\_Data(0x28);  
Write\_Data(0x29);  
Write\_Data(0x2a);

Write\_Command(0x93);  
Write\_Data(0x2b);  
Write\_Data(0x2c);  
Write\_Data(0x2d);  
Write\_Data(0x2e);

Write\_Command(0x94);  
Write\_Data(0x30);  
Write\_Data(0x31);  
Write\_Data(0x32);  
Write\_Data(0x3f);

Write\_Command(0x99);  
Write\_Data(0x00);  
Write\_Data(0x21);  
Write\_Data(0x23);  
Write\_Data(0x26);

Write\_Command(0x9a);  
Write\_Data(0x27);  
Write\_Data(0x28);  
Write\_Data(0x29);  
Write\_Data(0x2a);

Write\_Command(0x9b);  
Write\_Data(0x2b);  
Write\_Data(0x2c);  
Write\_Data(0x2d);  
Write\_Data(0x2e);



```
Write_Command(0x9c);  
Write_Data(0x30);  
Write_Data(0x35);  
Write_Data(0x3b);  
Write_Data(0x3f);
```

```
Write_Command(0x12);  
Write_Data(0xa5);
```

```
Write_Command(0x15);  
Write_Data(0xa5);
```

```
}
```

MIDAS

design • manufacture • supply