





About Akro-Mils®

Akro-Mils Mission

Akro-Mils Canada is committed to providing innovative storage and material handling products of uncompromising quality at a fair price. We support this commitment with professional representation and consistent, superior service to meet the needs of our customers. If you are ever less than 100% satisfied with the quality of any Akro-Mils product, or if you have any suggestions on how we can improve our service, please give me a call-

> Jim Morrison General Manager, Akro-Mils Canada

We accept





The Akro-Mils Advantage

Akro-Mils Canada products save time and money by helping to increase material handling and distribution efficiency. Our broad range of storage, organization, and transport products helps to speed cycle times, maintain accurate inventories, optimize storage space, and improve parts protection. For quality products backed by more than 50 years of reliable delivery and responsive customer service, look to the Akro-Mils Canada advantage.

All New Products ... All the Time

Akro-Mils Canada introduces more new products to the Canadian market on a regular basis than does any other comparable manufacturer. We stay ahead of the pack by being INNOVATIVE. We offer fast service, competitive pricing, and we are extremely responsive to our customers' needs. This catalogue details our standard product lines. Please feel free to contact us for special sizes and configurations.

New! Powder Coating

Akro-Mils Canada's new powder coating capabilities provide not only a high-quality, durable finish to our standard and custom transport products, but a also a resource for custom powder coating your own products in large or short volume runs. Powder coating increases the value of a product by improving the quality, appearance, and durability in a cost-effective way.

Quality Systems Produce Top-Quality Products

Each of Akro-Mils Canada's suppliers are in compliance with quality process standards and effective quality management systems in the design, production, and distribution of plastic storage products. To you, our valued customer, this certification ensures you will continue to receive consistent, high-quality products from Akro-Mils Canada. Products manufactured in our Akron, Ohio; Wadsworth, Ohio; Sandusky, Ohio; Milford, Ohio; Ontario, California; and our Nanterre Cedex France facilities are within the ISO 9001:2000 certified system. We are working to certify our other facilities in the near future.

Canada-wide Network of Logistics Professionals

Akro-Mils Canada maintains a nationwide network of sales consultants, dealers, and distributors. We keep them updated as to new developments and products, so they may be positioned to help you. We support them fully and do not sell direct to end-users.

Ready to Ship to Meet Your Needs

You may draw on full inventories in our warehouses for fast shipping. Our multiple manufacturing locations assure a reliable supply of stock. Our dealers rate our responsiveness and customer service among the best, and our after-sales support is second to none. End-users, please consult your Akro-Mils Canada distributor for terms and conditions of sale.

Efficient and Knowledgeable Customer Service

Our team of customer service specialists is prepared to answer all of your questions. Call us to learn more about our products and services, or contact your local dealer or distributor. At Akro-Mils Canada, your satisfaction is our priority – every time!



Table of Contents

	Storage Bins			Small Parts Storage	
	AkroBins®	6		Steel Storage Cabinets	46
	Louvered Hanging Systems	7		Mobile Steel Cabinet Rack	46
	Rail Hanging Systems	8		Storage-Go-Round	46
New	Cabinet Systems	9		Plastic Storage Cabinets	47
New	Super-Size AkroBins® & Dollies	10		Portable Organizers	47
New	Stack-N-Store Bins	10		Storage Cases	48
	Shelf Bins	11	New!	ProBox™Tool Boxes	48
New	Shelving Systems	12	New!	Tool Rack	48
	DPick Rack Systems	13	New!	Wrench Holder	48
	Economy Bins	14		Tilt & Locks	49
	1800 Series AkroBins®	14		Akro/Logic™ Organizers	49
	ESD AkroBins®	15		Roto-Shelf	49
	ESD Hanging System	15	I	Carts & Transport Systems	
	ESD Shelf Bins	15		ProCart™	52-53
	ESD Grids	15		File Manager Cart	53
	Totes & Containers			Shelf Cart	53
	Nest & Stack Totes	18		VERSA/Deck™	54-55
	Bi-Color Stack & Nest Totes	19		Platform Trucks – Wood Deck	56-58
	KeepBoxes [™]	19		Platform Trucks – Work Height	59
New	Attached Lid Containers	20-22		Skids – Semi-Live & Dead	59
	Detached Lid Containers	22		Platform Trucks – Steel	60
	Akro-Grids	23		Shelf & Multi-Shelf Carts	61
	Straight Wall Containers	24-25		Compact Tote Truck	61
	Heavy-Duty Boxes, Totes & Trays	26-27		Bin Carts	61
	Tote Caddy	27		Portable Tables & Carts	62
	Cross-Stack Akro-Tubs	28		High-End Narrow Aisle Truck	63
	Agricultural Containers	29		Tray Service Cart	63
	Specialty Containers	29		Box Trucks	63
	Food Processing Containers	30-31		Heavy-Duty Work Benches	64
	Bulk Boxes	32-33		Mobile Work Tables	65
	Pallets	34-35	ı	Trucks & Dollies	
	Recycling & Waste Transport Syst	ems		Wood Dollies	68-69
	Recycling Containers	38		Polyethylene Dollies	70
	MegaKart®	39		Steel Dollies	70
	BossKart [®]	39		Aluminum Dollies	70
	Versa-Kart [®]	39		Hand Trucks	71
	Akro-Cart	40		Specialty Hand Trucks	72-73
	Whisper Series	40		Drum Handling Equipment	74-75
	Tilt-Truck	41	1	Reference	
	Akro-Lift	41		Materials Definitions & Benefits	76
	AkroClean™ Janitor Cart	42		Caster & Wheel Definitions	76
	Compact Cleaning Cart	43		Model Number Index	77-79





AkroBins®
Pick, sort, store, and label small parts with versatile AkroBins.



11 Shelf Bins A colorful, durable replacement for flimsy, corrugated bins.



1800 Series
AkroBins®
Extra-deep bins hold large,
heavy, or bulky items.



Hanging Systems
Hang AkroBins for
convenient parts storage
and retrieval.

Cabinet Systems



Shelving Systems Creates an efficient storage system with shelf bins or Stak-N-Store bins.



15ESD Containers
Safely store and transport sensitive electronic components.



Protect parts and products from dust, damage, and theft.

Super-size



Pick Rack Systems Improve workspace organization and efficiency.



AkroBins® Extra-large, deep bins store and organize large, bulky items.



Economy Bins General purpose storage bins stack on shelves or nest for compact storage.




10 Stak-N-Store Stackable containers with wide openings for bulky items.



AkroBins[®]



- · Control inventories, shorten assembly times, and minimize parts handling.
- Heavy-duty bins securely stack atop each other, sit on shelving, and hang from Akro-Mils racks, panels, rails, and carts.
- Molded of high-density polypropylene, AkroBins are unaffected by weak acids and alkalis.
- Sturdy, one-piece construction is water, rust, and corrosion-proof.
- Guaranteed not to crack or break under normal load conditions as stated in our 1-year limited warranty.
- Autoclavable up to 250° F.
- Available in 12 sizes and 4 colors: Red, Yellow, Blue, and Stone.





When compared to the competition, AkroBins:

- Support more weight when stacked.
- Handle more abuse.
- Hold more weight without cracking.















AkroBins

30235

30239


30230

		Out	side Di	imension	ıs				lr	nside Din	nensions	;			Bin Load	
Model		Inches			mm			Incl	nes			m	ım		Capacity	Ctn.
No.	L	W	Н	L	W	Н	L	W	Н	Х	L	W	Н	Х	On Rack**	Qty.
30210	5¾	41/8	3	137	105	76	43/4	31/16	2 ¹³ ⁄16	4	120	87	71	102	10 lbs.	24
30220	7¾	41/8	3	187	105	76	6¾	31/16	213/16	6	171	87	71	152	10 lbs.	24
30224	10 ⁷ /s	41/8	4	276	105	102	101/4	33/16	3¾	9	260	87	95	229	30 lbs.	12
30230	10 ⁷ /s	51/2	5	276	140	127	101/4	43/8	43/4	9	260	111	121	229	30 lbs.	12
30234	14¾	51/2	5	375	140	127	14 ¹ /16	43/8	43/4	12 ¹³ /16	357	111	121	325	50 lbs.	12
30235	10 ⁷ /s	11	5	276	279	127	101/4	10	43/4	9	260	254	121	229	50 lbs.	6
30239	10¾	81/4	7	273	210	178	10	6%16	63/4	8	254	167	171	203	50 lbs.	6
30240	14¾	81/4	7	375	210	178	14	6%16	63/4	12	356	167	171	305	60 lbs.	12
30250	14¾	16½	7	375	419	178	14	143/4	63/4	12	356	375	171	305	75 lbs.	6
30255	10 ⁷ /s	16½	5	276	419	127	93/4	15	43/4	81/2	248	381	121	216	60 lbs.	6
30265*	18	81/4	9	457	210	229	171⁄⁄s	63/4	81/4	14½	435	171	210	368	N/A	6
30270*	18	16½	11	457	419	279	17½	14¾	101/4	13¾	435	375	260	349	N/A	3

One color per carton: Specify Red, Blue, Yellow, or Stone.

*Note 30265 and 30270 are not designed for use with hanging systems.

Accessories:



Dividers

Lengthwise dividers keep items separated in the bin.


Dividers

Model No.	Fits AkroBins	Pkg. Qty.
40210	30210 (1)	6
40220	30220 (1)	6
40230	30230 (1), 30235 (3)	6
40239	30239 (1)	6
40245	30240 (1), 30250 (1)	6
40265	30265 (1)	6
40270	30270 (3)	6

(Max. # of dividers)

*30224, 30255, 30234 no dividers available.

Bin Lids*





Model No.	Fits AkroBins	Ctn. Qty.
30211	30210	24
30221	30220	24
30231	30230	12
30236	30235	6


*Assembly required - hinge pins included.

^{**} CAUTION: When using bins with hanging systems, do not exceed the weight capacity for the rack which may be less than the total sum of bin capacities.

Louvered Hanging Systems

- Take back valuable floor space maximize parts storage and handling efficiency.
- Louvered Panels used with AkroBins® offer the ultimate in storage flexibility.*
- Secure stationary racks to the wall or floor and wall-mountable panels to a solid structure.
- Six different models are available to accommodate up to 288 AkroBins.
- Easy, one-person assembly.

*AkroBins sold separately, see page 6.



30653 Louvered Floor Rack shown with 30239 AkroBins.



Develop a customized storage system by grouping any of our Louvered Panels.



Double-Sided Snap Fastener
Louvered Floor Rack

(Snap fasteners greatly reduce rack assembly time.) 36" L x 20" W x 60" H 914 x 508 x 1524 mm. 700 lb. capacity.



30653 **Louvered Floor Rack** 35³/₄" L x 32" W x 75¹/₈" H 908 x 813 x 1908 mm. 2000 lb. capacity.



30618 **Louvered Panel** 18" L x 19" H 457 x 483 mm. 160 lb. capacity.



98636 **Bench Rack** 36" L x 8" W x 21" H 914 x 203 x 533 mm. 120 lb. capacity.



30636 **Louvered Panel** 35³/4" L x 19" H 908 x 483 mm. 160 lb. capacity.



98600 **Bench Rack** 27³/₄" L x 8" W x 21" H 705 x 203 x 533 mm. 120 lb. capacity.

Ordering Information:

Louvered Panels And Bench Racks

Use this chart to determine the quantity of same-size AkroBins required to fill each panel.

						AkroBir	ns Model I	No. (Bin W	t. Capacit	ty)		
Model		Ctn.	30210	30220	30224	30230	30234	30235	30239	30240	30250	30255
No.	Description	Qty.	(10 lbs.)	(10 lbs.)	(30 lbs.)	(30 lbs.)	(50 lbs.)	(50 lbs.)	(50 lbs.)	(60 lbs.)	(75 lbs.)	(60 lbs.)
30618	18" x 19" Louvered Panel	4	16	16	12	9	9	-	-	-	-	3
30636	35 ³ / ₄ " x 19" Louvered Panel	4	32	32	24	18	18	9	8	8	4	6
	35 ³ / ₄ " x 37" (2 Panels)		72	72	36	36	36	18	16	16	8	12
	35 ³ / ₄ " x 55" (3 Panels)		104	104	54	54	54	27	28	28	14	18
	35 ³ / ₄ " x 73" (4 Panels)		144	144	72	72	72	36	36	36	18	24
98600	27 ³ / ₄ " Bench Rack	1	30	30	18	12	12	6	6	6	-	-
98636	36" Bench Rack	1	40	40	24	18	18	9	8	8	4	6

Louvered Floor Racks

Use this chart to determine the quantity of same-size AkroBins required to fill each floor rack.


				Dime	nsion	ıs		AkroBins Model Number (Bin Wt. Capacity)									
Model		- 1	nche	S		mm		30210	30220	30224	30230	30234	30235	30239	30240	30250	30255
No.	Description	L	W	Н	L	W	Н	(10 lbs.)	(10 lbs.)	(30 lbs.)	(30 lbs.)	(50 lbs.)	(50 lbs.)	(50 lbs.)	(60 lbs.)	(75 lbs.)	(60lbs.)
30626	Double-Sided Snap Fastener Louvered Rack	36	20	60	914	508	1524	192	192	144	108	108	54	48	48	24	36
30653	Louvered Floor Rack	35¾	32	751/8	908	813	1908	288	288	192	144	144	72	72	72	36	48

Rail Hanging Systems



- Rail systems offer an economical storage solution to get the most from your AkroBins.
- Single and double rail units provide more flexibility in bin placement and hold multiple sizes of AkroBins.*
- Mobile kit available to mobilize two-sided racks.
- Steel rail is ideal for work stations.

*AkroBins sold separately, see page 6.



Bench racks, wall-mount, and single- or doublesided models are available to create a complete storage system.



30006 **1-Sided, 12 Rail** 250 lb. capacity.



30008 **1-Sided, 16 Rail** 250 lb. capacity.



30012 **2-Sided Rack, 12 Rail** 500 lb. capacity.



30016 **2-Sided Rack, 16 Rail** 500 lb. capacity.



30812 **Bin Cart w/ Casters** 14-gauge steel work top. 250 lb. capacity.

Ordering Information:

Rail Racks & Bin Cart

Use this chart to determine the quantity of same-size AkroBins required to fill each rack and cart.

					Dimer	nsion	5		AkroBins Model Number (Bin Wt. Capacity)									
Model		Ctn.		Inche	s		mm		30210	30220	30224	30230	30234	30235	30239	30240	30250	30255
No.	Description	Qty.	L	W	Н	L	W	Н	(10 lbs.)	(10 lbs.)	(30 lbs.)	(30 lbs.)	(50 lbs.)	(50 lbs.)	(50 lbs.)	(60 lbs.)	(75 lbs.)	(60 lbs.)
30006	Rack, 1-Sided, 12 Rail	2	36	14 ¹ /8	53	914	359	1346	96	96	-	-	-	-	24	24	12	-
30008	Rack, 1-Sided, 16 Rail	3	36	141/8	53	914	359	1346	-	-	48	48	48	24	-	-	-	16
30012	Rack, 2-Sided, 12 Rail	1 2	36	20	53	914	508	1346	192	192	-	-	-	-	48	48	24	-
30016	Rack, 2-Sided, 16 Rail	l 3	36	20	53	914	508	1346	-	-	96	96	96	48	-	-	-	32
30812	Bin Cart	2	381/2	24	36½	978	610	927	96	96	64	48	48	24	24	24	12	16



30812 Bin Cart shown with 30230 AkroBins.



Two-Sided Racks can be mobilized with the mobile kit.

Mobile Kit - Casters & Handle

Model	Ctn.	Fits Hanging
No.	Qty.	System No.
30424	1	30012, 30016

30148 Steel Rail

Wall-mountable unit accepts 6 sizes of AkroBins. 110 lb. capacity.

Steel Rail

Use this chart to determine the quantity of same-size AkroBins required to fill the steel rail.

			Dimen	sions			AkroBins Model Number (Bin Wt. Capacity)					
Model	Model Ctn. Inches			mm 30		30210	30220 30224		30230	30234	30255	
No.	Qty.	L	Н	L	Н	(10 lbs.)	(10 lbs.)	(30 lbs.)	(30 lbs.)	(50 lbs.)	(60 lbs.)	
30148	1	48	3	1219	76	11	11	11	8	6	3	

Cabinet Systems





AkroBin Cabinet Louvered panels on back wall and doors hold up to 138 bins



AkroBin Cabinet with 3 Shelves Louvered panels and 3 full (24") shelves hold up to 102 bins

AkroBin Cabinet 36"W x 24"D x 78"H

SKU

Number

AC36243AS

AC3624Y3AS

· Delivered fully assembled and ready to use.

· All cabinets lock and come with two keys.

cabinets for your unique storage requirements.

SKU Number	Description	Bin Model No.	Bin Dimensions L x W x H	Qty. of Bins
AC3624	Cabinet w/ Louvered Panels on Back and Doors, no Bins	_	-	-
AC3624Y	Cabinet w/ Louvered Panels on Back and Doors with Bins	30210 30220 30230	5-3/8" x 4-1/8" x 3" 7-3/8" x 4-1/8" x 3" 10-7/8" x 5-1/2" x 5"	48 48 24
		30240 30250	14-3/4" x 8-1/4" x 7" 14-3/4" x 16-1/2" x 7"	12 6

Bin Model

No.

30210

30220

30250

Bin Dimensions

LxWxH

5-3/8" x 4-1/8" x 3"

7-3/8" x 4-1/8" x 3"

14-3/4" x 16-1/2" x 7"

Qty.

48

48

6

of Bins

• Perfect for protecting parts and products from dust, damage, and theft.

Cabinets feature louvered panels on doors and/or back walls.Choose from solid, quick-view, or secure-view (metal mesh) doors.

Available with or without yellow AkroBin® packages to customize

• All cabinets are 16-gauge steel; Quick-View cabinet is 20-gauge steel.



Shelf Bin Pick Rack Cabinet



AkroBin Cabinet w/ 3 Shelves 36"W x 24"D x 78"H

Description

Cabinet w/ 3 Shelves, and Louvered Panels on Back Wall and Doors, no Bins

Cabinet w/ 3 Shelves, and

Louvered Panels on Back

Wall and Doors with Bins

SKU Number	Description	Bin Model No.	Bin Dimensions L x W x H	Qty. of Bins
AC3618	Cabinet w/ Louvered Panels on Back Wall, no Bins	_	_	-
AC3618Y	Cabinet w/ Louvered Panels	30230	10-7/8" x 5-1/2" x 5"	24
	on Back Wall with Bins	30240	14-3/4" x 8-1/4" x 7"	12
		30250	14-3/4" x 16-1/2" x 7"	6

Shelf Bin Pick Rack Cabinet 36"W x 18"D x 78"H

SKU Number	Description	Bin Model No.	Bin Dimensions L x W x H	Qty. of Bins
APRC	Cabinet w/ 9 shelves	-	-	-
	(8 slanted), no Bins			
APRC120Y	Cabinet w/ 9 shelves	30120	11-5/8" x 4-1/8" x 4"	72
	(8 slanted) with Bins			

Quick-View Security Bin Cabinet 36"W x 18"D x 78"H

SKU Number	Description	Bin Model No.	Bin Dimensions L x W x H	Qty. of Bins
AC3618QV	Cabinet w/Quick View Doors,		-	-
	Louvered Back, no Bins			
AC3618QV240	Cabinet w/Quick View Doors,	30240	14-3/4" x 8-1/4" x 7"	36
	Louvered Back with Bins			
AC3618QV250	Cabinet w/Quick View Doors,	30250	14-3/4" x 16-1/2" x 7"	18
	Louvered Back with Bins			

Secure-View Security Bin Cabinet 36"W x 18"D x 78"H

Secure-view Sec	secure-view security bill cabillet 30 W X 10 D X 76 H									
SKU		Bin Model	Bin Dimensions	Qty.						
Number	Description	No.	LxWxH	of Bins						
AC3618SV	Cabinet w/ Secure View Mesh	_	-	-						
	Doors, Louvered Back, no Bins									
AC3618SV240	Cabinet w/ Secure View Mesh	30240	14-3/4" x 8-1/4" x 7"	36						
	Doors, Louvered Back with Bins									
AC3618SV250	Cabinet w/ Secure View Mesh	30250	14-3/4" x 16-1/2" x 7"	18						
	Doors, Louvered Back with Bins									



AkroBin Cabinet with Flush Doors Louvered panel on back wall holds up to 42 bins



Quick-View Security Bin Cabinet Lexan™ door panels; louvered back wall panel holds up to 36 bins



Secure-View Security Bin Cabinet Steel mesh door panels; louvered back wall panel holds up to 36 bins

oer-Size AkroBins & Doll



Available in 5 sizes and 3 colors: Red. Yellow. and Blue.



30281



30282




30283



30290

- · Control inventories, shorten assembly times, and minimize parts handling.
- Heavy-duty bins securely stack atop each other, or sit on shelving.
- Molded of high-density polypropylene, AkroBins are unaffected by weak acids and alkalis.
- · Sturdy, one-piece construction is water, rust, and corrosion-proof.
- · Guaranteed not to crack or break under normal load conditions as stated in our 1-year limited warranty.
- Autoclavable up to 250° F.



Super-Sized AkroBins

	Outside Dimensions						Inside Dimensions					Max.	Stacking				
Model Inches mm			Inches mm			Capacity	Capacity	Ctn.									
No.	L	W	Н	L	W	Н	L	W	Н	Х	L	W	Н	Χ	Per Bin	/=Qty. Stacked	Qty.
30280	20	12 ³ /8	6	508	314	152	16 ⁷ /8	10 ¹¹ / ₁₆	5³⁄8	15½	429	271	137	394	100lbs.	40lb./10	4
30281	20	12 ³ /8	8	508	314	203	16 ⁷ /8	10 ¹¹ / ₁₆	7 ³ /8	$15\frac{1}{2}$	429	271	187	394	150lbs.	50lb./7	3
30282	20	12 ³ /8	12	508	314	305	16 ⁷ /8	10 ¹¹ /16	11 ³ /8	$15\frac{1}{2}$	429	271	289	394	200lbs.	60lb./5	2
30283	20	18 ³ /8	12	508	467	305	16 ⁷ /8	16 ⁹ /16	11 ³ /8	$15\frac{1}{2}$	429	421	289	394	300lbs.	150lb./5	1
30290	291/4	183⁄8	12	743	467	305	26½	16 ⁹ ⁄16	11 ³ /8	243/4	664	421	289	629	300lbs.	150lb./5	1

One color per carton: Specify Red, Blue, or Yellow. Not recommended to hang on rack or panel systems.

Dollies

Model	Dimensions			Ctn.	Capacity	
No.	L	W	Н	Qty.	Lbs.	Casters
RU842HR2018	20"	18³⁄8"	31/2"	1	500	2" Polyolefin
RU842HR2918	29 ¹ /4"	18³⁄8"	3 ¹ /2"	1	500	2" Polyolefin





tak-N-Store Bins





13014





- · The perfect way to organize heavy, bulky items.
- Bins stack to form tall, stable storage arrangements on floors or standard industrial shelving.
- 75 lb. weight capacity.
- · Color: Gray, Red, Blue.



Stak-N-Store Bins

			Outsid	le Dimensions				
Model		Capacity	Ctn.					
No.	L	W	Н	L	W	Н	Cu. Ft.	Qty.
13014	17 ¹ / ₂	10 ⁷ /8	121/2	445	276	318	.98	4
13017	15 ¹ / ₄	19 ⁷ /8	12 ⁷ /16	387	505	316	1.7	3
13018	17 ¹ / ₂	16½	121/2	445	419	318	1.6	2

Order in carton quantities.

Stak-N-Store Bi	n Dollies								
Model	D	imensior	าร	Ctn.	Capacity				
No.	L	W	Н	Qty.	Lbs.	Casters			
RU843HR1617	16 ⁵ /8"	15 ³ /4"	4½"	1	900 lbs.	3 " Polyolefin			
Compatible with Model 13018									
RU843HR1519	19 ¹ /4"	14 ⁵ /8"	4½"	1	900 lbs.	3 " Polyolefin			
Compatible with	Model 13	017							





Stack bins together to form a storage system.




Shelf Bins



Shelf bins tilt out for complete access to contents.

- Shelf Bins outlast corrugated bins paying for themselves in reduced replacement costs.
- Durable polypropylene bins can be fully loaded without bulging or cracking.
- Works with 12", 18", and 24" deep shelving, or vertical storage and retrieval units.
- Available in 13 sizes and 3 colors: Red, Yellow, and Blue.
















Shelf Bins

			Dimensions	5				imensio	ns				er Bin	
Model	Inche	S	n	nm		Inches			mm		Ctn	Small	Large	Optional
No.	L W	Н	L V	W H	L	W	Н	L	W	Н	Qty.	30101	30102	Divider
12" Shelf	Bin													
30 110	11 ⁵ /8 2 ³ /4	4	295	70 102	101/4	15/8	4	260	41	102	24	3	-	None
30 120	11 ⁵ /8 4 ¹ /8	4	295 1	105 102	101/4	3	4	260	76	102	24	5	2	40120
30 130	115/8 65/8	4	295 1	168 102	101/4	51/2	4	260	140	102	12	9	4	40130
30 150	115/8 83/8	4	295 2	219 102	101/4	71/8	4	260	181	102	12	11	4	40150
30 170	11 ⁵ / ₈ 11 ¹ / ₈	4	295 2	283 102	101/4	10	4	260	254	102	12	15	6	40170
18" Shelf	Bin													
30 128	17 ⁷ /8 4 ¹ /8	4	454 1	105 102	16½	3	4	419	76	102	12	8	3	40120
30 138	17 ⁷ /8 6 ⁵ /8	4	454 1	168 102	16½	51/2	4	419	140	102	12	15	6	40130
30 158	17 ⁷ /8 8 ³ /8	4	454 2	213 102	16½	71/8	4	419	181	102	12	15	6	40150
30 178	17 ⁷ /8 11 ¹ /8	4	454 2	283 102	16½	10	4	419	254	102	12	25	12	40170
24" Shelf	Bin													
30 124	235/8 41/8	4	600 1	105 102	221/8	3	4	562	76	102	12	11	4	40120
30 164	235/8 65/8	4	600 1	168 102	221/8	$5^{1/2}$	4	562	140	102	6	21	8	40130
30 184	235/8 83/8	4	600 2	213 102	221/8	71/8	4	562	181	102	6	25	8	40150
30 174	23 ⁵ /8 11 ¹ /8	4	600 2	283 102	221/8	10	4	562	254	102	6	35	16	40170


One color per carton. Specify color: Red, Yellow, or Blue.




030-550 030-600 C30-605

Dividers

Optional Accessories:



Black polypropylene dividers create compartments. Sizes to fit all bins except 30110. Each bin accepts up to 7 compartment dividers.



Extended Label Holders

Designed for larger bar code scanning. Label holders fit all shelf bins except the 30110.



Bin Cups

Bin Cups lift out easily for parts retrieval and fit all Shelf Bins. (Refer to Shelf Bin chart for number of cups per bin.)

Shelf Boxes

	Outside Dimension									
Model Inches mm								city		
No.	L	W	Н	L	W	Н	cu. ft.	liters		
030-550	241/4	6	53/4	616	152	146	.84	23.8		
030-600	18	103/8	10	457	263	254	.84	23.8		
C30-605	16	16	8¾16	406	406	208	.90	25.5		

Dividers

Model No.	Fits Shelf Bins	Width	Pkg. Qty.
40120	30120, 30124, 30128	41/8"	24
40130	30130, 30138, 30164	6 ⁵ /8"	24
40150	30150, 30158, 30184	83/8"	24
40170	30170, 30174, 30178	11½"	24

Extended Label Holders

Model		Dime	ensions	Pkg.		
No.	Description	W	Н	Qty.		
40410	10° Angle	4"	21/4"	24		
40445	45° Angle	4"	21/4"	24		

Bin Cups

Dill Cups					
Model		Dir	nensio	ns	Ctn.
No.	Description	L	W	Н	Qty.
30101	Small Bin Cup	31/4"	2"	3"	48
30102	Large Bin Cun	5"	23/4"	3"	24

Shelving Systems

Shelf Bin Systems 13 shelf unit holds up to 96, 18" deep bins or 144, 12" deep bins





- Shelving can be ordered independently or purchased with Akro-Mils Shelf Bins and Stak-N-Store Bins to create an efficient storage system.
- Easy to assemble with nuts and bolts only on the top and bottom shelves.
- Adjustable compression clips secure shelves.
- Closed base keeps debris and small parts from slipping underneath.
- Bin colors: Shelf Bins—Yellow, Stak-N-Store Bins— Gray.

12" Shelf Bin System 12"D x 36"W x 75"H

SKU		Bin Model	Bin Dimensions	
Number	Description	No.	LxWxH	Qty. of Bins
AS1275	Shelving, no Bins	-	-	-
AS1275110Y	Shelving with Bins	30110	11 ⁵ / ₈ " x 2 ³ / ₄ " x 4"	144
AS1275120Y	Shelving with Bins	30120	115/8" x 41/8" x 4"	96
AS1275130Y	Shelving with Bins	30130	115/8" x 65/8" x 4"	60
AS1275150Y	Shelving with Bins	30150	115/8" x 83/8" x 4"	48
AS1275170Y	Shelving with Bins	30170	11 ⁵ /8" x 11 ¹ /8" x 4"	36

18" Shelf Bin System 18"D x 36"W x 75"H

SKU Number	Description	Bin Model No.	Bin Dimensions L x W x H	Qty. of Bins
AS1875	Shelving, no Bins	_	_	_
AS1875128Y	Shelving with Bins	30128	17 ⁷ /8" x 4 ¹ /8" x 4"	96
AS1875138Y	Shelving with Bins	30138	17 ⁷ /8" x 6 ⁵ /8" x 4"	60
AS1875158Y	Shelving with Bins	30158	17 ⁷ /8" x 8 ³ /8" x 4"	48
AS1875178Y	Shelving with Bins	30178	17 ⁷ /8" x 11 ¹ /8" x 4"	36

Stak-N-Store System 18"D x 42"W x 75"H

SKU Number	Description	Bin Model No.	Bin Dimensions L x W x H	Qty. of Bins	Bonus Bins*
AS187542	18" x 42" x 75"	-	-	-	-
	Shelving, no Bins				
AS187513017	18" x 42" x 75"	13017	15-1/4" x 19-7/8" x	10	2
	Shelving with Bins		12- ⁷ /16"		

^{*}Due to case pack, Bonus Bins are included, at no extra charge.

New Stak-N-Store System 18"D x 36"W x 75"H

NEW Stak N Ste	ne system to b	A DO WAY	J 11		
SKU Number	Description	Bin Model No.	Bin Dimensions L x W x H	Qty. of Bins	Bonus Bins*
AS187536	18" x 36" x 75"	-	-	-	-
	Shelving, no Bins				
AS187513014	18" x 36" x 75"	13014	17½" x 10½" x	15	1
	Shelving with Bins		12 ¹ /2"		
AS187513018	18" x 36" x 75"	13018	17½" x 16½" x	10	-
	Shelving with Bins		12 ¹ /2"		
AS1875ASSOR	18" x 36" x 75"	13014	17½" x 10 ⁷ /8" x	6	2
	Shelving with		12½" (13014)		
	Bin Mix	13018	17½" x 16½" x	6	-
			12½" (13018)		

^{*}Due to case pack, Bonus Bins are included, at no extra charge.

350-pound capacity per shelf when assembled and installed per instructions.



Easy Shelf Adjustment: Quickly change shelf height with compression clips





AS187513018

Pick Rack Systems





Bench Pick Rack Holds up to 24 bins on 3 shelves



Angled shelves increase picking efficiency



Double Sided Pick Rack Holds up to 192 bins on 16 shelves Maximum 800 lb. weight capacity

• Improve workspace organization and efficiency with rack and bin systems.

- Convenient, high-density storage with up to 192 bins.
- · Easy to assemble.
- Angled shelves keep parts at the front of bins for easy access.
- Choose from 4 styles available separately or in a package with Akro-Mils yellow Shelf Bins.

Single Sided Pick Rack 12"D x 36"W x 60"H

SKU Number	Description	Bin Model No.	Bin Dimensions L x W x H	Qty. of Bins	Bonus Bins*
APRS	Single Sided	_	_	-	-
	Pick Rack, no Bins				
APRS110Y	Rack with Bins	30110	11 ⁵ /8" x 2 ³ /4" x 4"	96	-
APRS120Y	Rack with Bins	30120	11 ⁵ /8" x 4 ¹ /8" x 4"	64	8
APRS130Y	Rack with Bins	30130	115/8" x 65/8" x 4"	40	8
APRS150Y	Rack with Bins	30150	115/8" x 83/8" x 4"	32	4
APRS170Y	Rack with Bins	30170	11 ⁵ /8" x 11 ¹ /8" x 4"	24	-

^{*}Due to case pack, Bonus Bins are included, at no extra charge.

Bench Pick Rack 12"D x 36"W x 21"H

SKU		Bin Model	Bin Dimensions	Qty. of
Number	Description	No.	LxWxH	Bins
APRBENCH	Bench Pick Rack, no Bins	-	-	-
APRBENCH 120	Bench Pick Rack with Bins	30120	11 ⁵ /8" x 4 ¹ /8" x 4"	24
APRBENCH 150	Bench Pick Rack with Bins	30150	11 ⁵ /8" x 8 ³ /8" x 4"	12

Double Sided Pick Rack 24"D x 36"W x 60"H

SKU Number	Description	Bin Model No.	Bin Dimensions L x W x H	Qty. of Bins	Bonus Bins*
APRD	Double Sided	_	-	-	-
	Pick Rack, no Bins				
APRD110Y	Rack with Bins	30110	11 ⁵ /8" x 2 ³ /4" x 4"	192	_
APRD120Y	Rack with Bins	30120	11 ⁵ /8" x 4 ¹ /8" x 4"	128	16
APRD130Y	Rack with Bins	30130	115/8" x 65/8" x 4"	80	4
APRD150Y	Rack with Bins	30150	11 ⁵ /8" x 8 ³ /8" x 4"	64	8
APRD170Y	Rack with Bins	30170	11 ⁵ /8" x 11 ¹ /8" x 4"	48	-

^{*}Due to case pack, Bonus Bins are included, at no extra charge.

Mobile Kit

SKU	
Number	Description
APRDMOBILE	Mobile Kit
	For Double Sided Pick Rack



Double Sided Pick Rack & Mobile Kit Creates a mobile double sided pick rac


Creates a mobile double sided pick rack Maximum 500 lb. weight capacity

Economy B



A large bar code label area makes content identification simple.

- The only small parts bin that can nest and stack.
- Organize work areas and expand storage space without adding shelving.
- Versatile Economy Bins make full use of shelf depth on 12" or 18" deep shelving and stack to fill space between shelves.
- Sturdy one-piece construction is water, rust, and corrosion-proof.
- · Unaffected by weak acids and alkalis.
- Molded from co-polymer polypropylene.
- · Guaranteed not to crack or break under normal load conditions as stated in our 1-year limited warranty.
- Autoclavable up to 250° E
- · Available in 5 sizes.









30716 Black








30796 Black

30776 Black

30718 Black 30778 Black

Economy Bins

		Outside Dimensions													
Model No.	L	Inches W	н	L	mm W	н	Ctn. Qty.								
30796 Black	81/%	65%	5	225	168	127	10 each								
30716 Black	11%	65/8	5	302	168	127	10 each								
30776 Black	17%	65/8	7	454	168	178	10 each								
30718 Black	11%	8¾	5	302	213	127	8 each								
30778 Black	17%	8¾	7	454	213	178	8 each								





Storage systems for large, heavy, and bulky items.



30358

- · Concentrate storage, reduce and control inventories, minimize material handling, and organize supplies.
- · Strong, durable co-polymer polypropylene construction.
- Designed to fit on 18" shelving for concentrated storage.
- One black cross-wise divider included per bin.
- Available in 2 sizes: $8\frac{1}{4}$ " and 11" width.
- Color: Beige.





1800 Series AkroBins

		_	-															
		Out	side [Dimens	nsions Inside Dimensions													
Model		Inche	5		mm			Inc	hes			mı	m		Ctn.	Dividers	Pkg.	Capacity
No.	L	W	Н	L	W	Н	L	W	Н	Χ	L	W	Н	Χ	Qty.	Model No.	Qty.	Lbs.
30348	20½	81/4	7	521	210	178	20	7¾	6½	20	508	187	165	508	6	40348	6	60
30358	20½	11	7	521	279	178	20	101/8	6½	20	508	257	165	508	6	40358	6	75

ESD Containers

AkroBins[®]

- Akro-Mils ESD containers dissipate electrostatic charges which can severely damage sensitive electronic components.
- Sturdy, one-piece construction is water, rust, and corrosion proof, and heat resistant to 300°E.




Hanging Systems

- Storage systems provide convenient parts storage and retrieval.
- Six options let you choose the system that works best for you.



Shelf Bins

- Shelf Bins provide an economical solution to electronic component storage problems.
- Works with 12", 18", and 24" deep shelving or vertical storage and retrieval units.



Grids

- Grids are compatible with most racks, shelving, and automated material handling equipment.
- Ribbed design gives added strength.






	Outside Dimensions							Inside Dimensions								
Model		Inche	S		mm			Inc	hes			m	m		Capacity	Ctn
No.	L	W	Н	L	W	Н	L	W	Н	Х	L	W	Н	Х	On Rack	Qty.
30210ESD	5¾	4½	3	136	105	76	43/4	31/16	2 ¹³ ⁄16	4	121	87	71	102	10 lbs.	24
30220ESD	7¾	4½	3	187	105	76	6 ³ / ₄	31/16	2 ¹³ ⁄16	6	171	87	71	152	10 lbs.	24
30230ESD	10 ⁷ /s	5½	5	276	140	127	10 ¹ / ₄	4³⁄8	43/4	9	260	111	121	229	30 lbs.	12
30235ESD	10 ⁷ /s	11	5	276	279	127	10 ¹ / ₄	10	43/4	9	260	254	121	229	50 lbs.	6
30240ESD	14¾	8 ¹ /4	7	375	210	178	14	6%16	6³⁄4	12	356	167	171	305	60 lbs.	12



Use this chart to determine the quantity of same-size AkroBins required to fill each panel.

See pages 5-6 for hanging system features.

				AkroBins N	Model No. (Bin W	t. Capacity)	
Model		Ctn.	30210ESD	30220ESD	30230ESD	30235ESD	30240ESD
No.	Description	Qty.	(10 lbs.)	(10 lbs.)	(30 lbs.)	(50 lbs.)	(60 lbs.)
30618	18" x 19" Louvered Panel	4	16	16	9	-	-
30636	35¾" x 19 Louvered Panel	4	32	32	18	9	8
98600	27¾" Bench Rack	1	30	30	12	6	6
98636	36" Bench Rack	1	40	40	18	9	8



charges away from the storage system. Designed to convert existing Akro-Mils racks and hanging systems

(see pages 5-6).

Louvered Floor Racks

Use this chart to determine the quantity of same-size AkroBins required to fill each floor rack.

Bins sold separately.

Model		li	nches		AkroBin Model Number							
No.	Description	L	W	Н	L	W	Н	30210ESD	30220ESD	30230ESD	30235ESD	30240ESD
30626	Double-Sided Snap											
	Fastener Louvered Rack	36	20	60	914	508	1524	192	192	108	54	48
30653	Louvered Floor Rack	35¾	32	75½	908	813	1908	288	288	144	72	72

ESD Shelf Bins

Model Inches mm Inches mm Ctn No. L W H L W H L W H L W H Qty. 20120550 1156 416 4 205 105 102 1016 2 4 260 76 102 24		Outside Dimension									Inside Dimension						
	Model		Inches	;		mm		l I	nche	s		mm		Ctn			
20120ESD 1156 416 4 305 105 102 1016 2 4 260 76 102 24	No.	L	W	Н	L	W	Н	L	W	Н	L	W	Н	Qty.			
30120E3D 11/8 4/8 4 293 103 102 10/4 3 4 200 /0 102 24	30120ESD	11%	41⁄8	4	295	105	102	101/4	3	4	260	76	102	24			
30128ESD 17% 4% 4 454 105 102 16½ 3 4 419 76 102 12	30128ESD	17¾	41/8	4	454	105	102	16½	3	4	419	76	102	12			
30124ESD 23% 4½ 4 600 105 102 22½ 3 4 562 76 102 12	30124ESD	23%	41/⁄8	4	600	105	102	221/8	3	4	562	76	102	12			

ESD Grids

ESD GITUS																	
		Out	tside I	Dimensi	ons					In	side Din	nension	15				
Model		Inches			mm				Inches					mm			Ctn.
No.	L	W	Н	L	W	Н	Α	В	C	D	E	Α	В	C	D	Е	Qty.
33164ESD	16 ¹ / ₂	10 ⁷ /8	4	419	276	102	93/8	14 ¹⁵ /16	14 ¹³ /16	93/16	3 ⁷ /8	238	379	376	233	98	12
33224ESD	223/8	17³/8	4	568	441	102	151/16	201/16	20	15	37/8	383	510	508	381	98	6









18-19

Nest & Stack Totes

Durable NST's for storage, transfer & shipping applications.



26-27

Heavy-Duty Industrial Boxes Rugged boxes and trays

Rugged boxes and trays for the most demanding applications.

Tote Caddy

supplies transport.

Convenient, portable tote caddy for easy



30-31

Specialty

Containers

unique applications.

Containers for

Food Processing Containers
Nesting and stacking



Nesting and stacking containers designed for food applications.



22

20-21

Detached Lid

Attached Lid

Reusable ALC's for shipping,

distribution, and storage.

Containers

Containers
Durable containers and
separate lids for storage
and distribution.



20

27

Akro-Tub & Tub Rack

Heavy-duty tub & rack for manufacturing, distribution, and food industries.



32-33

Bulk Boxes
A variety of Bulk Box

A variety of Bulk Box sizes for large, hard-to-move items.



23

Akro-Grids

Organize small parts with these colorful, dividable containers.



29

Agricultural Containers

Containers designed to maintain freshness and safeguard fragile produce.



34-35

Pallets

Light to heavy-duty pallets for manufacturing, distribution, and food industries.



24-25

Straight Wall Containers

Reusable SWC's provide efficient cubing on pallets and in trucks.



Nest & Stack Totes




Nest & Stack Totes stack when full; turn 180° and nest when empty.

- Extremely durable industrial-grade totes.
- Gray NST's are manufactured from FDA-approved materials.
- Available in 9 sizes and 3 colors: Red, Blue, and Gray.






l NS



One color per carton. Specify Red, Blue, or Gray. * NST 35180 is made of high-density polypropylene









Nest & Stack Totes solid steel Dollies are available for efficient parts transport.

Optional Accessories:



Label Holders

Model No. 35101. Clear plastic label holders attach easily to NST's, with or without the lid in place. Holders accommodate labels up to 3" x 5". One size fits all totes.

Label Holders

Model No.	Package Qty.
35010	6

Nest & Stack Totas Dollies

Nest & Stack lotes pollies													
Model No.	L	imensioi W	ns H	Ctn. Qty.	Capacity Lbs.	Casters							
RU843HR1828	275/8"	175⁄8"	4¾"	1	900 lbs.	3 " Polyolefin							
Compatible with	Model 35	300											
RU843HR1822	213/4"	173/4"	43/4"	1	900 lbs.	3 "Polyolefin							
Compatible with	Models 3	35225 and	d 35230										
RU843HR1422	21%"	14"	4¾"	1	900 lbs.	3 " Polyolefin							
Compatible with	Model 35	240											



Lids

Lids snap tight to protect contents. See lids chart for matching lid size.

Lids Chart


Lius Ciiai t		
NST Model No.	Optional Lids Model No.	Lid Ctn. Qty.
35180	35181	6
35185	35181	6
35190	35191	6
35195	35191	6
35200	35201	6
35225	35231	3
35230	35231	3
35240	35241	3
35300	35301	3

Bi-Color Stack & Nest Totes

• Stack when loaded to protect contents, nest when empty with 180° turn -

50% nesting ratio.

- Available in solid and ventilated versions.
- Modular to 48" x 45" pallet.
- Compatible with automated handling equipment.
- Standard colors include Gray/Red, Gray/Blue, Gray/Green, Green/Blue, Lt. Blue/Blue.















SN15120709

SN24150999

SN24220913

SN24221113

Bi-Color Stack & Nest Totes



	Outside Dimensions							Insid						
Model		Inches			mm		Inches				mm		Capacity	
No.	L	W	Н	L	W	Н	L	W	Н	L	W	Н	Lbs.	Kg
SN15120709	15	12	7½	381	305	191	11½	10¾	7	293	264	178	35	15
SN24150709	24	15	7½	610	381	191	20½	13¾	7	521	340	178	35	15
SN24150999	24	15	9½	610	381	240	201/2	13¾	9	521	340	229	45	20
SN24220913	24	22½	9	610	572	229	211/5	20½	8 ² /3	553	520	218	45	20
SN24221113	24	22	11	610	559	279	211/5	20½	10 ² ∕₃	553	520	269	45	20
11020	23 ² / ₃	15 ⁴ /s	4 ² /3	600	400	117	-	-	-	-	-	-	-	-

KeepBoxesTM

- KeepBoxes stack and nest for optimal space usage
- Clearly identify contents through transparent bases
- Attached lids snap securely closed to protect contents from dust or damage





Durable full-length steel hinge pins for lids

66497CLDGN

Ribbing reinforces sides to prevent flexing under loads

Tilt & Locks


Model No.	Description	L	Inches W	н	L	mm W	Н	Ctn. Qty.
66486CLDBL	12-Gallon KeepBox	21½	15	12½	546	381	318	6
66499CLSIL	68-Quart KeepBox	23	16 ⁵ ⁄⁄8	14	584	422	356	6
66497CLDGN	18-Gallon KeepBox	21½	15	17	546	381	432	3

Attached Lid Containers



Designed to stack together for easy pallet loading.

- Reusable shipping, distribution, order picking, and storage containers.
- Attached lids snap securely closed to protect contents from dust or damage.
- ALC's stack and nest for optimal space use.
- Containers interwork for easy pallet loading.
- · Color: Gray, Blue.











Attached Lid Containers solid steel Dolly (Model No. RU843HR1420) is compatible with Models 39085, 39120, 39170 for efficient parts transport.


Akro-ALC's

Model	Outside Inches	Dimens	sions mm		-	Insi nche		nension	Top mm		Inside Inch		nsion Bo mi		Cubic	Capacity	Ctn.
No.	L W H	L	W F	ı	L	W	Н	L	W	Н	L	W	L	W	Ft.	Gal.	Qty.
39085	21½ 15 9	546	381 22	9	19¾	14½	8%	502	368	219	18 ⁷ ⁄16	13 ¹ / ₄	468	337	1.12	8.5	6
39120	21½ 15 12½	546	381 31	8	19¾	14½	12	502	368	305	18 ⁷ ⁄16	13 ¹ / ₄	468	337	1.62	12	6
39170	21½ 15 17	546	381 43	32	19¾	14½	16 ⁷ /8	502	368	429	187/16	13 ¹ / ₄	468	337	2.28	17	3

Order in carton quantities


Akro-ALC's Dolly

Model	D	imensior	าร	Ctn.	Capacity	
No.	L	W	Н	Qty.	Lbs.	Casters
RU843HR1420	19¾"	14½"	4¾"	1	900 lbs.	3 " Polyolefin
Compatible with	Models 39	9085, 391	120, 391	70		



Industrial Attached Lid Containers

- Heavy-duty containers for industrial applications.
- Stack and nest design for maximum space usage.
- Injection-molded HDPE construction resists impact, moisture, and most chemicals.
- Tie holes in both ends to provide additional security.
- Containers interwork for easy pallet loading.
- Model AR15141300 is ideal for liquid distribution applications – it holds four, one-gallon jugs or nine 750 ml bottles.





Attached lid containers cube pallets and allow better space utilization of trailers and warehouses.



























See pages 68-70 for a selection of wood, plastic and steel dollies.





		C	Outside D	imensio	ns			Insid	le Dimen	sions Bo	ttom			
Model		Inches			mm			Inches			mm		Capa	acity
No.	L	W	Н	L	W	Н	L	W	Н	L	W	Н	Lbs.	Kg
AR15141300	14¾	13½	135/16	374	343	338	1111/4	111/4	11½	286	286	302	50	23
AR20120702	20	11 ¹¹ /16	71/2	510	295	190	16 ⁷ /s	91/16	61/16	430	245	153	40	18
AR21150902	21¾	15½	9%	552	387	245	18¾	13	81/2	467	330	215	60	27
AR21151202	21¾	15½	12 ¹³ /16	552	387	325	17 ⁷ /s	12½	11½	455	320	285	60	27
AR21151700	21¾	15½	17	552	387	431	175/16	12 ⁷ /16	15 ¹⁵ ⁄16	455	316	404	60	27
AS22131202	22¾	13	12 ⁷ /s	567	330	327	181/5	10 ³ / ₃₂	111/5	483	254	298	60	27
AP22161000	21¾	16½	10 ¹ / ₄	552	419	260	189/32	14	84/5	464	356	222	60	27
AR24201202	24	19½	125/8	610	495	320	201/2	16 ¹⁹ / ₃₂	101/5	520	421	279	80	36
AR27170902	27½16	16 ⁷ /s	9%	687	430	240	23%0	143/32	8	610	360	203	80	36
AR27171202	271/8	16 ⁷ /s	12½	689	430	320	23½	134/5	10%o	600	350	278	100	45
AS28211502	28	20¾	15 ⁷ ⁄16	710	530	390	25	18	14	635	460	355	100	45
AS34242012	34	24	19%	865	610	500	29%	19½	18 ³ / ₃₂	760	495	460	100	45

Attached Lid Containers cont.



Dual-purpose attached lid opens out for full access to container when loading



In flow racks or on shelving, the quarter-half lids open up and back for access through the top of the container.




On the picking or assembly line, the hinged front gate drops down for complete, easy product access.

BinBox[™] Container

- Bi-directional attached lid allows easy loading, secure shipping, and quick picking.
- Lid can be secured with ties for extra spillage/theft protection.

Reinforcing ribs on lid add strength for stacking

Nesting stops prevent container jamming




BinBox™ Container

				Size				
Model		Inches			mm		Capa	acity
No.	L	W	Н	L	W	Н	Lbs.	Kg
AB21150900	21 ³ / ₄	15 ¹ / ₄	91/4	552	387	235	60	27

Bi-Fold Lid Containers

- Ideal for distribution of small orders up to .78 cubic feet.
- Interwork with 21" x 15" attached lid containers.
- The attached-recessed lid flaps fold in half and lock against the side of the container for ease of conveying and nesting.
- Interlocking fingers on lid provides secure closure and stacking strength.

Textured areas allow for identification label placement and easy label removal



Lids have reinforcing ribs for extra strength

Bi-Fold Lid Containers

	Size											
Model		Inches			mm		Capa	acity				
No.	L	W	Н	L	W	Н	Lbs.	Kg				
AF21150602	21½	15 ¹ / ₄	65⁄8	546	387	168	60	27				



Detached Lid Containers







Handles

Several handle styles available

- Open for easy gripping.
- Closed for increased security.
- Ergonomic for comfortable lifting.
- Handle styles vary by model.

- Lids are available in recessed style for secure stacking, strapping style for banding use, and high cube for additional storage space.
- Containers stack, nest, and interwork.
- Textured bottom standard on most models to prevent slippage on conveyors. Smooth bottoms also available.
- 24" x 20" containers cube 48" x 40" pallets, 4 per layer.



Detached Lid Containers

			Size						
Model		Inches			mm		Capacity		
No.	L	W	Н	L	W	Н	Lbs.	Kg	
21" x 15"									
DL21150512	213//8	15¼	5¾	543	387	170	50	23	
DL21150712	213/8	15¼	77/8	543	387	200	50	23	
DL21150900	213/8	15 ¹ / ₄	9%16	543	387	243	60	27	
DL21151202	213/8	15¼	12¾	543	387	314	-	-	
24" x 20"									
DL24200614	24	20	6¾	610	508	171	50	23	
DL24201014	24	20	10¾	610	508	264	80	36	
DL24201202	24	20	123/8	610	508	314	80	36	

21" x 15" Detached Lids

		Dimensions						
Model No.	Description	L"	W"	Н"				
DR21150100	Recessed Lid	21¾	15 ¹ ⁄16	11/4				
	mm/kg	543	384	30				

24" x 20" Detached Lids

		Dimensions						
Model No.	Description	L"	W"	H"				
DR24200100	Recessed Lid	24	20	1 ¹ /16				
	mm/kg	610	508	29				

Akro-Grids



Modular box dividers maximize space.

- Versatile work-in-process transfer containers.
- Injection molded from high-density polyethylene.
- · Resist most solvents and chemicals.
- Compatible with most racks, shelving, and automated material handling equipment.
- Ribbed design adds strength.
- Dividers allow subdivision of the containers down to a 1 1/4" square compartment size.
- Dividers, lids, and label holders sold separately.
- Available in 8 sizes and 3 colors: Red, Blue, or Gray.
- Models 33164 and 33224 are available with ESD protection (see page 15).

Divider slots allow you to create hundreds of different compartment sizes



Strong stacking rims and external ribbing provide added strength

Optional label holders for content identification







Inside Dimension



33105





Akro-Grids

		Outside Dimensions Inside Dimer					nsion	s												
Model	- I	nches			mm				Inches					mm			Capa	city	Weight	Ctn.
No.	L	W	Н	L	W	Н	Α	В	C	D	Е	Α	В	C	D	Е	Cu. Ft.	Cm	Capacity	Qty.
33105	10¾	81/4	5	276	210	127	611/16	95/16	91/8	6½	4%	170	237	232	165	117	.16	.004	25	20
33164	16½	10 ⁷ /s	4	419	276	102	9%	$14^{15}/_{16}$	14 ¹³ / ₁₆	93/16	3%	238	380	376	233	98	.29	.008	20	12
33166	16½	10%	6	419	276	153	95/16	141/8	14¾	91/8	5%6	237	378	375	232	141	.44	.012	35	8
33168	16½	10%	8	419	276	203	95/16	14 ¹⁵ /16	14%	91/16	7%16	237	380	371	230	192	.59	.016	40	6
33220	22¾	17%	10	568	441	254	151/4	201/8	19¾	14¾	9%	387	511	505	378	251	1.66	.047	50	2
33224	22¾	17%	4	568	441	102	151/16	201/16	20	15	3%	383	510	508	381	98	.61	.017	30	6
33226	22¾	17%	6	568	441	153	151//8	201/8	19%	14¾	5%	384	511	505	378	149	.96	.027	40	4
33228	22¾	17¾	8	568	441	203	151//8	201⁄8	19¾	141/8	77/16	384	511	505	378	189	1.30	.036	50	3



Solid steel dolly for efficient parts transport

AkroGrids Steel Dolly

Model	Dimensions			Ctn.	Capacity	
No.	L	W	Н	Qty.	Lbs.	Casters
RU843HR1621	21¾"	16¾"	4¾"	900 lbs.	1	3 " Polyolefin
Compatible with	Models 33	3220 333	224 332	226 3322	3	

Optional Accessories:

Dividers



Dividers allow sub-division of the containers down to a $1^{1}/4$ " square compartment size. Black.

Long Divider	Short Divider	Fits Grid No.	Pkg. Qty.
42105 (5)	41105 (7)	33105	6
42164 (7)	41164 (11)	33164	6
42166 (7)	41166 (11)	33166	6
42168 (7)	41168 (11)	33168	6
42220 (11)	41220 (15)	33220	6
42224 (11)	41224 (15)	33224	6
42226 (11)	41226 (15)	33226	6
42228 (11)	41228 (15)	33228	6

Clear Plastic Covers



Clear plastic dust covers keep contents clean yet visible. Molded corner guides provide secure stacking.

Model	Fits	Ctn.
No.	Grid No.	Qty.
33101	33105	10
33161	33166, 33168, 33164	4
33221	33228, 33220,	
	33226, 33224	3

Label Holders




Clear plastic label holders snap securely on any side of the container.

Model		Pkg.
No.	Description	Qty.
35010	Fits all Akro-Grids, except	
	33164 and 33224	6
35011	Fits grids No. 33164, 33224	16

Straight Wall Containers

- Reusable shipping, storage, and work-inprocess containers.
- Straight walls provide efficient internal and external space usage.
- Solid-sided containers have smooth inner walls for easy, sanitary cleaning.
- Mesh-sided containers allow hot or cold air ventilation.
- Injection-molded from high-density polyethylene.
- Available in 4 sizes and 3 styles.
- Modular design cubes 48" x 45" and 48" x 40" pallets.
- Interworking sizes allow mixed stacking on pallets.
- Compatible with automated handling systems.
- SW prefix denotes standard bottom.
- SX prefix denotes cross cube bottom.
- Lids snap tightly in place protecting contents from contaminants. Tie holes allow lids to be secured with ties.
- · Color: Gray.








Handholes on all four sides provide an easy grip from any angle.

Three Styles Per Size:





Mesh Base/Mesh Sides





SWC's

Solid Base/Mesh Sides

			Outside Dimensions						Ins	ide D	imensi	ons			
Mesh Side	Mesh Side	Solid Side		Inches			mm		Inches			mm			Ctn.
& Base	w/Solid Base	& Base	L	W	Н	L	W	Н	L	W	Н	L	W	Н	Qty.
37208	37278	37288	15¾	11¾	81/4	400	298	210	141/4	10 ¹ ⁄⁄4	8	362	260	203	12
37608	37678	37688	23¾	$15\frac{3}{4}$	81/4	603	400	210	221/4	14½	8	565	362	203	4
37612	37672	37682	23¾	$15\frac{3}{4}$	121/4	603	400	311	221/4	14½	12	565	362	305	3
37616	37676	37686	23¾	15¾	16½	603	400	410	221/4	141/4	16	565	362	406	2



Solid steel dolly for efficient parts transport

Straight Wall Container Dolly


Order in carton quantities

Model	D	imensior	ıs	Ctn.	Capacity	
No.	L	W	Н	Qty.	Lbs.	Casters
RU843HR1624	24%"	16¾"	4¾"	900 lbs.	1	3 " Polyolefin
Compatible with	Models 3	7608, 376	578, 376	88, 37612	2, 37672, 3	37682, 37616, 37676, 37686

Industrial-Duty Straight Wall Containers



Our SX Cross Cube containers have a special bottom that allows larger containers to stack on top of smaller containers.





Custom Interior Dunnage


For special product applications, we will analyze your needs and design custom interior packaging to protect your product.



Straight Wall Com	anicis							
			Outside	Dimensions				
Model		Inches			mm		Capac	ity
No.	L	W	Н	L	W	Н	Lbs.	Kg
SW12070502	12	7½	5	305	191	127	60	27
SW15120602	15	12	5½	381	305	140	100	45
SW151208A2	15	12	7½	381	305	191	100	45
SX151208A4	15	12	7½	381	305	191	100	45
SW15121002	15	12	9½	381	305	241	100	45
SW24111002	24	11	9½	610	279	241	100	45
SW241504A2	24	15	4	610	381	102	100	45
SX241504A4	24	15	4	610	381	102	100	45
SW24150602	24	15	5½	610	381	140	100	45
SW241508A2	24	15	7½	610	381	191	100	45
SX241508A4	24	15	7½	610	381	191	100	45
SW24151002	24	15	9½	610	381	241	100	45
SX24151000	24	15	9½	610	381	241	100	45
SW241511A2	24	15	11	610	381	279	100	45
SX241511A4	24	15	11	610	381	279	100	45
SW24151502	24	15	14½	610	381	368	100	45
SW24220802	24	22	7½	610	559	191	100	45
SW24221102	24	22	11	610	559	279	100	45
SW32150802	32	15	7½	813	381	191	100	45
SW48150802	48	15	7½	1219	381	191	100	45
SX48150800	48	15	7½	1219	381	191	100	45



Interworking sizes allow mixed stacking on 48" x 40" and 48" x 45" pallets.



Lids

			Outside I	Dimensions		
Model		Inc	hes	Straight Wall		
No.	Description	L	W	L	W	Footprint
SL12070100	Vacuum Formed	113/4	71/4	298	184	12" x 17"
SL15120100	Injection Molded	15	12	381	305	15" x 12"
SL24150100	Injection Molded	24	15	6091/16	381	24" x 15"
SL24110100	Injection Molded	24	11 ⁷ / ₃₂	6091/16	285	24" x 11"
SL24220100	Injection Molded	241/32	221/16	6101/32	560	24" x 22"

Heavy-Duty Industrial Boxes



• Ideal for a wide range of applications such as shipping & storage, organizing workstations, and assembly operations.

• HDPE structural foam construction for durability.


Tote Boxes

• Lightweight, stackable, and strong to replace steel containers.



- Vented and solid styles.
 - 150 lb. capacity.
 - Colors: Black or Blue.





HT19100400



Hopper Boxes



- Great space savers for shelving and workstations.
- · Easy front access for picking efficiency.
- · An excellent alternative to steel hoppers.
- Available in 2 sizes, stack 4 high when loaded.

HT15100622

- 150 lb. capacity.
- Colors: Black or Blue (other colors available with a flushout charge).



HH24110900

HT19100422

Hopper Boxes

Model		Inches			mm	Capacity		
No.	L	W	Н	L	W	Н	Lbs.	Kg
HH19110700	19 ¹ / ₄	11	6¾	489	279	171	150	68
HH24110900	23½	11	9	597	279	229	150	68

Industrial Tote Trays

- Available in two styles: solid bottom or ½" diameter drainage holes.
- Space savers: nestable and stackable.
- Designed for rugged conveyor use or picking operations.
- 100 lb. capacity.
- · Color: Black.



Industrial Tote Trays

Model		Inches			mm	Capacity		
No.	L	W	Н	L	W	Н	Lbs.	Kg
HI20140320	20	14	2¾	508	356	70	100	45
HI20140300	20	14	2¾	508	356	70	100	45
HI20140400	20	14	4	508	356	102	100	45
HI20140420	20	14	4	508	356	102	100	45

Stacking & Nesting Boxes



- The boxes stack and nest for transport and workstation space savings.
- Available in 3 sizes.
- 150 lb. capacity.
- Colors: Black or Blue (other colors available with a flushout charge).



HS22130600

Stacking & Nesting Boxes

Model		Inches			mm	Capacity		
No.	L	W	Н	L	W	Н	Lbs.	Kg
HS22130600	22	13	5¾	559	330	141	150	68
HS24160900	24	16	9	610	406	229	150	68
HS28170900	28	16¾	8¾	711	425	222	150	68

Tote Caddy

- Hand-held tool and supply caddy.
- Deep compartments hold loose parts, cleaning supplies, or tools for easy transport.
- Molded of heavy-duty, industrial-grade polypropylene for lasting durability.
- · Color: Blue.



Tote Caddy


Model		Inches			mm	Ctn.	
No.	L	W	Н	L	W	Н	Qty
09185	13¾	18 ¹ / ₄	83/4	349	464	222	6

Cross-Stack Akro-Tub



Stacking grooves allow stable 90° stacks

- Industrial-grade 90° nest and stack tub.
- Nesting when empty conserves storage space.
- Molded-in side handles for comfortable lifting.
- Manufactured from FDA-approved materials.
- Smooth surface is easy to clean.
- Compatible with standard 36" shelving and conveyor systems.
- · Color: Gray.





Cross-Stack Akro-Tub

	Outside Dimensions											
Model	Inches							Capacity	Ctn.			
No.	L	W	Н	Α	В	L	W	Н	Α	В	Gal.	Qty.
34301	17 ¹ / ₄	11	8	13 ¹ / ₄	73/4	438	279	203	337	196	3.85	6
34302	17 ¹ / ₄	11	12	12 ⁵ /8	7	438	279	305	319	178	5.51	6
34303	233/4	17 ¹ / ₄	8	19³⁄4	14	603	438	203	502	354	9.81	6
34304	233/4	17 ¹ / ₄	12	19	13 ¹ / ₄	603	438	305	484	337	14.38	6

Akro-Tub & Rack



- Tub manufactured from FDA-approved materials.
- Smooth surface is easy to clean.
- Nests when empty to conserve storage space.
- Use the Akro-Tub Rack (RA6TR4MR) to provide easy loading and transport of multiple Akro-Tubs.
- 75 lb. capacity per tub.
- · Color: Gray.



Tubs nest for convenient storage



Akro-Tub

Outside Dimensions											
Model		Inches mm								Ctn.	
No.	L	W	Н	Α	В	L	W	Н	Α	В	Qty.
34240	19	24½	9½	20½	15½	483	622	241	521	394	6

Order in carton quantities.

Akro-Tub Rack

ARTO TOD HOCK	•						
Model		Inches			mm		
No.	Н	W	D	Н	W	D	Casters
RA6TR4MR*	73	24	24	1854	609	609	4" x 2" Moldon Rubber – 2 Rigid, 2 Swivel

*Tubs sold separately.



slides for up to 600-lb. total capacity. Welded steel frame with 12-gauge base and bolted-on casters. Color: Gray.

Tubs sold separately.

Akro-Tubs on angle-iron

Agricultural Containers

- Easy-to-clean containers are durable and reusable to save money for growers, packers, shippers, and retailers.
- Stack when full, nest when empty for space efficiency.
- Ventilated designs for quick cooling, temperature control, and drainage.

Harvesting Containers

- Suitable for mushrooms, grapes, asparagus, and other small fruits and vegetables.
- Stacking posts permit rigid stacking with a 180° turn.
- Nesting ratio of 2.6:1 to save storage space and shipping costs.
- · Color: Gray.

Model	Inches				mm	Capacity		
No.	L	W	Н	L	W	Н	Lbs.	Kg
AG24160752	24	16½	71/4	610	410	185	60	27



AG24160752

Produce Lugs

- Perfect harvesting and shipping tray for mushrooms or other small products.
- Locking pegs limit container movement to prevent product damage during transport.
- Capable of holding 8, 12, and 16 oz cartons or loose product.
- Produce Lugs stack and nest with either a 180° or 90° turn.
- Color: Gray.

Model		Inches			mm	Capacity		
No.	L	W	Н	L	W	Н	Lbs.	Kg
AG20160422	19½	16¾	4³/16	495	415	105	10	5



Specialty Containers Commissary Case

- Open-weave design for efficient cooling to keep food fresh.
- Lengthwise zinc-plated steel bails fold in for secure stacking and out for space-saving nesting.
- Cases fit six per layer on a 48" x 40" pallet.
- · Color: Beige.



Commissary Case

Model		Inches			mm	Capacity		
No.	L	W	Н	L	W	Н	Lbs.	Kg
CC20141160	20	14 ⁷ /16	11	510	365	280	60	27

JumboLugs

- Stacking grooves allow rigid 90° stacks.
- · Fits standard cart and rack sizes.
- Compatible with most conveyor systems.
- Optional Lid: Model No. LJ25160200 (Lid)
- Available in Natural, Gray, Yellow, Red, Green



Jumbo Lugs

Model		Inches			mm		Capacity		
No.	L	W	Н	L	W	Н	Lbs.	Kg	
JL25160968	25	16	81/2	635	405	215	100	45	
LJ25160200	253/8	16 ⁷ /16	19/16	645	418	40	-	-	

Food Process Containers

- Designed to fit a wide range of shipping, handling, and storage applications for food processors, distributors, and retailers.
- · All products molded from approved materials and designs.
- Resist temperature extremes (-20°F to 120°F).



NestPac Containers

- · Ideal for poultry, meat, and seafood processing, distribution, and many other foodservice and grocery applications.
- · Containers stack with lids, cross-stacking 5 per layer on a 48" x 40" pallet.
- · Nest when empty for space-saving storage and return shipment.
- · Smooth interiors for easy cleaning.
- · Available with drain holes.
- · Colors: Blue, Gray, Beige.




Lid

NL24160259



NestPac containers allow sanitary handling during distribution.



NestPac Containers


		(Outside [s					
Model	Inches				mr	n	Capa	Drain	
No.	L	W	Н	L	W	Н	Lbs.	Kg	Holes
C18-541E	245/16	16 ⁵ /16	8¾	620	415	222	50	23	No
NP24160887	245/16	16 ⁵ ⁄16	8	620	415	205	50	23	Yes
NP24161194	245/16	16 ⁵ ⁄16	10 ¹³ /16	620	415	275	80	36	No
NP24161195	245/16	16 ⁵ /16	10 ¹³ /16	620	415	275	80	36	Yes
NL24160259 Lid	24³⁄s	16¾	1 ¹³ /16	620	415	45	-	-	-



Aluminum dolly provides easy transport of full ChillPac Containers with bails. 1800 lb. capacity. Model No. DY22190700

hillPac Container System

- Available in 7", 10", and 13" interworking heights.
- · Molded-in handles for easy lifting.
- 24" x 20" footprint cubes standard food industry pallets.
- Suitable for in-store display use.
- Compatible with most automated systems.
- Colors: Blue, Beige.



of containers and contents

airflow to maintain uniform coolness






ChillPac Container System

Model		Inches	Capa	pacity				
No.	L	W	Н	L	W	Н	Lbs.	Kg
CP24200760	24	20	6 ⁷ /s	610	508	175	60	27
CP24201360	24	20	13¾	610	508	340	100	45
CP24201060	24	20	9%16	610	508	243	80	36
DY22190700 Dolly	22 ³ /8	18 ⁷ /s	8	568	479	203	1800	810

ChillTrays

- Open weave design allows quick chilling/cooling of meat, poultry, or seafood for in-plant handling and distribution.
- Reinforced sides and bottoms prevent flexing under loads.
- Reinforced design for weight loads of 40+ lbs.
- Smooth surfaces are easy to clean.
- · Color: Beige.










Lengthwise bails fold in to prevent product damage.


ChillTrays


Model	Inches mm							Capacity	
No.	L	W	Н	L	W	Н	Lbs.	Kg	
CT29260922	29½	26 ¹ /16	9	70	662	229	80	36	
CD28270120	27½	26 ¹ /16	11/3	669	662	33	40	18	

MultiPac™ Container










- 24" x 20" x 6.7" size optimizes internal space usage.
- Cubes 48" x 40" pallets for transport efficiency, lower costs.
- Colors: Blue/Gray.



MultiPac™ Container

Model	Inches				mm		Capa	acity
No.	L	W	Н	L	W	Н	Lbs.	Kg
MP24200722	24	20	6 ¹¹ /16	610	508	170	30	13.6


Bulk Boxes



Bulk Boxes are easy to collapse and stack securely, loaded or folded, to save freight and storage costs

- Manufactured from HDPE structural foam plastic for strength and long service.
- Durability for hundreds of round trips with low cost per-trip.
- · Backed by a 3-year warranty.

Post & pocket panels or snap-lock latches for smooth collapse and set-up



Structural foam lids provide heavy-duty strength and prevent contamination. Available on select Bulk Boxes.

Heavy-Duty Bulk Box

- · The Heavy-Duty line is structural foam molded and will support loads up to 2,500 lbs.
- · Reinforced base with 3 steel runners for durability.
- Interlocking side panels form continuous reinforcing ribs for strength.
- 4-way fork entry for easy handling.
- Colors: Black, Blue, and Lt. Gray.

Drop doors allow easy access to product: 0, 1, or 2 door options

Drop doors allow quick, easy access to contents



Steel corner hit plates deflect fork tines and extend box life

Heavy-Duty Bulk Boxes


Model	Inches				mm			Capacity		
No.	L	W	Н	L	W	Н	Lbs.	Kg		
BH48403420	475/8	39³⁄4	33 ⁷ /8	1210	1010	860	2500	1134		
BH48453420	475/8	445/8	34	1210	1133	864	2500	1134		
Lids										
TH484002001	48¾	40 ⁷ /16	21//8	1229	1027	54	-	-		
TH484502001	481/4	45½	21/4	1226	1149	57	-	-		



TH484002001

Extended Length Bulk Box

- Extended length holds extra-large, extra-long parts.
- · Unique, reinforced design delivers secure, rigid stacking.
- · Solid, one-piece base for handling any load up to 2,000 lbs.
- · Long side walls collapse first to prevent wall bowing in storage.
- · Color: Black.



Spring-loaded latches ease assembly and knock-down


Optional steel hit plates deflect fork tines to prevent spearing

Extended Length Bulk Boxes

Model		Inches			mm		Capa	city
No.	L	W	Н	L	W	Н	Lbs.	Kg
BS64483411	64½	48	34	1638	1219	864	2000	907

Industry Standard Bulk Box

- Industry Standard Bulk
 Boxes are perfect for many
 manufacturing applications,
 providing superior product
 protection for loads up
 to 1,800 lbs.
- 2 drop doors for quick access.
- Interlocking side panels form continuous reinforcing ribs for strength.
- Structural foam construction gives long service life.
- Optional lids protect contents from debris.
- · Colors: Black, Blue.



Industry Standard Bulk Boxes

			Outside Dimensions										
acity	Capa		mm			Inches	Model						
Kg	Lbs.	Н	W	L	Н	W	L	No.					
817	1800	635	762	816	25	30	32	BS32302500					
817	1800	864	762	816	34	30	32	BS32303420					
817	1800	864	1143	1219	34	45	48	BX48453420					
								Lids					
-	-	64	781	832	21/2	30¾	32¾	TS32300200					
-	-	51	1168	1245	2	46	49	TS48450300					
	-	64	781	832		30¾	32¾	Lids TS32300200					



TS32300200

General Purpose Bulk Box

- A perfect choice for lighter-weight material handling. General Purpose Bulk Boxes can be used in applications from agriculture and general manufacturing to plastic parts transport.
- Redesigned base and walls provide an increased capacity to 1,500 lbs.
- 4-way fork lift entry for easy movement.
- Side latches secure panels and doors.
- Optional lid to protect contents from debris.
- Color: Gray.



General Purpose Bulk Boxes


Model		Inches	Capa	Capacity				
No.	L	W	Н	L	W	Н	Lbs.	Kg
BG48403302	48	40	34	1219	1016	864	1500	680
Lid								
TS48400200	49	41³/₃₂	2	1245	1044	51	-	-



TS48400200

Pallets

- Reusable for hundreds of round trips and lower overall cost per-trip.
- Lightweight design for safer handling.
- Compatible with automated handling equipment.
- Superior resistance to moisture, most chemicals, and temperature extremes.
- 100% recyclable for environmental and cost savings.



Medium-Duty Nestable Pallet

- \bullet Available in 48" x 40" and 48" x 48" footprints.
- 4,000 lbs. dynamic load capacity.
- 9 reinforced feet uniformly distribute the load.
- Available with solid deck.



Medium-Duty Nestable Pallet

Model	Inches mm							pacity	
No.	L	W	Н	L	W	Н	Lbs.	Kg	
PM484006001	48	40	6	1219	1016	152	4000	1800	
PM484806001	48	48	6	1219	1219	152	4000	1800	



Medium-Duty Rackable Pallet

- Available in 48" x 40" and 48" x 48" footprints.
- 4,000 lbs. dynamic load capacity.
- 6 rails on base for safe racking.
- Available with solid deck.



Medium-Duty Rackable Pallet

Model		Inches	Capa	pacity				
No.	L	W	Н	L	W	Н	Lbs.	Kg
PM484006331	48	40	6 ¹ /4	1219	1016	159	4000	1800
PM484806331	48	48	6 ¹ /4	1219	1219	159	4000	1800



Standard Nestable Pallet

- Available in 48" x 40" footprint.
- 2,000 lbs. dynamic load capacity.
- 9 reinforced feet uniformly distribute the load.
- · Available with ventilated deck.
- 4-way entry accommodates fork trucks and pallet jacks.
- Lightweight design 29 lbs. for easy lifting.



Standard Nestable Pallet

Model	Inches mm							Capacity	
No.	L	W	Н	L	W	Н	Lbs.	Kg	
PS484006001	481/2	401/2	61/4	1233	1030	159	2000	900	



Standard Stackable Pallet

- Available in 48" x 40" footprint.
- 1,500 lbs. dynamic load capacity.
- Rackable with center support or decking with 9-post construction for strength.
- 2-piece, snap together design allows components to be replaced without purchasing a new pallet.
- Solid deck with textured, anti-skid surface.
- 4-way entry accommodates fork trucks and pallet jacks.



PS484006331

Standard Stackable Pallet

Model		Inches			mm		Capa	acity
No.	L	W	Н	L	W	Н	Lbs.	Kg
PS484006331	48	40	5½	1219	1016	141	1500	680



Heavy-Duty Universal Pallet

- Edge rackable to 2,800 lbs. choose from molded-in plastic or steel reinforcement rods to match your capacity requirements.
- Available in 48" x 40" footprint.
- Angled 4-way entry points guide fork tines for easy handling.



Heavy-Duty Universal Pallet

Dimensions								
Model	Inches			mm			Capacity	
No.	L	W	Н	L	W	Н	Lbs.	Kg
PU484006331	48	40	5½	1219	1016	141	5000	2268







Recycling
Containers
Fits office or home recycling programs.



Whisper Series
Exceptionally quiet waste handling container.



Janitor Cart
Smart features designed
to help work faster and
more efficiently.



MegaKart
Economical container for mobile waste transport.



Akro-Tilt Trucks Lightweight tipping trucks for heavyweight jobs.



Compact Cleaning Cart
Revolutionary cleaning cart to save time.



BossKart
Exceptionally durable
and strong mobile
waste container.

39



 $\begin{array}{c} Akro/Lift \\ \text{Clean, efficient, and safe} \\ \text{dumping system.} \end{array}$

41



Akro-Carts
Non-tipping carts
for waste collection,
transport, and disposal.



Recycling Containers


- Variety of sizes simplifies separation of glass, paper, and plastic for sorting or pickup.
- Durable plastic construction with a UV inhibitor to resist fading.
- Withstands a wide temperature range -20° F to 120° F.
- Containers are imprinted with "WE RECYCLE" to increase program awareness.
- · Color: Blue.











Recycling Containers


Model		Inches			mm		Capa	acity
No.	L	W	Н	L	W	Н	cu. ft.	liters
C75-605	16 ¹ /16	16 ¹ /16	8³⁄16	408	408	208	.9	25.5
075-611	20 ³ / ₄	15	12	527	381	305	1.69	48
RC25171401	25	17	13	635	432	330	2.54	72
Bulk Box							lbs.	Kg
BX48452520	48	45	25	1219	1143	635	1800	810
BX48453420	48	45	34	1219	1143	804	1800	810
Bulk Box Lid								
TS48450300	48¾	45 ¹ / ₄	23/4	1238	1149	70	-	-



Patented design allows carts to nest with installed lids and latchbars for compact shipping and storage



Foot Tilt Pocket molded above axle for maximum leverage and utility



Option: Lids can be ordered with patented latch feature to restrict full opening to 110 degrees.

- · 65 and 96-Gallon carts designed for residential waste management.
- · Compatible with automated and semiautomated systems.
- Attached lid swings out of the way for easy dumping.
- · Injection molded for exceptional durability and cost effectiveness.
- · Can be stacked and transported with factory-installed lids and latch bars.
- Resists damage from oil and most chemicals, engineered for rigidity and strength.
- · All carts are compatible with Hydraulic Akro/Lift (page 41).
- · Colors: Dark Green, Dark Blue, Light Gray.



MegaKart®

	Capacity		Inches			mm			Load	
Model No.	Gallons	W	D	Н	W	D	Н	Wheel Dia.	Rating	Ship Wt.
79596	96	28	32	46	711	813	1168	12"	335 lbs.	43 lbs.
79565	65	26	27	42	660	686	1067	10"	230 lbs.	35 lbs.

Please specify color when ordering

BossKart® & Versa-Kart®



Ergonomic Handles: Molded as part of container body. Lid handle for easy access.



Scuff Rails: Molded in the base for added durability. Expanded



footprint for stability.



Foot Tilt: Easy access to axle for maximum leverage and utility.

- 65 and 96-Gallon carts designed for residential waste management.
- Compatible with automated and semi-automated systems.
- · Attached lid swings out of the way for easy dumping.
- · Rotationally molded for uniformly thick, seamless walls with stressfree corners.
- Features a unique corner shape and pleats for exceptional strength.
- All carts are compatible with Hydraulic Akro/Lift (page 41).
- · Colors: Dark Green, Dark Blue, Light Gray.



Attached lid's convex shape allows over-loading and

BossKart®

	Capacity		Inches			mm			Load	
Model No.	Gallons	W	D	Н	W	D	Н	Wheel Dia.	Rating	Ship Wt.
79496	96	29	36	46	737	914	1168	12"	335 lbs.	42 lbs.
79465	65	28	33	41	711	838	1041	10"	230 lbs.	34 lbs.

evenly during lift cycle

Please specify color when ordering.

Versa-Kart®

Model No.	Model No.	Model No.	Capacity	I	Inche	s		mm		Load	Approx.
Green*	Blue*	Gray*	Gallons	W	D	Н	W	D	Н	Rating	Ship Wt.
V2124VK3518	V2119VK3518	V2118VK3518	35	221/4	23	37½	565	584	902	120 lbs.	23 lbs.
*Black lid is standard	with all models.										

(8" diameter on the 35-gallon model)

Akro-Carts



Frame is made from 16-gauge zinc-plated steel tubing on medium-duty models and powdercoated steel on heavy-duty models.

- Make transport and disposal within a facility fast, safe, and clean.
- Medium-duty and heavy-duty styles to fit your needs.
- Latch bars extend around the frame for added strength.
- · Wide mouth and low profile for easy loading.
- Medium-duty carts have riveted joints.
- Heavy-duty cart has welded joints.
- All carts are compatible with Hydraulic Akro/Lift (page 41).
- All carts available in Gray (Black Lid), Blue (Blue Lid) and Green (Green Lid).





Heavy-duty piano hinge keeps lid propped open during use.





Wheels and Axles: Medium-duty 60 and 90 gal. Akro-Carts feature 12" dia. wheels, high-impact plastic hubs with semi-pneumatic tires and 16-gauge steel tubing axle.



Wheels and Axles: Heavy-duty 90 gal. features ⁵/8" dia. solid steel shaft axle.

Akro-Carts

Model No.	Model No.		ı	nche	:S		mm		Load	Approx.
Without Lid*	With Lid	Description	W	D	Н	W	D	Н	Rating	Ship Wt.
76460	76461	Medium-Duty 60 Gal. Cap.	30½	48	33½	775	1219	851	300 lbs./136 kg.	51 lbs./23 kg. (w/lid)
76490	76491	Medium-Duty 90 Gal. Cap.	30½	47	39½	775	1194	1003	350 lbs./159 kg.	56 lbs./25 kg. (w/lid)
76590	76591	Heavy-Duty 90 Gal. Cap.	30½	47	39½	775	1194	1003	450 lbs.204 kg.	71 lbs.32 kg. (w/lid)

Please specify colors when ordering.
*Carts without lids cannot have lids added after production. Single units are shipped completely assembled.
When multiple units are ordered, lids are shipped separately and require assembly.

Whisper Series



Lift pockets and casters mounted with stainless steel fasteners



Caster assembly is 7-gauge solid steel. Mounting bolts are molded in base

- 3/8" thick roto-molded LLDPE walls are impact and dent resistant. UV resistant to prevent damage from sunlight.
- Molded LLDPE pocket liners for durability and noise reduction.
- Lid ribbed for strength and rapid water deflection.
- Smooth, reinforced corners and sidewalls are easy to clean.
- Molded-in color will not chip or peel. Resists damage from harsh chemicals and petroleum based liquids.



Whisper Series

			Inch	ies						
Model No.	Size	Ht. Front	Ht. Back	Length	Depth	Ht. Front	Ht. Back	Length	Depth	Ship Wt.
ACR-2	2-yard	38¾"	46"	71³⁄4"	34 ⁷ /8"	975	1168	1822	886	290 lbs.
ACR-3	3-yard	441/2"	55 ⁵ /16"	71 ³ /4"	40 ⁷ /8"	1130	1405	1822	1038	390 lbs.
ACR-4	4-yard	51"	63"	71 ³ /4"	47"	1295	1600	1822	1194	420 lbs.
ACR-6	6-yard	51"	68"	71 ³ / ₄ "	70 ³ /4"	1295	1727	1822	1747	460 lbs.

Akro-Tilt Trucks



Trucks tip for easy manual emptying.

Full, wrap-around tubular frame is 1" treated steel reinforced with 3/4" pipe insert.

- · Lightweight tipping trucks for heavy-weight jobs (up to 2000 lbs.).
- Ergonomic design makes trucks easy to maneuver.
- · Caster wheel has roller bearings for extra stability when pushing, pulling, or turning.
- · Handle is arc welded and reinforced for optimum durability.
- Wrap-around tubular frame is constructed of 1" powdercoated steel for enhanced appearance & rust protection.
- Designed for use with Hydraulic Akro/Lift (See below).
- All trucks available in: Gray, Red, Yellow, or Blue.





Medium-Duty 100 gal.



77505 Heavy-Duty 100 gal.



Super Heavy-Duty with optional lid 200 gal.

Model			Inches	5		mm		Wheel	Сара	acity	Load	Ship
No.	Description	W	D	Н	W	D	Н	Dia.	Gallons	Cu. Yds.	Rating	Wt.
77405	Medium-Duty 100	27	54	36	686	1372	914	12"	100	1/2	600 lbs/272 kg.	94 lbs./43 kg.
77410	Medium-Duty 200	33	66	42	838	1676	1067	12"	200	1	600 lbs/272 kg.	137 lbs./62 kg.
77505	Heavy-Duty 100	27	54	36	686	1372	914	10"	100	1/2	1000 lbs./454 kg.	115 lbs./ 53 kg.
77510	Heavy-Duty 200	33	66	42	838	1676	1067	10"	200	1	1000 lbs./454 kg.	150 lbs./58 kg.
77610	Super Heavy-Duty 200	33	66	42	838	1676	1067	12"	200	1	2000 lbs./907 kg.	170 lbs.77 kg.



Akro-Tilt Trucks

Optional Akro-Lid

Convex shape adds strength and provides room for overpacking. Available only for Medium-Duty 200, Heavy-Duty 200, and Super Heavy-Duty 200 (color: Black). A full-width, heavy-duty piano hinge in the middle keeps the lid propped open during use and allows front and back access.

Optional Lid For Akro-Tilt Trucks

Model		Inches mm				mm	m Fits Akro-Tilt Truck Ship					
No.	Description	W	D	Н	W	D	Н	Model	Wt.			
77002	Black Lid	34	67	5	864	1702	127	77410, 77510, 77610	12 lbs./5 kg.			

Akro/Lift



emptying of Akro-Carts, Versa-Karts, and Akro-Tilt Trucks

- Empties into containers, bailers, or compactors up to 57" high.
- · Cylinder mounts and main hinge are reinforced with ³/₄" steel.
- All moving parts are enclosed for worker safety.
- Weather-proof, hand-held remote control is standard.
- 12-Volt DC battery or specify voltage: 1-phase: 110, 220; 3-phase: 220, 230, 460, 575 (Canada).
- Standard finish is gray enamel. Custom colors available.



Hydraulic Akro/Lift

							Akı	ro-Ca	art	Tilt	-Truck	Ver	a-Kart		
Model		Inc	hes		mm		Cle	aran	ce	Cle	arance	Clea	arance		Ship
No.	Description	W I	DН	W	D	Н	R"	V"	Н"	R"	V" H"	R"	V" H"	Capacity	Wt.
78100	Hydraulic Akro/Lift	421/6 4	15 47	1080	1143	1194	115	93	115	132	93 132	109	90 109	1000 lbs./454 kg.	700lbs./317 kg.

AkroClean[™] Janitor Cart





The AkroClean Janitor Cart is designed to hold more supplies, keep trash concealed, separate wet and dry zones, and support a full mop bucket for easy transport. Add the sleek design, no-tip stability, and removable front platform, and you have one very effective cleaning, hauling, supply-storing cart.





The compartment door is easily removable for cleaning and open access to shelves.




The rear middle shelf is removable without tools.



The door latch fits standard security locks to create a locking storage cabinet.



Lift the lid and release the anchor strap to remove the liner.



AkroClean[™] Janitor Cart Ordering Information and Specifications:**

Dimensions: 55 "L x 23½" "W x 42" H (1397 x 597 x 1067mm)

Cart w/o Front Platform: 40 "L x 23½" "W x 42" H (1016 x 597 x 1067mm)

Material: Structural Web Plastic

Two, 10" dia. high-density rubber wheels; four, 4" casters

Model Number: 30955BRGRY – Ice Burgundy 30955BLGRY – Ice Slate

Additional Interior Shelf*: Model No. 30955SHELF (order separately)

^{*} One interior shelf included with AkroClean Janitor Cart.

^{**}Assembly required.

AkroClean™ Compact Cleaning Cart



Ideal for use in any application:

- Office
- Hospital
- · Schools & Universities
- Theaters
- Hotel
- Shopping Center
- Convention Center And Many More

The AkroClean Compact Cleaning Cart combines smart features to improve your cleaning efficiency.

- The only cleaning cart in the industry with a molded-in vacuum storage area.
- · Zippered, vinyl refuse bag conceals trash.
- Front platform securely holds a mop bucket or a 32-gallon refuse container.
- Ideal for office use, the cart's compact size and contoured design makes it highly maneuverable in tight spaces, avoiding damage to walls and furnishings.

Experience a revolution in your cleaning productivity with the AkroClean Compact Cleaning Cart!





AkroClean Compact Cleaning Cart Ordering Information and Specifications:

Dimensions:	40 ³ / ₁₆ " L x 23" W x 39" H
Material:	Structural Web Plastic
Wheels:	Two 8" non-marking, high-density rubber wheels; Two 3" non-marking, plate-style swivel casters
Model Number:	30945 Gray



Small Parts Storage



Steel Cabinets Industrial-strength small parts storage.

Mobile Rack

parts storage.

Hangs Akro-Mils steel

cabinets for mobile small



Storage Cases
The perfect case for storing and organizing supplies.



Tilt & Locks
Versatile small parts
organizer with tilt-out,
locking storage bins.



Storage-Go-Round
Rotating system for efficient small parts storage.



Tool Boxes
Tough-looking hard-working toolboxes for home or office.

48

Tool Rack
Organize wrenches,
screwdrivers, pliers and



Akro/Logic[™]
Organizers
Compartmentalized storage case with removable bins.



Plastic Cabinets
Economical cabinets store,
consolidate, and organize
small parts.



48Wrench Holder
Easy, organized access to up to 15 wrenches by size.

other long-handled tools.




Roto-Shelf
Move parts between
workstations with this
mobile storage unit.



Portable
Organizers
Compartmentalized case
for organized, portable
parts storage.



Steel Storage Cabinets



Steel cabinets stack together for highdensity storage.

- · Store, consolidate, and organize small parts.
- Two cabinets fit side by side on standard 36" wide shelving.
- · Drawers are removable and are rust, corrosion, and dent-proof.
- · No sharp edges to damage parts.
- Unique rear stop tab on each drawer prevents spills.
- · Additional dividers, labels, and replacement drawers can be purchased separately.
- · Color: Gray.

Chip-proof baked-Heavy-duty weldedsteel frame enamel finish Molded-in label holder and Strong high-impact transparent window allow polystyrene drawers instant content identification

19-Series Heavy-Duty Cabinets

Cabinet frame: 17" wide x 11" deep x 11" high with 109/16" drawer depth. Steel cabinets have five different drawer sizes. Each drawer includes two removable dividers and one label. Seven divider slots per drawer. Optional security cabinet with locking door.









17-Series Light-Duty Cabinets

Cabinet frames: 18" wide x 6" deep x 9¹/₂" high with 53/4" drawer depth.



17018



Two Drawer Depths



17-Series have 53/4" deep drawers. 19-Series have extra-deep 109/16" drawers for optimum storage flexibility.

Steel Storage Cabinets

Jicci Ji	orage Cabinets										
		Drawers			Drawer	Dimensio	ns				Dividers
Model		Per		Inches			mm		Ctn.	Drawer	25/Pkg.
No.	Description	Cabinet	W	Н	D	W	Н	D	Qty.	Model No.	Model No.
19-Series	Heavy-Duty 17" W	x 11" D x 1	11" H (4	32 x 279	x 279mn	n)					
19228	Storage Cabinet*	28	2¾6	21/16	10%6	56	52	268	1	20228	40228
19320	Storage Cabinet*	20	3¾6	21/16	10%6	81	52	268	1	20320	40320
19416	Storage Cabinet*	16	4	21/8	10%6	102	54	268	1	20416	40416
19715	Storage Cabinet*	15	3¾6	31/16	10%6	81	78	268	1	20715	40715
19909	Storage Cabinet*	9	5¾ ₆	31/16	10%6	132	78	268	1	20909	40909
19109	Security Cabinet	9	5¾6	31/16	10%6	132	78	268	1	20909	40909
	w/ locking door										
17-Series	Light-Duty 18" W	x 6" D x 9½	2" H (45	7 x 152	x 241mm)						
17018	Storage Cabinet	18	23/4	2½	5¾	70	64	146	1	20902	40901
17136	Storage Cabinet	36	2¾	1 ¹ /4	5¾	70	32	146	1	20502	40501

^{*}Available with a locking door when ordered in quantities of 50 or more.

Storage Cabinet Hanging Systems



Mobile Steel Cabinet Rack*

Double-sided, mobile rail rack holds 12 of the 19-Series cabinets with as many as 336 drawers. Supports up to 500 lbs.

Order These Components and Quantities

30012 Double-Sided Rail Rack - Qty: 1 30424 Mobile Kit - Qty: 1

19-Series Cabinets - Mix or Match - Qty: 12 98400 Suspension Straps (Set of 2 straps) -Qty: 12 Sets

*Assembly required



Storage-Go-Round*

Access 20 cabinets and as many as 560 drawers in less than three square feet of floor space. Holds up to 1,000 lbs. of parts.

Accommodates Akro-Mils 19-Series Steel Cabinets (sold separately)

Order These Components and Quantities

98325 Storage-Go-Round with turntable base Assembled Storage-Go-Round stands 31"L x 31"W x 60"H (787 x 787 x 1524 mm)

19-Series Cabinets - Mix or Match - Qty: 20

*Assembly required

Storage Cabinets



I.D. Size: 4³/₈W x 2H x 5¹/₄L



I.D. Size: 21/8W x 11/2H x 51/4L

Akro-Mils' clarified polypropylene drawers are the best in the industry!

- Unbreakable no cracked drawers in shipping unlike polystyrene drawers
- Flexible, strong, and see-through
- Chemical-resistant

- Strong plastic cabinets organize and protect components.
- A variety of drawer configurations provide versatile storage solutions.
- Cabinets stack securely and are wall mountable.
- Dividers won't get lost molded into cabinet back.



Frame back interlocks into face

Flexible, strong, and see-through drawers

Finger grip drawer pulls provide easy access

Rugged, high-impact polystyrene frame









Storage Cabinets

Model			Inches			mm		Ctn.
No.	Description	L	W	Н	L	W	Н	Qty.
10116	16-Drawer Cabinet	10%6	8½	63/8	268	216	162	1
10126	26-Drawer Cabinet	20	10 ¹¹ /s ₂	63/8	508	263	162	1
10124	24-Drawer Cabinet	20	15 ¹³ /16	63/8	508	402	162	1
10144	44-Drawer Cabinet	20	15 ¹³ /16	63/8	508	402	162	1
10164	64-Drawer Cabinet	20	15 ¹³ /16	63/8	508	402	162	1

16-Drawer Cabinet has 8 dividers. All other cabinets have 8 small and 4 large dividers.

Portable Organizers



New! Flat-bottom organizer holds large, bulky items in main compartment.

- Combination small and large parts storage.
- Unique design keeps parts and equipment from migrating to other compartments when lids are shut.
- Separate lid compartment holds small items.
- The main compartment holds larger, bulky items.
- Dividers included for both levels.
- Molded-in "feet" allow case to stand upright.
- Organizers are blue with clear lids and black latches. (Flat-bottom organizer has orange latches.)



Portable Organizers

Model				Inches			mm		Ctn.
No.	Description	No. of Compartments	L	W	Н	L	W	Н	Qty.
06115	Lid Storage Organizer	11 to 46 compartments	15	115/16	31/4	381	287	83	1
06118	Large Lid Storage Organizer	12 to 62 compartments	181/4	13¾	3%	464	340	92	1
06217	Flat-Bottom Organizer	9 to 32 compartments	11 ¹⁵ /16	15	31/8	303	381	98	6

Storage Cases



0 Fixed Dividers 4 Adjustable Divide

Medium Cases



Small & Medium Cases



Large Cases

		1
-	+	- 1
+	+	+
- 1	- 1	
- 1	1	
		ders

- Grid design in lid keeps items from spilling into other compartments.
- Cases available in 3 sizes with different divider configurations.
- Small and medium cases include 4 front-to-back adjustable dividers.
- Large cases include 5 front-to-back adjustable dividers.



Storage Cases

Model			Inches	5		mm		Maximum	Ctn.
No.	Description	L	W	Н	L	W	Н	Compartments	Qty.
05705	Small Case (2 Fixed Dividers)	85/8	51/8	15⁄8	219	130	41	15	12
05709	Small Case (0 Fixed Dividers)	85/8	51/8	15⁄8	219	130	41	5	12
05805	Medium Case (2 Fixed Dividers)	11	7	23/8	279	178	60	15	6
05807	Medium Case (1 Fixed Divider)	11	7	23/8	279	178	60	10	6
05905	Large Case (2 Fixed Dividers)	14¾	91/2	21/2	365	241	64	18	6

ProBox[™] Tool Boxes



Extra-large trays optimize storage

- ProBox design provides secure stacking on shelves and pallets.
- Carry fully loaded boxes with confidence. Steel draw latch snaps tightly closed.
- Oversized padlock eye accepts larger padlocks for securing tools in ProBox.

Tool Rack

Model			Inches			mm		Ctn.
No.	Description	L	W	Н	L	W	Н	Qty.
09912	12" ProBox*	12	6	4	305	152	102	12
09514	14" ProBox	14	8 ¹ / ₈	8 ¹ /8	356	197	206	6
09517	17" ProBox	17	9¾	8¾	432	235	245	4
09920	20" ProBox	20	10 ¹ / ₄	10 ⁵ ⁄⁄8	508	260	271	4

* Does not include tray or padlock eye. 17" and 14" trays are red

09920 09514 09517

Tool Rack

- Organizes up to 96 tools.
- · Securely mounts to wall.
- · Color: Red





Tool Rack

Model		Inches			Ctn.			
No.	Description	L	W	Н	L	W	Н	Qty.
08024RED	Tool Rack	6	24½	23/4	152	613	70	12

Wrench Holder



- Stores up to 15 wrenches.
- Securely mounts to wall.
- Color: Black



Wrench Holder

Model		Inches				Ctn.		
No.	Description	L	W	Н	L	W	Н	Qty.
08186	Wrench Holder	1	71/8	83/6	115/8	181	295	12

Tilt & Locks



Bins tilt out completely and, when removed, stand alone for easy access.

- Versatile small parts organizer.
- Locking storage bins make this unit great in vehicles, mounted behind doors, or anywhere a convenient storage center is needed.
- Three sizes stack and lock together to form a customized storage center.
- Color: Blue frame with black latches and clear bins.

Tilt & Lo	ocks							
Model			Inches			mm		Ctn.
No.	Description	L	W	Н	L	W	Н	Qty.
08146	Small	19%	2¾	51/4	498	70	133	1
08166	Medium	19%	3¾	6%	498	95	175	1
08186	Large	19%	5¾	83/8	498	146	213	1
								-



Akro/Logic Organ



- European-inspired organizers for convenient transport and compartmentalized storage.
- Removable bins are interchangeable with other Akro/Logic organizers.
- Heavy-duty polypropylene base and shatterproof polycarbonate lid withstand years of abuse.
- Color: Blue base with red latches and handle.

Akro/Logic™ Multi Case

		Bins		Case Dimensions						
Model		Per		Inches mm						
No.	Description	Case	L	W	Н	L	W	Н	Qty.	
14217	Multi Case 17	17	12 ⁷ ⁄⁄8	16 ¹ /4	21/8	327	413	54	4	
14212	Multi Case 12	12	12 ⁷ /s	16 ¹ / ₄	31/8	327	413	79	3	

(Product of Denmark)


Shatter-proof, "see-through" lid protects contents Exclusive lid design holds remaining bins in place when others are removed Latches slide and lock to prevent accidental opening

Roto-Shelf

- Mobile storage unit can easily be moved to different work areas.
- Roto-Shelf is ideal for assembly components.
- 197/8" wide unit takes up very little floor space.
- Four shelves rotate on an independent central metal shaft.
- · Color: Gray.

Roto-She	lf				
Model	Inches		m	Ctn.	
No.	D	Н	W	Н	Qty.
02420	19 ⁷ / ₈	37½	502	953	1

Shelf depth - $2\frac{1}{8}$ " Shelf diameter - $19\frac{7}{8}$ " 75 lbs. per shelf 300 lb. total wt. capacity



Heavy-duty structural foam shelves

Shelves rotate on steel post for easy access

Six compartments in each shelf help keep parts and tools organized

Industrial-strength wheels provide easy movement





52-53 ProCart[™]

The first box-top to flat-top utility cart.



60

Steel Platform Trucks

Medium and heavy-duty steel trucks.



High-End Narrow Aisle Truck Slim truck for use where space is limited.



53

Office Carts

Lightweight carts for office management.



Compact Tote Truck

All-purpose truck with fold-down handle.



63

Tray Service Cart Heavy-duty service cart holds dishes, books, or supplies for easy transport.



54-55

VERSA/Deck™

Versatile cart with multiple handle, rail, and caster options.



61

Shelf & Multi-Shelf Carts Sturdy, all-welded steel

shelving carts.



63

Box Trucks Steel box on wheels for distribution, order picking, or manufacturing.



56-58

Wood Platform

Trucks

Platform trucks with hardwood decks.



62

Portable Tables & Carts

Steel carts for pulling stock, assembly operations, or other heavy tasks.



Heavy-Duty Work Bench Durable work

station with optional accessory packages.



Mobile Work

Tables

Medium and heavy-duty potable work centers.



Work Height Platform Trucks

Fixed and adjustable height decks.



ProCartTM

- A customizable work center for the assembly line, warehouse, or wherever you need portable storage.
- Side gates flip up or down to convert to a flat-top or box-top cart.
- High-density polyethylene structural foam construction is dent-resistant, rust-proof, and never needs painting.
- Optional nine-rail hanging system (pg. 53) holds up to 80 AkroBins.
- Optional middle shelf (100 lb. capacity).
- 400lb (180 kg) maximum cart load. 200 lb. (90 kg) capacity per top and bottom shelf.
- Assembly required.



ProCart converts from box top to flat top – quickly adapting to the task at hand.



Large ProCart (Model 30936) with top and bottom side gates in "box-top" position.

Small ProCart (Model 30930)

with top shelf side gates in "flat-top" position.



ProCart™ Ordering Information

Outside Dimensions											
Model			Inches		mm						
No.	Description	L	W	Н	L	W	Н	Color	Qty.		
30936	Large cart	45	24	343/4	1143	610	883	Gray/Beige	1		
30930	Small cart	40	19½	343/4	1016	495	883	Gray/Beige	1		

Easy assembly – requires Phillips screwdriver and rubber mallet

Large Cart Model No. 30936





Small Cart Model No. 30930








ProCart Accessories:

ProCart Middle Shelf

Add a middle shelf to the ProCart for more efficient use of lower cart space. Two height options. 100 lb. capacity. 40"L x 20"W x 3"H (1016 x 508 x 76mm). Fits large ProCart only. Color: Gray. Model No. 30936SHELF







Shelf can be installed in two positions.

AkroBins® Ordering Information

To create a customized ProCart with AkroBins, use the chart below to determine the quantity of AkroBins that will fit your ProCart. Carts, rail kits, and bins must be ordered separately. When ordering, please specify Red, Yellow, Blue, or Stone colored bins.



Optional 9-Rail Hanging System Ordering Information

The 9-Rail Hanging System is required to hang some AkroBins and modular cabinets on your ProCart. For large cart rails, order Model No. 30906 - for small cart rails, order Model No. 30900.



Use this chart when ordering one size AkroBins for your ProCart:

Bin Model No.	30210	30220	30224	30230	30234	30235	30239	30240	30250	30255
Bin Dim. (L'' x W'' x H'')	53/8 x 41/8 x 3	7 ³ / ₈ x 4 ¹ / ₈ x 3	10 ⁷ /8 x 4 ³ /16 x 4	10 ⁷ / ₈ x 5 ½ x 5	14 ³ / ₄ x 5 ¹ / ₂ x 5	10 ⁷ / ₈ x 11 x 5	10 ³ / ₄ x 8 ¹ / ₄ x 7	14 ³ /4 x 8 ¹ /4 x 7	14 ³ / ₄ x 16 ¹ / ₂ x 7	10 ³ / ₄ x 16 ¹ / ₂ x 5
30936 (large cart)	80	80	48	36	36	18	16	16	8	12
30930 (small cart)	70	70	42	30	-	12	12	_	_	-

File Manager Cart



- · Easy assembly legs quickly snap together, no tools needed
- · Rolls under most work areas
- Includes File Manager Box for organizing letter and legal folders
- 45-pound capacity



	.90. 0							
Model			Inches			Ctn.		
No.	Description	L	W	Н	L	W	Н	Qty.
95418	File Manager Cart	211/3	145/16	231/8	557	365	587	1



Shelf Cart

- Easy assembly legs quickly snap together, no tools needed
- Free work space of printers, CPUs, books, and more
- 45-pound capacity



Sileii Cai	t .							
Model			Inches			mm		Ctn.
No.	Description	L	W	Н	L	W	Н	Qty.
95492	Shelf Cart	19	14 ⁵ /16	231/8	484	365	587	1





VERSA/Deck[™]

- Versatile, structural foam cart with multiple handle and caster options.
- Sturdy, easy-to-clean deck resists most chemicals and damage from long-term exposure to weather.
- · All decks are steel reinforced.
- · Maximize deck space with outside deck handles.
- Choose the deck size, caster type, and handle style to create the exact configuration you need.
- Decks are available in two sizes: 24" x 48" and 30" x 60".
- Deck colors: Blue or Gray.





VERSA/Deck™ is perfect for transporting long, tall, or bulky items.





Common VERSA/Deck™ Configurations



24" x 48" R90181 Deck R92411 18" Handle

30" x 60" R90281 Deck R93011 24" Handle



24" x 48" R90181 Deck Two R94817 48" Rails One R94815 48" Rail

30" x 60" R90281 Deck Two R94817 60" Rails One R96015 60" Rail



24" x 48" R90181 Deck Two R92418 24" Handles One R92416 24" Handle

30" x 60" R90281 Deck Two R93019 30" Handles One R93016 30" Handle



24" x 48" R90181 Deck One R92411 18" Handle Two R94817 48" Rails

30" x 60" R90281 Deck One R93011 24" Handle Two R96017 60" Rails



24" x 48" R90181 Deck Two R92418 24" Handles

30" x 60" R90281 Deck Two R93019 30" Handles



24" x 48" R90181 Deck Two R92411 18" Handles One R94815 48" Rail

30" x 60" R90281 Deck Two R93011 24" Handles One R96015 60" Rail



VERSA/Deck shown with Akro-Mils SWC's and Akro-Grids (See pages 23-25).



Step 1
Pick a deck size.

Step 2
Pick a caster type.

Step 3
Refer to the decks & casters charts for model numbers.

Step 4

Pick handle and rail styles, and determine the quantity needed of each type.


Step 5
Refer to the handle and rail charts for model numbers.

Step 6 Call your Akro-Mils distributor to order.



Deck Sizes

Holes are drilled for handle ordered.



24" x 48" (610mm x 1219mm) 30" x 60" (762mm x 1524mm) Color: Gray or Blue



Casters & Wheels

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 76 for more caster information.







Moldon

Pneumatic



Pro-Tech





24" x 48" Decks & Casters

	aster	Castei	r Size	Load	Ship. Wt.
No. Ty	<i>р</i> е	Inches	mm	Rating	w/o handles
R90152 M	oldon Rubber	5	127	1400 lbs.	65 lbs.
R90181 Pr	neumatic	8	203	1200 lbs.	69 lbs.
R90162 Po	olyolefin	6	152	1500 lbs.	61 lbs.
R90163 Pc	olyurethane	6	152	2000 lbs.	61 lbs.
R90182 M	oldon Rubber	8	203	2000 lbs.	81 lbs.
R90184 Po	olyolefin	8	203	1500 lbs.	65 lbs.
R90110 Pr	neumatic	10	254	1600 lbs.	77 lbs.
R90153 Pe	erforma	5	127	1500 lbs.	57 lbs.
R90164 Pr	o-Tech Non-Marking	6	152	2700 lbs.	61 lbs.
R90183 Pr	o-Tech Non-Marking	8	203	2700 lbs.	61 lbs.
R90185 G	ray Round Performa	8	203	2400 lbs.	61 lbs.

Note: Decks are available in Gray or Blue. Specify color when ordering.

30" x 60" Decks & Casters

Model	Caster	Caster	Size	Load	Ship. Wt.
No.	Туре	Inches	mm	Rating	w/o handles
R90252	Moldon Rubber	5	127	1400 lbs.	89 lbs.
R90281	Pneumatic	8	203	1200 lbs.	93 lbs.
R90262	Polyolefin	6	152	1500 lbs.	85 lbs.
R90263	Polyurethane	6	152	2000 lbs.	85 lbs.
R90282	Moldon Rubber	8	203	2000 lbs.	105 lbs.
R90284	Polyolefin	8	203	1500 lbs.	89 lbs.
R90210	Pneumatic	10	254	1600 lbs.	101 lbs.
R90253	Performa	5	127	1500 lbs.	81 lbs.
R90264	Pro-Tech Non-Marking	6	152	2700 lbs.	85 lbs.
R90283	Pro-Tech Non-Marking	8	203	2700 lbs.	85 lbs.
R90285	Gray Round Performa	8	203	2400 lbs.	85 lbs.



Handle – Outside Deck



Open Style/ Swayback 18" R92411 24" R93011



Crossbar/ Swayback 18" R92412 24" R93012

Handle – Indeck



Open Style/ Swayback 24" R92413 30" R93013



Open Style/ Straight 24" R92414 30" R93014



Crossbar/ Straight 24" R92416 30" R93016



Crossbar/ Swayback 24" R92418 30" R93019

Handle Rails – Indeck



Open Style/Straight 48" R94815 60" R96015



Crossbar/Straight 48" R94817 60" R96017



Handles & Rails for 24" x 48" VERSA/Deck Cart

Hamaics	a mans n	3. E. X	TO VERSIA	DCCK Care		
Model	Siz	:e				Ship.
No.	Inches	mm	Style	Handle	Color	Wt.
Outside De	ck					
R92411	18	457	Open	Swayback	Gray	5
R92412	18	457	Crossbars	Swayback	Gray	6
Indeck						
R92413	24	610	Open	Swayback	Gray	6
R92414	24	610	Open	Straight	Gray	6
R92416	24	610	Crossbar	Straight	Gray	8
R92418	24	610	Crossbar	Swayback	Gray	8
Handle Rai	ls Indeck					
R94815	48	1219	Open	Straight	Gray	7
R94817	48	1219	Crossbar	Straight	Gray	14

Handles & Rails for 30" x 60" VERSA/Deck Cart

Model	Siz	ze				Ship.
No.	Inches	mm	Style	Handle	Color	Wt.
Outside De	eck					
R93011	24	610	Open	Swayback	Gray	9
R93012	24	610	Crossbar	Swayback	Gray	10
Indeck						
R93013	30	762	Open	Swayback	Gray	10
R93014	30	762	Open	Straight	Gray	10
R93016	30	762	Crossbar	Straight	Gray	12
R93019	30	762	Crossbar	Swayback	Gray	12
Handle Rai	ls Indeck					
R96015	60	1524	Open	Straight	Gray	8
R96017	60	1524	Crossbar	Straight	Gray	16

Platform Trucks Wood Deck



make transport of heavy loads easy. (Shown with Akro-Mils containers. See pages 18-25)

- · Heavy-duty platform trucks with kiln-dried, tongue and groove hardwood decks.
- Caster options allow 1,180 to 5,400 lb. capacities.
- Choose from multiple options in deck type, size, handles, casters, running gear patterns, bumpers, and wheel locks.
- Decks are 4/4 (1" thick).
- Shipped completely assembled and ready to use.



Deck Sizes









HOW TO ORDER

Step 1 Pick deck size.

Step 2 Pick deck style Series 1, 2, or 3.

Step 3 Pick superstructure A through H.

Step 4 Pick running gears 1 through 7.

Step 5 Pick caster type & size.

Step 6

Create a model number and call your Akro-Mils distributor

27" x 54"

30" x 60"

36" x 72"



Series 1

All Wood

- Shown with removable lattice pipe handle at swivel end.
- Two swivel, two rigid casters.
- See caster options for capacity.



Series 2

Wood Deck with Steel Frame

- · Heavy-duty cart for concentrated loads.
- 2" x 2" x 1/8" welded steel angle frame. (on 36" x 72" deck, 2" x 2" x 3/16")
- Shown with removable lattice pipe handle at swivel end.
- The wood deck is reinforced with longitudinal stiffeners for maximum capacity. (See caster options for capacity.)
- Two swivel, two rigid casters.



Series 3

Wood Deck with Steel Corners

- Steel plates protect corners from damage.
- Shown with open pipe handle
- Reinforcing center sill supports the deck lengthwise from beneath.
- Series 3 trucks feature 12" load wheels in combination with 8" swivel casters. See "Casters and Wheels Series 3" chart on page 57.

Also Available

Super Heavy-Duty Wood Deck Steel Frame Trucks



- Steel C-channel underdeck reinforcements.
- Capacity 1,200 to 4,000 lbs. depending on caster type.
- Contact your Akro-Mils distributor to order.

Superstructures

Choose a handle style from the chart below to fit your platform truck. Open, lattice, and stake styles are removable to fit oversize loads. Fixed handles are only available on Series 1 & 2 trucks.







Cross bar handle

26³/₄" above deck. Cross bars prevent small items from sliding through.




Pipe stakes 36" above deck. Available on Series 1 & 2



Hardwood stakes* 31" above deck. Available on Series 3 decks only.

Superstructures (Handles & Stakes)

Series 1 & 2 Removable Fixed Θ $\bigcirc 0$ Series 3 Removable



 Series 3
 Caster Type & Load Capacity Moldon Rubber
 Polyurethane
 Steel


 Running Gear 1 & 3
 3280 lbs.
 5400 lbs.
 5400 lbs.

 Running Gear 2
 2780 lbs.
 4500 lbs.
 4500 lbs.

Note: For Series 3 model numbers, specify load wheel type (M,Y, or S) and a 12" wheel diameter. Swivel casters are standard 8" diameter.

*See page 76 for full description of casters and wheels.

HOW TO CREATE YOUR MODEL NUMBER



For a 30" x 60" wood with steel frame platform truck with one removable open pipe handle and two rigid, two swivel 6"polyolefin casters, your model number will look like this: RPT30602A5P6

Options & Accessories*:

Floor Locks



Prevent unwanted truck movement Step down to lock, trip to release. Normally installed between swivel casters.

- Non-slip rubber base
- Solid steel construction
- Zinc plated for corrosion resistance
- For use on trucks with non-tilt running

Wheel Locks



Control truck movement: prevent wheels from turning. Available on all wheels. Normal installation on two swivel wheels.

Corner Bumpers



Protect walls, doors, furniture from damage.

Continuous Bumpers



Complete edge protection for all platform trucks.

*Accessories and special-order products are not returnable



Six deep pockets hold clipboards, tape guns, and other bulky items. Durable canvas with nylon hanging straps and velcro fasteners. 16"W x 26"H. Fits all platform trucks. Order separately. Color: Black.

od Platform Dec

Our Premium Decks are constructed from the highest quality hardwoods to ensure maximum service under extreme conditions.


Premium Wood Decks

- · Custom platform hardwood decks.
- Choose the deck, size, wheels, and running gear to best fit your application.
- Premium hardwood decks in 1½" (5/4) or 1" (4/4) thickness.
- Decks are predrilled to accept a $4'' \times 4^{1/2}''$ top plate with bolt hole spacing of $2\frac{3}{4}$ " x $3\frac{5}{16}$ ".





Decks, handles, and casters must be ordered separately. Refer to page 56 for caster and handle options. (Shipped unassembled. Assembly available for extra charge.)



HOW TO ORDER

Select the model no. from the chart and add "44" or "54" to specify 4/4" or 5/4" thickness.

Use this chart when ordering premium 5/4 or 4/4 wood platform decks. Boards run lengthwise.

Deck						1	Deck Lengtl	า			
Width	24"	36"	42"	46"	48"	54"	60"	66"	72"	84"	96"
24"	R6100	R6101	R6111	R6121	R6131		R6139				
27"					R6144	R6151					
30"					R6141	R6170	R6171	R6175	R6191		R6193
36"					R6180		R6181		R6199	R6194	

Note: When ordering, add "44" or "54" to specify 4/4" or 5/4" thickness. Example: R615144 is a 54" x 27" premium deck with 4/4" thick boards.

SERIES 1



Deck Only

- Tongue & groove deck construction.
- 1" (4/4) thick hardwood deck with routered edges.
- Predrilled for running gear 5.
- Predrilled for (1) handle.

Series 1 Wood Decks

Series 1 Wood Decks									
Model	9	Size	Ship						
No.	Inches	mm	Wt.						
RPTD24481	24 x 48	609 x 1219	33 lbs.						
RPTD27541	27 x 54	686 x 1372	42 lbs.						
RPTD30601	30 x 60	762 x 1524	54 lbs.						
RPTD36721	36 x 72	914 x 1829	74 lbs.						

Decks are predrilled to accept a 4"x 4¹/₂" top plate with bolt hole spacing of 23/4" x 35/16".

SERIES 2



- Deck Only
 Tongue & groove hardwood in angle frame.
- 1" (4/4) thick hardwood deck with routered edges.
- · Predrilled for running gear 5. Equipped for (1) handle, with 2 sockets installed.

Series 2 Wood Decks

Model		Size	Ship
No.	Inches	mm	Wt.
RPTD24482	24 x 48	609 x 1219	58 lbs.
RPTD27542	27 x 54	686 x 1372	69 lbs.
RPTD30602	30 x 60	762 x 1524	83 lbs.
RPTD36722	36 x 72	914 x 1829	122 lbs.

Options for Premium and Standard Wood Decks:

Running Gear Detail

Rigid caster




Swivel caster



Fixed wheel on axle

Running Gear Options for Premium and Standard Wood Decks







*Standard running gear





Series 1 & 2





Decks, handles, and casters must be ordered separately. Refer to page 56 and 57 for caster and handle options. (Assembly required)

Platform Trucks Work Height



Hardwood Deck



Structural Foam Deck



Expanded Metal Shelf

- · Hardwood or structural foam deck available.
- Ergonomic height reduces the strain of lifting and bending.
- 26½"H fixed or adjustable height decks.
- Adjustable height trucks have 3 deck height settings; $24\frac{1}{2}$ " to $30\frac{1}{2}$ "H on trucks with 6" wheels, and $25\frac{1}{2}$ " to $31\frac{1}{2}$ "H on trucks with 8" wheels.
- See optional accessories, page 57.
- · Optional expanded metal lower shelf (Special-order products are not returnable.)



DECK SIZES 24" x 48" & 30" x 60"

Fixed Height Platform Trucks

Model	Caster	Caster	Size	
Hardwood	Structural Foam	Type*	Inches	mm
24" x 48" Decks (61	10 x 1219mm)			
RWH24481A5M6	RWHV24481A5M6	Moldon	6	152
RWH24481A5M8	RWHV24481A5M8	Moldon	8	203
RWH24481A5Y6	RWHV24481A5Y6	Polyolefin	6	152
30" x 60" Decks (76	52 x 1524mm)			
RWH30601A5M6	RWHV30601A5M6	Moldon	6	152
RWH30601A5M8	RWHV30601A5M8	Moldon	8	203
RWH30601A5Y6	RWHV30601A5Y6	Polyolefin	6	152
*Coo page 76 for full do	scription of castors and wh	hoole		

^{*}See page 76 for full description of casters and wheels.

Adjustable Height Platform Trucks

Model No	о.	Caster	Caster	Size
Hardwood	Structural Foam	Type*	Inches	mm
24" x 48" Decks (610	x 1219mm)			
RWH24481A5M6A	RWHV24481A5M6A	Moldon	6	152
RWH24481A5M8A	RWHV24481A5M8A	Moldon	8	203
RWH24481A5Y6A	RWHV24481A5Y6A	Polyolefin	6	152
30" x 60" Decks (762	x 1524mm)			
RWH30601A5M6A	RWHV30601A5M6A	Moldon	6	152
RWH30601A5M8A	RWHV30601A5M8A	Moldon	8	203
RWH30601A5Y6A	RWHV30601A5Y6A	Polyolefin	6	152

Skids Semi-Live & Dead



DECK SIZES

24" x 36" 27" x 54" 36" x 60" 30" x 48" 36" x 72" 24" x 48" 24" x 60" 30" x 60"

Dead Skids Specify size when ordering.

Model No.	Underclearance	Capacity					
All Wood Dead Skid							
RA121DS*	7½" (184mm)	3000 lbs.					
Wood Deck Steel Frame Dead Skids							
R121DS	7½" (184mm)	3000 lbs.					
All Steel Dead Skid							
R120DS	7½" (303mm)	3000 lbs.					
*Not available in 24" x 3	6", 27" x 54", and 24" x 60" deck	sizes.					

Model No	Caster	Caster	Size	
Hardwood	Structural Foam	Type*	Inches	mm
24" x 48" Decks (610	x 1219mm)			
RWH24481A5M6A	RWHV24481A5M6A	Moldon	6	152
RWH24481A5M8A	RWHV24481A5M8A	Moldon	8	203
RWH24481A5Y6A	RWHV24481A5Y6A	Polyolefin	6	152
30" x 60" Decks (762	x 1524mm)			
RWH30601A5M6A	RWHV30601A5M6A	Moldon	6	152
RWH30601A5M8A	RWHV30601A5M8A	Moldon	8	203
RWH30601A5Y6A	RWHV30601A5Y6A	Polyolefin	6	152

DECK SIZES

24" x 48" 27" x 54"

30" x 48" 30" x 60" 30" x 72"

36" x 60" 36" x 72"




Specify size when ordering.

Model	Caster	Caster	Caste	r Size	Underclearance
No.	Capacity	Type*	Inches	mm	of Tongue
All Wood Semi-	Live Skids				
RA756MR**	1800 lbs.	Moldon	6 x 2	152 x 51	6 ⁷ /8" (175mm)
RA778MR**	2200 lbs.	Moldon	8 x 2	203 x 51	9½" (232mm)
RA796PL**	2500 lbs.	Phenolic	6 x 2	152 x 51	6 ⁷ /8" (175mm)
RA7218PL	3000 lbs.	Phenolic	8 x 2	203 x 51	9½" (232mm)
Wood Deck Stee	el Frame Sen	ni-Live Skids	5		
R756MR	1800 lbs.	Moldon	6 x 2	152 x 51	6 ⁷ /8" (175mm)
R778MR	2200 lbs.	Moldon	8 x 2	203 x 51	9 ¹ /8" (232mm)
R796PL	2500 lbs.	Phenolic	6 x 2	152 x 51	6 ⁷ /8" (175mm)
R7218PL	3000 lbs.	Phenolic	8 x 2	203 x 51	9 ¹ /8" (232mm)
All Steel Semi-Li	ive Skids				
R746MR	1800 lbs.	Moldon	6 x 2	152 x 51	6 ⁷ /8"(175mm)
R768MR	2200 lbs.	Moldon	8 x 2	203 x 51	9½" (232mm)
R786PL	2500 lbs.	Phenolic	6 x 2	152 x 51	6 ⁷ /8" (175mm)
R7208PL	3000 lbs.	Phenolic	8 x 2	203 x 51	9 ¹ /8" (232mm)

Not available in 24" x 36", 27" x 54", and 30" x 72" deck sizes.

*See page 76 for full description of casters and wheels

Optional Lift Jack





- For easy transport of most semi-live skids.
- Specify "T" or loop handlé style.
- For female socket, change Model No. prefix to "RF"
- Pipe is 43" long

Optional Lift Jack

- p 4: - : : : : : : : : : : : : : : : : :		
Model No.	Caster Type*	Caster Size
RM716MR	Moldon Rubber	6" (152mm)
RM718MR	Moldon Rubber	8" (303mm)
RM716PL	Phenolic	6" (152mm)
RM718PL	Phenolic	8" (303mm)

^{*}See page 76 for full description of casters and wheels.


Platform Trucks Steel



Shown with Akro-Mils SWC's and Akro-Grids. See pages 23-25.

Medium and heavy-duty steel trucks with longitudinal steel underdeck reinforcements.

- Standard two swivel, two rigid casters.
- Special-order platform trucks are available. See pages 56 and 57 to select from multiple options in handles, casters, and running gears. (Special-order products are not returnable.)
 - Caster options allow 800 to 2,200 lb. capacity.



HEAVY-DUTY DECK SIZES

24" x 36" 27" x 54" 30" x 72" 24" x 48" 30" x 48" 36" x 60" 24" x 60" 30" x 60" 36" x 72"



Standard cross bar handle

Heavy-Duty

Specify size when ordering.

neavy-buty	-F	,				
Model	Caster	Caster	Caster Size (Sv	wivel & Rigid)	Deck H	leight
No.	Capacity	Type*	Inches	mm	Inches	mm
R2108FPB	1200 lbs.	Full Pneumatic	8 (4 Ply)	203	111/2	292
R21210FPB	1200 lbs.	Full Pneumatic	10 (2 Ply)	254	131/2	343
R2125MRB	1500 lbs.	Moldon Rubber	5 x 2	127 x 51	8	203
R21412FPB**	1600 lbs.	Full Pneumatic	12 (2 Ply)	305	171/4	438
R2161012FPB	1700 lbs.	Full Pneumatic	. ,, -	wivel – 254 Rigid – 305	141/2	368
R2146MRB	1800 lbs.	Moldon Rubber	6 x 2	152 x 51	9	229
R2168MRB	2200 lbs.	Moldon Rubber	8 x 2	203 x 51	11	279
R2165PLB	2200 lbs.	Phenolic	5 x 2	127 x 51	8	203
R2165PYB	2200 lbs.	Polyurethane	5 x 2	127 x 51	8	203
R2165SSB	2200 lbs.	Semi-Steel	5 x 2	127 x 51	8	203

^{**} Not available in 24" x 36", 24" x 48", and 24" x 60" deck sizes. *See page 76 for full description of casters and wheels.

MEDIUM-DUTY DECK SIZES

18" x 36" 24" x 36" 20" x 32" 24" x 48" Specify size when ordering.



Standard open pipe handle

Medium-Duty

Model Caster		Caster	Caster Size (Sv	wivel & Rigid)
No.	Capacity	Type*	Inches	mm
RMD2104MRA	800 lbs.	Moldon Rubber	4 x 2	102 x 51
RMD2105SRA	800 lbs.	Soft Rubber	5 x 11/4	127 x 32

^{*}See page 76 for full description of casters and wheels.

Options & Accessories*:

Floor Locks



Prevent unwanted truck movement. Step down to lock, trip to release. Normally installed between swivel casters.

- Non-slip rubber base
- Solid steel construction
- Zinc plated for corrosion resistance
- For use on trucks with non-tilt running gear only

Wheel Locks



Control truck movement: prevent wheels from turning. Available on all wheels. Normal installation on two swivel wheels.

Corner Bumpers



Protect walls, doors, furniture from damage.

*Accessories and special-order products are not returnable.

Continuous Bumpers



Complete edge protection for all platform trucks.

Shelf & Multi-Shelf Carts



Specify

24" x 60"

27" x 54"

30" x 48"

30" x 60"

36" x 72"

size when ordering.

- Heavy-duty carts designed for daily work.
- Welded steel cart rolls smoothly on long-wearing casters.
- Built to withstand loads up to 2,200 lbs.
- Swayback-style tubular push handle. (Models R1S5HR and R1S8MR have straight handles)
- Choose from several caster options as well as: rubber matting, lips up or down, a writing shelf, and drawers. (See pg. 62)
- · Ships completely assembled and ready to use.



Shelf Carts

Model	Caster	Caster	Cast	er Size			ght To Shelf		elf rance
No.	Capacity	Type*	Inches	mm	Shelves	Inches	mm	Inches	mm
R1S8FP2*	1200 lbs.	Full Pneumatic	8 (4 Ply)	203 x 102	2	34	864	203/4	527
R1S10FP2*	1200 lbs.	Full Pneumatic	10 (2 Ply)	254 x 51	2	36	914	203/4	527
R1S12FP2**	1600 lbs.	Full Pneumatic	12 (2 Ply)	305 x 51	2	393/4	1010	203/4	527
R1S5HR [†]	1800 lbs.	Polyolefin	5 x 2	127 x 51	2	30 ¹ / ₄	768	203/4	527
R1S5HR2	1800 lbs.	Polyolefin	5 x 2	127 x 51	2	30 ¹ / ₄	768	203/4	527
R1S5HR2LD	1800 lbs.	Polyolefin	5 x 2	127 x 51	2	25	635	15½	394
R1S8MR [†]	2200 lbs.	Moldon Rubber	8 x 2	203 x 51	2	331/4	845	203/4	527
R1S8MR2	2200 lbs.	Moldon Rubber	8 x 2	203 x 51	2	331/4	845	203/4	527
R1S8MR2LD	2200 lbs.	Moldon Rubber	8 x 2	203 x 51	2	28	711	15½	394
*Not available in 1	8" x 30" and 1	8" x 36" deck sizes. **	Only available in	27" x 54" 30" x 48	3" 30" x 60" 2	and 36" x 72"	†Straight hand	dle	

CART

18" x 30"

18" x 36"

24" x 36"

24" x 42"

24" x 48"

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 76 for more caster information.

Multi-Shelf Carts

Model	Caster	Caster	Cast	er Size		Overall	Height		Shelf cing
No.	Capacity	Type*	Inches	mm	Shelves	Inches	mm	Inches	mm
R2ST5HR	1800 lbs.	Polyolefin	5 x 2	127 x 51	2	30 ¹ / ₄	768	203/4	527
R2ST8MR	2200 lbs.	Moldon Rubber	8 x 2	203 x 51	2	33 ¹ / ₄	845	203/4	527
R3ST5HR	1800 lbs.	Polyolefin	5 x 2	127 x 51	3	30 ¹ / ₄	768	95/8	244
R3ST8MR	2200 lbs.	Moldon Rubber	8 x 2	203 x 51	3	33 ¹ / ₄	845	95/8	244
R4ST5HR	1800 lbs.	Polyolefin	5 x 2	127 x 51	4	63 ¹ / ₄	1619	17	432
R4ST8MR	2200 lbs.	Moldon Rubber	8 x 2	203 x 51	4	66 ¹ /4	1695	17	432
R5ST5HR	1800 lbs.	Polyolefin	5 x 2	127 x 51	5	63 ¹ / ₄	1619	12 ¹ / ₄	311
R5ST8MR	2200 lbs.	Moldon Rubber	8 x 2	203 x 51	5	66 ¹ / ₄	1695	12 ¹ / ₄	311

*See page 76 for full description of casters and wheels.

act Tote Truck



Supply Caddy

Store supplies in the Heavy-Duty Supply Caddy. Six deep pockets hold clipboards, tape guns, and other bulky items. Durable canvas with nylon hanging straps and velcro fasteners. 16"W x 26"H. Fits all Compact Tote Trucks. Order separately:

Model No. R90000. Color: Black. 1 per carton.

- · All-purpose material handling and transport cart with fold-down handle.
- · Deck is constructed of lightweight, highdensity structural foam.
- Two fixed, two swivel casters make cart easy to maneuver. (Swivel casters on R90041 are toe-touch locking casters).
- Deck Size all models: $35\frac{1}{2}$ "L x $22\frac{1}{2}$ "W (904 x 568 mm)

Steel handle is powder coated to resist rusting and folds down flush to deck

Non-skid platform surface prevents load from shifting during transport

Use the molded-in handle to hang the Compact Tote Truck or to secure tie-down straps (not included)



Compact Tote Truck Ordering Information

Wheel Model Dia. x W		Load Rating		Overall Height		Deck Height		
No.	Inches	mm	Lbs.	kg	Inches	mm	Inches	mm
R90031	3 x 1	76 x 25	300	136	34	864	7	178
R90041	4 x1	102 x 25	500	227	35	889	8	203
R90062	6 x 2	153 x 51	1000	454	37	940	9	229

Easy assembly - requires Phillips screwdriver and rubber mallet



Push/pull handle has three positions for easy maneuvering

Bin Carts

- A convenient combination of a heavy-duty cart with sturdy AkroBins for organized, portable storage of parts or supplies.
- 13-gauge steel, all-welded construction with $1\frac{1}{2}$ " x $\frac{1}{8}$ " angle iron steel.
- Drawer is $15\frac{1}{2}$ "W x $5\frac{1}{2}$ "H x $16\frac{1}{2}$ "D.
- Bolt-on polyurethane casters 5" x 1¹/₄"; 2 rigid, 2 swivel with total lock brakes.
- Fully assembled with 36" panel and 8 AkroBins.
- One lip down on top shelf for easy access to work surface.
- Frame color: Blue or Gray.
- AkroBin colors: Red, Yellow, Blue, Stone.



Model No. RBCB18365Y shown with optional writing shelf

Bin Cart with Bottom-Shelf Storage

- Cart Dimensions: 18"W x 36"L x 36"H or 24"W x 36"L x 36"H.
- Standard with tubular push handle.
- · Optional writing shelf.
- Bin Model No. 30240 (See pg. 4 for sizes). • 18" x 36" Model No. RBCB18365Y.
- 24" x 36" Model No. RBCB24365Y. Please specify frame color and bin color.



Model No. RBCT24365Y shown with optional wood inserts

Bin Cart with Top-Shelf Storage

- Dimensions: 24"W x 36"L x 36"H.
- · Tubular push handle.
- Optional wood inserts.
- Bin Model No. 30239 (See pg. 4 for sizes).
- Model No. RBCT24365Y Please specify frame color and bin color.

Portable Tables & Car

- Durable carts for pulling stock, assembly operations, or other heavy tasks.
- · Welded steel frame construction with soft rubber casters for easy maneuverability.
- Overall height: 36".
- Ships completely assembled and ready to use.
- 800 lb. capacity.



PT Series

- 4 swivel, 5" x 11/4" soft rubber casters.
- Shelf spacing: 2-shelf 27" (558 mm), 3-shelf 12½" (318 mm)
- 13-gauge steel.
- 11/2" hemmed lip

MD Series

- 2 swivel, 2 rigid, 5" x 11/4" soft rubber casters.
- 2-shelf 26" (660 mm), 3-shelf 12" (305 mm)
- · Tubular push handle.
- 16-gauge steel.
- 2" hemmed lip.

PT SERIES **CART SIZES**

18" x 30" 24" x 36" 18" x 36" 24" x 42"

24" x 30" 24" x 48" Specify shelf size when ordering.

PT Series Model No. Description RPT2ST5SR 2-Shelf Cart RPT3ST5SR 3-Shelf Cart

MD SERIES CART SIZES

18" x 24" 18" x 36" 18" x 30" 24" x 36" Specify shelf size when ordering.

MD Series

Model No. Description RMD2ST5SR 2-Shelf Cart RMD3ST5SR 3-Shelf Cart

*Special-order products are not returnable

Options & Accessories*:

Drawer



Easily accessible storage drawer. 15½ W x 5½ H x 16½"D O.D.

Writing Shelf



Handy, angled shelf with

Rubber Matting



Rubber mats for all standard size shelves.

Wheel Locks



Control truck movement and prevent wheels from turning. Available on all wheels. Normal installation on two swivel wheels.

High-End Narrow Aisle Truck





- Extra-narrow aisle truck for order-picking and stocking where space is limited.
- Slim design fits easily in tight areas.
- Centered, 8" wheels and casters at each corner allow cart to turn within its own diagonal space.
- Available in plywood deck with steel frame, all steel deck, or galvanized steel deck.
- 1,500 lb. capacity.



CART SIZES
Specify deck size

when ordering

Steel & Wood Deck 18" x 48" 24" x 48" 18" x 60" 24" x 60"

Galvanized Deck 16" x 48" 24" x 48" 16" x 60" 24" x 60" **High-End Narrow Aisle**

Model	Deck	Caster	Deck Height		Height Heigh		
No.	Type	Capacity	Inches mm		Inches	mm	
R215HE	Plywood	1500 lbs.	121/4	311	66 ¹ /2	1689	
R214HE	Steel	1500 lbs.	11	279	64 ¹ / ₂	1638	
R214HEGA	Galvanized	1500 lbs.	11	279	64 ¹ / ₂	1638	

Tray Service Cart

- · Excellent for libraries and manufacturing operations.
- 2 swivel, 2 fixed casters.

CART SIZES

18" x 30" 24" x 36" 18" x 36" 24" x 48"

Specify size when ordering.

Tray Service Cart

Model	Caster	Caster	Caster Size		Overall	Height
No.	Capacity	Type*	Inches	mm	Inches	mm
R2T5HR	1800 lbs.	Polyolefin	5 x 2	127 x 51	321/2	826
R2T8MR	2200 lbs.	Moldon Rubber	8 x 2	203 x 51	351/2	902

*See page 76 for full description of casters and wheels.

Standard Casters Shown (other caster options available):



Polyolefin



Moldon Rubber Caster Note:

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 76 for more caster information.



Box Trucks

Expanded Metal Box



Expanded metal for easy cleaning, good airflow, and visibility of contents. 31¹/₂" overall height; 25" inside depth.

- All box trucks have 2 swivel, 2 rigid,
 5" x 2" polyolefin casters.
- Solid steel or expanded metal sides available.
- 1,800 lb. capacity.
- · Available with optional lid.



Box Trucks

BOX SIZES

24" x 36" 30" x 36"

24" x 48" 30" x 48" Specify size when ordering.

Model		Overa	ll Ht.	Inside D	epth
No.	Description	Inches	mm	Inches	mm
R1B5HR	Steel Box Truck	30½	775	24	607
R1B5HRLD	Steel Box Truck w/ Lid	30 ¹ / ₂	775	24	607
R1B5HRX	Expanded Metal Box Truck	31½	800	25	635
R1B5HRXLD	Expanded Metal Box Truck w/ Lid	31½	800	25	635



Standard CasterPolyolefin
See page 76 for more caster information.

Heavy-Duty Work Benches




Optional Accessory Packages

Keep your work center organized with AkroBins® and cabinets. Choose from three accessory packages below or create your own combination from our extensive line of bins and containers (order custom combinations separately). Please specify one bin color per package: Red, Blue, Stone, or Yellow.



Accessory Package 1



Accessory Package 2




Accessory Package 3

- · Heavy-duty, steel frame workbench.
- · Steel or premium hardwood work surface.
- 34" fixed or adjustable work heights.
- Bench sizes: 30" x 60", 30" x 72".
- Blue or Gray powder coated finish.



Hardwood Surface Premium 1¹/₄" finished oak with rounded edges for a smooth, durable working surface.



Accessories to fit 30" x 60" workbench

Package 1

- 2 Bench Racks (Model 98600 Gray)
- 48 AkroBins (Model 30220)
- 6 Large AkroBins (Model 30239)

Package 2

- 1 Rail Kit
- 24 Medium AkroBins (Model 30230)
- 6 Large AkroBins (Model 30239)

Package 3

- 1 Rail Kit
- 1 20-Drawer cabinet (Model 19320)
- 1 set Suspension straps (Model 98400)
- 24 Small AkroBins (Model 30220)
- 6 Large AkroBins (Model 30239)

Accessories to fit 30" x 72" workbench

Package 1

- 2 Bench Racks (Model 98636 Gray)
- 36 Medium AkroBins (Model 30230)
- 6 Large AkroBins (Model 30239)


Package 2

- 1 Rail Kit
- 24 Medium AkroBins (Model 30230)
- 6 Large AkroBins (Model 30239)

Package 3

- 1 Rail Kit
- 1 20-Drawer cabinet (Model 19320)
- 1 set Suspension straps (Model 98400)
- 24 Small AkroBins (Model 30220)
- 6 Large AkroBins (Model 30239)





Mobile Work Tables



Heavy-Duty Work Table

- Industrial-grade mobile workstation with a welded-steel frame and steel-reinforced premium oak top – ships fully assembled.
- 24"L x 48"W work area with 9 adjustable height settings from 36" x 48".
- 5" x 2" bolted on polyurethane casters; two rigid, two swivel with total lock brakes.
- Wrap-around steel back stop keeps items from falling behind work table.
- Blue, Red, or Gray powder coated finish.
- Model No. RHWB2448P5PY0. Please specify frame color.



Work Table with Accessory Package

- 24" x 48" Adjustable height work table.
- 1 Rail Kit.
- 24 Small AkroBins (Model 30220).
- 12 Medium AkroBins (Model 30230).
- Model No. RHWB2448P5PY1.
 Please specify frame color and bin color.



Work Table with Accessory Package

Medium-Duty Work Table

- Industrial-grade work table with steel-reinforced hardwood top – ships fully assembled.
- Size: 24"L x 48"W x 36"H.
- Two steel drawers $15\frac{1}{2}$ "W x $5\frac{1}{2}$ "H x $16\frac{1}{2}$ "D.
- 2 swivel, 2 rigid bolted-on soft rubber casters; 5" x 1¹/₄". Total lock brakes on swivel casters.
- Frame colors: Red, Gray or Blue.
- Model No. RMWB24485SRTP.
 Specify frame color when ordering.



Handy, 13"W x 16" D





68-69

Wood Dollies Quality wood dollies for many loading applications.



70

Polyethylene Dollies

High-impact, durable polyethylene construction.



70

Steel Dolles

Smooth rolling dollies for heavy-duty applications



70

Aluminum Dollies Corrosion resistant, lightweight, and durable.



71

Hand Trucks

Medium and heavy-duty steel hand trucks for all types of loads.



72-73

Specialty

Hand Trucks

Unique designs to transport cylinders or other odd-shaped loads.



74-75

Drum Handling

Equipment

Equipment designed for operator safety and ease in handling or storing drums.



Dollies

Wood Dollies

- Constructed from select kiln-dried hardwoods to prevent warping and shrinkage.
- All boards are cut and planed to 7/8" with guaranteed consistent quality.
- Four, 3" polyolefin swivel casters offer 900 lb. capacity. (See caster options for up to 1,400 lb. capacity.)
- · Shipped fully assembled.



Solid Dolly

- Three cross battens on 36" and 48" length.
- Smooth, treated deck with countersunk bolts.
- Deck boards run lengthwise.

	V
•	

	Size						
Model No.	Inches	mm	Wt.				
RD2416S3P	24 x 16	610 x 406	17 lbs.				
RD2718S3P	27 x 18	686 x 457	21 lbs.				
RD3018S3P	30 x 18	762 x 457	23 lbs.				
RD3624S3P	36 x 24	914 x 610	29 lbs.				
RD4824S3P	48 x 24	1219 x 610	36 lbs.				


Carpet End Dolly

• Padded carpeting protects furniture and appliances.



	Size				
Model No.	Inches	mm	Wt.		
RD2416CE3P	24 x 16	610 x 406	14 lbs.		
RD2718CE3P	27 x 18	686 x 457	15 lbs.		
RD3018CE3P	30 x 18	762 x 457	16 lbs.		
RD3624CE3P	36 x 24	914 x 610	17 lbs.		


Flush Dolly



•	Smooth,	open	deck.

		>	ize	
_	Model No.	Inches	mm	Wt.
-	RD2416F3P	24 x 16	610 x 406	16 lbs
46	RD2718F3P	27 x 18	686 x 457	17 lbs
	RD3018F3P	30 x 18	762 x 457	19 lbs
	RD3624F3P	36 x 24	914 x 610	21 lbs
	RD4824F3P	48 x 24	1219 x 610	26 lbs

Rubber Cap Dolly





	Size						
Model No.	Inches	mm	Wt.				
RD2718RC3P	27 x 18	686 x 457	15 lbs.				
RD3018RC3P	30 x 18	762 x 457	16 lbs.				

Regular Dolly

- Strength and reliability at an economy price.
- All rails are 4" wide.

	Size				
Model No.	Inches	mm	Wt.		
RD2416R3P	24 x 16	610 x 406	13 lbs.		
RD2718R3P	27 x 18	686 x 457	14 lbs.		
RD3018R3P	30 x 18	762 x 457	15 lbs		
RD3624R3P	36 x 24	914 x 610	16 lbs.		

All Carpet Solid Dolly

- Strength and reliability at an economy price.
- \bullet Fully carpeted* deck prevents damage to cargo.
- *Pattern of carpet may vary.



	2	ize	
Model No.	Inches	mm	Wt.
RD2416AC3P	24 x 16	610 x 406	19 lbs.
RD3018AC3P	30 x 18	762 x 457	23 lbs
RD3624AC3P	36 x 24	914 x 610	32 lbs.

Dolly Options:



3", 4", 5" brake kits installed on 2 swivel casters.



Tow Eye R1495 Tow Handle R2515


Caster Options*

Model No.	Description	Capacity
3P	3 " Polyolefin Casters	900 lbs.
4P	4 " Polyolefin Casters	1200 lbs.
5P	5 " Polyolefin Casters	1400 lbs.
3H	3 " Hard Rubber Casters	900 lbs.
4H	4" Hard Rubber Casters	1200 lbs.
3R	3½" Non-Marking Rubber Casters	900 lbs.
Broke kite in	stalled on two swivel sasters - entional (non	roturnable)

	5 /2 Mon Marking Masser Casters	500 105.
Brake kits i	nstalled on two swivel casters – optional (non-	returnable)
R1130	3 " Brake Kits for Hard Rubber Casters	
R1151	3 " Brake Kits for Polyolefin Casters	
R1146	4 " Brake Kits	
R1156	5 " Brake Kits	

^{*}See page 76 for full description of casters and wheels.

Deck Heights by Caster Size:




Wood Dolly Components

Our Premium Decks are constructed from the highest quality hardwoods to ensure maximum service under extreme conditions.

Premium Wood


- Select a dolly deck to replace a damaged deck or to fit your specialized casters.
- Dolly decks on this page do not include casters.
 See page 68 for complete dolly and caster packages.
- Premium decks are constructed from select hardwood boards for lasting strength and durability.
- Available in $1\frac{1}{4}$ " (5/4) or 1" (4/4) thickness.
- Smooth, routered edges.



HOW TO ORDER

Order from the charts by specifying deck size (W x L), deck type, and thickness to create a model number.

Premium 5/4 (11/4") and 4/4 (1") Decks



For a premium 18" x 24" solid dolly deck with 4/4 (1") thickness, your model number will look like this: RPD1824544

PREMIUM DECK SIZES

18" x 24" 18" x 30" 24" x 36"

Specify size when ordering



Add optional casters and hardware to premium decks to create a premium dolly. See page 68 for options. Assembly required.

Solid Deck (S)











- * Installed hardware.
- ** Rubber cap only available on 27" x 18" and 30" x 18".


Standard Wood

- Select a dolly deck to replace a damaged deck or to fit your specialized casters.
- Dolly decks on this page do not include casters. See pages 68 for complete dolly and caster packages.
- Standard hardwood decks are 7/8" thick.
- · Constructed from select kiln-dried hardwoods.

HOW TO ORDER

Order from the charts by specifying deck size (W x L) and deck type to create a model number.

Standard 7/8" Decks



deck with 7/8" thickness, your model

number will look like this: RSD2416S

STANDARD DECK SIZES

24" x 16" 27" x 18" 30" x 18" 36" x 24"

48" x 24"

Specify size when ordering.

Polyethylene Dollies





1,200 lb. weight capacity - steel reinforced, onepiece deck design.

- · High-impact, durable polyethylene construction.
- Easy to clean, non-porous platform will not rot, mildew, or splinter.
- 1,200 lb. weight capacity.
- · Quick, easy assembly.
- Colors: Blue or Gray.





Plate-style 4" polyolefin swivel casters for maximum maneuverability and easy replacement



Polyethlene Dollies

		Dimensions		Overall H		
Model No.	Description	Inches	mm	Inches	mm	Color
RMD3018RC4PNA	Padded Deck Dolly	30 x18	762 x 457	83/4	222	Gray
RMD3018RC4PNAB	Padded Deck Dolly	30 x18	762 x 457	83/4	222	Blue
RMD3018F4PNA	Flush Deck Dolly	30 x18	762 x 457	73/4	197	Gray
RMD3018F4PNAB	Flush Deck Dolly	30 x18	762 x 457	73/4	197	Blue

Steel Dollies

- · Open structural angle dollies, 1½" x 1½" x ¾16".
- Durable powder coated finish.
- Solid decks are smooth, 13-gauge steel.
- $1\frac{1}{2}$ " lip turned down for a smooth surface. Order lips up for a contained area.



Steel Dollies

Lips Down	Lips Up		Caster Caster Size		Deck Height		
Model No.	Model No.	Capacity	Type* Inches mm		Inches	mm	
Solid Dolly							
RD843HR	RU843HR	900 lbs.	Polyolefin	3 x 1 ¹ / ₄	76 x 32	3 ⁷ /8	98
RD843SS	RU843SS	1000 lbs.	Semi-Steel	3 x 1 ¹ / ₄	76 x 32	3 ⁷ /8	98
RD844HR	RU844HR	1200 lbs.	Polyolefin	$4 \times 1^{1/2}$	102 x 38	5 ¹ /8	130
RD844SS	RU844SS	1600 lbs.	Semi-Steel	$4 \times 1^{1/2}$	102 x 38	5 ¹ /8	130
Open Angle Structural Dolly							
RD853HR	RU853HR	900 lbs.	Polyolefin	3 x 1 ¹ / ₄	76 x 32	4	102
RD853SS	RU853SS	1000 lbs.	Semi-Steel	3 x 1 ¹ / ₄	76 x 32	4	102
RD854HR	RU854HR	1200 lbs.	Polyolefin	$4 \times 1^{1/2}$	102 x 38	5 ¹ / ₄	133
RD854SS	RU854SS	1600 lbs.	Semi-Steel	4 x 1½	102 x 38	5 ¹ / ₄	133

^{*}See page 76 for full description of casters and wheels

DECK SIZES

16" x 27" 18" x 30" 18" x 24" 24" x 36" Specify size when ordering.



Wheel **Specifications:**

3" x 1¹/₄", 4" x 1¹/₂" Polyolefin



3" x 11/4", 4" x 11/2" Semi-Steel



Resilex

Aluminum Dollies





Lips Up

- · Corrosion resistant, lightweight, and durable.
- $1\frac{1}{2}$ " lip turned down for a smooth surface or lips up for a contained area
- · Deck is bolted together with galvanized fasteners.
- Bolt-on swivel casters.
- · Ships completely assembled and ready to use.

Aluminum Dollies Lips Down Caster Caster Size **Deck Height** Model No. Capacity Type* Inches mm Inches mm Lips Down RDADRX4 1200 lbs Resilex 4 x 1-1/4 102 x 32 6-3/4 171 RDADP4 1200 lbs Polyolefin 4 x 1-1/4 102 x 32 6-3/4 171 Lips Up RDAURX4 1200 lbs Resilex 4 x 1-1/4 102 x 32 8 203 RDAUP4 1200 lbs Polyolefin 4 x 1-1/4 102 x 32

*See page	6 for full description of casters a	and wheels.

DECK SIZES

36" x 24" 30" x 18" 24" x 18"

Specify size when ordering.

Hand Trucks

Medium-Duty

- · Medium-duty hand trucks for day-to-day work.
- Welded-steel construction supports up to 300 lbs.
- ⁷/₈" OD structural pipe frame, ½" wall, 13-gauge.
- Standard 7" x 14" steel nose plate.
- Ships completely assembled and ready to use.
- ⁵/₈" diameter axle.
- Two position bracket fits 8" or 10" wheels.
 - · Heavy flat bar and tube for climbing stairs.
 - Optional 10" x 14" or 14" x 14" nose plates available.

*Special-order products are not returnable.

Heavy-Duty

- · Heavy-duty hand trucks for all types of loads.
- Welded-steel hand trucks support up to 500 lbs.
- 1" OD structural pipe frame, 13-gauge steel.
- ⁵/₈" diameter axle.
- Standard 8" x 14" steel nose plate.
- Optional 10" x 14" or 14" x 14" noseplate available.*
- Two position bracket fits 8" or 10" wheels.
- Deep-V cross straps available for specialized loads.*

*Special-order products are not returnable.

Wheel Specifications:

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance. or load capacity. See page 76 for more caster information.



Semi-Pneumatic 10" x 2.75



Full Pneumatic 10" x 3.50"



Moldon Rubber 8" x 2"

Handle Styles:



Flow Back





Optional 24" folding nose extensions available. Suffix FN to any model no. Not intended for field installation. (Specialorder products are not returnable.)

Medium-Duty Hand Trucks

Model No.	Wheel Type	Wheel Inches	Size mm	Overall I	leight mm	Overall \ Inches	Vidth mm	Ship Wt.
Flow Back								
R3008MR	Moldon Rubber	8	203	45	1143	19 1/8	498	37 lbs.
R3010FP	Full Pneumatic	10	254	45	1143	22	559	35 lbs.
R3010SP	Semi-Pneumatic	10	254	45	1143	20	508	35 lbs.
Dual Grip								
R3208MR	Moldon Rubber	8	254	47	1194	20	508	35 lbs.
R3210FP	Full Pneumatic	10	254	47	1194	20	508	35 lbs.
R3210SP	Semi-Pneumatic	10	254	47	1194	20	508	35 lbs.

Heavy-Duty Hand Trucks

Model	Wheel	Whee	Size	Overall	Height	Overall \	Vidth	Ship
No.	Туре	Inches	mm	Inches	mm	Inches	mm	Wt.
Flow Back								
R4008MR	Moldon Rubber	8	203	45	1143	19³/ ₄	502	43 lbs.
R4008MR2	Moldon Rubber	8	203	52	1321	19³/ ₄	502	48 lbs.
R4010FP	Full Pneumatic	10	254	45	1143	22	559	41 lbs.
R4010FP2	Full Pneumatic	10	254	52	1321	22	559	46 lbs.
R4010SP	Semi-Pneumatic	10	254	45	1143	20	508	41 lbs.
R4010SP2	Semi-Pneumatic	10	254	52	1321	22	559	46 lbs.
Vertical Single	e Loop							
R4108MR	Moldon Rubber	8	203	46	1168	19³/₄	502	43 lbs.
R4108MR2	Moldon Rubber	8	203	53	1346	19³/ ₄	502	48 lbs.
R4110FP	Full Pneumatic	10	254	46	1168	20	508	41 lbs.
R4110FP2	Full Pneumatic	10	254	53	1346	22	559	46 lbs.
R4110SP	Semi-Pneumatic	10	254	46	1168	20	508	41 lbs.
R4110SP2	Semi-Pneumatic	10	254	53	1346	20	508	46 lbs.
Dual Grip								
R4208MR	Moldon Rubber	8	203	47	1194	20	508	43 lbs.
R4208MR2	Moldon Rubber	8	203	51	1295	20	508	48 lbs.
R4210FP	Full Pneumatic	10	254	47	1194	22	559	41 lbs.
R4210FP2	Full Pneumatic	10	254	51	1295	22	559	46 lbs.
R4210SP	Semi-Pneumatic	10	254	47	1194	20	508	41 lbs.
R4210SP2	Semi-Pneumatic	10	254	51	1295	20	508	46 lbs.
Dual Loop	-			-		-		-
R4510SP	Semi-Pneumatic	10	254	46	1168	20	508	41 lbs.
R4510SP2	Semi-Pneumatic	10	254	53	1346	20	508	46 lbs.



Dual Grip with Vinyl Grips



Specialty Hand Trucks

Cylinder/Gas Trucks



Model	Wheel	Wheel Size		
No.	Туре	Inches	mm	
RCTD40SP	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70	
Base Plate - 1	14"W x 6"D (356 x 152mm)	OAH - 45"	1143	

Single & Dual Gas Trucks

- Heavy-duty truck designed to handle 330 cu. ft. cylinders.
- Available in single and dual cylinder models.
- Includes heavy-duty holding chain.
- Hard rubber swivel caster.
- Color: Yellow.

Model		Wheel	Wheel Size		
No.	Description	Туре	Inches	mm	
RGTS10FP	Single	Full Pneumatic	10 x 3 ¹ / ₂	254 x 89	
RGTD10FP	Dual	Full Pneumatic	10 x 3 ¹ / ₂	254 x 89	
RGTS10SP	Single	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70	
RGTD10SP	Dual	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70	
Base Plate –	14"W x 6"D	(356 x 152mm)	OAH - 45"	1143	



Dual Cylinder Truck with T-Handle

- Handles cylinders in a medium-duty application.
- Priced economically with its T-handle design.
- Two heavy-duty holding chains and tool tray.
- · Color: Yellow.



Single Cylinder Hand Truck

- Perfect for medium to large cylinders.
- Also transports boxes or other bulky items.
- Includes heavy-duty holding chain.
- Color: Yellow.

Model	Wheel	Wheel Size			
No.	Туре	Inches	mm		
RCT40LW	Lightweight	8 x 1 ³ / ₄	203 x 44		
Base Plate -	17"W x 8"D (432 x 203mm)	OAH - 43"	1092		



Model	Wheel	Wheel Size		
No.	Туре	Inches	mm	
RCTV40SP	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70	
Base Plate -	14"W x 7"D (356 x 178mm)	OAH - 48"	1219	



Dual Cylinder Truck with Dual Handle

- Carries cylinders in a medium-duty application.
- · Welded tank holders.
- Two heavy-duty holding chains and
- · Dual handle with vinyl grips.
- Color: Yellow.



Dual Cylinder Truck with Continuous Handle

- Heavy-duty truck accommodates most cylinder tanks.
- Includes heavy-duty holding chain and tool tray.
- Easily carries two 300 cu. ft. tanks.
- Color: Yellow.

Model	Wheel	Wheel Size		
No.	Туре	Inches	mm	
RCT50SP	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70	
Base Plate -	20"W x 9"D (508 x 229mm)	OAH - 45"	1143	

Model Wheel		Wheel Size			
No.	Туре	Inches	mm		
RCT30FP	Full Pneumatic	10 x 3 ¹ / ₂	254 x 89		
RCT30SP	Semi-Pneumatic	10 x 2 ³ / ₄	254 x 70		
Base Plate -	20"W x 11"D (508 x 279mm)	OAH - 39"	991		

Dual-Purpose Hand Truck

- Dual-function hand truck converts to platform position for oversize loads.
- 40"H hand truck.
- 37"L platform bed.
- Welded, 1" structural pipe frame with \frac{1}{8}" walls.
- Large, 7" x 14" nose plate.
- Up to 600 lbs. capacity in platform mode.
- Color: 4008 Model is Red, 4010 Models are Silver.





Dual-Purpose Hand Truck

Model	Wheel	Wheel/Caster	Overall	Height	Overall	Width	Ship
No.	Type	Size	Inches	mm	Inches	mm	Wt.
RDT4008SP	Semi-Pneumatic	8"/3"(203/76)	46	1168	19⁵/₃	498	46 lbs.
RDT4010FP	Full Pneumatic	10"/5" (254/127)	46	1168	22	559	50 lbs.
RDT4010SP	Semi-Pneumatic	10"/5" (254/127)	46	1168	20	508	50 lbs.

Color: 4008 Model is Red, 4010 Models are Silver.

Pail Truck



- · Multi-purpose hand truck for carting 5-gallon pails.
- Cross straps with supporting arms hold pails in place while in transit.
- Welded, 1" structural pipe frame with $\frac{1}{8}$ " walls.
- Up to 300 lbs. capacity.
- RPT40 holds 4 pails, RPT50 holds 5 pails.

Pail Truck

Model	Wheel	Wheel Size		Overall Height		Overall Width		Ship
No.	Туре	Inches	mm	Inches	mm	Inches	mm	Wt.
RPT4010SP	Semi-Pneumatic	10	254	55	1397	18	457	46 lbs.
RPT5010SP	Semi-Pneumatic	10	254	67½	1715	18	457	50 lbs.

Drum Handling Equipment

Drum Hand Truck

- Transport 30 and 55-gallon drums with ease.
- Strong rugged construction for heavy-duty drum handling.

Drum Hand Truck

Model	Wheel	Wheel Size		Wheel Size		Roller	Load
No.	Type	Inches	mm	Bearing	Capacity		
R9508MR	Moldon	8 x 2	203 x 51	³ / ₄ " (19mm)	1000 lbs.		
R9510MR	Moldon	10 x 2½	254 x 64	1" (25mm)	1200 lbs.		



Spill-less Open Drum Truck

- Easily transports open drums, reduced danger of spillage.
- Handles 55-gallon drums.

Spill-less Open Drum Truck

Model Wheel Size				
No.	Description	Inches	mm	
R93	Rigid Handle	6 x 2	152 x 51	
R93H	Hinged Handle	6 x 2	152 x 51	



Cradle Combo Truck

- · A drum truck and cradle in one.
- Distributes weight over four wheels for operator safety.
- Handles 30 and 55-gallon drums with ease.

Cradle Combo Truck

Model	Wheel	Wheel Size		Roller	Load
No.	Type	Inches	mm	Bearing	Capacity
R9508MR2	Moldon	8 x 2	203 x 51	³ / ₄ " (19mm)	1000 lbs.
		6 x 2	152 x 51	³ /4"(19mm)	
R9510MR2	Moldon	10 x 2½	254 x 64	1" (25mm)	1200 lbs.
		6 x 2	152 x 51	³ / ₄ " (19mm)	



Drum Dollies



Drums load easily onto this cross-style dolly.

For the ease of rolling 30 and 55-gallon drums.



Cross-Style			
Model		Load	
No.	Wheel Type	Capacity	Diameter
R9030HR	3" Swivel Polyolefin	900 lbs.	20 ¹ /4 ID
R9055HR	3" Swivel Polyolefin	900 lbs.	24 ¹ /4 ID
R9030SS	3" Swivel Semi-Steel	1000 lbs.	20 ¹ /4 ID
R9055SS	3" Swivel Semi-Steel	1000 lbs.	24 ¹ /4 ID
R90555HR	5" Swivel Polyolefin	1500 lbs.	24½ ID




Ring Dollies

Model		Load	
No.	Wheel Type	Capacity	Diameter
R9230HR	3" Swivel Polyolefin	900 lbs.	19½ ID
R9255HR	3" Swivel Polyolefin	900 lbs.	23½ ID
R9230SS	3" Swivel Semi-Steel	1000 lbs.	19½ ID
R9255SS	3" Swivel Semi-Steel	1000 lbs.	23 ¹ / ₂ ID
R92555HR	5" Swivel Polyolefin	1500 lbs.	23½ ID

Drum Racks

- Allows for easy handling and storage of drums.
- Saves storage space.
- · Heavy-duty welded steel construction.
- · Accessible with fork lift from all sides.
- Racks can be stacked to store additional drums.





Drum Racks

Model		Size (H	Single Rack			
No.	Description	Inches	mm	Load Capacity		
R992	Two-Drum Rack	10 x 45½ x 28	254 x 1156 x 711	1600 lbs.		
R993	Three-Drum Rack	10 x 74 x 28	254 x 1880 x 711	2400 lbs.		

Drum Cradles

- Drum cradles allow easy transport and draining of 55-gallon drums.
- Single and dual handles retract for storage.
- Cradles support loads to 600 lbs.
- Some assembly required.
 - Model R91HW2 has swivel casters to allow easier turning in limited space. Two handles provide greater stability and operator control.

Drain 55-gallon drums easily with drum cradles.



Drum Cradles

Model	
No.	Description
R91HW	With 1 Handle and 4 Rigid Wheels
R91HW2	With 2 Handles and 2 Swivel Casters, 2 Rigid Wheels

Materials Definitions & Benefits

Each resin has properties that make it ideal for a specific purpose. We manufacture our plastic products using the grade most suited to the product's end use. Listed below are the quality resins we use and their attributes. Akro-Mils reserves the right to change product materials without notice.

Polypropylene

Rigid and very strong. High impact resistance. Hard surface resists scratches. Withstands temperatures between -20 and 150°F.

■ Co-Polymer Polypropylene

Unique additives increase strength, rigidity, and impact resistance.

■ High Density Polyethylene

Extremely rigid and very strong. Highly impact and chemical resistant. Extremely hard surface is resistant to scratches. Withstands temperatures between -20 and 150° F.

Co-Polymer Polyethylene

Unique additives increase impact resistance over standard high-density polyethylene.

■ Polystyrene

More flexible to withstand impacts. Withstands temperatures between -30 and 115° F.

■ High-Impact Polystyrene

A part of the Styrene family, but superior in UV, impact, and weather resistance. High-gloss surface. Withstands temperatures up to 180°F.

Structural Foam/Web

Advanced molding process makes an extremely durable product that will withstand heavy loads and high levels of abuse. Withstands temperatures between -30 and 120° F.

■ FDA Approved Materials

Resins and colorants are FDA-approved for use in the food industry.

■ ESD Materials

Provides the highest degree of electrostatic discharge protection available with consistent uniform surface resistivities in the static dissapative range of 10°-10° ohms/sq.

Casters & Wheels

A generous selection of caster and wheel options allows Platform Trucks, Hand Trucks, Dollies, and Shelf Carts to be customized to fit hundreds of applications, surfaces, and conditions. Caster and wheel choices allow you to resolve problems of noise control, floor protection, impact and abrasion resistance, or load capacity.

Caster Types



Phenolic

Economical, highcapacity wheel rolls easily and is resistant to chemicals and oils.



Polyurethane

A heavy-duty wheel with polyurethane cushion tread bonded to a cast iron core. Resists most chemicals and oils.



Moldon Rubber

A quiet, shockabsorbing wheel with rubber cushion tread bonded to a cast iron core.



Non-Marking

Soft rubber cushion tread on polished aluminum hub provides maximum floor protection and shock resistance



Hi-Tech Performa Wheels

Hi-Tech Performa wheels in flat or round tread designs, resist damage from weather, water, steam, or metal shavings. Thermoplastic elastomer treads are load-rated up to 500 lbs. per wheel.



Steel

Extremely durable, high-capacity cast iron wheel rolls easily under heavy loads and is highly resistant to abrasion.



Polyolefin

A heavy-duty, lightweight, non-marking plastic wheel that resists most chemicals and oils, and has excellent impact resistance.



Semi-Pneumatic

Co-polymer polypropylene wheel on an aluminum hub. Specifically designed for material handling equipment.



Full Pneumatic

Air-filled for excellent shock protection, floor protection, and easy operation over rough surfaces.



Pro-Tech Wheels

The Pro-Tech polyurethane wheel is a non-marking, cushion ride design that can be ordered with non-metallic, delrin bearings that are unaffected by water, steam, oil, and most acids. Pro-Tech wheels are load-rated up to 750 lbs.

Caster Composition	on					F	Floor	Sur	face					Floc	or Co	veri	ngs			Othe	r Fac	tors	To Consider
E= Excellent G= Good F= Fair NR= Not Recommended	/kº	sohalt Br	idul C	artie Til	e Joncrete Liv	noleum	eel Ribl	sed sur	ooth A	dinal Co	its of	r Harsh	etal chi	stal sci	ags Le	ated as	seam Not Not	jetion Jise (1	shion	oad Re	esistand apacity	S A Principal	se Reistante
Standard Caster/Wheels																							
Polyolefin	F	F	G	G	F	F	G	G	G	F	G	G	NR	G	Е	G	F	NR	G	G	E	G	
Moldon Rubber	Е	Е	E	Е	E	G	G	Е	G	F	F	Е	E	F	G	Е	Е	Ε	E	F	F	F	
Pneumatic	Е	Е	Е	Е	Е	Е	Е	Е	G	F	F	G	G	F	G	Е	Е	Е	Е	F	F	F	
Steel	NR	NR	NR	F	NR	NR	G	F	G	F	G	G	NR	G	F	NR	F	NR	NR	Е	E	Е	
Polyurethane	Е	Е	G	Е	E	G	G	Е	G	G	G	G	G	G	G	Е	Е	G	G	Е	G	Е	
Phenolic	NR	NR	NR	G	E	NR	G	G	G	F	G	F	NR	Е	Е	Е	Е	NR	E	Е	E	G	
Pro-Tech	Е	Е	G	Е	Е	G	G	Е	G	G	G	G	G	G	G	Е	Е	G	G	Е	G	Е	
Performa																							
Black Flat 5"	Е	Е	G	Е	Е	G	G	Е	G	G	G	G	G	G	G	Е	Е	G	G	Е	G	Е	
Gray Round 8"	E	Е	G	Е	E	G	G	Е	G	G	G	G	G	G	G	Е	Е	G	G	E	G	Е	

Index

242049	300168	3093052	3908520	7741041
570548	3010111	3093652	3912020	7750541
570948	3010211	3310123	3917020	7751041
580548	3011011	3310523	4012011	7761041
580748	3012011	3316123	4013011	7810041
590548	3012411	3316423	4015011	7946539
611547	3012811	3316823	4017011	7949639
6118 47	3013011	3322023	402206	79565
621747	3013811	3322123	4022846	7959639
814649	301488	3322423	402306	9541853
816649	3015011	3322623	402396	9549253
818649	3015811	3322823	402456	98325
918527	3016411	3424028	402656	98400
951449	3017011	3430128	402706	98600
951749	3017411	3430228	4032046	98636
991249	3017811		4041011	•
		3430328		075-611
992049	3018411	3430428	40416	08024RED 49
1011647	302106	3501018,23	4044511	30120ESD 15
1012447	302116	3501123	40501	30124ESD 15
1012647	302206	35180	40715	30128ESD 15
1014447	302216	3518118	4090146	30210ESD 15
1016447	302246	3518518	4090946	30220ESD 15
1102019	302306	3519018	4110523	30230ESD 15
1301410	302316	3519118	4116423	30235ESD 15
1301710	302346	3519518	4116623	30240ESD 15
1301810	302356	3520018	4116823	302656
1421249	302366	3520118	4122023	302706
1421749	302396	3522518	4122423	30716 BLACK 14
1701846	302406	3523018	4122623	30718 BLACK 14
1713646	302506	3523118	4122823	30776 BLACK 14
1910946	302556	3524018	4210523	30778 BLACK 14
1922846	3028010	3524118	4216423	30796 BLACK 14
1932046	3028110	3530018	4216623	30945 GRAY 43
1941646	3028210	3530118	4216823	30955BLGRY42
1971546	3028310	3720824	4222023	30955BRGRY42
1990946	3029010	3727824	4222423	30955SHELF 42
2022846	3034814	3728824	4222623	33164ESD15
2032046	3035814	3760824	4222823	33224ESD 15
2041646	304248,46	3761224	7646040	3H 68
2050246	30618	3761624	7646140	3P68
2071546	30626	3767224	76490	3R68
2090246	30636	3767624	7649140	4H 68
2090946	30653	3767824	7659040	4P68
300068	308128	3768224	76591	5P68
300088	3090053	3768624	7700241	66486CLDBL 19
300128,46	3090653	3768824	7740541	66497CLDGN 19

Index

66499CLSIL19	AR2717120221	DR2115010022	R1S12FP2 61	R4208MR2 71
AB2115090022	AS127512	DR2420010022	R1S5HR61	R4210FP 71
AC36189	AS1275110Y12	DY2219070030	R1S5HR261	R4210FP2 71
AC3618QV 9	AS1275120Y12	HH1911070026	R1S5HR2LD 61	R4210SP 71
AC3618QV240 9	AS1275130Y12	HH2411090026	R1S8FP2 61	R4210SP2 71
AC3618QV250 9	AS1275150Y12	HI20140300 27	R1S8MR 61	R4510SP 71
AC3618SV9	AS1275170Y12	HI2014032027	R1S8MR2 61	R4510SP2 71
AC3618SV2409	AS187512	HI2014040027	R1S8MR2LD61	R4ST5HR61
AC3618SV2509	AS1875128Y12	HI2014042027	R2108FPB 60	R4ST8MR
AC3618Y9	AS18751301412	HL14100000 26	R21210FPB60	R5ST5HR61
AC36249	AS18751301712	HL21130000 26	R2125MRB60	R5ST8MR 61
AC36243AS9	AS18751301812	HS2213060027	R21412FPB60	R610058
AC3624Y 9	AS1875138Y12	HS24160900 27	R2146MRB 60	R610158
AC3624Y3AS9	AS1875158Y12	HS28170900 27	R214HE63	R611158
ACR-240	AS1875178Y12	HT15100600 26	R214HEGA 63	R612158
ACR-340	AS18753612	HT1510062226	R215HE63	R613158
ACR-440	AS18754212	HT1610042226	R2161012FPB60	R613958
ACR-640	AS1875ASSOR12	HT1910040026	R2165PLB 60	R614158
AF21150602 22	AS2115170221	HT1910042226	R2165PYB60	R614458
AG2016042229	AS2213120221	HT2213060026	R2165SSB 60	R615158
AG2416075229	AS2821150221	HT2213062226	R2168MRB 60	R617058
AP2216100021	AS3424201221	JL2516096829	R2ST5HR61	R617158
APRBENCH13	BG4840330233	LJ2516020029	R2ST8MR61	R617558
APRBENCH 120 13	BH4840342032	MP2420072231	R2T5HR63	R618058
APRBENCH 150 13	BH4845342032	NL24160259 30	R2T8MR 63	R618158
APRC9	BS32302500 33	NP2416088730	R3008MR 71	R619158
APRC120Y9	BS32303420 33	NP2416119430	R3010FP 71	R619358
APRD13	BS64483411 32	NP2416119530	R3010SP 71	R619458
APRD110Y13	BX4845252038	PM48400600134	R3208MR 71	R619958
APRD120Y13	BX4845342033	PM48400633134	R3210FP 71	R7208PL 59
APRD130Y13	BX4845342038	PM48480600134	R3210SP 71	R7218PL 59
APRD150Y13	C18-541E 30	PM48480633134	R3ST5HR61	R746MR 59
APRD170Y13	C75-605 38	PS484006001 35	R3ST8MR 61	R756MR 59
APRDMOBILE13	CC2014112229	PS484006331 35	R4008MR 71	R768MR 59
APRS13	CD2826012031	PU48400633135	R4008MR2 71	R778MR 59
APRS110Y13	CP2420076030	R113068	R4010FP 71	R786PL 59
APRS120Y13	CP2420106030	R114668	R4010FP2 71	R796PL 59
APRS130Y13	CP2420136030	R115168	R4010SP 71	R9000057
APRS150Y13	CT2926092231	R115668	R4010SP2 71	R9003161
APRS170Y13	DL2115051222	R120DS59	R4108MR 71	R9004161
AR1514130021	DL2115071222	R121DS59	R4108MR2 71	R9006261
AR2012070221	DL21150900 22	R1B5HR63	R4110FP 71	R9011055
AR2115090221	DL2115120222	R1B5HRLD63	R4110FP2 71	R9015255
AR2115120221	DL2420061422	R1B5HRX63	R4110SP 71	R9015355
AR2420120221	DL2420101422	R1B5HRXLD63	R4110SP2 71	R9016255
AR2717090221	DL24201202 22	R1S10FP2 61	R4208MR 71	R9016355

Index

R9016455	R9508MR2 74	RD844SS70	RPTD27541 58	RWHV24481A5Y6A59
R9018155	R9510MR 74	RD853HR70	RPTD27542 58	RWHV30601A5M6 59
R9018255	R9510MR2 74	RD853SS70	RPTD30601 58	RWHV30601A5M6A 59
R9018355	R9601555	RD854HR70	RPTD30602 58	RWHV30601A5M8 59
R9018455	R9601755	RD854SS70	RPTD36721 58	RWHV30601A5M8A 59
R9018555	R99275	RDADP4 70	RPTD36722 58	RWHV30601A5Y659
R9021055	R99375	RDADRX4 70	RSD241669	RWHV30601A5Y6A59
R9025255	RA121DS59	RDAUP470	RSD271869	SL12070100 25
R9025355	RA6TR4MR 28	RDAURX4 70	RSD301869	SL15120100 25
R9026255	RA7218PL59	RDT4008SP 73	RSD362469	SL24110100 25
R9026355	RA756MR 59	RDT4010FP 73	RSD482469	SL24150100 25
R9026455	RA778MR 59	RDT4010SP 73	RU842HR201810	SL2422010025
R9028155	RA796PL59	RGTD10FP72	RU842HR291810	SN1512070919
R9028255	RC2517140138	RGTD10SP72	RU843HR70	SN2415070919
R9028355	RCT30FP 72	RGTS10FP 72	RU843HR142020	SN2415099919
R9028455	RCT30SP72	RGTS10SP 72	RU843HR142218	SN2422091319
R9028555	RCT40LW72	RHWB2448P5PY0 65	RU843HR151910	SN2422111319
R9030HR75	RCT50SP72	RHWB2448P5PY1 65	RU843HR161710	SW1207050225
R9030SS 75	RCTD40SP72	RHWB3060 64	RU843HR162123	SW1512060225
R90555HR75	RCTV40SP72	RHWB3072 64	RU843HR162424	SW151208A2 25
R9055HR75	RD2416AC3P 68	RM716MR59	RU843HR182218	SW1512100225
R9055SS 75	RD2416CE3P68	RM716PL59	RU843HR182818	SW24111002 25
R91HW 75	RD2416F3P 68	RM718MR59	RU843SS70	SW241504A2 25
R91HW275	RD2416R3P68	RM718PL59	RU844HR70	SW2415060225
R9230HR75	RD2416S3P68	RMD2104MRA 60	RU844SS70	SW241508A2 25
R9230SS 75	RD2718CE3P68	RMD2105SRA 60	RU853HR70	SW24151002 25
R9241155	RD2718F3P68	RMD2ST5SR62	RU853SS70	SW241511A2 25
R9241255	RD2718R3P68	RMD3018F4PNA70	RU854HR70	SW2415150225
R9241355	RD2718RC3P68	RMD3018F4PNAB70	RU854SS70	SW2422080225
R9241455	RD2718S3P68	RMD3018RC4PNA70	RWH24481A5M6 59	SW2422110225
R9241655	RD3018AC3P 68	RMD3018RC4PNAB70	RWH24481A5M6A 59	SW3215080225
R9241855	RD3018CE3P68	RMD3ST5SR 62	RWH24481A5M8 59	SW4815080225
R92555HR75	RD3018F3P 68	RMWB24485SRTP 65	RWH24481A5M8A 59	SX151208A425
R9255HR75	RD3018R3P68	RPD182469	RWH24481A5Y659	SX241504A425
R9255SS	RD3018RC3P68	RPD183069	RWH24481A5Y6A59	SX241508A425
R9374	RD3018S3P68	RPD243669	RWH30601A5M6 59	SX24151000 25
R9301155	RD3624AC3P 68	RPT2448 57	RWH30601A5M6A 59	SX241511A425
R9301255	RD3624CE3P68	RPT2754 57	RWH30601A5M8 59	SX48150800 25
R9301355	RD3624F3P 68	RPT2ST5SR62	RWH30601A5M8A 59	TH48400200132
R9301455	RD3624R3P68	RPT3060 57	RWH30601A5Y659	TH484502001 32
R9301655	RD3624S3P68	RPT3672 57	RWH30601A5Y6A59	TS32300200 33
R9301955	RD4824F3P 68	RPT3ST5SR62	RWHV24481A5M6 59	TS48400200 33
R93H 74	RD4824S3P68	RPT4010SP 73	RWHV24481A5M6A 59	TS48450300 33
R9481555	RD843HR 70	RPT5010SP 73	RWHV24481A5M8 59	TS48450300 38
R9481755	RD843SS70	RPTD24481 58	RWHV24481A5M8A 59	
R9508MR 74	RD844HR 70	RPTD24482 58	RWHV24481A5Y6 59	

Discover Unmatched Opportunities For Your Plastic & Rubber Needs with these Industry-Leading Companies from Myers Industries...



Allibert-Buckhorn™ is
the European leader in
reusable plastic pallets,
hand-held totes, bulk
transport containers,
IBC's, and custom
material handling
products for automotive,
industrial, agriculture, food,
chemical, and retail distribution markets.





Myers Industries, Inc. (NYSE: MYE) is an international manufacture of polymer products for industrial, agricultural, automotive, commercial and consumer markets. In addition to the material handling brands featured, product solutions both standard and custom are available from Myers' other industry-leading companies:



Dillen Products[®]— North America's foremost manufacturer of horticultural pots, trays, hanging baskets, and related items for growers, nurseries, and retail garden centers.



Listo Products[™] — The premier innovator in the design and molding of decorative resin planters with unique textures and color effects, serving the retailer/consumer.



Pro Cal™— Manufactures a variety of injection-molded and pressure-formed nursery pots and specialty graphic containers for professional growers.



Buckhorn Rubber Products[™]— A leading producer of engineered, molded rubber hoses, seals, and other custom parts for markets including agriculture, heavy-truck, construction. and water control.



Michigan Rubber Products™— A top designer and manufacturer of rubber components, systems, and assemblies for the automotive industry.



WEK Industries[™]— Sets the standard for engineered, plastic blow-molded components for automotive, motorcycle, and all-terrain vehicles.



Patch Rubber™— Produces the largest selection of tire repair and retread products in the U.S., specialty items such as reflective highway tapes, and custom rubber sheet stock.



raaco International®— The European solution for plastic bins and storage systems serving industrial and commercial markets.



Myers Tire Supply[®]— The largest U.S. distributor of tools, equipment, and supplies for tire, wheel, and undervehicle service professionals.

Learn More at www.myersind.com



