

NTC thermistors for temperature measurement

SMD NTC thermistors, case size 0402 (1005), automotive series

Series/Type: B572**V5

Date: January 2016

© EPCOS AG 2016. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



B572**V5

Temperature measurement and compensation SMD NTC thermistors, case size 0402 (1005)

Automotive series

SMD

Applications

Temperature measurement and compensation

Features

- Qualification based on AEC-Q200 Rev-D
- Multilayer SMD NTC with inner electrodes
- Nickel barrier termination
- For temperature measurement up to 150 °C
- Excellent long-term aging stability in high temperature and high humidity environment
- UL approval (E69802)

Options

Alternative resistance ratings, resistance tolerances and B value tolerances available on request.

Delivery mode

Cardboard tape, 180-mm reel

Operating temperature range

General technical data

Operating temperature range		ор	-10 130	
Max. power	(at 25 °C, on PCB)	P ₂₅ 1)	150	mW
Resistance tolerance		$\Delta R_R/R_R$	±1, ±3, ±5	%
Rated temperature		T _R	25	°C
Dissipation factor	(on PCB)	$\delta_{th}{}^{1)}$	approx. 2.5	mW/K
Thermal cooling time constant	(on PCB)	$\tau_c^{1)}$	approx. 3	s
Heat capacity		C _{th} 1)	approx. 7.5	mJ/K
-				

Т

Electrical specification and ordering codes

R_{25} Ω	ΔR _R /R _R %	No. of R/T characteristic	B _{25/50} K	B _{25/85}	B _{25/100} K	Ordering code
4.7 k	±5	8502	3940	3980	4000 ±3%	B57251V5472J060
10 k	±1	8509	3380	3435	3455 ±1%	B57232V5103F360
10 k	±3, ±5	8509	3380	3435	3455 ±1%	B57232V5103+360
10 k	±5	8502	3940	3980	4000 ±3%	B57251V5103J060


+ = Resistance tolerance

 $F = \pm 1\%$ (only for B57232V5103F360)

 $H = \pm 3\%$

 $J = \pm 5\%$

Dimensional drawing



Dimensions in mm Approx. weight 4.5 mg

-40

150

°C

¹⁾ Depends on mounting situation



B572**V5

SMD NTC thermistors, case size 0402 (1005)

Automotive series

SMD

Reliability data

Tests of SMD NTC thermistors are based on AEC-Q200 Rev-D. The parts are mounted on standardized PCB.

Test	Standard	Test conditions	$\Delta R_{25}/R_{25}$ (typical)	Remarks
Pre- and post-stress electrical test		Resistance at: 25 °C and 100 °C		
High temperature exposure (storage)	MIL-STD-202, method 108	Test temperature: 150 °C Duration: 1000 h Unpowered	< 5%1)	
Temperature cycling	JESD22, method JA-104	Lower test temperature: -40 °C Upper test temperature: 150 °C Number of cycles: 1000 Transfer time: < 10 s Dwell time: 15 min Air – Air	< 5% ²⁾	
Biased humidity	MIL-STD-202, method 103	Test temperature: 85 °C Rel. humidity of air: 85% Duration: 1000 h Test voltage: V _{NTC} = 0.3 V DC	< 5%²)	
Operational life	MIL-STD-202, method 108	Test temperature: 150 °C P _{max} = 0.35 mW Duration: 1000 h	< 5%2)	
External visual	MIL-STD-883E, method 2009	Visual inspection		
Physical dimensions	JESD22, method JB-100	Measured with calibers		Within the specified values
Resistance to solvents	MIL-STD-202, method 215	Not applicable for SMD thermistors (component has no marking, color coding or coating)		
Mechanical shock	MIL-STD-202, method 213	Peak value: 1500 <i>g</i> Half sine Condition F	< 5%1)	
Vibration	MIL-STD-202, method 204	Acceleration: 5 g Sweep time: 20 min Frequency range: 10 2000 Hz 3×12 cycles	< 5%1)	

¹⁾ Except B57232V5103+360 $\Delta R_{25}/R_{25}$ (typical) < 1%

²⁾ Except B57232V5103+360 $\Delta R_{25}/R_{25}$ (typical) < 3%



Temperature mea	Temperature measurement and compensation				
SMD NTC thermis	stors, case size (0402 (1005)	Automo	tive series	
		SMD			
Test	Standard	Test conditions	$\Delta R_{25}/R_{25}$ (typical)	Remarks	
Resistance to soldering heat	MIL-STD-202, method 210	Dip: 260 °C; 10 s 1 heat cycle	< 3%³)		
ESD	AEC-Q200-002 method -002	Discharge capacitance: 150 pF Discharge resistance: $2 \text{ k}\Omega$ Charging voltage: 6 kV Contact discharge 2 pulses in each polarity	< 5%4)		
Solderability	J-STD-002	a) Dip: 235 °C; 5 s: aging 4 h @ 155 °C b) Dip: 215 °C; 5 s: steam aging 8 h @ 92 °C c) Dip: 260 °C; 7 s: steam aging 8 h @ 92 °C		95% of termination wetted	
Electrical characterization		R(25 °C), R(100 °C), B(25/100)		Within the specified values	
Flammability	UL-94, V-0 or V-1	Not applicable for SMD thermistors (component is not coated or encapsulated with plastic materials)			
Board flex	AEC-Q200-005 method -005	Max. bending: 1 mm Duration @ max. bending: 60 s	< 5%5)		
Terminal strength	AEC-Q200-006 method -006	Max. F: 5 N	< 5%5)		
Resistance drift		Reflow soldering profile	< 1%		

Wave soldering profile

after soldering

 $[\]begin{array}{lll} 3) & \text{Except B57232V5103+360 } \Delta P_{\text{gs}}/P_{\text{gs}} \text{ (typical)} < 1\% \\ 4) & \text{Except B57232V5103+360 } \Delta P_{\text{gs}}/P_{\text{gs}} \text{ (typical)} < 3\% \\ 5) & \text{Except B57232V5103+360 } \Delta P_{\text{gs}}/P_{\text{gs}} \text{ (typical)} < 2\% \\ \end{array}$



B572**V5

SMD NTC thermistors, case size 0402 (1005)

Automotive series

SMD

R/T characteristics

R/T No.	8502		8509		
T (°C)	B _{25/100} = 4000 K		B _{25/100} = 3455 K		
. (•)	R_T/R_{25} α (%/K)		R_{T}/R_{25} α (%/		
-55.0	96.158	7.4	44.605	5.9	
-50.0	66.892	7.1	33.281	5.8	
-45.0	47.127	6.9	25.044	5.6	
-40.0	33.606	6.6	19.003	5.4	
-35.0	24.243	6.4	14.536	5.3	
-30.0	17.681	6.2	11.206	5.1	
-25.0	13.032	6.0	8.7041	5.0	
-20.0	9.702	5.8	6.8104	4.8	
-15.0	7.2923	5.6	5.3665	4.7	
-10.0	5.5314	5.4	4.2576	4.6	
-5.0	4.2325	5.3	3.4001	4.4	
0.0	3.2657	5.1	2.7326	4.3	
5.0	2.54	4.9	2.2096	4.2	
10.0	1.9907	4.8	1.7973	4.1	
15.0	1.5716	4.7	1.4703	4.0	
20.0	1.2494	4.5	1.2093	3.9	
25.0	1.0000	4.4	1.0000	3.7	
30.0	0.80552	4.3	0.83113	3.6	
35.0	0.65288	4.1	0.69418	3.6	
40.0	0.53229	4.0	0.58255	3.5	
45.0	0.43645	3.9	0.49112	3.4	
50.0	0.35981	3.8	0.41587	3.3	
55.0	0.29819	3.7	0.35365	3.2	
60.0	0.24837	3.6	0.30197	3.1	
65.0	0.20787	3.5	0.25888	3.0	
70.0	0.17479	3.4	0.22278	3.0	
75.0	0.14763	3.3	0.19243	2.9	
80.0	0.12523	3.2	0.16681	2.8	
85.0	0.10667	3.2	0.1451	2.8	
90.0	0.091227	3.1	0.12663	2.7	
95.0	0.078319	3.0	0.11088	2.6	
100.0	0.067488	2.9	0.097381	2.6	
105.0	0.058363	2.9	0.085788	2.5	
110.0	0.050647	2.8	0.075795	2.4	
115.0	0.044098	2.7	0.067155	2.4	
120.0	0.03852	2.7	0.059663	2.3	
125.0	0.033752	2.6	0.053146	2.3	
130.0	0.029663	2.6	0.047463	2.2	
135.0	0.026146	2.5	0.042493	2.2	
140.0	0.023111	2.4	0.038134	2.1	
145.0	0.020484	2.4	0.034302	2.1	
150.0	0.018203	2.3	0.030925	2.1	



_						
п	empera	ture m	easuren	nent and	compensation	п

B572**V5

SMD NTC thermistors, case size 0402 (1005)


Automotive series

SMD

Taping and packing

1 Taping of SMD NTC thermistors

1.1 Cardboard tape for case size 0402 and 0603 (taping to IEC 60286-3)



Dimensions (mm)

	Case size 0402 (8-mm tape)	Case size 0603 (8-mm tape)	Tolerance
$A_0 \times B_0$	0.60×1.15	0.95×1.80	±0.2
T ₂	0.70	1.10	
T	0.60	0.95	max.
D_0	1.50	1.50	±0.10
P_0	4.00	4.00	±0.101)
P_2	2.00	2.00	±0.05
P ₁	2.00	4.00	±0.10
W	8.00	8.00	±0.30
E	1.75	1.75	±0.10
F	3.50	3.50	±0.05
G	0.75	0.75	min.

^{1) ≤0.2} mm over 10 sprocket holes.




B572**V5

SMD NTC thermistors, case size 0402 (1005)

Automotive series

SMD

1.2 Blister tape for case size 0805 and 1206 (taping to IEC 60286-3)



Dimensions (mm)

	Case size	Case size	Tolerance
	0805	1206	
	(8-mm tape)	(8-mm tape)	
$A_0 \times B_0$	1.50×2.30	1.80×3.40	±0.2
K_0	1.40	1.40	max.
T ₂	2.5	2.5	max.
D_0	1.50	1.50	+0.10/-0
D ₁	0.30	0.30	min.
P ₀	4.00	4.00	±0.10 ²⁾
P_2	2.00	2.00	±0.05
P ₁	4.00	4.00	±0.10
W	8.00	8.00	±0.30
E	1.75	1.75	±0.10
F	3.50	3.50	±0.05
G	0.75	0.75	min.

^{2) ≤0.2} mm over 10 sprocket holes.




B572**V5

Temperature measurement and compensation SMD NTC thermistors, case size 0402 (1005)

Automotive series

SMD

1.3 Reel packing





Dimensions in mm

	8-mm tape		
	180-mm reel	330-mm reel	
A	180 +0/-3	330 +0/-2.0	
$\overline{W_{1}}$	8.4 +1.5/-0	8.4 +1.5/-0	
W_2	14.4 max.	14.4 max.	

Leader, trailer







KKE0289-Q-E



Tomposotuse		and compensation	
Telliberature	measurement	and compensant	, J

B572**V5

SMD NTC thermistors, case size 0402 (1005)

Automotive series

SMD

1.4 Packing units for discrete chip and array chip

	th			. 180 mm	330 mm
Case size	Chip thickness	Cardboard tape	Blister tape	Ø 180-mm reel	Ø 330-mm reel
inch/mm	th	W	W	pcs.	pcs.
0402/1005	0.5 mm	8 mm	_	10000	50000
0603/1608	0.8 mm	8 mm	8 mm	4000	16000
0805/2012	0.8 mm	_	8 mm	4000	16000
	1.2 mm	_	8 mm	3000	12000
1206/3216	0.8 mm	_	8 mm	3000	12000
	1.2 mm	_	8 mm	3000	12000

2 Packing codes

The last two digits of the complete ordering code state the packing mode:

Last two digits			
60	SMD	Cardboard tape	180-mm reel packing
62	SMD	Blister tape	180-mm reel packing
70	SMD	Cardboard tape	330-mm reel packing
72	SMD	Blister tape	330-mm reel packing



Temperature measurement and compensation	B572**V5
SMD NTC thermistors, case size 0402 (1005)	Automotive series
QMD	

SME

Mounting instructions

1 Soldering

1.1 SMD NTC thermistors

SMD NTC thermistors can be provided with a nickel barrier termination or on special request with silver-palladium termination. The usage of mild, non-activated fluxes for soldering is recommended as well as a proper cleaning of the PCB.

The nickel barrier layer of the silver/nickel/tin termination (see figure 1) prevents leaching of the silver base metalization layer. This allows great flexibility in the selection of soldering parameters.

The tin prevents the nickel layer from oxidizing and thus ensures better wetting by the solder. The nickel barrier termination is suitable for all commonly-used soldering methods.

Note: SMD NTCs with AgPd termination are not approved for lead-free soldering.




Figure 1
SMD NTC thermistors, structure of nickel barrier termination

1.1.1 Solderability (test to IEC 60068-2-58)

Preconditioning: Immersion into flux F-SW 32.

Evaluation criterion: Wetting of soldering areas ≥95%.

Solder	Bath temperature (°C)	Dwell time (s)
SnPb 60/40	215 ±3	3 ±0.3
SnAg (3.0 4.0), Cu (0.5 0.9)	245 ±3	3 ±0.3

1.1.2 Resistance to soldering heat (test to IEC 60068-2-58)

Preconditioning: Immersion into flux F-SW 32. Evaluation criterion: Leaching of side edges ≤1/3.

Solder	Bath temperature (°C)	Dwell time (s)
SnPb 60/40	260 ±5	10 ±1
SnAg (3.0 4.0), Cu (0.5 0.9)	260 ±5	10 ±1




Temperature measurement and compensation B572**V5
SMD NTC thermistors, case size 0402 (1005) Automotive series


SMD


Wave soldering

Temperature characteristic at component terminal with dual wave soldering



Solder joint profiles for silver/nickel/tin terminations





KKE0288-H-E

not soldered in preferred direction



B572**V5


SMD NTC thermistors, case size 0402 (1005)

Automotive series

SMD

Reflow soldering

Recommended temperature characteristic for reflow soldering following JEDEC J-STD-020D



Profile feature		Sn-Pb eutectic assembly	Pb-free assembly
Preheat and soak		-	
- Temperature min	T_{smin}	100 °C	150 °C
- Temperature max	T _{smax}	150 °C	200 °C
- Time	t_{smin} to t_{smax}	60 120 s	60 180 s
Average ramp-up rate	T_{smax} to T_p	3 °C/ s max.	3 °C/ s max.
Liquidous temperature	T _L	183 °C	217 °C
Time at liquidous	t∟	60 150 s	60 150 s
Peak package body temperature	T _p ¹⁾	220 °C 235 °C ²⁾	245 °C 260 °C ²⁾
Time (t _P) ³⁾ within 5 °C of specified		20 s ³⁾	30 s ³⁾
classification temperature (T _c)		20 5%	30 8%
Average ramp-down rate	T _p to T _{smax}	6 °C/ s max.	6 °C/ s max.
Time 25 °C to peak temperature		maximum 6 min	maximum 8 min

¹⁾ Tolerance for peak profile temperature $(T_{\mbox{\tiny P}})$ is defined as a supplier minimum and a user maximum.

Note: All temperatures refer to topside of the package, measured on the package body surface. Number of reflow cycles: 3

²⁾ Depending on package thickness. For details please refer to JEDEC J-STD-020D.


³⁾ Tolerance for time at peak profile temperature (t_P) is defined as a supplier minimum and a user maximum.



KKE0071-A-E

-	DE70+*\/F
Temperature measurement and compensation	B572**V5
SMD NTC thermistors, case size 0402 (1005)	Automotive series
SMD	
Solder joint profiles for silver/nickel/tin terminations	


Too much solder Pad geometry too large



Good solder joint

1.1.3 Recommended geometry of solder pads

TNT0565-G-E



Recommended maximum dimensions (mm)

Case size inch/mm	А	В	С
0402/1005	0.6	0.6	1.7
0603/1608	1.0	1.0	3.0
0805/2012	1.3	1.2	3.4
1206/3216	1.8	1.2	4.5

1.1.4 Notes

Iron soldering should be avoided, hot air methods are recommended for repair purposes.



B572**V5

SMD NTC thermistors, case size 0402 (1005)

Automotive series

SMD

2 Conductive adhesion

An alternative to soldering is the gluing of thermistors with conductive adhesives. The benefit of this method is that it involves no thermal stress. The adhesives used must be chemically inert.

3 Clamp contacting

Pressure contacting by means of clamps is particularly suitable for applications involving frequent switching and high turn-on powers.

4 Sealing and potting

When thermistors are sealed, potted or overmolded, there must be no mechanical stress caused by thermal expansion during the production process (curing / overmolding process) and during later operation. The upper category temperature of the thermistor must not be exceeded. Ensure that the materials used (sealing / potting compound and plastic material) are chemically neutral.

5 Cleaning

If cleaning is necessary, mild cleaning agents such as ethyl alcohol and cleaning gasoline are recommended. Cleaning agents based on water are not allowed. Ultrasonic cleaning methods are permissible.

6 Storage

In order to maintain their solderability, thermistors must be stored in a non-corrosive atmosphere. Humidity, temperature and container materials are critical factors.

Do not store SMDs where they are exposed to heat or direct sunlight. Otherwise, the packing material may be deformed or SMDs may stick together, causing problems during mounting. After opening the factory seals, such as polyvinyl-sealed packages, use the SMDs as soon as possible.

The components should be left in the original packing. Touching the metallization of unsoldered thermistors may change their soldering properties.

Storage temperature: $-25~^{\circ}\text{C}$ up to 45 $^{\circ}\text{C}$

Relative humidity (without condensation): ≤75% annual mean

<95%, maximum 30 days per annum

Solder the thermistors listed in this data book after shipment from EPCOS within the time specified:

SMDs: 12 months for Ni-barrier termination

6 months for AgPd termination



B572**V5


SMD NTC thermistors, case size 0402 (1005)

Automotive series


SMD

7 Placement and orientation of SMD NTC thermistors on PCB


a) Component placement



It is recommended that the PC board should be held by means of some adequate supporting pins such as shown left to prevent the SMDs from being damaged or cracked.




b) Cracks



When placing a component near an area which is apt to bend or a grid groove on the PC board, it is advisable to have both electrodes subjected to uniform stress, or to position the component's electrodes at right angles to the grid groove or bending line (see c) Component orientation).

c) Component orientation



Choose a mounting position that minimizes the stress imposed on the chip during flexing or bending of the board.



B572**V5

SMD NTC thermistors, case size 0402 (1005)

Automotive series

SMD

Cautions and warnings

General

See "Important notes".

Storage

- Store thermistors only in original packaging. Do not open the package prior to processing.
- Storage conditions in original packaging: storage temperature −25 °C ... +45 °C, relative humidity ≤75% annual mean, <95% maximum 30 days per annum, dew precipitation is inadmissible.</p>
- Do not store thermistors where they are exposed to heat or direct sunlight. Otherwise, the packing material may be deformed or components may stick together, causing problems during mounting.
- Avoid contamination of thermistor surface during storage, handling and processing.
- Avoid storage of thermistors in harmful environments like corrosive gases (SO_x, Cl etc).
- Use the components as soon as possible after opening the factory seals, i.e. the polyvinyl-sealed packages.
- Solder SMD NTC thermistors within the time specified after shipment from EPCOS. For SMD components with nickel barrier termination 12 months, for SMD components with AgPd termination 6 months.

Handling

- NTC thermistors must not be dropped. Chip-offs or any other damage must not be caused during handling of NTCs.
- Do not touch components with bare hands. Gloves are recommended.
- Avoid contamination of thermistor surface during handling.
- Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.

Solderina

- Use resin-type flux or non-activated flux.
- Insufficient preheating may cause ceramic cracks.
- Rapid cooling by dipping in solvent is not recommended.
- Complete removal of flux is recommended.



B572**V5

SMD NTC thermistors, case size 0402 (1005)

Automotive series

SMD

Mounting

- Ensure that no thermo-mechanical stress occurs due to production processes (curing or overmolding processes) when thermistors are sealed, potted or overmolded or during their subsequent operation. The maximum temperature of the thermistor must not be exceeded. Ensure that the materials used (sealing/potting compound and plastic material) are chemically neutral.
- Electrodes/contacts must not be scratched or damaged before/during/after the mounting process.
- Contacts and housing used for assembly with the thermistor must be clean before mounting.
- Ensure that adjacent materials are designed for operation at temperatures comparable to the surface temperature of the thermistor. Be sure that surrounding parts and materials can withstand the temperature.
- Avoid contamination of the thermistor surface during processing.
- The connections of sensors (e.g. cable end, wire end, plug terminal) may only be exposed to an environment with normal atmospheric conditions.
- Avoid using chemical substances as mounting aids. It must be ensured that no water or other liquids enter the NTC thermistors (e.g. through plug terminals). In particular, water based substances (e.g. soap suds) must not be used as mounting aids for sensors.

Operation

- Use thermistors only within the specified operating temperature range.
- Use thermistors only within the specified power range.
- Environmental conditions must not harm the thermistors. Only use the thermistors under normal atmospheric conditions or within the specified conditions.
- Contact of NTC thermistors with any liquids and solvents should be prevented. It must be ensured that no water enters the NTC thermistors (e.g. through plug terminals). For measurement purposes (checking the specified resistance vs. temperature), the component must not be immersed in water but in suitable liquids (e.g. perfluoropolyethers such as Galden).
- Avoid dewing and condensation unless thermistor is specified for these conditions.
- Be sure to provide an appropriate fail-safe function to prevent secondary product damage caused by malfunction.

This listing does not claim to be complete, but merely reflects the experience of EPCOS AG.



Temperature measurement and compensation	B572**V5
SMD NTC thermistors, case size 0402 (1005)	Automotive series

SMD

Symbols and terms

Symbol	English	German
Α	Area	Fläche
B B _{25/100}	B value B value determined by resistance measurement at 25 °C and 100 °C	B-Wert B-Wert, ermittelt durch Widerstandsmessungen bei 25 °C und 100 °C
C_{th}	Heat capacitance	Wärmekapazität
1	Current	Strom
N	Number (integer)	Anzahl (ganzzahliger Wert)
$\begin{aligned} &P_{25} \\ &P_{diss} \\ &P_{el} \\ &P_{max} \end{aligned}$	Maximum power at 25 °C Power dissipation Electrical power Maximum power within stated temperature range	Maximale Leistung bei 25 °C Verlustleistung Elektrische Leistung Maximale Leistung im angegebenenTemperaturbereich
$\begin{array}{l} \Delta R_{\text{p}}/R_{\text{B}} \\ \\ R_{\text{ins}} \\ R_{\text{P}} \\ \\ R_{\text{R}} \\ \\ \Delta R_{\text{p}}/R_{\text{R}} \\ \\ R_{\text{S}} \\ \\ R_{\text{T}} \end{array}$	Resistance tolerance caused by spread of B value Insulation resistance Parallel resistance Rated resistance Resistance tolerance Series resistance at temperature T (e.g. R ₂₅ = resistance at 25 °C)	Widerstandstoleranz, die durch die Streuung des B-Wertes verursacht wird Isolationswiderstand Parallelwiderstand Nennwiderstand Widerstandstoleranz Serienwiderstand Widerstand bei Temperatur T (z.B. R ₂₅ = Widerstand bei 25 °C)
$\begin{array}{c} T \\ \Delta T \\ t \\ T_A \\ T_{max} \end{array}$	Temperature Temperature tolerance Time Ambient temperature Upper category temperature Lower category temperature Operating temperature	Temperatur Temperaturtoleranz Zeit Umgebungstemperatur Obere Grenztemperatur (Kategorietemperatur) Untere Grenztemperatur (Kategorietemperatur) Betriebstemperatur
T _R T _{surf}	Rated temperature Surface temperature	Nenntemperatur Oberflächentemperatur
$egin{array}{c} V \ V_{ins} \ V_{op} \ V_{test} \end{array}$	Voltage Insulation test voltage Operating voltage Test voltage	Spannung Isolationsprüfspannung Betriebsspannung Prüfspannung



Temperature measurement and compensation	B572**V5
SMD NTC thermistors, case size 0402 (1005)	Automotive series

SMD

Symbol	English	German
α	Temperature coefficient	Temperaturkoeffizient
Δ	Tolerance, change	Toleranz, Änderung
δ_{th}	Dissipation factor	Wärmeleitwert
$\tau_c \\ \tau_a$	Thermal cooling time constant Thermal time constant	Thermische Abkühlzeitkonstante Thermische Zeitkonstante

Abbreviations / Notes

Symbol	English	German
SMD	Surface-mounted devices	Oberflächenmontierbares Bauelement
*	To be replaced by a number in ordering codes, type designations etc.	Platzhalter für Zahl im Bestellnummern- code oder für die Typenbezeichnung.
+	To be replaced by a letter.	Platzhalter für einen Buchstaben.
	All dimensions are given in mm.	Alle Maße sind in mm angegeben.
	The commas used in numerical values denote decimal points.	Verwendete Kommas in Zahlenwerten bezeichnen Dezimalpunkte.



Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed guestions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).



Important notes

7. The trade names EPCOS, Alu-X, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PQSine, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, TFAP, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.