


Midas Components Limited Electra House 32 Southtown Road Great Yarmouth Norfolk NR31 0DU England Telephone Fax Email Website +44 (0)1493 602602 +44 (0)1493 665111 sales@midasdisplays.com www.midasdisplays.com



DOC.

DATASHEET STATEMENT

- 1. The following icons are absolutely designed by Midas independently in 2007-SEP. They are not in common use in the LCD industry yet but just used for marking out Midasproducts' characteristics quickly and simply without any special meaning. Midas reserves the composing right and copyright.

 No one else is allowed to adopt these icons without Midas approval.
- 2. The ISO9001 logo used in this document is authorized by SGS (www.sgs.com). Midas had already successfully passed the strict and professional ISO9001:2000 Quality Management System Certification and got the certificate (No.: CN07/00404)
- 3. The technologies/techniques/crafts which denoted by the following icons are not exclusively owned by Midas, but also shared by Midas LCD strategic cooperators, however all these technologies/techniques/crafts have been finally confirmed by Midas professional engineers and QC department.
- **4.** As the difference in test standard and test conditions, also Midas insufficient familiarity with the actual LCD using environment, all the referred information in this DATASHEET (including the icons) only have two functions:
 - 4.1: providing quick reference when you are judging whether or not the product meets your requirements.
 - 4.2: listing out definitely the tolerance.

SAMPLE APPROVAL document rather than consider this DATASHEET as the standard for judging whether or not the LCD meets your requirements. Once you instruct Midas to a mass-production without definite demand for providing sample before, Midas will disclaim all responsibility if the mass-production is proved not meeting with your requirements.

- 5. The sequence of the icons is random and doesn't indicate the importance grade.
- 6. Icons explanation

Midas 2006 version logo. Midas is an integrated manufacturer of flat panel display (FPD). Midas supplies TN, HTN, STN, FSTN monochrome LCD panel; COB, COG, TAB LCD module; and all kinds of LED backlight.



FAST RESPONSE TIME

This icon on the cover indicates the product is with high response speed; Otherwise not.



PROTECTION CIRCUIT

This icon on the cover indicates the product is with protection circuit; Otherwise not.



HIGH CONTRAST

This icon on the cover indicates the product is with high contrast; Otherwise not.



LONG LIFE VERSION

This icon on the cover indicates the product is long life version (over 9K hours guaranteed); Otherwise not.



WIDE VIEWING SCOPE

This icon on the cover indicates the product is with wide viewing scope; Otherwise not.



Anti UV VERSION

This icon on the cover indicates the product is against UV line. Otherwise not.



RoHS COMPLIANCE

This icon on the cover indicates the product meets ROHS requirements; Otherwise not.



OPERATION TEMPERATURE RANGE

This icon on the cover indicates the operating temperature range (X-Y).



3TIMEs 100% QC EXAMINATION

This icon on the cover indicates the product has passed Midas thrice 100% QC.
Otherwise not.



TWICE SELECTION OF LED MATERIALS

This icon on the cover indicates the LED had passed Midas twice strict selection which promises the product's identical color and brightness; Otherwise not.



Vlcm = 3.0V

This icon on the cover indicates the product can work at 3.0V exactly; otherwise not.



N SERIES TECHNOLOGY (2008 developed)

New structure, new craft, new technology and new materials inside both LCD module and LCD panel to improve the "RainBow"

Midas LCD Part Number System

```
COG
                 132033
                                                                                  S
                                 Α
                                               6
                                                                                                 Т
                                                                                                        L
          2
                       3
                                 4
                                        5
                                               6
                                                      7
                                                             8
                                                                    9
                                                                                 10
                                                                                        11
                                                                                                12
                                                                                                       13
 1
                                                                                                              14
                                                                                                                      15
                                                                                                                             16
         =
                   MC: Midas Components
                   Blank: COB (chip on board) COG: chip on glass
                   No of dots
                                      (e.g. 240064 = 240 \times 64 \text{ dots})
                                                                             (e.g. 21605 = 2 \times 165 mm C.H.)
3
         =
         =
                   Series
4
         =
                   Series Variant:
                                       A to Z - see addendum
                                                          9: 9 o'clock
                                                                             12: 12 o'clock
         =
                   3: 3 o'clock
                                      6: 6 o'clock
6
                   S: Normal (0 to + 50 deg C) W: Wide temp. (-20 to + 70 deg C) X: Extended temp (-30 + 80 Deg C)
7
         =
8
                   Character Set
                   Blank: Standard (English/Japanese)
                   C: Chinese Simplified (Graphic Displays only)
                   CB: Chinese Big 5 (Graphic Displays only)
                   H: Hebrew
                   K: European (std) (English/German/French/Greek)
                   L: English/Japanese (special)
                   M: European (English/Scandinavian)
                   R: Cyrillic
                   W: European (English/Greek)
                   U: European (English/Scandinavian/Icelandic)
         =
                   Bezel Height (where applicable /available)
                                                       LED Connection
                              Top of Bezel to Top
                                                                               Array or
                                                      Common (via pins 1
                                    of PCB
                                                                               Edge Lit
                                                             and 2)
                             9.5mm / not
                    Blank
                                                        via pins 15+ 16-
                                                                                 Array
                             applicable
                    2
                             8.9 \; \mathrm{mm}
                                                            Common
                                                                                 Array
                    3
                             7.8 \; \mathrm{mm}
                                                            Separate
                                                                                 Array
                    4
                             7.8 \text{ mm}
                                                            Common
                                                                                 Array
                    5
                            9.5 \text{ mm}
                                                            Separate
                                                                                 Array
                    6
                             7~\mathrm{mm}
                                                            Common
                                                                                 Array
                    7
                             7 \text{ mm}
                                                            Separate
                                                                                 Array
                    8
                                                            Common
                             6.4 \text{ mm}
                                                                                 Edge
                             6.4 \text{ mm}
                                                            Separate
                                                                                 Edge
                             5.5 \text{ mm}
                                                            Common
                                                                                 Edge
                    A
                    В
                             5.5 \text{ mm}
                                                            Separate
                                                                                 Edge
                    D
                             6.0mm
                                                            Separate
                                                                                 Edge
                    E
                             5.0mm
                                                            Separate
                                                                                 Edge
                    \mathbf{F}
                             4.7mm
                                                            Common
                                                                                 Edge
                    \mathbf{G}
                             3.7mm
                                                            Separate
                                                                                  \mathbf{EL}
                             7 \text{ mm}
                                                            Separate
                                                                                 Edge
                   T: TN S: STN B: STN Blue G: STN Grey F: FSTN F2: FFSTN V: VA (Vertically Aligned)
10
11
         =
                   P: Positive N: Negative
12
                   R: Reflective M: Transmissive T: Transflective
         =
                   Backlight: Blank: Reflective L: LED
13
         =
                   Backlight Colour: Y: Yellow-Green W: White B: Blue R: Red A: Amber O: Orange G: Green RGB: R.G.B.
14
                   Driver Chip:
                                      Blank: Standard I: I<sup>2</sup>C S: SPI T: Toshiba T6963C A: Avant SAP1024B
                                                                                                                      R: Raio RA6963
15
         =
                   Voltage Variant: e.g. 3 = 3v
16
         =
```

BOOKBINDING AREA

STANDARD DOC.

CONTENTS

PAGE 2/19

1.	GENERAL SPECIFICATIONS	Page 3
2.	MECHANICAL SPECIFICATIONS	Page 3
3.	ABSOLUTE MAXIMUM RATINGS	Page 3
4.	ELECTRONICAL CHARACTERISTIC	Page 3
5.	OPTICAL CHARACTERISTICS	Page 4
6.	ELECTRICAL SPECIFICATIONS	Page 5
7.	EXTERNAL DIMENSION	Page 7
8.	PIN ASSIGNMENT	Page 8
9.	POWER SUPPLY	Page 8
10.	REFLECTOR OF SCREEN AND DDRAM ADDRESS	Page 8
11.	INSTRUCTION TABLE	Page 9
12.	INSTRUCTION DESCRIPTION	Page 10
13.	CGRAM	Page 14
14.	DDRAM	Page 14
15.	INITIALIZATION	Page 15
16.	INTERFACE TO MPU	Page 17
17.	FONT MAP	Page 18
18.	PACKING DETAIL	Page 19

BOOKBINDING AREA					
	PRODUCT	MODE NO.	PAGE	2/40	
	SPEC.	MC42005A6W-FPTLW	PAGE	3/19	

1. GENERAL SPECIFICATIONS

ITEM	NOMINAL DIMENSIONS / AVAILABLE OPTIONS
DISPLAY FORMAT	20 Characters by 4 Lines
LCD PANEL OPTIONS	FSTN (Silver-Gray color)
POLARIZER OPTIONS	Positive, Transflective
BACKLIGHT OPTIONS	Edge type LED backlight (White color)
VIEWING ANGLE OPTIONS	6:00 (Bottom)
TEMPERATURE RANGE OPTIONS	Wide temp. range (-20°C ~ 70°C)
CONTROLLERIC	SUNPLUS
DISPLAY DUTY	1/16
DRIVING BIAS	1/5

2. MECHANICAL SPECIFICATIONS

OVERALL SIZE	RALL SIZE LED backlight version: 98.0 x 60.0 x max 14.5					
VIEWING AREA	76.0W x 26.0H	mm	HOLE-HOLE	93.0W x 55.0H	mm	
CHARACTER SIZE	2.95 W x 4 <mark>.</mark> 75H	mm	CHARACTER PITCH	0.60W x 0.60H	mm	
DOT SIZE	0.55W x 0.55H	mm	DOT PITCH	0.05W x 0.05H	mm	

3. ABSOLUTE MAXIMUM RATINGS

ITEM	SYMBOL	CONDITION	MIN	MAX	UNIT
POWER SUPPLY (LOGIC)	Vdd	25°C	-0.3	7.0	٧
POWER SUPPLY (LCD)	V0	25°C	Vdd -13.5	Vdd +0.3	V
INPUT VOLTAGE	Vinan	25°C	-0.3	Vdd +0.3	V
OPERATING TEMPERATURE	Vopr		-20	70	°C
STORAGE TEMPERATURE	Vstg		-30	80	°C

4. ELECTRONICAL CHARACTERISTIC*


ITEM	CVMDOL	CONDITION	ST				
ITEM	SYMBOL	CONDITION	MIN	MIN TYP		UNIT	
Input voltage	Vdd	+5V	4.7	5.0	5.5	V	
Supply current	ldd	Vdd=5V		1.4		mA	
•••		-20°C	4.35		4.80		
Recommended LCD driving		0°C	4.30		4.85		
voltage for normal temp.	Vdd - V0	Vdd - V0	25 [°] C	4.30	4.50	4.80	V
Version module		50°C	4.20		4.75		
		70°C	4.10		4.65		
LED forward voltage	Vf	25°C	2.9		3.4	V	
LED forward current	If	25°C		30	40	mA	
LED reverse Current	Ir	25°C		20		μA	
LED color range	X coordinate	25°C If = 30mA	0.25		0.28		
LED Color range	Y coordinate	25°C If = 30mA	0.26		0.29		
LED illuminance (Without LCD)	Lv	25°C If = 30mA	200		260	cd/m²	
LED life time		25°C If = 30mA	50K**			Hours	


PRODUCT MODE NO. SPEC. MC42005A6W-FPTLW PAGE 4/19


5. OPTICAL CHARACTERISTIC


FOR TN TYPE LCD MODULE (TA=25°C, Vdd=5.0V ± 0.25V)										
ITEM	TYP	MAX	UNIT							
VIEWING ANGLE	Ф2 – Ф1	17 - 4	30			deg				
VIEWING ANGLE	Θ	K=4	25			ueg				
CONTRAST RATIO	K			2						
RESPONSE TIME(RISE)	T R			120	150	ms				
RESPONSE TIME(FALL)	TF			120	150	ms				

FOR STN TYPE LCD MODULE (TA=25 °C, Vdd=5.0V ± 0.25V)									
ITEM	SYMBOL	CONDITION	MIN	TYP	MAX	UNIT			
VIEWING ANGLE	Ф2-Ф1	17 - 4	40			dog			
VIEWING ANGLE	Θ	K=4	60			deg			
CONTRAST RATIO	K			6					
RESPONSE TIME(RISE)	TR			150	250	ms			
RESPONSE TIME(FALL)	TF			150	250	ms			









BOOKBINDING AREA					
	PRODUCT	MODE NO.	PAGE	5/19	
	SPEC.	MC42005A6W-FPTLW	PAGE	5/19	

6. ELECTRICAL SPECIFICATIONS

6.1 DC CHARACTERISTICS (VDD = 4.5V to 5.5V, TA = 25 °C)

CHARACTERISTICS	CAMBOI	LIMIT			UNIT	TEST CONDITION
CHARACTERISTICS	STWIBUL	MIN.	TYP.	MAX.	UNII	TEST CONDITION
INPUT HIGH VOLTAGE	VIH1	2.2		Vdd	V	Pins (E. RS. R/W. DB0 - DB7)
INPUT LOW VOLTAGE	VIL1	-0.3		0.6	V	FIIIS (E. N.S. N/W. DBU - DB7)
INPUT HIGH CURRENT	Іін	-2.0		2.0	μΑ	Pins (RS. R/W. DB0 - DB7)
INPUT LOW CURRENT	lıL	-20	-50	-100	μΑ	Vdd = 5.0V
OUTPUT HIGH VOLTAGE (TTL)	Vон1	2.4		Vdd	V	Iон = - 0.1mA Pins: DB0 - DB7
OUTPUT LOW VOLTAGE (TTL)	V _{OL1}			0.4	V	IoL = 0.1mA Pins: DB0 - DB7

6.2 AC CHARACTERISTICS (VDD = 4.5V to 5.5V, TA = 25 °C)

Write mode


CHADACTEDISTICS	CVMDOL		LIMIT			TEST CONDITION
CHARACTERISTICS	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
ENABLE CYCLE TIME	tc	500			ns	Pin E
ENABLE PULSE WIDTH	tpw	230			ns	Pin E
ENABLE RISE/ FALL TIME	tr, tr	<u></u>	nIIfa	.20	ns	Pin E
ADDRESS SETUP TIME	tsp1	40	11 <u>u</u> 1a	CLUI	ns	Pins RS, R/W, E
ADDRESS HOLD TIME	tHD1	10			ns	Pins RS, R/W, E
DATA SETUP TIME	tsp2	80			ns	Pins: DB0 - DB7
DATA HOLD TIME	tHD2	10			ns	Pins: DB0 - DB7

Read mode


CHARACTERISTICS	CAMBOI	LIMIT			LINUT	TEST CONDITION
CHARACTERISTICS	STWIBUL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
ENABLE CYCLE TIME	tc	500			ns	Pin E
ENABLE PULSE WIDTH	tpw	230			ns	Pin E
ENABLE RISE/ FALL TIME	tr, tr			20	ns	Pin E
ADDRESS SETUP TIME	tsp1	40			ns	Pins RS, R/W, E
ADDRESS HOLD TIME	tHD1	10			ns	Pins RS, R/W, E
DATA OUTPUT DELAY TIME	to			120	ns	Pins: DB0 - DB7
DATA HOLD TIME	tHD2	5			ns	Pins: DB0 - DB7

BOOKBINDING AREA						
	PRODUCT	MODE NO.	PAGE	6/19		
	SPEC.	MC42005A6W-FPTLW	IAGL	0/13		

6.3.1 WRITE MODE TIMING DIAGRAM





6.3.2 READ MODE TIMING DIAGRAM




BOOKBINDING AREA						
	PRODUCT	MODE NO.	PAGE	7/40		
	SPEC.	MC42005A6W-FPTLW	PAGE	1/19		

7. EXTERNAL DIMENSIONS








воокві	BOOKBINDING AREA						
	PRODUCT	MODE NO.	PAGE	9/40			
	SPEC.	MC42005A6W-FPTLW	PAGE	0/19			

8.PIN ASSIGNMENT

PIN	SYMBOL	FUNCTION					
1	Vss	GND					
2	Vdd	Power supply for LCM (+5.0V)					
3	V0	Contrast Adjust					
4	RS	Register Select Signal					
5	R/W	Data Read / Write					
6	E Enable Signal						
7-14	DB0 - DB7	Data bus line					
15	LED+	Power supply for BKL (+5.0V)					
16	LED-	Power supply for BKL (0V)					

9.POWER SUPPLY



10. REFLECTOR OF SCREEN AND DRAM ADDRESS

Display position	1-1	1-2	1-3	1-4	1-5	1-6	1-7	1-8	1-9	1-10
	1-1	1-2	1-3		1-5			1-0		
DDRAM address	00	01	02	03	04	05	06	07	80	09
Display position	1-11	1-12	1-13	1-14	1-15	1-16	9-17	1-18	1-19	1-20
DDRAM address	0A	0B	0C	0D	0E	0F	10	11	12	13
Display position	3-1	3-2	3-3	3-4	3-5	3-6	3-7	3-8	3-9	3-10
DDRAM address	14	15	16	17	18	19	1A	1B	1C	1D
Display position	3-11	3-12	3-13	3-14	3-15	3-16	3-17	3-18	3-19	3-20
DDRAM address	1E	1F	20	21	22	23	24	25	26	27
Display position	2-1	2-2	2-3	2-4	2-5	2-6	2-7	2-8	2-9	2-10
DDRAM address	40	41	42	43	44	45	46	47	48	49
Display position	2-11	2-12	2-13	2-14	2-15	2-16	2-17	2-18	2-19	2-20
DDRAM address	4A	4B	4C	4D	4E	4F	50	51	52	53
Display position	4-1	4-2	4-3	4-4	4-5	4-6	4-7	4-8	4-9	4-10
DDRAM address	54	55	56	57	58	59	5A	5B	5C	5D
Display position	4-11	4-12	4-13	4-14	4-15	4-16	4-17	4-18	4-19	4-20
DDRAM address	5E	5F	60	61	62	63	64	65	66	67

¹⁻¹ means first character of line 1 on screen

BOOKBINDING AREA	<u> </u>		
PRODUCT	MODE NO.	PAGE	9/19
SPEC.	MC42005A6W-FPTLW	PAGE	9/19

11. INSTRUCTION TABLE

In a face of the control of the cont				Inst	ructio	n Co	de				Description	Execution
Instruction	RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0	Description	Time(fosc= 270kHz)
Clear Display	0	0	0	0	0	0	0	0	0	1	Write 20H to DDRAM set DDRAM address to 00H from AC	1.52ms
Return Home	0	0	0	0	0	0	0	0	1	ı	Set DDRAM address to 00H from AC and return cursor to its original position if shifted. The contents of DDRAM are not changed.	1.52ms
Entry Mode Set	0	0	0	0	0	0	0	1	I/D	SH	Assign cursor moving direction and enable the shift of entire display	38 µs
Display ON/OFF Control	0	0	0	0	0	0	1	D	С	В	Set display(D) cursor(C) and blinking of cursor(B) on/off	38 µs
Cursor or Display Shift	0	0	0	0	0	1	S/C	R/L	_	-	Set cursor moving and display shift control bit, and the direction, without changing DDRAM data	38 µs
Function Set	0	esi	gr	0	1	DL	n u N	fa	ctı	ure -	Set interface data length(DL:8bit/4bit), number of display line (N:2line/1line) and,display font type F:5X11dots / 5X8dots	38 µs
Set CGRAM Address	0	0	0	1	AC5	AC4	AC3	AC2	AC1	AC0	Set CGRAM address in address counter	38 µs
Set DDRAM Address	0	0	1	AC6	AC5	AC4	AC3	AC2	AC1	AC0	Set DDRAM address in address counter	38 µs
Read Busy Flag and Address	0	1	BF	AC6	AC5	AC4	AC3	AC2	AC1	AC0	Whether during internal operation or not can be known by reading BF The contents of address counter can also be read	0 µs
Write Data to RAM	1	0	D7	D6	D5	D4	D3	D2	D1	D0	Write data into internal RAM (DDRAM/CGRAM)	38 µs
Read data from RAM	1	1	D7	D6	D5	D4	D3	D2	D1	D0	Read data from internal RAM (DDRAM/CGRAM)	38 µs

PRODUCT MODE NO. SPEC. MC42005A6W-FPTLW PAGE 10/19

12. INSTRUCTION DESCRIPTION

A. Clear Display

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	0	0	0	0	0	1

Clear all the display data by writing 20H (space code) to all DDRAM address, and set DDRAM address to 00H into AC (address counter).

Return cursor to the original status, namely, bring the cursor to the left edge on the first line of the display.

Make the entry mode increment (I/D = HIGH)

B. Return Home

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	0	0	0	0	1	-

Set DDRAM address to 00H into the address counter.

Return cursor to its original site and return display to its original status,if shifted. Contents of DDRAM does not change.

C. Entry Mode Set

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	0	0	0	1	I/D	SH

Set the moving direction of cursor and display.

I/D:Increment /decrement of DDRAM address(cursor or blink)

I/D=High,cursor/blink moves to right and DDRAM address is increased by 1.

I/D=low,cursor/blink moves to left and DDRAM address is decreased by 1.

*CGRAM operates the same way as DDRAM, when reading from or writing to CGRAM.

SH:Shift of entire display

When DDRAM read (CGRAM read/write) operation or SH=Low,shifting of entire display is not performed.if SH=High, and DDRAM write operation,shift of entire display is performed according to I/D value(I/D=High,shift left, I/D=Low, shift right).

BOOKBINDING AREA

PRODUCT	MODE NO.	DAGE	11/19
SPEC.	MC42005A6W-FPTLW	PAGE	11/19

D. Display ON/OFF Control

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	0	0	1	D	С	В

D:Display ON/OFF control bit

When D=High, entire display is turned on.

When D=Low, display is turned off, but display data remains in DDRAM.

C:Cursor ON/OFF control bit

When C=High, cursor is turned on.

When C=Low, cursor is disappeared in current display, but I/D register preserves its data.

B:Cursor Blink ON/OFF control bit

When B=High, cursor blink is on, which performs alternately between all the High data and display characters at the cursor position.

When B=Low ,blink is off.

E. Cursor or Display Shift

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	1 e 05 i	90	• om	aon	u fa	S/C	R/L	SU	ppl

Shifting of right/left cursor position or display without writing or reading of display data.

This instruction is used to correct or search display data.

During 2-line mode display, cursor moves to the 2nd line after the 40th digit of the 1st line.

Note that display shift is performed simultaneously in all the lines.

When displayed data is shifted repeatedly, each line is shifted individually.

When display shift is performed, the contents of the address counter are not changed.

S/C	R/L	Operation
0	0	Shift cursor to the left, AC is decreased by 1
0	1	Shift cursor to the right, AC is increased by 1
1	0	Shift all the display to the left,cursor moves according to the display
1	1	Shift all the display to the right, cursor moves according to the display

BOOKBINDING AREA

PRODUCT	MODE NO.	PAGE	12/10
SPEC.	MC42005A6W-FPTLW	FAGE	12/13

F. Function set

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	0	0	1	DL	N	F	-	-

DL:Interface data length control bit

When DL=High, it means 8-bit bus mode with MPU.

When DL=Low, it means 4-bit bus mode with MPU.

When 4-bit bus mode, it needs to transfer 4-bit data twice.

N:Display line number control bit

When N=Low, 1-line display mode is set.

When N=High, 2-line display mode is set.

F:Display font type control bit

When F=Low, 5x8 dots format display mode is set.

When F=High, 5x11 dots format display mode.

G. Set CGRAM Address

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	lesi	on.	• 1 m	AC5	AC4	AC3	AC2	AC1	AC0

Set CGRAM address to AC.

This instruction makes CGRAM data available from MPU.

H. Set DDRAM Address

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	0	1	AC6	AC5	AC4	AC3	AC2	AC1	AC0

Set DDRAM address to AC.

This instruction makes DDRAM data available from MPU.

When 1-line display mode (N=Low), DDRAM address is from 00H to 4FH In 2-line display mode(N=High), DDRAM address in the 1st line is from 00H to 27H and DDRAM address in the 2nd line is from 40H to 67H

PRODUCT MODE NO. SPEC. MC42005A6W-FPTLW PAGE 13/19

I. Read Busy Flag & Address

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
0	1	BF	AC6	AC5	AC4	AC3	AC2	AC1	AC0

This instruction shows whether IC is in internal operation or not .

If BF is High, internal operation is in progress and shall wait until BF is to be Low, which by then the next instruction can be performed. In this instruction you and also read the value of the address counter.

J. Write data to RAM

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
1	0	D7	D6	D5	D4	D3	D2	D1	D0

Write binary 8-bit data to DDRAM/CGRAM.

The selection of RAM from DDRAM, and CGRAM, is set by the previous address set instruction (DDRAM address set, CGRAM address set).

RAM set instruction can also determine the AC direction to RAM.

After write operation, the address is automatically increased /decreased by 1,according the entry mode.

K. Read data from RAM

RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0
1	1	D7	D6	D5	D4	D3	D2	D1	D0

Read binary 8-bit data from DDRAM/CGRAM.

The selection of RAM is set by the previous address set instruction. If the address set instruction of RAM is not performed before this instruction, the data that has been read first is invalid, as the direction of AC is not yet determined. If RAM data is read several times without RAM address instructions set before read operation, the correct RAM data can be obtained from the second. But the first data would be incorrect, as there is no time margin to transfer RAM data.

	BOOKBINDING AREA	A.		
Г	PRODUCT	MODE NO.	DAGE	14/19
	SPEC.	MC42005A6W-FPTLW	PAGE	14/19

In case of DDRAM read operation, cursor shift instruction plays the same role as DDRAM address set instruction, it also transfers RAM data to output data register.

After read operation, address counter is automatically increased/decreased by 1 according to the entry mode.

After CGRAM read operation, display shift may not be executed correctly.

Note:In case of RAM write operation,AC is increased/decreased by 1 as in read operation.

At this time,AC indicates the next address position, but only the previous data can be read by the read instruction.

13. RELATIONSHIP BETWEEN CHARACTER CODE AND CGRAM

	С	ha	rac	ter	CO	de			C	GR.	AM	Add	dre	SS		(CG	RAI	M D	ata			Pattern
D7	D6	D5	D4	D3	D	2 C)1	D0	A5	A4	A3	A2	A1	A0	P7	P6	P5	P4	P3	P2	P1	P0	number
0	0	0	0	Χ	0	0)	0	0	0	0	0	0	0	Х	Χ	Х	0	1	1	1	0	pattern 1
												0	0	1	Х	Χ	Х	1	0	0	0	1	
									4			0	1	0	Х	Χ	Х	1	0	0	0	1	
												0	1	1	X	Х	Х	1	1	1	1	1	
												1	0	0	Х	Χ	X	1	0	0	0	1	
												1	0	1	Х	X	Х	1	0	0	0	1	
												1	1	0	X	X	Х	1	0	0	0	1	
												1	1	1	X	X	Χ	0	0	0	0	0	
					S		9	n			18	an	u	fa	1 C	tı	ır		•	9	5 U	Гр	ply
0	0	0	0	Χ	1	•	1	1	0	0	0	0	0	0	Х	Χ	Х	1	0	0	0	1	pattern8
												0	0	1	Х	Χ	Х	1	0	0	0	1	
												0	1	0	Х	Χ	Х	1	0	0	0	1	
												0	1	1	Х	Χ	Х	1	1	1	1	1	
												1	0	0	Х	Χ	Х	1	0	0	0	1	
												1	0	1	Х	Χ	Х	1	0	0	0	1	
												1	1	0	Х	Χ	Х	1	0	0	0	1	
												1	1	1	Х	Х	Х	0	0	0	0	0	

14. DISPLAY DATA RAM(DDRAM)


DDRAM stores display data of maximum 80x8 bits(80 characters). DDRAM address is set in the address counter(AC) as a hexadecimal number

MSB						LSB
AC6	AC5	AC4	AC3	AC2	AC1	AC0

BOOKBINDING AREA				
	PRODUCT	MODE NO.	DAGE	15/19
	SPEC.	MC42005A6W-FPTLW	PAGE	15/19


15. INITIALIZATION

15.1 8-bit interface mode (Condition: fosc = 270KHZ)




BOOKBINDING AREA				
	PRODUCT	MODE NO.	DAGE	16/19
	SPEC.	MC42005A6W-FPTLW	PAGE	10/19


15.2 4-bit interface mode (Condition: fosc = 270KHZ)



BOOKBINDING AREA				
	PRODUCT	MODE NO.	DAGE	17/19
	SPEC.	MC42005A6W-FPTLW	PAGE	17/19

16.INTERFACE TO MPU





from DB4 to DB7. (while the rest of 4 bus lines from

Data transfer is completed when 4-bits of data is transferred twice.(upper 4-bits of data, then lower

DB0 toDB3 are not used.)

4-bits of data.)

Features design • manufacture • supply

- 1. Interface to an 8-bit or 4-bit MPU is available.
- 2. 192 types of alphanumeric, symbols and special characters can be displayed with the built in character generator (ROM).
- 3. Other preferred characters can be displayed by character generator (RAM).
- 4. Various instructions may be programmed.
 - Clear display
 - Cursor at home
 - On/Off cursor
 - Blink character
 - Shift display
 - Shift cursor
 - Read/Write display data .etc.
- 5. Compact and light weight design which can easily be integrated into end products.
- 6. Single power supply +5V drive (except for extended temperature type).
- 7. Low power consumption.

BOOKBINDING AREA				
	PRODUCT	MODE NO.	DAGE	18/19
	SPEC.	MC42005A6W-FPTLW	PAGE	10/19

17. STANDARD FONT MAP

Upper 4bit Lower	LLLL	LLLH	LLHL	LLHH	LHLL	LHLH	LHHL	LHHH	HLLL	HLLH	HLHL	НЬНН	HHLL	ННГН	HHHL	нннн
4bit LLLL	CG RAM (1)															
LLLH	(2)															
LLHL	(3)															
LLHH	(4)															
LHLL	(5)															
LHLH	(6)															
LHHL	(7)															
LHHH	(8)															
HLLL	(1)															
HLLH	(2)															
HLHL	(3)															
HLHH	(4)															
HHLL	(5)															
HHLH	(6)															
HHHL	(7)															
нннн	(8)															

BOOKBINDING AREA				
	PRODUCT	MODE NO.	DAGE	19/19
	SPEC.	MC42005A6W-FPTLW	PAGE	19/19

18. PACKING DETAIL

WITH LED BKL
45 PCS/BOX
10 BOXES/CARTON
450 PCS/CARTON
20.00 KGS/CTN(G.W.)
0.07 M ³ /CARTON

WITHOUT LED BKL
45 PCS/BOX
10 BOXES/CARTON
450 PCS/CARTON
18.00 KGS/CTN(G.W.)
0.07 M³/CARTON

NOTE

- 1. The weight is estimated for reference only.
- 2. Packing detail may be changed without notice.

